

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914079

Luminaire Tested: DFN2DIP-PN4F0-040D090US927-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P914079  
REPORT IS A COMBINATION OF REPORTS P901220 AND P898053  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-040D090US927-RLONL  
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9751.7 lumens  
Efficiency: N/A  
Efficacy: 97.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 100  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P914079  
CATALOG NUMBER: DFN2DIP-PN4F0-040D090US927-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P914079

CATALOG NUMBER: DFN2DIP-PN4F0-040D090US927-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	36	36	36	28
1	93	89	85	82	83	80	77	74	62	60	59	46	45	44	32	31	31	31	31	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	28	27	26	26	26	26	20
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	25	24	22	22	22	22	18
4	71	61	53	48	63	55	48	44	43	39	35	33	30	27	23	21	20	20	20	20	15
5	65	54	47	41	58	49	42	37	39	34	30	29	26	24	21	19	17	17	17	17	13
6	60	49	41	35	54	44	37	32	35	30	27	27	23	21	19	17	15	15	15	15	12
7	55	44	36	31	49	40	33	28	32	27	23	24	21	18	17	15	14	14	14	14	11
8	51	40	32	27	46	36	30	25	29	24	21	22	19	16	16	14	12	12	12	12	10
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11	11	11	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10	10	10	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	956	956	956
5°	957	941	947
10°	948	923	916
15°	935	892	869
20°	918	850	811
25°	900	803	754
30°	876	755	683
35°	853	703	620
40°	829	650	548
45°	802	590	483
50°	773	530	419
55°	744	466	357
60°	709	398	294
65°	670	330	265
70°	622	266	240
75°	562	235	219
80°	474	198	191
85°	330	133	144

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1282 cd/sqm



TEST NUMBER: P914079

CATALOG NUMBER: DFN2DIP-PN4F0-040D090US927-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.7	1.3
10°-20°	336.9	3.5
20°-30°	473.1	4.9
30°-40°	515.7	5.3
40°-50°	473.9	4.9
50°-60°	372.2	3.8
60°-70°	242.3	2.5
70°-80°	124.7	1.3
80°-90°	36.1	0.4
90°-100°	79.3	0.8
100°-110°	295.8	3.0
110°-120°	784.4	8.0
120°-130°	1301.0	13.3
130°-140°	1382.0	14.2
140°-150°	1284.4	13.2
150°-160°	1032.6	10.6
160°-170°	665.4	6.8
170°-180°	229.0	2.3
0°-30°	932.7	9.6
0°-40°	1448.4	14.9
0°-60°	2294.6	23.5
0°-90°	2697.6	27.7
90°-120°	1159.5	11.9
90°-150°	5127.0	52.6
90°-180°	7054.0	72.3
0°-180°	9751.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1310	1310	1310	1310	1310	
5°	1310	1304	1288	1299	1296	124
15°	1246	1233	1192	1170	1158	351
25°	1131	1093	1014	966	948	520
35°	974	914	810	735	709	610
45°	796	717	593	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	58
90°	2	21	35	44	47	9
95°	113	56	68	77	75	134
105°	529	582	106	125	132	566
115°	1001	1031	1074	268	143	986
125°	1415	1438	1471	1483	1489	1262
135°	1752	1780	1795	1813	1809	1353
145°	2032	2030	2060	2072	2063	1271
155°	2237	2222	2243	2253	2239	1031
165°	2357	2347	2352	2364	2352	666
175°	2411	2399	2403	2415	2398	229
180°	2406	2406	2406	2406	2406	



TEST NUMBER: P914079

CATALOG NUMBER: DFN2DIP-PN4F0-040D090US927-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1309.6	1309.6	1309.6	1309.6	1309.6
2.5°	1315.6	1309.6	1296.6	1308.5	1306.1
5°	1309.6	1303.7	1288.2	1298.9	1295.5
7.5°	1298.9	1291.9	1275.3	1279.9	1274.1
10°	1284.8	1276.4	1252.8	1249.1	1242.1
12.5°	1267.0	1256.3	1224.2	1217.2	1204.1
15°	1245.6	1232.6	1192.3	1169.8	1158.0
17.5°	1220.8	1201.7	1151.9	1125.9	1106.9
20°	1192.3	1168.5	1109.3	1079.7	1053.6
22.5°	1161.5	1134.2	1065.4	1025.2	1007.5
25°	1130.7	1092.7	1014.5	966.0	948.1
27.5°	1094.0	1053.6	967.1	911.4	884.1
30°	1054.9	1009.7	914.9	854.5	822.5
32.5°	1016.9	962.3	865.2	794.1	764.4
35°	974.3	913.8	809.5	734.8	708.7
37.5°	932.8	867.5	757.3	675.5	645.9
40°	888.9	817.8	702.8	618.7	587.9
42.5°	843.8	768.0	648.3	560.5	531.0
45°	796.5	717.0	592.6	508.4	480.0
47.5°	751.5	667.3	539.3	455.1	429.0
50°	701.6	617.5	487.1	405.3	380.5
52.5°	653.0	564.1	437.4	359.1	336.6
55°	605.6	513.2	385.2	314.1	291.6
57.5°	557.1	462.2	339.0	272.6	253.7
60°	507.2	412.4	290.3	230.0	211.0
62.5°	458.8	363.9	248.8	192.0	182.6
65°	408.9	312.8	206.2	166.0	162.3
67.5°	361.6	265.5	166.0	145.8	142.2
70°	311.7	219.3	137.4	125.6	120.8
72.5°	264.4	176.6	114.9	105.5	103.1
75°	218.0	135.1	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.8	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	1.7	20.9	34.7	43.6	46.9
92.5°	43.6	36.6	41.7	45.3	46.9
95°	113.1	55.6	67.8	76.7	74.9
97.5°	203.7	61.0	88.7	94.0	95.7
100°	308.2	69.7	99.3	113.1	116.6
102.5°	423.0	419.7	102.7	121.8	127.1
105°	529.3	581.6	106.2	125.3	132.3
107.5°	652.9	696.3	109.8	128.8	135.9
110°	771.3	807.8	304.8	130.6	137.5



TEST NUMBER: P914079

CATALOG NUMBER: DFN2DIP-PN4F0-040D090US927-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	882.8	914.0	884.5	134.0	139.3
115°	1001.1	1030.6	1074.3	268.2	142.8
117.5°	1103.8	1138.6	1168.3	919.2	463.1
120°	1218.8	1244.8	1276.3	1297.1	1062.1
122.5°	1316.2	1344.1	1379.0	1389.3	1391.2
125°	1415.4	1438.1	1471.2	1483.4	1488.6
127.5°	1505.9	1530.3	1556.6	1574.0	1575.6
130°	1591.3	1619.3	1638.3	1657.5	1655.9
132.5°	1678.4	1701.1	1720.1	1735.9	1734.2
135°	1751.6	1779.5	1795.0	1812.6	1809.1
137.5°	1828.1	1849.0	1866.5	1883.9	1878.7
140°	1902.9	1917.0	1936.0	1951.7	1943.1
142.5°	1965.8	1978.0	2000.5	2014.4	2005.7
145°	2031.9	2030.0	2059.7	2071.9	2063.2
147.5°	2089.2	2084.1	2113.6	2122.3	2115.4
150°	2145.1	2132.9	2160.8	2171.1	2162.4
152.5°	2192.0	2178.1	2204.2	2214.7	2202.5
155°	2237.3	2221.8	2242.6	2253.0	2239.1
157.5°	2273.9	2260.0	2275.7	2287.9	2273.9
160°	2305.2	2294.7	2305.2	2315.6	2303.4
162.5°	2333.0	2322.6	2331.3	2343.5	2327.8
165°	2357.4	2347.0	2352.2	2364.4	2352.2
167.5°	2376.6	2366.1	2371.4	2383.6	2367.9
170°	2392.3	2381.8	2385.3	2397.5	2381.8
172.5°	2402.7	2392.3	2395.8	2408.0	2392.3
175°	2411.3	2399.1	2402.7	2414.8	2397.5
177.5°	2414.8	2402.7	2404.5	2416.7	2401.0
180°	2406.2	2406.2	2406.2	2406.2	2406.2



TEST NUMBER: P914079  
 CATALOG NUMBER: DFN2DIP-PN4F0-040D090US927-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.43	5.11	5.57	6.23	7.79	0.40	1.08	1.53	2.20	3.76
	3H	6.10	6.71	7.24	7.84	9.41	1.58	2.18	2.72	3.31	4.89
	4H	6.71	7.28	7.86	8.41	9.99	2.02	2.59	3.17	3.72	5.30
	6H	7.12	7.65	8.28	8.78	10.37	2.33	2.86	3.49	3.99	5.59
	8H	7.25	7.75	8.41	8.89	10.48	2.42	2.92	3.58	4.07	5.65
	12H	7.30	7.78	8.47	8.92	10.53	2.46	2.93	3.62	4.08	5.68
4H	2H	4.43	5.01	5.59	6.14	7.72	0.98	1.55	2.13	2.68	4.26
	3H	6.25	6.73	7.41	7.88	9.48	2.31	2.79	3.48	3.95	5.54
	4H	6.94	7.38	8.10	8.52	10.14	2.86	3.30	4.02	4.44	6.05
	6H	7.45	7.82	8.62	8.99	10.59	3.27	3.64	4.44	4.81	6.41
	8H	7.62	7.97	8.79	9.13	10.75	3.39	3.74	4.56	4.90	6.52
	12H	7.71	8.03	8.90	9.20	10.82	3.45	3.77	4.64	4.94	6.56
8H	4H	6.90	7.25	8.06	8.41	10.02	3.13	3.48	4.29	4.64	6.25
	6H	7.46	7.75	8.65	8.95	10.56	3.64	3.93	4.83	5.13	6.75
	8H	7.68	7.93	8.87	9.11	10.74	3.83	4.08	5.03	5.26	6.90
	12H	7.81	8.03	9.01	9.21	10.88	3.94	4.17	5.14	5.34	7.01
12H	4H	6.84	7.16	8.03	8.33	9.95	3.12	3.44	4.31	4.61	6.24
	6H	7.43	7.69	8.63	8.87	10.50	3.69	3.94	4.88	5.12	6.76
	8H	7.65	7.87	8.85	9.05	10.72	3.89	4.12	5.09	5.29	6.96