

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903358

Luminaire Tested: DFN2DIP-PN4F0-090D120US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903358
REPORT IS A COMBINATION OF REPORTS P899764 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-090D120US830-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17220.3 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 191.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903358

CATALOG NUMBER: DFN2DIP-PN4F0-090D120US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P903358

CATALOG NUMBER: DFN2DIP-PN4F0-090D120US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	40	34	30	33	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	28	33	28	24	27	23	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2559	2559	2559
5°	2563	2519	2535
10°	2538	2470	2453
15°	2503	2389	2326
20°	2457	2276	2170
25°	2409	2150	2019
30°	2346	2021	1828
35°	2284	1883	1660
40°	2220	1739	1467
45°	2147	1580	1292
50°	2070	1419	1121
55°	1991	1247	957
60°	1899	1067	788
65°	1793	884	710
70°	1665	713	643
75°	1504	629	586
80°	1270	529	510
85°	885	355	386

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2802 cd/sqm

TEST NUMBER: P903358

CATALOG NUMBER: DFN2DIP-PN4F0-090D120US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.6	1.9
10°-20°	902.0	5.2
20°-30°	1266.4	7.4
30°-40°	1380.5	8.0
40°-50°	1268.8	7.4
50°-60°	996.5	5.8
60°-70°	648.6	3.8
70°-80°	333.9	1.9
80°-90°	95.4	0.6
90°-100°	221.3	1.3
100°-110°	703.3	4.1
110°-120°	1203.6	7.0
120°-130°	1582.9	9.2
130°-140°	1776.7	10.3
140°-150°	1742.3	10.1
150°-160°	1461.5	8.5
160°-170°	969.3	5.6
170°-180°	338.8	2.0
0°-30°	2497.0	14.5
0°-40°	3877.5	22.5
0°-60°	6142.8	35.7
0°-90°	7220.6	41.9
90°-120°	2128.2	12.4
90°-150°	7230.1	42.0
90°-180°	10000.0	58.1
0°-180°	17220.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3506	3506	3506	3506	3506	
5°	3506	3490	3449	3477	3468	332
15°	3335	3300	3192	3132	3100	940
25°	3027	2925	2716	2586	2538	1392
35°	2608	2446	2167	1967	1897	1632
45°	2132	1920	1586	1361	1285	1647
55°	1621	1374	1031	841	781	1449
65°	1095	838	552	444	435	1085
75°	584	362	254	232	229	617
85°	136	70	60	60	60	156
90°	3	39	106	99	102	17
95°	157	188	193	193	188	175
105°	649	658	664	670	670	685
115°	1208	1225	1220	1216	1208	1195
125°	1757	1784	1775	1765	1762	1570
135°	2272	2306	2312	2309	2300	1756
145°	2758	2780	2797	2801	2789	1724
155°	3154	3163	3173	3188	3178	1452
165°	3432	3428	3428	3450	3435	968
175°	3571	3562	3556	3577	3559	339
180°	3577	3577	3577	3577	3577	

TEST NUMBER: P903358

CATALOG NUMBER: DFN2DIP-PN4F0-090D120US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3506.0	3506.0	3506.0	3506.0	3506.0
2.5°	3521.8	3506.0	3470.9	3503.0	3496.5
5°	3506.0	3490.1	3448.8	3477.3	3467.9
7.5°	3477.3	3458.5	3414.1	3426.5	3410.7
10°	3439.3	3417.1	3353.8	3344.0	3325.2
12.5°	3391.8	3363.3	3277.4	3258.6	3223.5
15°	3334.6	3299.7	3191.9	3131.6	3100.0
17.5°	3268.0	3217.2	3083.8	3014.2	2963.4
20°	3191.9	3128.3	2969.7	2890.6	2820.6
22.5°	3109.4	3036.4	2852.2	2744.5	2697.1
25°	3027.0	2925.3	2715.9	2586.0	2538.2
27.5°	2928.7	2820.6	2589.0	2439.9	2366.8
30°	2824.0	2703.1	2449.3	2287.7	2201.9
32.5°	2722.3	2576.2	2316.3	2125.8	2046.4
35°	2608.2	2446.3	2167.2	1967.3	1897.2
37.5°	2497.1	2322.4	2027.5	1808.4	1729.3
40°	2379.6	2189.4	1881.4	1656.2	1573.8
42.5°	2259.1	2056.2	1735.6	1500.7	1421.5
45°	2132.2	1919.5	1586.5	1360.9	1284.9
47.5°	2011.7	1786.5	1443.8	1218.2	1148.6
50°	1878.4	1653.1	1304.1	1085.0	1018.6
52.5°	1748.1	1510.1	1170.8	961.4	901.2
55°	1621.2	1373.8	1031.0	840.9	780.6
57.5°	1491.3	1237.5	907.6	729.8	679.0
60°	1357.9	1104.1	777.3	615.7	564.9
62.5°	1228.0	974.2	666.2	514.1	488.8
65°	1094.7	837.5	552.0	444.3	434.6
67.5°	967.8	710.6	444.3	390.1	380.7
70°	834.5	587.1	368.0	336.3	323.5
72.5°	707.6	472.6	307.6	282.4	276.1
75°	583.7	361.6	253.8	231.6	228.6
77.5°	460.1	256.8	199.9	187.2	180.8
80°	345.7	184.2	152.1	139.7	139.7
82.5°	241.0	123.9	104.7	98.3	98.3
85°	136.3	69.7	60.2	60.2	60.2
87.5°	50.8	25.3	25.3	22.2	22.2
90°	3.2	38.8	105.7	99.2	102.5
92.5°	66.8	90.6	93.8	97.1	97.1
95°	157.4	187.7	193.0	193.0	187.7
97.5°	262.0	290.1	302.0	302.0	302.0
100°	382.9	407.6	416.2	416.2	413.0
102.5°	510.1	528.4	540.3	543.6	540.3
105°	649.2	657.8	664.3	669.7	669.7
107.5°	787.2	800.2	800.2	802.3	787.2
110°	921.0	938.2	938.2	938.2	929.6

TEST NUMBER: P903358

CATALOG NUMBER: DFN2DIP-PN4F0-090D120US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1065.4	1083.8	1080.5	1072.0	1065.4
115°	1207.8	1225.1	1219.6	1216.4	1207.8
117.5°	1349.1	1372.8	1357.7	1349.1	1340.5
120°	1491.5	1515.1	1491.5	1491.5	1481.8
122.5°	1620.9	1651.1	1636.0	1627.3	1620.9
125°	1756.7	1783.7	1775.1	1765.4	1762.1
127.5°	1889.4	1922.8	1910.9	1898.0	1889.4
130°	2013.4	2052.2	2046.8	2040.3	2028.4
132.5°	2152.5	2182.7	2184.8	2169.7	2161.2
135°	2272.2	2305.6	2312.2	2308.9	2300.3
137.5°	2405.9	2432.9	2438.3	2436.1	2423.2
140°	2523.5	2550.4	2565.5	2565.5	2553.6
142.5°	2644.3	2671.3	2679.8	2683.0	2671.3
145°	2758.5	2780.1	2797.4	2800.7	2788.8
147.5°	2861.0	2887.9	2901.0	2906.3	2894.5
150°	2966.7	2985.0	2996.9	3006.6	2996.9
152.5°	3060.5	3078.8	3094.0	3105.9	3094.0
155°	3154.3	3163.0	3172.7	3187.8	3178.1
157.5°	3235.3	3241.7	3247.1	3268.6	3253.6
160°	3307.5	3314.0	3317.2	3335.6	3322.6
162.5°	3374.3	3374.3	3377.6	3398.1	3383.0
165°	3431.5	3428.3	3428.3	3449.8	3434.7
167.5°	3483.3	3473.6	3473.6	3495.1	3480.1
170°	3522.1	3513.4	3510.2	3531.8	3513.4
172.5°	3549.0	3540.4	3537.2	3558.8	3540.4
175°	3570.6	3562.0	3555.6	3577.0	3558.8
177.5°	3582.5	3573.8	3567.3	3585.7	3567.3
180°	3577.0	3577.0	3577.0	3577.0	3577.0

TEST NUMBER: P903358

CATALOG NUMBER: DFN2DIP-PN4F0-090D120US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.61	10.38	10.64	11.42	12.80	5.58	6.35	6.61	7.38	8.76
	3H	11.29	11.98	12.33	13.02	14.42	6.76	7.45	7.80	8.49	9.90
	4H	11.90	12.55	12.95	13.59	15.00	7.21	7.86	8.26	8.91	10.32
	6H	12.32	12.92	13.38	13.96	15.39	7.53	8.13	8.59	9.18	10.60
	8H	12.44	13.01	13.51	14.08	15.50	7.62	8.19	8.69	9.25	10.67
	12H	12.51	13.05	13.58	14.10	15.55	7.66	8.20	8.73	9.26	10.70
4H	2H	9.62	10.28	10.68	11.32	12.73	6.17	6.82	7.23	7.86	9.27
	3H	11.45	11.99	12.52	13.06	14.49	7.51	8.05	8.58	9.13	10.55
	4H	12.14	12.64	13.21	13.70	15.15	8.06	8.56	9.13	9.62	11.06
	6H	12.66	13.08	13.74	14.17	15.61	8.48	8.90	9.56	9.99	11.43
	8H	12.83	13.23	13.91	14.31	15.76	8.61	9.00	9.69	10.08	11.54
	12H	12.93	13.29	14.03	14.38	15.84	8.67	9.03	9.77	10.12	11.58
8H	4H	12.11	12.50	13.19	13.58	15.04	8.34	8.73	9.42	9.81	11.27
	6H	12.67	13.00	13.78	14.12	15.57	8.85	9.18	9.96	10.30	11.76
	8H	12.89	13.18	14.00	14.28	15.75	9.05	9.33	10.16	10.44	11.91
	12H	13.03	13.28	14.14	14.38	15.89	9.16	9.42	10.28	10.51	12.03
12H	4H	12.06	12.41	13.15	13.51	14.97	8.34	8.70	9.44	9.79	11.25
	6H	12.65	12.94	13.76	14.04	15.51	8.90	9.19	10.01	10.29	11.77
	8H	12.87	13.12	13.98	14.22	15.73	9.11	9.37	10.23	10.46	11.98

END OF REPORT