

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903390

Luminaire Tested: DFN2DIP-PN4F0-100D110US830-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P903390  
REPORT IS A COMBINATION OF REPORTS P899748 AND P896497  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-100D110US830-RLLFLL  
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 17187.2 lumens  
Efficiency: N/A  
Efficacy: 89.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 192.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9952  
Total Harmonic Distortion (THDi): 0.069  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P903390  
CATALOG NUMBER: DFN2DIP-PN4F0-100D110US830-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P903390

CATALOG NUMBER: DFN2DIP-PN4F0-100D110US830-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47	47	47	47
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40	40	40	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	42	41	39	34	34	34	34
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30	30	30	30
4	75	64	57	51	69	60	53	48	51	46	42	42	38	35	34	32	30	26	26	26	26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23	23	23	23
6	64	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20	20	20	20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18	18	18	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16	16	16	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15	15	15	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14	14	14	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2844	2844	2844
5°	2848	2799	2817
10°	2820	2744	2726
15°	2781	2654	2584
20°	2730	2529	2411
25°	2677	2389	2244
30°	2606	2246	2031
35°	2537	2092	1844
40°	2467	1932	1630
45°	2385	1755	1436
50°	2301	1576	1246
55°	2212	1385	1063
60°	2110	1185	876
65°	1992	982	789
70°	1850	792	715
75°	1671	699	651
80°	1411	588	567
85°	983	394	429

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 2567 cd/sqm



TEST NUMBER: P903390

CATALOG NUMBER: DFN2DIP-PN4F0-100D110US830-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	365.1	2.1
10°-20°	1002.2	5.8
20°-30°	1407.1	8.2
30°-40°	1533.9	8.9
40°-50°	1409.8	8.2
50°-60°	1107.2	6.4
60°-70°	720.7	4.2
70°-80°	371.0	2.2
80°-90°	104.0	0.6
90°-100°	202.9	1.2
100°-110°	644.7	3.8
110°-120°	1103.3	6.4
120°-130°	1451.0	8.4
130°-140°	1628.6	9.5
140°-150°	1597.1	9.3
150°-160°	1339.7	7.8
160°-170°	888.5	5.2
170°-180°	310.5	1.8
0°-30°	2774.5	16.1
0°-40°	4308.3	25.1
0°-60°	6825.3	39.7
0°-90°	8020.9	46.7
90°-120°	1950.9	11.4
90°-150°	6627.6	38.6
90°-180°	9166.0	53.3
0°-180°	17187.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3896	3896	3896	3896	3896	
5°	3896	3878	3832	3864	3853	369
15°	3705	3666	3546	3480	3444	1044
25°	3363	3250	3018	2873	2820	1547
35°	2898	2718	2408	2186	2108	1814
45°	2369	2133	1763	1512	1428	1830
55°	1801	1526	1146	934	867	1610
65°	1216	931	613	494	483	1206
75°	649	402	282	257	254	686
85°	152	77	67	67	67	174
90°	3	36	97	91	94	17
95°	144	172	177	177	172	161
105°	595	603	609	614	614	628
115°	1107	1123	1118	1115	1107	1095
125°	1610	1635	1627	1618	1615	1439
135°	2083	2114	2119	2116	2109	1610
145°	2529	2548	2564	2567	2556	1580
155°	2892	2899	2908	2922	2913	1331
165°	3146	3142	3142	3162	3148	887
175°	3273	3265	3259	3279	3262	311
180°	3279	3279	3279	3279	3279	



TEST NUMBER: P903390

CATALOG NUMBER: DFN2DIP-PN4F0-100D110US830-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3895.5	3895.5	3895.5	3895.5	3895.5
2.5°	3913.1	3895.5	3856.6	3892.1	3885.1
5°	3895.5	3877.9	3831.9	3863.8	3853.2
7.5°	3863.8	3842.7	3793.4	3807.2	3789.7
10°	3821.4	3796.7	3726.4	3715.6	3694.7
12.5°	3768.8	3736.9	3641.5	3620.6	3581.7
15°	3705.1	3666.2	3546.5	3479.6	3444.4
17.5°	3631.0	3574.6	3426.5	3349.0	3292.6
20°	3546.5	3475.8	3299.7	3211.8	3134.0
22.5°	3454.9	3373.7	3169.1	3049.5	2996.7
25°	3363.3	3250.4	3017.6	2873.2	2820.2
27.5°	3254.0	3134.0	2876.6	2710.9	2629.8
30°	3137.7	3003.4	2721.4	2541.9	2446.6
32.5°	3024.8	2862.4	2573.7	2362.0	2273.7
35°	2897.9	2718.1	2408.0	2185.8	2108.0
37.5°	2774.6	2580.4	2252.8	2009.3	1921.4
40°	2644.0	2432.7	2090.5	1840.2	1748.6
42.5°	2510.1	2284.5	1928.5	1667.5	1579.5
45°	2369.1	2132.7	1762.8	1512.2	1427.7
47.5°	2235.2	1985.0	1604.2	1353.6	1276.2
50°	2087.1	1836.8	1449.0	1205.5	1131.8
52.5°	1942.3	1677.9	1300.9	1068.2	1001.3
55°	1801.3	1526.4	1145.7	934.3	867.3
57.5°	1657.0	1374.9	1008.4	810.9	754.4
60°	1508.8	1226.8	863.7	684.1	627.6
62.5°	1364.4	1082.4	740.2	571.2	543.1
65°	1216.4	930.6	613.4	493.7	482.9
67.5°	1075.3	789.6	493.7	433.5	423.0
70°	927.2	652.3	408.8	373.6	359.5
72.5°	786.2	525.1	341.9	313.8	306.7
75°	648.6	401.7	282.0	257.3	253.9
77.5°	511.3	285.4	222.2	207.9	200.9
80°	384.1	204.6	169.1	155.2	155.2
82.5°	267.8	137.6	116.3	109.2	109.2
85°	151.5	77.4	66.9	66.9	66.9
87.5°	56.5	28.1	28.1	24.7	24.7
90°	2.9	35.6	96.9	91.0	93.9
92.5°	61.3	83.0	86.0	89.0	89.0
95°	144.3	172.0	176.9	176.9	172.0
97.5°	240.3	265.9	276.8	276.8	276.8
100°	350.9	373.6	381.5	381.5	378.6
102.5°	467.6	484.4	495.3	498.2	495.3
105°	595.1	603.0	609.0	613.9	613.9
107.5°	721.6	733.5	733.5	735.5	721.6
110°	844.2	860.1	860.1	860.1	852.2



TEST NUMBER: P903390

CATALOG NUMBER: DFN2DIP-PN4F0-100D110US830-RLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	976.7	993.4	990.5	982.6	976.7
115°	1107.2	1122.9	1118.0	1115.1	1107.2
117.5°	1236.7	1258.4	1244.5	1236.7	1228.8
120°	1367.2	1388.9	1367.2	1367.2	1358.3
122.5°	1485.8	1513.4	1499.6	1491.7	1485.8
125°	1610.3	1635.0	1627.1	1618.3	1615.2
127.5°	1731.9	1762.6	1751.7	1739.8	1731.9
130°	1845.6	1881.2	1876.2	1870.3	1859.4
132.5°	1973.1	2000.8	2002.8	1989.0	1981.0
135°	2082.8	2113.5	2119.4	2116.5	2108.6
137.5°	2205.5	2230.1	2235.1	2233.1	2221.3
140°	2313.2	2337.9	2351.7	2351.7	2340.9
142.5°	2423.9	2448.6	2456.5	2459.5	2448.6
145°	2528.7	2548.4	2564.3	2567.2	2556.4
147.5°	2622.6	2647.3	2659.2	2664.1	2653.3
150°	2719.5	2736.3	2747.1	2756.1	2747.1
152.5°	2805.5	2822.3	2836.1	2847.0	2836.1
155°	2891.5	2899.4	2908.3	2922.2	2913.2
157.5°	2965.6	2971.6	2976.5	2996.2	2982.4
160°	3031.9	3037.8	3040.7	3057.6	3045.7
162.5°	3093.1	3093.1	3096.2	3114.9	3101.1
165°	3145.5	3142.5	3142.5	3162.3	3148.5
167.5°	3193.0	3184.1	3184.1	3203.9	3190.0
170°	3228.6	3220.7	3217.7	3237.4	3220.7
172.5°	3253.3	3245.4	3242.4	3262.2	3245.4
175°	3273.1	3265.2	3259.2	3279.0	3262.2
177.5°	3283.9	3276.0	3270.1	3286.9	3270.1
180°	3279.0	3279.0	3279.0	3279.0	3279.0



TEST NUMBER: P903390  
 CATALOG NUMBER: DFN2DIP-PN4F0-100D110US830-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.46	11.27	11.46	12.27	13.59	6.43	7.23	7.42	8.23	9.55
	3H	12.14	12.86	13.14	13.87	15.21	7.62	8.33	8.62	9.34	10.68
	4H	12.75	13.43	13.77	14.44	15.79	8.07	8.75	9.08	9.76	11.11
	6H	13.17	13.80	14.20	14.82	16.18	8.39	9.01	9.41	10.03	11.39
	8H	13.30	13.90	14.33	14.93	16.29	8.48	9.07	9.51	10.10	11.46
	12H	13.36	13.93	14.40	14.95	16.34	8.52	9.08	9.55	10.11	11.49
4H	2H	10.48	11.16	11.50	12.17	13.52	7.02	7.70	8.04	8.71	10.06
	3H	12.31	12.87	13.34	13.91	15.28	8.37	8.94	9.40	9.98	11.34
	4H	13.00	13.52	14.04	14.55	15.94	8.92	9.44	9.96	10.47	11.85
	6H	13.52	13.96	14.57	15.02	16.40	9.34	9.78	10.38	10.84	12.22
	8H	13.69	14.11	14.74	15.16	16.55	9.47	9.88	10.51	10.93	12.32
	12H	13.79	14.16	14.86	15.23	16.63	9.53	9.90	10.60	10.97	12.37
8H	4H	12.97	13.38	14.02	14.43	15.83	9.20	9.61	10.25	10.66	12.06
	6H	13.54	13.88	14.61	14.97	16.36	9.72	10.06	10.79	11.15	12.54
	8H	13.75	14.05	14.83	15.13	16.54	9.91	10.21	10.99	11.28	12.70
	12H	13.89	14.16	14.98	15.23	16.68	10.03	10.29	11.11	11.36	12.82
12H	4H	12.92	13.29	13.98	14.36	15.76	9.20	9.58	10.27	10.64	12.04
	6H	13.51	13.81	14.59	14.89	16.30	9.77	10.07	10.85	11.14	12.55
	8H	13.73	14.00	14.81	15.07	16.52	9.98	10.24	11.06	11.31	12.77