

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903446

Luminaire Tested: DFN2DIP-PN4F0-120D070US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903446
REPORT IS A COMBINATION OF REPORTS P899680 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-120D070US830-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15453.0 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 178.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903446

CATALOG NUMBER: DFN2DIP-PN4F0-120D070US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P903446

CATALOG NUMBER: DFN2DIP-PN4F0-120D070US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	97	93	90	95	91	88	85	80	78	75	70	68	66	60	59	58
2	93	85	79	74	87	80	75	71	71	67	63	62	59	56	54	52	50
3	85	76	68	63	79	71	65	60	63	58	54	55	52	48	48	46	43
4	78	67	60	54	73	64	57	51	56	51	47	50	46	42	44	40	38
5	72	60	52	47	67	57	50	45	51	45	41	45	41	37	40	36	33
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	30
7	62	49	42	36	58	47	40	35	42	36	32	38	33	29	33	29	27
8	57	45	37	32	54	43	36	31	39	33	29	34	30	26	31	27	24
9	54	41	34	29	50	39	33	28	36	30	26	32	27	24	28	25	22
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	26	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3412	3412	3412
5°	3418	3359	3380
10°	3384	3293	3271
15°	3337	3185	3101
20°	3276	3035	2893
25°	3213	2867	2692
30°	3128	2695	2437
35°	3045	2510	2213
40°	2960	2319	1956
45°	2862	2106	1723
50°	2761	1892	1495
55°	2655	1662	1276
60°	2532	1422	1051
65°	2391	1178	947
70°	2220	951	858
75°	2005	839	781
80°	1694	705	680
85°	1180	473	515

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2862 cd/sqm

TEST NUMBER: P903446

CATALOG NUMBER: DFN2DIP-PN4F0-120D070US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	438.1	2.8
10°-20°	1202.7	7.8
20°-30°	1688.5	10.9
30°-40°	1840.6	11.9
40°-50°	1691.7	10.9
50°-60°	1328.6	8.6
60°-70°	864.8	5.6
70°-80°	445.2	2.9
80°-90°	119.5	0.8
90°-100°	129.1	0.8
100°-110°	410.3	2.7
110°-120°	702.1	4.5
120°-130°	923.3	6.0
130°-140°	1036.4	6.7
140°-150°	1016.3	6.6
150°-160°	852.6	5.5
160°-170°	565.4	3.7
170°-180°	197.6	1.3
0°-30°	3329.4	21.5
0°-40°	5170.0	33.5
0°-60°	8190.3	53.0
0°-90°	9619.8	62.3
90°-120°	1241.5	8.0
90°-150°	4217.6	27.3
90°-180°	5833.0	37.7
0°-180°	15453.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4675	4675	4675	4675	4675	
5°	4675	4654	4598	4636	4624	443
15°	4446	4400	4256	4176	4133	1253
25°	4036	3900	3621	3448	3384	1856
35°	3478	3262	2890	2623	2530	2177
45°	2843	2559	2115	1815	1713	2195
55°	2162	1832	1375	1121	1041	1932
65°	1460	1117	736	592	580	1447
75°	778	482	338	309	305	823
85°	182	93	80	80	80	209
90°	2	23	62	58	60	15
95°	92	109	113	113	109	102
105°	379	384	388	391	391	400
115°	705	715	712	710	705	697
125°	1025	1040	1036	1030	1028	916
135°	1326	1345	1349	1347	1342	1025
145°	1609	1622	1632	1634	1627	1005
155°	1840	1845	1851	1860	1854	847
165°	2002	2000	2000	2012	2004	565
175°	2083	2078	2074	2087	2076	198
180°	2087	2087	2087	2087	2087	

TEST NUMBER: P903446

CATALOG NUMBER: DFN2DIP-PN4F0-120D070US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4674.6	4674.6	4674.6	4674.6	4674.6
2.5°	4695.7	4674.6	4628.0	4670.6	4662.0
5°	4674.6	4653.5	4598.3	4636.5	4623.9
7.5°	4636.5	4611.3	4552.1	4568.7	4547.6
10°	4585.8	4556.2	4471.7	4458.7	4433.6
12.5°	4522.4	4484.3	4369.8	4344.7	4298.1
15°	4446.2	4399.5	4255.9	4175.5	4133.3
17.5°	4357.3	4289.5	4111.7	4018.9	3951.1
20°	4255.9	4171.0	3959.6	3854.1	3760.7
22.5°	4145.9	4048.5	3803.0	3659.3	3596.1
25°	4036.0	3900.3	3621.2	3447.9	3384.2
27.5°	3904.9	3760.7	3452.0	3253.2	3155.7
30°	3765.3	3604.2	3265.7	3050.3	2935.8
32.5°	3629.7	3434.9	3088.4	2834.4	2728.5
35°	3477.6	3261.7	2889.6	2623.0	2529.6
37.5°	3329.4	3096.5	2703.3	2411.1	2305.6
40°	3172.8	2919.2	2508.6	2208.3	2098.3
42.5°	3012.1	2741.5	2314.2	2000.9	1895.5
45°	2842.9	2559.3	2115.3	1814.7	1713.2
47.5°	2682.2	2382.0	1925.0	1624.4	1531.4
50°	2504.5	2204.2	1738.8	1446.6	1358.2
52.5°	2330.8	2013.5	1561.0	1281.9	1201.6
55°	2161.6	1831.7	1374.8	1121.2	1040.8
57.5°	1988.3	1649.9	1210.0	973.1	905.3
60°	1810.6	1472.2	1036.3	821.0	753.2
62.5°	1637.4	1298.9	888.3	685.4	651.7
65°	1459.6	1116.7	736.1	592.5	579.5
67.5°	1290.4	947.4	592.5	520.2	507.7
70°	1112.7	782.8	490.6	448.4	431.3
72.5°	943.5	630.2	410.2	376.5	368.1
75°	778.3	482.0	338.5	308.8	304.7
77.5°	613.6	342.4	266.6	249.6	241.0
80°	461.0	245.5	202.8	186.2	186.2
82.5°	321.4	165.1	139.6	131.0	131.0
85°	181.8	92.9	80.3	80.3	80.3
87.5°	67.8	33.6	33.6	29.6	29.6
90°	1.9	22.6	61.6	57.9	59.8
92.5°	39.0	52.9	54.8	56.6	56.6
95°	91.8	109.4	112.6	112.6	109.4
97.5°	152.9	169.2	176.2	176.2	176.2
100°	223.3	237.8	242.8	242.8	240.9
102.5°	297.6	308.2	315.2	317.1	315.2
105°	378.7	383.7	387.5	390.7	390.7
107.5°	459.2	466.7	466.7	468.1	459.2
110°	537.2	547.3	547.3	547.3	542.2



TEST NUMBER: P903446

CATALOG NUMBER: DFN2DIP-PN4F0-120D070US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	621.5	632.3	630.4	625.3	621.5
115°	704.6	714.6	711.5	709.6	704.6
117.5°	786.9	800.8	792.0	786.9	781.9
120°	870.0	883.8	870.0	870.0	864.3
122.5°	945.5	963.1	954.3	949.2	945.5
125°	1024.7	1040.5	1035.5	1029.8	1027.9
127.5°	1102.1	1121.6	1114.7	1107.2	1102.1
130°	1174.5	1197.1	1194.0	1190.2	1183.3
132.5°	1255.7	1273.3	1274.5	1265.7	1260.7
135°	1325.5	1344.9	1348.8	1346.8	1341.8
137.5°	1403.4	1419.2	1422.3	1421.1	1413.5
140°	1472.1	1487.8	1496.6	1496.6	1489.7
142.5°	1542.5	1558.2	1563.2	1565.1	1558.2
145°	1609.2	1621.7	1631.8	1633.7	1626.8
147.5°	1669.0	1684.7	1692.2	1695.4	1688.5
150°	1730.6	1741.3	1748.2	1753.9	1748.2
152.5°	1785.3	1796.0	1804.8	1811.8	1804.8
155°	1840.0	1845.0	1850.8	1859.5	1853.9
157.5°	1887.3	1891.0	1894.1	1906.8	1897.9
160°	1929.4	1933.2	1935.0	1945.7	1938.1
162.5°	1968.4	1968.4	1970.3	1982.2	1973.4
165°	2001.7	1999.8	1999.8	2012.4	2003.6
167.5°	2031.9	2026.3	2026.3	2038.8	2030.0
170°	2054.6	2049.6	2047.7	2060.2	2049.6
172.5°	2070.3	2065.2	2063.3	2075.9	2065.2
175°	2082.8	2077.8	2074.1	2086.6	2075.9
177.5°	2089.8	2084.7	2080.9	2091.7	2080.9
180°	2086.6	2086.6	2086.6	2086.6	2086.6

TEST NUMBER: P903446

CATALOG NUMBER: DFN2DIP-PN4F0-120D070US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.49	13.43	13.34	14.30	15.39	8.46	9.40	9.31	10.27	11.35
	3H	14.18	15.02	15.04	15.90	17.01	9.65	10.50	10.52	11.37	12.49
	4H	14.79	15.59	15.68	16.47	17.60	10.11	10.90	10.99	11.79	12.91
	6H	15.22	15.96	16.12	16.85	17.99	10.44	11.17	11.33	12.06	13.20
	8H	15.36	16.05	16.26	16.96	18.10	10.53	11.23	11.43	12.14	13.27
	12H	15.42	16.08	16.33	16.99	18.15	10.58	11.24	11.48	12.14	13.30
4H	2H	12.52	13.32	13.41	14.20	15.33	9.07	9.86	9.95	10.74	11.87
	3H	14.36	15.02	15.26	15.94	17.08	10.43	11.09	11.32	12.00	13.14
	4H	15.06	15.66	15.97	16.58	17.74	10.98	11.58	11.89	12.49	13.66
	6H	15.59	16.10	16.51	17.04	18.21	11.41	11.92	12.33	12.86	14.03
	8H	15.77	16.25	16.69	17.18	18.36	11.54	12.02	12.46	12.95	14.13
	12H	15.87	16.30	16.81	17.25	18.44	11.61	12.04	12.55	12.99	14.18
8H	4H	15.04	15.52	15.96	16.45	17.63	11.27	11.75	12.19	12.68	13.86
	6H	15.61	16.01	16.56	16.98	18.16	11.79	12.19	12.74	13.17	14.35
	8H	15.83	16.18	16.79	17.15	18.35	11.99	12.34	12.95	13.30	14.50
	12H	15.98	16.29	16.94	17.24	18.49	12.11	12.42	13.07	13.38	14.62
12H	4H	15.00	15.43	15.94	16.38	17.57	11.28	11.72	12.22	12.66	13.85
	6H	15.59	15.94	16.55	16.90	18.10	11.84	12.20	12.80	13.16	14.36
	8H	15.82	16.13	16.78	17.08	18.33	12.06	12.37	13.02	13.33	14.57