

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903458

Luminaire Tested: DFN2DIP-PN4F0-120D100US830-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P903458  
REPORT IS A COMBINATION OF REPORTS P899734 AND P896497  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-120D100US830-RLLFLL  
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 17955.4 lumens  
Efficiency: N/A  
Efficacy: 89.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 201.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9781  
Total Harmonic Distortion (THDi): 0.075  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P903458  
CATALOG NUMBER: DFN2DIP-PN4F0-120D100US830-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P903458

CATALOG NUMBER: DFN2DIP-PN4F0-120D100US830-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54	54	54	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46	46	46	46
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	39	39	39	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38	34	34	34	34
4	76	66	58	52	71	61	55	49	53	48	44	46	42	38	38	36	33	30	30	30	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26	26	26	26
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26	23	23	23	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	21	21	21	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21	19	19	19	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19	17	17	17	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18	16	16	16	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3412	3412	3412
5°	3418	3359	3380
10°	3384	3293	3271
15°	3337	3185	3101
20°	3276	3035	2893
25°	3213	2867	2692
30°	3128	2695	2437
35°	3045	2510	2213
40°	2960	2319	1956
45°	2862	2106	1723
50°	2761	1892	1495
55°	2655	1662	1276
60°	2532	1422	1051
65°	2391	1178	947
70°	2220	951	858
75°	2005	839	781
80°	1694	705	680
85°	1180	473	515

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2862 cd/sqm



TEST NUMBER: P903458

CATALOG NUMBER: DFN2DIP-PN4F0-120D100US830-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	438.1	2.4
10°-20°	1202.7	6.7
20°-30°	1688.5	9.4
30°-40°	1840.6	10.3
40°-50°	1691.7	9.4
50°-60°	1328.6	7.4
60°-70°	864.8	4.8
70°-80°	445.2	2.5
80°-90°	122.1	0.7
90°-100°	184.5	1.0
100°-110°	586.1	3.3
110°-120°	1003.0	5.6
120°-130°	1319.1	7.3
130°-140°	1480.6	8.2
140°-150°	1451.9	8.1
150°-160°	1217.9	6.8
160°-170°	807.7	4.5
170°-180°	282.3	1.6
0°-30°	3329.4	18.5
0°-40°	5170.0	28.8
0°-60°	8190.3	45.6
0°-90°	9622.4	53.6
90°-120°	1773.5	9.9
90°-150°	6025.1	33.6
90°-180°	8333.0	46.4
0°-180°	17955.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4675	4675	4675	4675	4675	
5°	4675	4654	4598	4636	4624	443
15°	4446	4400	4256	4176	4133	1253
25°	4036	3900	3621	3448	3384	1856
35°	3478	3262	2890	2623	2530	2177
45°	2843	2559	2115	1815	1713	2195
55°	2162	1832	1375	1121	1041	1932
65°	1460	1117	736	592	580	1447
75°	778	482	338	309	305	823
85°	182	93	80	80	80	209
90°	3	32	88	83	85	18
95°	131	156	161	161	156	146
105°	541	548	554	558	558	571
115°	1006	1021	1016	1014	1006	996
125°	1464	1486	1479	1471	1468	1308
135°	1894	1921	1927	1924	1917	1464
145°	2299	2317	2331	2334	2324	1436
155°	2629	2636	2644	2656	2648	1210
165°	2860	2857	2857	2875	2862	807
175°	2976	2968	2963	2981	2966	283
180°	2981	2981	2981	2981	2981	



TEST NUMBER: P903458

CATALOG NUMBER: DFN2DIP-PN4F0-120D100US830-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4674.6	4674.6	4674.6	4674.6	4674.6
2.5°	4695.7	4674.6	4628.0	4670.6	4662.0
5°	4674.6	4653.5	4598.3	4636.5	4623.9
7.5°	4636.5	4611.3	4552.1	4568.7	4547.6
10°	4585.8	4556.2	4471.7	4458.7	4433.6
12.5°	4522.4	4484.3	4369.8	4344.7	4298.1
15°	4446.2	4399.5	4255.9	4175.5	4133.3
17.5°	4357.3	4289.5	4111.7	4018.9	3951.1
20°	4255.9	4171.0	3959.6	3854.1	3760.7
22.5°	4145.9	4048.5	3803.0	3659.3	3596.1
25°	4036.0	3900.3	3621.2	3447.9	3384.2
27.5°	3904.9	3760.7	3452.0	3253.2	3155.7
30°	3765.3	3604.2	3265.7	3050.3	2935.8
32.5°	3629.7	3434.9	3088.4	2834.4	2728.5
35°	3477.6	3261.7	2889.6	2623.0	2529.6
37.5°	3329.4	3096.5	2703.3	2411.1	2305.6
40°	3172.8	2919.2	2508.6	2208.3	2098.3
42.5°	3012.1	2741.5	2314.2	2000.9	1895.5
45°	2842.9	2559.3	2115.3	1814.7	1713.2
47.5°	2682.2	2382.0	1925.0	1624.4	1531.4
50°	2504.5	2204.2	1738.8	1446.6	1358.2
52.5°	2330.8	2013.5	1561.0	1281.9	1201.6
55°	2161.6	1831.7	1374.8	1121.2	1040.8
57.5°	1988.3	1649.9	1210.0	973.1	905.3
60°	1810.6	1472.2	1036.3	821.0	753.2
62.5°	1637.4	1298.9	888.3	685.4	651.7
65°	1459.6	1116.7	736.1	592.5	579.5
67.5°	1290.4	947.4	592.5	520.2	507.7
70°	1112.7	782.8	490.6	448.4	431.3
72.5°	943.5	630.2	410.2	376.5	368.1
75°	778.3	482.0	338.5	308.8	304.7
77.5°	613.6	342.4	266.6	249.6	241.0
80°	461.0	245.5	202.8	186.2	186.2
82.5°	321.4	165.1	139.6	131.0	131.0
85°	181.8	92.9	80.3	80.3	80.3
87.5°	67.8	33.6	33.6	29.6	29.6
90°	2.7	32.3	88.0	82.7	85.4
92.5°	55.7	75.5	78.2	80.9	80.9
95°	131.2	156.4	160.9	160.9	156.4
97.5°	218.4	241.8	251.7	251.7	251.7
100°	319.1	339.7	346.9	346.9	344.2
102.5°	425.1	440.4	450.3	452.9	450.3
105°	541.0	548.2	553.6	558.1	558.1
107.5°	656.0	666.8	666.8	668.6	656.0
110°	767.5	781.8	781.8	781.8	774.7



TEST NUMBER: P903458

CATALOG NUMBER: DFN2DIP-PN4F0-120D100US830-RLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	887.9	903.1	900.5	893.2	887.9
115°	1006.5	1020.9	1016.4	1013.7	1006.5
117.5°	1124.3	1144.1	1131.4	1124.3	1117.0
120°	1242.8	1262.6	1242.8	1242.8	1234.8
122.5°	1350.7	1375.8	1363.3	1356.1	1350.7
125°	1464.0	1486.4	1479.2	1471.1	1468.5
127.5°	1574.5	1602.3	1592.4	1581.7	1574.5
130°	1677.8	1710.1	1705.7	1700.3	1690.4
132.5°	1793.8	1818.9	1820.7	1808.2	1800.9
135°	1893.5	1921.4	1926.7	1924.1	1916.8
137.5°	2005.0	2027.4	2031.9	2030.1	2019.3
140°	2102.9	2125.3	2138.0	2138.0	2128.1
142.5°	2203.6	2226.0	2233.2	2235.9	2226.0
145°	2298.8	2316.8	2331.2	2333.8	2323.9
147.5°	2384.2	2406.7	2417.4	2422.0	2412.1
150°	2472.3	2487.6	2497.5	2505.5	2497.5
152.5°	2550.4	2565.7	2578.3	2588.2	2578.3
155°	2628.7	2635.8	2643.9	2656.5	2648.4
157.5°	2696.0	2701.4	2705.9	2723.9	2711.3
160°	2756.3	2761.6	2764.3	2779.6	2768.8
162.5°	2812.0	2812.0	2814.6	2831.7	2819.1
165°	2859.6	2856.8	2856.8	2874.8	2862.3
167.5°	2902.7	2894.6	2894.6	2912.6	2900.0
170°	2935.1	2927.9	2925.2	2943.2	2927.9
172.5°	2957.5	2950.3	2947.6	2965.6	2950.3
175°	2975.5	2968.3	2963.0	2980.9	2965.6
177.5°	2985.4	2978.2	2972.8	2988.0	2972.8
180°	2980.9	2980.9	2980.9	2980.9	2980.9



TEST NUMBER: P903458  
 CATALOG NUMBER: DFN2DIP-PN4F0-120D100US830-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.75	12.61	12.68	13.55	14.77	7.71	8.57	8.64	9.52	10.74
	3H	13.43	14.20	14.37	15.15	16.40	8.90	9.67	9.85	10.63	11.87
	4H	14.04	14.77	15.00	15.73	16.98	9.36	10.08	10.31	11.04	12.30
	6H	14.47	15.14	15.44	16.10	17.37	9.68	10.35	10.65	11.31	12.58
	8H	14.60	15.23	15.57	16.21	17.48	9.77	10.41	10.75	11.39	12.65
	12H	14.66	15.26	15.64	16.24	17.53	9.82	10.42	10.80	11.40	12.68
4H	2H	11.77	12.50	12.73	13.45	14.71	8.31	9.04	9.28	10.00	11.25
	3H	13.60	14.21	14.58	15.20	16.47	9.67	10.27	10.64	11.26	12.53
	4H	14.30	14.85	15.28	15.83	17.13	10.22	10.77	11.20	11.75	13.04
	6H	14.82	15.29	15.81	16.30	17.59	10.64	11.11	11.63	12.12	13.41
	8H	15.00	15.44	15.99	16.44	17.74	10.77	11.21	11.76	12.21	13.51
	12H	15.09	15.49	16.11	16.51	17.82	10.83	11.23	11.85	12.25	13.56
8H	4H	14.27	14.71	15.27	15.71	17.02	10.50	10.94	11.50	11.94	13.25
	6H	14.84	15.21	15.86	16.25	17.55	11.02	11.39	12.04	12.43	13.73
	8H	15.06	15.38	16.09	16.41	17.73	11.21	11.53	12.24	12.56	13.88
	12H	15.20	15.48	16.23	16.51	17.87	11.33	11.62	12.37	12.64	14.01
12H	4H	14.22	14.62	15.24	15.64	16.95	10.51	10.91	11.52	11.92	13.23
	6H	14.82	15.14	15.84	16.17	17.49	11.07	11.39	12.10	12.42	13.74
	8H	15.04	15.32	16.07	16.34	17.71	11.28	11.57	12.32	12.59	13.96