

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914256

Luminaire Tested: DFN2DIP-PN4F0-090D090US927-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P914256  
REPORT IS A COMBINATION OF REPORTS P899709 AND P896497  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-090D090US927-FLLFLL  
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13368.1 lumens  
Efficiency: N/A  
Efficacy: 86.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 155  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9963  
Total Harmonic Distortion (THDi): 0.065  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P914256  
CATALOG NUMBER: DFN2DIP-PN4F0-090D090US927-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P914256  
 CATALOG NUMBER: DFN2DIP-PN4F0-090D090US927-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	59	59	59	53
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	46	44	42	37
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	33	29	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	30	26	24	21
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2025	2025	2025
5°	2028	1997	2011
10°	2012	1970	1984
15°	1982	1938	1942
20°	1942	1893	1898
25°	1903	1840	1848
30°	1853	1790	1785
35°	1805	1731	1717
40°	1747	1672	1653
45°	1689	1612	1588
50°	1626	1550	1512
55°	1560	1477	1442
60°	1485	1391	1362
65°	1403	1302	1268
70°	1299	1194	1167
75°	1154	1065	1074
80°	981	899	896
85°	709	614	599

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1766 cd/sqm



TEST NUMBER: P914256

CATALOG NUMBER: DFN2DIP-PN4F0-090D090US927-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	261.1	2.0
10°-20°	734.7	5.5
20°-30°	1079.6	8.1
30°-40°	1253.9	9.4
40°-50°	1252.4	9.4
50°-60°	1092.1	8.2
60°-70°	807.3	6.0
70°-80°	456.7	3.4
80°-90°	127.0	0.9
90°-100°	139.5	1.0
100°-110°	443.3	3.3
110°-120°	758.7	5.7
120°-130°	997.8	7.5
130°-140°	1120.0	8.4
140°-150°	1098.2	8.2
150°-160°	921.3	6.9
160°-170°	611.0	4.6
170°-180°	213.5	1.6
0°-30°	2075.4	15.5
0°-40°	3329.4	24.9
0°-60°	5673.8	42.4
0°-90°	7064.7	52.8
90°-120°	1341.5	10.0
90°-150°	4557.5	34.1
90°-180°	6303.0	47.1
0°-180°	13368.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2774	2774	2774	2774	2774	
5°	2774	2764	2734	2756	2750	263
15°	2641	2625	2590	2601	2588	744
25°	2390	2369	2324	2329	2324	1100
35°	2062	2036	1993	1977	1963	1288
45°	1678	1659	1619	1590	1579	1295
55°	1270	1254	1222	1190	1176	1135
65°	856	840	814	790	776	847
75°	448	443	429	414	419	478
85°	109	107	104	96	93	122
90°	2	24	67	62	65	13
95°	99	118	122	122	118	110
105°	409	415	419	422	422	432
115°	761	772	769	767	761	753
125°	1107	1124	1119	1113	1111	990
135°	1432	1453	1458	1455	1450	1107
145°	1739	1752	1763	1765	1758	1086
155°	1988	1994	2000	2009	2003	915
165°	2163	2161	2161	2175	2165	610
175°	2251	2245	2241	2255	2243	214
180°	2255	2255	2255	2255	2255	



TEST NUMBER: P914256

CATALOG NUMBER: DFN2DIP-PN4F0-090D090US927-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2774.1	2774.1	2774.1	2774.1	2774.1
2.5°	2790.3	2777.0	2747.6	2774.1	2769.1
5°	2774.1	2763.7	2734.3	2755.5	2750.4
7.5°	2755.5	2739.7	2710.2	2731.8	2726.4
10°	2726.4	2707.7	2675.7	2696.9	2689.0
12.5°	2686.1	2670.3	2638.4	2651.6	2646.3
15°	2640.9	2625.1	2590.2	2601.0	2587.7
17.5°	2584.8	2569.0	2534.2	2547.5	2534.2
20°	2523.4	2507.6	2470.2	2478.1	2467.6
22.5°	2462.3	2438.3	2403.4	2403.4	2398.0
25°	2390.1	2368.9	2323.6	2328.7	2323.6
27.5°	2310.0	2291.3	2256.8	2248.9	2235.6
30°	2230.2	2208.7	2168.8	2160.8	2150.1
32.5°	2144.8	2128.9	2086.1	2070.0	2059.3
35°	2062.1	2035.5	1992.7	1976.7	1963.3
37.5°	1968.7	1944.6	1901.9	1883.3	1869.9
40°	1872.7	1851.2	1808.5	1784.7	1774.0
42.5°	1779.3	1757.8	1715.4	1688.5	1672.7
45°	1678.0	1659.4	1619.1	1590.0	1579.3
47.5°	1579.3	1560.6	1517.8	1488.4	1472.6
50°	1475.1	1461.8	1424.4	1387.1	1373.8
52.5°	1373.8	1355.1	1320.6	1291.2	1272.5
55°	1269.9	1253.8	1221.8	1189.9	1176.5
57.5°	1165.8	1152.5	1117.7	1085.7	1074.9
60°	1061.6	1051.1	1013.8	984.4	976.4
62.5°	960.3	941.6	915.0	888.4	877.7
65°	856.4	840.3	813.6	789.6	776.3
67.5°	749.7	736.2	712.3	693.7	682.9
70°	650.9	640.2	616.2	597.5	587.0
72.5°	549.6	538.8	525.5	506.9	499.0
75°	448.1	442.9	429.4	413.5	418.9
77.5°	357.4	346.7	341.4	333.4	325.5
80°	266.9	264.0	258.6	250.7	245.4
82.5°	181.4	181.4	178.9	168.1	168.1
85°	109.2	106.7	104.2	95.9	93.4
87.5°	48.1	42.7	37.4	29.5	26.6
90°	2.1	24.5	66.6	62.5	64.6
92.5°	42.1	57.1	59.2	61.2	61.2
95°	99.3	118.3	121.7	121.7	118.3
97.5°	165.2	182.8	190.4	190.4	190.4
100°	241.3	257.0	262.4	262.4	260.4
102.5°	321.5	333.1	340.6	342.6	340.6
105°	409.2	414.6	418.7	422.2	422.2
107.5°	496.2	504.4	504.4	505.7	496.2
110°	580.5	591.4	591.4	591.4	586.0



TEST NUMBER: P914256

CATALOG NUMBER: DFN2DIP-PN4F0-090D090US927-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	671.6	683.2	681.1	675.7	671.6
115°	761.4	772.2	768.8	766.8	761.4
117.5°	850.4	865.4	855.9	850.4	844.9
120°	940.2	955.1	940.2	940.2	934.0
122.5°	1021.7	1040.8	1031.3	1025.8	1021.7
125°	1107.4	1124.3	1119.0	1112.8	1110.8
127.5°	1191.0	1212.0	1204.6	1196.4	1191.0
130°	1269.2	1293.6	1290.2	1286.1	1278.7
132.5°	1356.8	1375.9	1377.2	1367.7	1362.3
135°	1432.3	1453.3	1457.5	1455.4	1450.0
137.5°	1516.6	1533.6	1537.0	1535.6	1527.5
140°	1590.7	1607.7	1617.2	1617.2	1609.7
142.5°	1666.8	1683.8	1689.2	1691.3	1683.8
145°	1738.9	1752.5	1763.3	1765.4	1757.9
147.5°	1803.5	1820.4	1828.6	1832.0	1824.6
150°	1870.1	1881.7	1889.1	1895.2	1889.1
152.5°	1929.2	1940.8	1950.3	1957.8	1950.3
155°	1988.4	1993.8	1999.9	2009.4	2003.3
157.5°	2039.3	2043.4	2046.8	2060.4	2050.9
160°	2084.9	2089.0	2091.0	2102.5	2094.4
162.5°	2127.0	2127.0	2129.1	2142.0	2132.5
165°	2163.1	2161.0	2161.0	2174.6	2165.1
167.5°	2195.7	2189.6	2189.6	2203.1	2193.6
170°	2220.2	2214.7	2212.7	2226.3	2214.7
172.5°	2237.1	2231.7	2229.7	2243.3	2231.7
175°	2250.7	2245.3	2241.2	2254.9	2243.3
177.5°	2258.2	2252.8	2248.7	2260.3	2248.7
180°	2254.9	2254.9	2254.9	2254.9	2254.9



TEST NUMBER: P914256  
 CATALOG NUMBER: DFN2DIP-PN4F0-090D090US927-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.99	10.88	10.92	11.83	13.06	9.55	10.44	10.48	11.39	12.62
	3H	11.65	12.45	12.60	13.41	14.66	11.17	11.97	12.11	12.92	14.18
	4H	12.24	13.00	13.20	13.96	15.22	11.76	12.51	12.72	13.47	14.74
	6H	12.65	13.34	13.62	14.31	15.59	12.16	12.85	13.13	13.82	15.09
	8H	12.75	13.42	13.73	14.40	15.67	12.26	12.92	13.24	13.91	15.18
	12H	12.81	13.43	13.79	14.41	15.71	12.31	12.93	13.29	13.91	15.21
4H	2H	10.45	11.21	11.42	12.17	13.43	10.10	10.86	11.07	11.82	13.08
	3H	12.32	12.95	13.30	13.95	15.22	11.92	12.55	12.90	13.54	14.82
	4H	13.04	13.62	14.03	14.60	15.90	12.62	13.20	13.61	14.19	15.49
	6H	13.56	14.06	14.56	15.07	16.37	13.14	13.63	14.13	14.64	15.94
	8H	13.71	14.18	14.71	15.18	16.49	13.29	13.75	14.28	14.75	16.06
	12H	13.79	14.21	14.80	15.23	16.55	13.35	13.77	14.36	14.79	16.11
8H	4H	13.24	13.70	14.24	14.71	16.02	12.87	13.33	13.87	14.34	15.65
	6H	13.88	14.26	14.90	15.31	16.62	13.50	13.88	14.52	14.93	16.24
	8H	14.10	14.44	15.13	15.47	16.80	13.72	14.05	14.74	15.08	16.41
	12H	14.23	14.53	15.27	15.56	16.93	13.83	14.13	14.87	15.16	16.53
12H	4H	13.23	13.65	14.24	14.67	15.98	12.87	13.28	13.88	14.30	15.62
	6H	13.91	14.25	14.94	15.28	16.61	13.54	13.88	14.57	14.91	16.24
	8H	14.15	14.45	15.19	15.48	16.85	13.78	14.08	14.81	15.10	16.48