

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914310

Luminaire Tested: DFN2DIP-PN4F0-110D040US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914310
REPORT IS A COMBINATION OF REPORTS P899624 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D040US927-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10211.2 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 144.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914310
CATALOG NUMBER: DFN2DIP-PN4F0-110D040US927-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P914310

CATALOG NUMBER: DFN2DIP-PN4F0-110D040US927-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	73
1	104	99	96	92	98	94	91	88	85	83	80	77	75	73	69	68	66	66	66	66	63
2	95	88	82	77	90	83	78	74	76	71	68	68	65	62	62	59	57	57	57	57	54
3	87	78	70	65	82	74	68	62	67	62	58	61	57	53	55	52	49	49	49	49	46
4	80	69	61	55	76	66	59	54	60	55	50	55	50	47	50	46	43	43	43	43	40
5	74	62	54	48	70	60	52	47	54	48	44	50	45	41	45	41	38	38	38	38	35
6	68	56	48	42	65	54	47	41	49	43	39	45	40	36	41	37	34	34	34	34	31
7	64	51	43	38	60	49	42	37	45	39	34	41	36	32	38	34	30	30	30	30	28
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	28	28	28	28	25
9	55	43	35	30	53	41	34	30	38	32	28	35	30	27	33	28	25	25	25	25	23
10	52	40	32	28	49	38	31	27	35	30	26	33	28	24	30	26	23	23	23	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2629	2629	2629
5°	2633	2588	2604
10°	2607	2537	2520
15°	2571	2454	2389
20°	2524	2338	2229
25°	2475	2209	2074
30°	2410	2077	1877
35°	2346	1934	1705
40°	2281	1786	1507
45°	2205	1623	1327
50°	2127	1457	1152
55°	2045	1280	983
60°	1951	1096	810
65°	1842	908	729
70°	1710	732	661
75°	1545	646	602
80°	1305	543	524
85°	909	365	397

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2205 cd/sqm



TEST NUMBER: P914310

CATALOG NUMBER: DFN2DIP-PN4F0-110D040US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.5	3.3
10°-20°	926.6	9.1
20°-30°	1300.9	12.7
30°-40°	1418.1	13.9
40°-50°	1303.4	12.8
50°-60°	1023.6	10.0
60°-70°	666.3	6.5
70°-80°	343.0	3.4
80°-90°	90.4	0.9
90°-100°	62.0	0.6
100°-110°	197.0	1.9
110°-120°	337.2	3.3
120°-130°	443.5	4.3
130°-140°	497.8	4.9
140°-150°	488.1	4.8
150°-160°	409.5	4.0
160°-170°	271.5	2.7
170°-180°	94.9	0.9
0°-30°	2565.1	25.1
0°-40°	3983.1	39.0
0°-60°	6310.1	61.8
0°-90°	7409.8	72.6
90°-120°	596.2	5.8
90°-150°	2025.6	19.8
90°-180°	2801.0	27.4
0°-180°	10211.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3602	3602	3602	3602	3602	
5°	3602	3585	3543	3572	3562	341
15°	3426	3390	3279	3217	3184	965
25°	3109	3005	2790	2656	2607	1430
35°	2679	2513	2226	2021	1949	1677
45°	2190	1972	1630	1398	1320	1691
55°	1665	1411	1059	864	802	1488
65°	1124	860	567	456	446	1115
75°	600	371	261	238	235	634
85°	140	72	62	62	62	161
90°	1	11	30	28	29	10
95°	44	53	54	54	53	49
105°	182	184	186	188	188	192
115°	338	343	342	341	338	335
125°	492	500	497	495	494	440
135°	637	646	648	647	644	492
145°	773	779	784	785	781	483
155°	884	886	889	893	890	407
165°	961	960	960	966	962	271
175°	1000	998	996	1002	997	95
180°	1002	1002	1002	1002	1002	



TEST NUMBER: P914310

CATALOG NUMBER: DFN2DIP-PN4F0-110D040US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3601.5	3601.5	3601.5	3601.5	3601.5
2.5°	3617.7	3601.5	3565.5	3598.4	3591.8
5°	3601.5	3585.3	3542.7	3572.1	3562.4
7.5°	3572.1	3552.7	3507.1	3519.9	3503.6
10°	3533.0	3510.2	3445.2	3435.1	3415.8
12.5°	3484.3	3454.9	3366.7	3347.3	3311.3
15°	3425.5	3389.5	3278.8	3217.0	3184.4
17.5°	3357.0	3304.8	3167.9	3096.2	3044.0
20°	3278.8	3213.5	3050.6	2969.3	2897.4
22.5°	3194.2	3119.1	2930.0	2819.3	2770.5
25°	3109.4	3005.0	2789.9	2656.4	2607.3
27.5°	3008.5	2897.4	2659.5	2506.3	2431.3
30°	2900.9	2776.8	2516.0	2350.0	2261.8
32.5°	2796.5	2646.4	2379.4	2183.7	2102.1
35°	2679.2	2512.9	2226.3	2020.9	1948.9
37.5°	2565.2	2385.7	2082.7	1857.6	1776.4
40°	2444.4	2249.1	1932.7	1701.3	1616.6
42.5°	2320.6	2112.1	1783.0	1541.6	1460.3
45°	2190.3	1971.7	1629.8	1398.0	1319.9
47.5°	2066.5	1835.2	1483.1	1251.4	1179.9
50°	1929.5	1698.2	1339.7	1114.5	1046.4
52.5°	1795.7	1551.2	1202.7	987.6	925.7
55°	1665.3	1411.2	1059.1	863.8	801.9
57.5°	1531.9	1271.1	932.2	749.7	697.4
60°	1395.0	1134.2	798.4	632.5	580.3
62.5°	1261.5	1000.8	684.4	528.1	502.1
65°	1124.5	860.3	567.1	456.5	446.4
67.5°	994.2	730.0	456.5	400.8	391.1
70°	857.2	603.1	377.9	345.5	332.3
72.5°	726.8	485.5	316.1	290.1	283.5
75°	599.6	371.4	260.7	237.9	234.8
77.5°	472.7	263.9	205.4	192.3	185.7
80°	355.1	189.2	156.3	143.5	143.5
82.5°	247.6	127.2	107.6	101.0	101.0
85°	140.1	71.6	61.9	61.9	61.9
87.5°	52.2	25.9	25.9	22.8	22.8
90°	0.9	10.9	29.6	27.8	28.7
92.5°	18.7	25.3	26.3	27.2	27.2
95°	44.1	52.6	54.1	54.1	52.6
97.5°	73.4	81.3	84.6	84.6	84.6
100°	107.3	114.2	116.6	116.6	115.7
102.5°	142.9	148.1	151.4	152.3	151.4
105°	181.9	184.3	186.1	187.6	187.6
107.5°	220.5	224.2	224.2	224.7	220.5
110°	258.0	262.8	262.8	262.8	260.5



TEST NUMBER: P914310

CATALOG NUMBER: DFN2DIP-PN4F0-110D040US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	298.5	303.6	302.7	300.3	298.5
115°	338.3	343.3	341.7	340.8	338.3
117.5°	377.9	384.6	380.4	377.9	375.6
120°	417.9	424.5	417.9	417.9	415.1
122.5°	454.1	462.6	458.4	455.9	454.1
125°	492.2	499.7	497.3	494.6	493.7
127.5°	529.3	538.7	535.4	531.7	529.3
130°	564.0	575.0	573.5	571.6	568.3
132.5°	603.0	611.5	612.1	607.8	605.5
135°	636.6	645.9	647.8	646.8	644.4
137.5°	674.1	681.6	683.1	682.5	678.9
140°	706.9	714.5	718.7	718.7	715.4
142.5°	740.8	748.4	750.8	751.7	748.4
145°	772.9	778.9	783.7	784.7	781.3
147.5°	801.5	809.1	812.7	814.2	810.9
150°	831.2	836.3	839.6	842.3	839.6
152.5°	857.5	862.5	866.8	870.1	866.8
155°	883.7	886.1	888.8	893.1	890.3
157.5°	906.4	908.2	909.7	915.8	911.5
160°	926.6	928.4	929.3	934.5	930.8
162.5°	945.3	945.3	946.3	952.0	947.8
165°	961.4	960.4	960.4	966.5	962.3
167.5°	975.9	973.1	973.1	979.2	974.9
170°	986.7	984.3	983.4	989.4	984.3
172.5°	994.3	991.9	990.9	997.0	991.9
175°	1000.4	997.9	996.1	1002.1	997.0
177.5°	1003.7	1001.2	999.4	1004.6	999.4
180°	1002.1	1002.1	1002.1	1002.1	1002.1



TEST NUMBER: P914310
 CATALOG NUMBER: DFN2DIP-PN4F0-110D040US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.40	13.46	13.15	14.22	15.13	8.37	9.42	9.11	10.18	11.09
	3H	14.10	15.05	14.86	15.81	16.76	9.57	10.52	10.33	11.29	12.23
	4H	14.72	15.61	15.50	16.39	17.34	10.04	10.93	10.81	11.70	12.66
	6H	15.16	15.98	15.94	16.76	17.73	10.37	11.19	11.16	11.98	12.94
	8H	15.29	16.07	16.09	16.88	17.85	10.47	11.25	11.26	12.05	13.02
	12H	15.36	16.10	16.16	16.90	17.90	10.52	11.26	11.32	12.06	13.05
4H	2H	12.45	13.34	13.23	14.12	15.07	8.99	9.88	9.77	10.66	11.61
	3H	14.30	15.04	15.09	15.85	16.82	10.36	11.10	11.15	11.92	12.89
	4H	15.00	15.67	15.81	16.49	17.49	10.92	11.59	11.73	12.40	13.40
	6H	15.53	16.11	16.36	16.95	17.96	11.35	11.93	12.18	12.77	13.77
	8H	15.71	16.26	16.54	17.09	18.11	11.49	12.03	12.31	12.86	13.88
	12H	15.82	16.31	16.67	17.16	18.18	11.56	12.05	12.41	12.90	13.92
8H	4H	14.99	15.53	15.81	16.36	17.38	11.22	11.76	12.04	12.59	13.61
	6H	15.57	16.01	16.42	16.89	17.91	11.75	12.19	12.60	13.07	14.09
	8H	15.78	16.18	16.65	17.05	18.09	11.94	12.34	12.80	13.21	14.24
	12H	15.94	16.29	16.80	17.15	18.24	12.07	12.42	12.94	13.28	14.37
12H	4H	14.95	15.44	15.80	16.29	17.31	11.23	11.72	12.08	12.57	13.60
	6H	15.54	15.94	16.41	16.81	17.84	11.80	12.19	12.66	13.07	14.10
	8H	15.77	16.12	16.64	16.99	18.08	12.02	12.37	12.89	13.23	14.32