

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914314

Luminaire Tested: DFN2DIP-PN4F0-110D050US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914314
REPORT IS A COMBINATION OF REPORTS P899642 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D050US927-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10912.4 lumens
Efficiency: N/A
Efficacy: 71.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 151.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914314

CATALOG NUMBER: DFN2DIP-PN4F0-110D050US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P914314

CATALOG NUMBER: DFN2DIP-PN4F0-110D050US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		73	73	73	68
1	102	98	94	91	97	93	90	87	83	80	78		74	72	70		65	64	63	59
2	94	87	81	76	88	82	77	72	73	69	66		66	62	60		58	56	54	50
3	86	77	70	64	81	73	66	61	65	60	56		59	55	51		52	49	47	43
4	79	68	61	55	74	65	58	53	59	53	49		53	48	45		47	44	41	38
5	73	61	53	47	69	58	51	46	53	47	42		48	43	39		43	39	36	33
6	68	56	47	42	64	53	46	40	48	42	37		43	38	35		39	35	32	29
7	63	50	42	37	59	48	41	36	44	38	33		40	35	31		36	32	29	26
8	58	46	38	33	55	44	37	32	40	34	30		37	32	28		33	29	26	24
9	55	42	35	30	52	40	34	29	37	31	27		34	29	25		31	27	24	22
10	51	39	32	27	48	37	31	26	34	29	25		31	27	23		29	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2629	2629	2629
5°	2633	2588	2604
10°	2607	2537	2520
15°	2571	2454	2389
20°	2524	2338	2229
25°	2475	2209	2074
30°	2410	2077	1877
35°	2346	1934	1705
40°	2281	1786	1507
45°	2205	1623	1327
50°	2127	1457	1152
55°	2045	1280	983
60°	1951	1096	810
65°	1842	908	729
70°	1710	732	661
75°	1545	646	602
80°	1305	543	524
85°	909	365	397

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2205 cd/sqm

TEST NUMBER: P914314

CATALOG NUMBER: DFN2DIP-PN4F0-110D050US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.5	3.1
10°-20°	926.6	8.5
20°-30°	1300.9	11.9
30°-40°	1418.1	13.0
40°-50°	1303.4	11.9
50°-60°	1023.6	9.4
60°-70°	666.3	6.1
70°-80°	343.0	3.1
80°-90°	91.1	0.8
90°-100°	77.5	0.7
100°-110°	246.3	2.3
110°-120°	421.5	3.9
120°-130°	554.3	5.1
130°-140°	622.2	5.7
140°-150°	610.1	5.6
150°-160°	511.8	4.7
160°-170°	339.4	3.1
170°-180°	118.6	1.1
0°-30°	2565.1	23.5
0°-40°	3983.1	36.5
0°-60°	6310.1	57.8
0°-90°	7410.5	67.9
90°-120°	745.3	6.8
90°-150°	2532.0	23.2
90°-180°	3502.0	32.1
0°-180°	10912.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3602	3602	3602	3602	3602	
5°	3602	3585	3543	3572	3562	341
15°	3426	3390	3279	3217	3184	965
25°	3109	3005	2790	2656	2607	1430
35°	2679	2513	2226	2021	1949	1677
45°	2190	1972	1630	1398	1320	1691
55°	1665	1411	1059	864	802	1488
65°	1124	860	567	456	446	1115
75°	600	371	261	238	235	634
85°	140	72	62	62	62	161
90°	1	14	37	35	36	11
95°	55	66	68	68	66	61
105°	227	230	233	234	234	240
115°	423	429	427	426	423	418
125°	615	625	622	618	617	550
135°	796	807	810	809	806	615
145°	966	974	980	981	977	604
155°	1105	1108	1111	1116	1113	508
165°	1202	1201	1201	1208	1203	339
175°	1250	1247	1245	1253	1246	119
180°	1253	1253	1253	1253	1253	

TEST NUMBER: P914314

CATALOG NUMBER: DFN2DIP-PN4F0-110D050US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3601.5	3601.5	3601.5	3601.5	3601.5
2.5°	3617.7	3601.5	3565.5	3598.4	3591.8
5°	3601.5	3585.3	3542.7	3572.1	3562.4
7.5°	3572.1	3552.7	3507.1	3519.9	3503.6
10°	3533.0	3510.2	3445.2	3435.1	3415.8
12.5°	3484.3	3454.9	3366.7	3347.3	3311.3
15°	3425.5	3389.5	3278.8	3217.0	3184.4
17.5°	3357.0	3304.8	3167.9	3096.2	3044.0
20°	3278.8	3213.5	3050.6	2969.3	2897.4
22.5°	3194.2	3119.1	2930.0	2819.3	2770.5
25°	3109.4	3005.0	2789.9	2656.4	2607.3
27.5°	3008.5	2897.4	2659.5	2506.3	2431.3
30°	2900.9	2776.8	2516.0	2350.0	2261.8
32.5°	2796.5	2646.4	2379.4	2183.7	2102.1
35°	2679.2	2512.9	2226.3	2020.9	1948.9
37.5°	2565.2	2385.7	2082.7	1857.6	1776.4
40°	2444.4	2249.1	1932.7	1701.3	1616.6
42.5°	2320.6	2112.1	1783.0	1541.6	1460.3
45°	2190.3	1971.7	1629.8	1398.0	1319.9
47.5°	2066.5	1835.2	1483.1	1251.4	1179.9
50°	1929.5	1698.2	1339.7	1114.5	1046.4
52.5°	1795.7	1551.2	1202.7	987.6	925.7
55°	1665.3	1411.2	1059.1	863.8	801.9
57.5°	1531.9	1271.1	932.2	749.7	697.4
60°	1395.0	1134.2	798.4	632.5	580.3
62.5°	1261.5	1000.8	684.4	528.1	502.1
65°	1124.5	860.3	567.1	456.5	446.4
67.5°	994.2	730.0	456.5	400.8	391.1
70°	857.2	603.1	377.9	345.5	332.3
72.5°	726.8	485.5	316.1	290.1	283.5
75°	599.6	371.4	260.7	237.9	234.8
77.5°	472.7	263.9	205.4	192.3	185.7
80°	355.1	189.2	156.3	143.5	143.5
82.5°	247.6	127.2	107.6	101.0	101.0
85°	140.1	71.6	61.9	61.9	61.9
87.5°	52.2	25.9	25.9	22.8	22.8
90°	1.1	13.6	37.0	34.8	35.9
92.5°	23.4	31.7	32.9	34.0	34.0
95°	55.1	65.8	67.6	67.6	65.8
97.5°	91.7	101.6	105.8	105.8	105.8
100°	134.0	142.8	145.8	145.8	144.7
102.5°	178.6	185.1	189.2	190.4	189.2
105°	227.4	230.4	232.7	234.5	234.5
107.5°	275.7	280.2	280.2	281.0	275.7
110°	322.5	328.6	328.6	328.6	325.5

TEST NUMBER: P914314

CATALOG NUMBER: DFN2DIP-PN4F0-110D050US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	373.1	379.5	378.4	375.4	373.1
115°	422.9	429.0	427.1	426.0	422.9
117.5°	472.5	480.8	475.5	472.5	469.4
120°	522.3	530.6	522.3	522.3	518.9
122.5°	567.6	578.2	572.9	569.9	567.6
125°	615.2	624.6	621.6	618.2	617.1
127.5°	661.6	673.4	669.2	664.6	661.6
130°	705.1	718.7	716.8	714.5	710.3
132.5°	753.8	764.4	765.2	759.9	756.8
135°	795.7	807.4	809.7	808.6	805.6
137.5°	842.6	852.0	853.9	853.1	848.6
140°	883.7	893.2	898.4	898.4	894.3
142.5°	926.0	935.5	938.5	939.6	935.5
145°	966.1	973.6	979.6	980.8	976.6
147.5°	1002.0	1011.4	1015.9	1017.8	1013.6
150°	1038.9	1045.4	1049.5	1052.9	1049.5
152.5°	1071.8	1078.2	1083.5	1087.7	1083.5
155°	1104.6	1107.6	1111.0	1116.3	1112.9
157.5°	1133.0	1135.2	1137.1	1144.7	1139.4
160°	1158.2	1160.5	1161.7	1168.1	1163.6
162.5°	1181.7	1181.7	1182.8	1190.0	1184.7
165°	1201.7	1200.6	1200.6	1208.2	1202.8
167.5°	1219.8	1216.4	1216.4	1224.0	1218.7
170°	1233.4	1230.4	1229.3	1236.8	1230.4
172.5°	1242.9	1239.8	1238.7	1246.3	1239.8
175°	1250.5	1247.4	1245.2	1252.7	1246.3
177.5°	1254.6	1251.6	1249.3	1255.7	1249.3
180°	1252.7	1252.7	1252.7	1252.7	1252.7

TEST NUMBER: P914314

CATALOG NUMBER: DFN2DIP-PN4F0-110D050US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.04	13.04	12.83	13.85	14.85	8.01	9.01	8.80	9.82	10.81
	3H	13.73	14.63	14.54	15.45	16.47	9.21	10.10	10.01	10.92	11.95
	4H	14.35	15.20	15.18	16.03	17.06	9.67	10.51	10.49	11.34	12.37
	6H	14.78	15.56	15.62	16.40	17.45	10.00	10.77	10.83	11.61	12.66
	8H	14.92	15.66	15.76	16.51	17.56	10.09	10.83	10.94	11.69	12.73
	12H	14.99	15.69	15.84	16.54	17.61	10.14	10.85	10.99	11.70	12.77
4H	2H	12.08	12.92	12.91	13.75	14.79	8.62	9.47	9.45	10.30	11.33
	3H	13.93	14.63	14.77	15.49	16.54	9.99	10.69	10.83	11.55	12.60
	4H	14.63	15.27	15.48	16.13	17.20	10.55	11.18	11.40	12.04	13.12
	6H	15.16	15.70	16.02	16.59	17.67	10.97	11.52	11.84	12.41	13.49
	8H	15.34	15.85	16.21	16.73	17.82	11.11	11.62	11.98	12.50	13.59
	12H	15.44	15.90	16.33	16.80	17.90	11.18	11.64	12.07	12.54	13.64
8H	4H	14.61	15.12	15.48	16.00	17.09	10.84	11.35	11.71	12.23	13.32
	6H	15.18	15.61	16.08	16.53	17.62	11.37	11.79	12.26	12.71	13.80
	8H	15.40	15.78	16.31	16.69	17.80	11.56	11.93	12.47	12.85	13.96
	12H	15.55	15.88	16.46	16.79	17.95	11.69	12.02	12.60	12.92	14.09
12H	4H	14.57	15.03	15.46	15.93	17.03	10.85	11.31	11.74	12.21	13.31
	6H	15.16	15.54	16.07	16.45	17.56	11.42	11.79	12.33	12.71	13.82
	8H	15.39	15.72	16.30	16.63	17.79	11.64	11.97	12.55	12.87	14.04