

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914348

Luminaire Tested: DFN2DIP-PN4F0-120D050US927-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P914348  
REPORT IS A COMBINATION OF REPORTS P899643 AND P896497  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-120D050US927-FLLFLL  
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12916.6 lumens  
Efficiency: N/A  
Efficacy: 78.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 163.9  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9781  
Total Harmonic Distortion (THDi): 0.075  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P914348  
CATALOG NUMBER: DFN2DIP-PN4F0-120D050US927-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P914348

CATALOG NUMBER: DFN2DIP-PN4F0-120D050US927-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	73
1	103	98	94	91	97	94	90	87	84	82	79	76	74	72	68	67	65	65	65	65	61
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	55	55	55	51
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	47	47	47	44
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40	40	40	40	37
5	72	60	51	45	68	57	50	44	52	46	41	47	42	38	43	39	35	35	35	35	33
6	67	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	31	31	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	28	28	28	25
8	57	45	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	25	25	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	22	22	22	20
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	20	20	20	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2700	2700	2700
5°	2704	2663	2681
10°	2682	2627	2645
15°	2643	2584	2589
20°	2590	2525	2531
25°	2537	2453	2465
30°	2470	2387	2380
35°	2407	2308	2290
40°	2330	2229	2204
45°	2252	2149	2117
50°	2168	2066	2016
55°	2079	1970	1923
60°	1979	1855	1817
65°	1870	1737	1691
70°	1732	1592	1556
75°	1539	1419	1432
80°	1307	1199	1195
85°	946	819	799

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2252 cd/sqm



TEST NUMBER: P914348

CATALOG NUMBER: DFN2DIP-PN4F0-120D050US927-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	348.1	2.7
10°-20°	979.5	7.6
20°-30°	1439.5	11.1
30°-40°	1671.9	12.9
40°-50°	1669.9	12.9
50°-60°	1456.0	11.3
60°-70°	1076.3	8.3
70°-80°	609.0	4.7
80°-90°	164.3	1.3
90°-100°	77.5	0.6
100°-110°	246.3	1.9
110°-120°	421.5	3.3
120°-130°	554.3	4.3
130°-140°	622.2	4.8
140°-150°	610.1	4.7
150°-160°	511.8	4.0
160°-170°	339.4	2.6
170°-180°	118.6	0.9
0°-30°	2767.2	21.4
0°-40°	4439.1	34.4
0°-60°	7565.0	58.6
0°-90°	9414.7	72.9
90°-120°	745.3	5.8
90°-150°	2532.0	19.6
90°-180°	3502.0	27.1
0°-180°	12916.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3699	3699	3699	3699	3699	
5°	3699	3685	3646	3674	3667	351
15°	3521	3500	3454	3468	3450	992
25°	3187	3158	3098	3105	3098	1466
35°	2749	2714	2657	2636	2618	1717
45°	2237	2212	2159	2120	2106	1727
55°	1693	1672	1629	1586	1569	1514
65°	1142	1120	1085	1053	1035	1129
75°	597	591	572	551	558	638
85°	146	142	139	128	124	162
90°	1	14	37	35	36	12
95°	55	66	68	68	66	61
105°	227	230	233	234	234	240
115°	423	429	427	426	423	418
125°	615	625	622	618	617	550
135°	796	807	810	809	806	615
145°	966	974	980	981	977	604
155°	1105	1108	1111	1116	1113	508
165°	1202	1201	1201	1208	1203	339
175°	1250	1247	1245	1253	1246	119
180°	1253	1253	1253	1253	1253	



TEST NUMBER: P914348

CATALOG NUMBER: DFN2DIP-PN4F0-120D050US927-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3698.9	3698.9	3698.9	3698.9	3698.9
2.5°	3720.4	3702.7	3663.4	3698.9	3692.1
5°	3698.9	3684.9	3645.7	3674.0	3667.2
7.5°	3674.0	3652.8	3613.6	3642.3	3635.2
10°	3635.2	3610.2	3567.6	3595.9	3585.3
12.5°	3581.5	3560.4	3517.8	3535.5	3528.3
15°	3521.2	3500.0	3453.6	3467.9	3450.2
17.5°	3446.5	3425.3	3378.9	3396.6	3378.9
20°	3364.6	3343.4	3293.7	3304.2	3290.2
22.5°	3283.0	3251.0	3204.5	3204.5	3197.4
25°	3186.8	3158.5	3098.1	3105.0	3098.1
27.5°	3080.0	3055.1	3009.1	2998.5	2980.8
30°	2973.6	2944.9	2891.7	2881.2	2866.8
32.5°	2859.6	2838.5	2781.5	2760.0	2745.7
35°	2749.4	2714.0	2657.0	2635.5	2617.8
37.5°	2624.9	2592.9	2535.9	2511.0	2493.2
40°	2497.0	2468.4	2411.3	2379.6	2365.3
42.5°	2372.5	2343.8	2287.2	2251.4	2230.2
45°	2237.4	2212.5	2158.9	2120.0	2105.7
47.5°	2105.7	2080.7	2023.8	1984.6	1963.4
50°	1966.8	1949.1	1899.3	1849.4	1831.7
52.5°	1831.7	1806.8	1760.8	1721.5	1696.6
55°	1693.2	1671.7	1629.0	1586.4	1568.7
57.5°	1554.3	1536.6	1490.2	1447.6	1433.2
60°	1415.5	1401.5	1351.7	1312.5	1301.9
62.5°	1280.4	1255.4	1220.0	1184.5	1170.2
65°	1141.9	1120.4	1084.9	1052.8	1035.1
67.5°	999.7	981.5	949.8	925.0	910.6
70°	867.9	853.6	821.5	796.6	782.7
72.5°	732.8	718.5	700.8	675.9	665.3
75°	597.4	590.6	572.4	551.4	558.5
77.5°	476.6	462.2	455.1	444.5	434.0
80°	355.8	352.0	344.9	334.4	327.2
82.5°	241.9	241.9	238.5	224.2	224.2
85°	145.7	142.3	138.9	127.9	124.5
87.5°	64.2	57.0	49.8	39.2	35.5
90°	1.1	13.6	37.0	34.8	35.9
92.5°	23.4	31.7	32.9	34.0	34.0
95°	55.1	65.8	67.6	67.6	65.8
97.5°	91.7	101.6	105.8	105.8	105.8
100°	134.0	142.8	145.8	145.8	144.7
102.5°	178.6	185.1	189.2	190.4	189.2
105°	227.4	230.4	232.7	234.5	234.5
107.5°	275.7	280.2	280.2	281.0	275.7
110°	322.5	328.6	328.6	328.6	325.5



TEST NUMBER: P914348

CATALOG NUMBER: DFN2DIP-PN4F0-120D050US927-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	373.1	379.5	378.4	375.4	373.1
115°	422.9	429.0	427.1	426.0	422.9
117.5°	472.5	480.8	475.5	472.5	469.4
120°	522.3	530.6	522.3	522.3	518.9
122.5°	567.6	578.2	572.9	569.9	567.6
125°	615.2	624.6	621.6	618.2	617.1
127.5°	661.6	673.4	669.2	664.6	661.6
130°	705.1	718.7	716.8	714.5	710.3
132.5°	753.8	764.4	765.2	759.9	756.8
135°	795.7	807.4	809.7	808.6	805.6
137.5°	842.6	852.0	853.9	853.1	848.6
140°	883.7	893.2	898.4	898.4	894.3
142.5°	926.0	935.5	938.5	939.6	935.5
145°	966.1	973.6	979.6	980.8	976.6
147.5°	1002.0	1011.4	1015.9	1017.8	1013.6
150°	1038.9	1045.4	1049.5	1052.9	1049.5
152.5°	1071.8	1078.2	1083.5	1087.7	1083.5
155°	1104.6	1107.6	1111.0	1116.3	1112.9
157.5°	1133.0	1135.2	1137.1	1144.7	1139.4
160°	1158.2	1160.5	1161.7	1168.1	1163.6
162.5°	1181.7	1181.7	1182.8	1190.0	1184.7
165°	1201.7	1200.6	1200.6	1208.2	1202.8
167.5°	1219.8	1216.4	1216.4	1224.0	1218.7
170°	1233.4	1230.4	1229.3	1236.8	1230.4
172.5°	1242.9	1239.8	1238.7	1246.3	1239.8
175°	1250.5	1247.4	1245.2	1252.7	1246.3
177.5°	1254.6	1251.6	1249.3	1255.7	1249.3
180°	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P914348  
 CATALOG NUMBER: DFN2DIP-PN4F0-120D050US927-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.62	13.73	13.35	14.48	15.39	12.18	13.29	12.91	14.04	14.95
	3H	14.30	15.30	15.04	16.06	17.00	13.81	14.82	14.56	15.58	16.51
	4H	14.90	15.84	15.66	16.62	17.56	14.41	15.36	15.18	16.13	17.07
	6H	15.31	16.19	16.09	16.97	17.93	14.82	15.69	15.60	16.48	17.44
	8H	15.43	16.26	16.21	17.06	18.02	14.94	15.77	15.72	16.57	17.53
	12H	15.49	16.28	16.28	17.07	18.06	14.99	15.78	15.78	16.57	17.56
4H	2H	13.11	14.05	13.88	14.83	15.77	12.76	13.70	13.53	14.47	15.42
	3H	15.00	15.79	15.78	16.60	17.56	14.60	15.39	15.38	16.19	17.16
	4H	15.73	16.44	16.52	17.25	18.24	15.31	16.03	16.10	16.83	17.82
	6H	16.26	16.88	17.07	17.71	18.71	15.83	16.46	16.65	17.29	18.28
	8H	16.42	17.00	17.23	17.82	18.83	15.99	16.57	16.80	17.40	18.41
	12H	16.50	17.03	17.34	17.87	18.89	16.06	16.59	16.90	17.44	18.45
8H	4H	15.94	16.52	16.76	17.35	18.36	15.57	16.15	16.39	16.98	17.99
	6H	16.59	17.07	17.43	17.94	18.95	16.21	16.69	17.06	17.56	18.57
	8H	16.81	17.24	17.67	18.11	19.13	16.43	16.86	17.29	17.72	18.75
	12H	16.96	17.34	17.82	18.19	19.28	16.56	16.93	17.42	17.79	18.87
12H	4H	15.94	16.46	16.78	17.31	18.33	15.58	16.10	16.42	16.95	17.97
	6H	16.62	17.05	17.48	17.92	18.94	16.26	16.69	17.11	17.55	18.58
	8H	16.88	17.25	17.74	18.11	19.19	16.51	16.88	17.36	17.74	18.82