

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906027

Luminaire Tested: DFN2DIP-PN4F0-080D060US835-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906027
REPORT IS A COMBINATION OF REPORTS P901174 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-080D060US835-RLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12740.0 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 122.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906027
CATALOG NUMBER: DFN2DIP-PN4F0-080D060US835-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P906027

CATALOG NUMBER: DFN2DIP-PN4F0-080D060US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53	53	53	53
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46	46	46	46
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44	39	39	39	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38	34	34	34	34
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	35	33	30	30	30	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26	26	26	26
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26	23	23	23	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21	21	21	21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21	19	19	19	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19	17	17	17	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	16	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2414	2414	2414
5°	2417	2376	2391
10°	2393	2329	2313
15°	2360	2253	2194
20°	2317	2147	2046
25°	2272	2028	1904
30°	2212	1906	1724
35°	2154	1775	1565
40°	2094	1640	1383
45°	2024	1490	1218
50°	1953	1338	1057
55°	1878	1176	903
60°	1791	1006	743
65°	1691	833	669
70°	1570	673	607
75°	1418	594	553
80°	1198	499	481
85°	835	335	364

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2024 cd/sqm



TEST NUMBER: P906027

CATALOG NUMBER: DFN2DIP-PN4F0-080D060US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	309.9	2.4
10°-20°	850.7	6.7
20°-30°	1194.3	9.4
30°-40°	1301.9	10.2
40°-50°	1196.6	9.4
50°-60°	939.7	7.4
60°-70°	611.7	4.8
70°-80°	314.9	2.5
80°-90°	83.9	0.7
90°-100°	66.8	0.5
100°-110°	248.9	2.0
110°-120°	660.2	5.2
120°-130°	1094.9	8.6
130°-140°	1163.0	9.1
140°-150°	1080.9	8.5
150°-160°	869.0	6.8
160°-170°	560.0	4.4
170°-180°	192.7	1.5
0°-30°	2354.9	18.5
0°-40°	3656.8	28.7
0°-60°	5793.1	45.5
0°-90°	6803.6	53.4
90°-120°	975.8	7.7
90°-150°	4314.7	33.9
90°-180°	5936.0	46.6
0°-180°	12740.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3306	3306	3306	3306	3306	
5°	3306	3292	3252	3279	3270	314
15°	3145	3112	3010	2953	2924	886
25°	2855	2759	2561	2439	2394	1313
35°	2460	2307	2044	1855	1789	1540
45°	2011	1810	1496	1284	1212	1553
55°	1529	1296	972	793	736	1366
65°	1032	790	521	419	410	1024
75°	550	341	239	218	216	582
85°	129	66	57	57	57	148
90°	1	18	29	37	40	12
95°	95	47	57	65	63	113
105°	445	489	89	105	111	476
115°	842	867	904	226	120	829
125°	1191	1210	1238	1248	1253	1062
135°	1474	1498	1511	1525	1522	1139
145°	1710	1708	1733	1744	1736	1069
155°	1883	1870	1887	1896	1884	868
165°	1984	1975	1980	1990	1980	560
175°	2029	2019	2022	2032	2018	193
180°	2025	2025	2025	2025	2025	



TEST NUMBER: P906027

CATALOG NUMBER: DFN2DIP-PN4F0-080D060US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3306.4	3306.4	3306.4	3306.4	3306.4
2.5°	3321.3	3306.4	3273.4	3303.5	3297.5
5°	3306.4	3291.5	3252.4	3279.4	3270.5
7.5°	3279.4	3261.6	3219.7	3231.5	3216.5
10°	3243.5	3222.6	3162.9	3153.7	3135.9
12.5°	3198.8	3171.8	3090.8	3073.0	3040.0
15°	3144.8	3111.8	3010.2	2953.4	2923.5
17.5°	3081.9	3034.0	2908.3	2842.6	2794.6
20°	3010.2	2950.2	2800.7	2726.1	2660.0
22.5°	2932.4	2863.5	2689.9	2588.3	2543.5
25°	2854.6	2758.8	2561.3	2438.8	2393.7
27.5°	2761.9	2660.0	2441.6	2301.0	2232.1
30°	2663.2	2549.2	2309.9	2157.5	2076.5
32.5°	2567.3	2429.6	2184.5	2004.8	1929.9
35°	2459.7	2307.0	2043.8	1855.3	1789.2
37.5°	2354.9	2190.2	1912.1	1705.4	1630.8
40°	2244.2	2064.8	1774.3	1561.9	1484.1
42.5°	2130.5	1939.1	1636.8	1415.3	1340.6
45°	2010.8	1810.2	1496.2	1283.5	1211.8
47.5°	1897.2	1684.8	1361.6	1148.9	1083.2
50°	1771.4	1559.1	1229.9	1023.2	960.6
52.5°	1648.6	1424.1	1104.1	906.7	849.9
55°	1528.9	1295.6	972.4	793.0	736.2
57.5°	1406.4	1167.0	855.9	688.3	640.3
60°	1280.6	1041.3	733.0	580.6	532.7
62.5°	1158.1	918.7	628.3	484.8	461.0
65°	1032.4	789.8	520.6	419.1	409.8
67.5°	912.7	670.2	419.1	367.9	359.1
70°	787.0	553.7	347.0	317.1	305.1
72.5°	667.3	445.7	290.2	266.4	260.3
75°	550.5	341.0	239.4	218.4	215.6
77.5°	434.0	242.2	188.6	176.5	170.5
80°	326.0	173.7	143.5	131.7	131.7
82.5°	227.3	116.8	98.7	92.7	92.7
85°	128.6	65.7	56.8	56.8	56.8
87.5°	47.9	23.8	23.8	21.0	21.0
90°	1.4	17.6	29.2	36.7	39.5
92.5°	36.7	30.8	35.1	38.1	39.5
95°	95.2	46.8	57.1	64.6	63.0
97.5°	171.4	51.3	74.6	79.2	80.6
100°	259.4	58.6	83.5	95.2	98.1
102.5°	356.0	353.2	86.5	102.5	107.0
105°	445.4	489.4	89.4	105.4	111.4
107.5°	549.5	586.0	92.4	108.4	114.3
110°	649.2	679.8	256.5	110.0	115.7



TEST NUMBER: P906027

CATALOG NUMBER: DFN2DIP-PN4F0-080D060US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	742.9	769.2	744.3	112.7	117.3
115°	842.5	867.4	904.1	225.7	120.2
117.5°	928.9	958.2	983.2	773.6	389.7
120°	1025.7	1047.6	1074.1	1091.6	893.8
122.5°	1107.6	1131.1	1160.5	1169.2	1170.8
125°	1191.2	1210.3	1238.1	1248.4	1252.7
127.5°	1267.4	1287.9	1310.0	1324.6	1326.0
130°	1339.2	1362.7	1378.7	1394.9	1393.5
132.5°	1412.5	1431.6	1447.6	1460.8	1459.4
135°	1474.1	1497.6	1510.6	1525.4	1522.4
137.5°	1538.4	1556.0	1570.8	1585.4	1581.1
140°	1601.4	1613.3	1629.3	1642.5	1635.2
142.5°	1654.3	1664.6	1683.6	1695.2	1687.9
145°	1710.0	1708.4	1733.3	1743.6	1736.3
147.5°	1758.2	1753.8	1778.7	1786.0	1780.3
150°	1805.2	1794.9	1818.4	1827.1	1819.8
152.5°	1844.7	1833.0	1854.9	1863.8	1853.5
155°	1882.8	1869.7	1887.3	1896.0	1884.3
157.5°	1913.6	1901.9	1915.1	1925.4	1913.6
160°	1940.0	1931.1	1940.0	1948.7	1938.5
162.5°	1963.3	1954.6	1961.9	1972.2	1959.0
165°	1983.9	1975.2	1979.5	1989.8	1979.5
167.5°	2000.0	1991.2	1995.7	2006.0	1992.7
170°	2013.3	2004.4	2007.4	2017.6	2004.4
172.5°	2022.0	2013.3	2016.2	2026.5	2013.3
175°	2029.3	2019.0	2022.0	2032.2	2017.6
177.5°	2032.2	2022.0	2023.5	2033.8	2020.6
180°	2024.9	2024.9	2024.9	2024.9	2024.9



TEST NUMBER: P906027
 CATALOG NUMBER: DFN2DIP-PN4F0-080D060US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.53	11.39	11.46	12.33	13.56	6.49	7.35	7.43	8.30	9.52
	3H	12.21	12.98	13.16	13.93	15.18	7.68	8.45	8.63	9.41	10.66
	4H	12.82	13.55	13.78	14.51	15.77	8.14	8.86	9.10	9.82	11.08
	6H	13.25	13.92	14.22	14.88	16.15	8.46	9.13	9.43	10.09	11.36
	8H	13.38	14.01	14.35	14.99	16.26	8.55	9.19	9.53	10.17	11.44
	12H	13.44	14.04	14.42	15.02	16.31	8.60	9.20	9.58	10.18	11.47
4H	2H	10.55	11.28	11.52	12.24	13.49	7.09	7.82	8.06	8.78	10.04
	3H	12.38	12.99	13.36	13.98	15.25	8.45	9.05	9.42	10.04	11.31
	4H	13.08	13.63	14.06	14.61	15.91	9.00	9.55	9.98	10.53	11.83
	6H	13.60	14.07	14.60	15.08	16.37	9.42	9.89	10.42	10.90	12.19
	8H	13.78	14.22	14.78	15.22	16.53	9.55	9.99	10.55	10.99	12.30
	12H	13.88	14.27	14.89	15.29	16.60	9.62	10.01	10.63	11.03	12.34
8H	4H	13.05	13.49	14.05	14.49	15.80	9.28	9.72	10.28	10.72	12.03
	6H	13.62	13.99	14.64	15.03	16.33	9.80	10.17	10.82	11.21	12.51
	8H	13.84	14.16	14.87	15.19	16.51	9.99	10.31	11.02	11.34	12.67
	12H	13.98	14.26	15.01	15.29	16.66	10.11	10.40	11.15	11.42	12.79
12H	4H	13.00	13.40	14.02	14.42	15.73	9.29	9.69	10.30	10.70	12.02
	6H	13.60	13.92	14.63	14.95	16.27	9.85	10.17	10.88	11.20	12.53
	8H	13.82	14.10	14.85	15.13	16.50	10.06	10.35	11.10	11.37	12.74