

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916821

Luminaire Tested: DFN2DIP-PN4F0-050D040US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916821
REPORT IS A COMBINATION OF REPORTS P901131 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-050D040US930-FLLONL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7264.3 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 74.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916821

CATALOG NUMBER: DFN2DIP-PN4F0-050D040US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P916821

CATALOG NUMBER: DFN2DIP-PN4F0-050D040US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		101	101	101	101		86	86	86		73	73	73		61	61	61
1	99	95	91	87		92	88	85	82		76	73	71		65	63	61		54	53	52
2	90	83	76	71		84	77	72	67		66	62	59		57	54	51		48	46	44
3	82	73	65	59		76	68	61	56		59	54	50		50	46	43		42	39	37
4	75	64	56	50		70	60	53	48		52	47	42		45	40	37		38	35	32
5	69	57	49	43		64	54	46	41		47	41	36		40	36	32		34	31	28
6	64	52	43	37		59	48	41	36		42	36	32		36	32	28		31	27	25
7	59	47	39	33		55	44	36	31		38	32	28		33	28	25		28	25	22
8	55	42	34	29		51	40	33	28		35	29	25		30	26	22		26	22	20
9	51	39	31	26		47	36	29	25		32	26	22		28	23	20		24	20	18
10	48	35	28	23		44	33	27	22		29	24	20		26	21	18		22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1158	1158	1158
5°	1160	1142	1150
10°	1150	1127	1134
15°	1133	1108	1110
20°	1111	1083	1086
25°	1088	1052	1057
30°	1059	1023	1021
35°	1032	990	982
40°	999	956	945
45°	966	922	908
50°	930	886	865
55°	892	845	825
60°	849	796	779
65°	802	745	725
70°	743	683	667
75°	660	609	614
80°	561	514	512
85°	406	351	343

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 966 cd/sqm

TEST NUMBER: P916821

CATALOG NUMBER: DFN2DIP-PN4F0-050D040US930-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.3	2.1
10°-20°	420.0	5.8
20°-30°	617.3	8.5
30°-40°	717.0	9.9
40°-50°	716.1	9.9
50°-60°	624.4	8.6
60°-70°	461.6	6.4
70°-80°	261.1	3.6
80°-90°	70.9	1.0
90°-100°	36.3	0.5
100°-110°	135.3	1.9
110°-120°	358.8	4.9
120°-130°	595.1	8.2
130°-140°	632.1	8.7
140°-150°	587.5	8.1
150°-160°	472.3	6.5
160°-170°	304.4	4.2
170°-180°	104.8	1.4
0°-30°	1186.6	16.3
0°-40°	1903.6	26.2
0°-60°	3244.1	44.7
0°-90°	4037.7	55.6
90°-120°	530.4	7.3
90°-150°	2345.2	32.3
90°-180°	3227.0	44.4
0°-180°	7264.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1586	1586	1586	1586	1586	
5°	1586	1580	1563	1576	1573	151
15°	1510	1501	1481	1487	1480	425
25°	1367	1354	1328	1332	1328	629
35°	1179	1164	1139	1130	1123	736
45°	959	949	926	909	903	740
55°	726	717	698	680	673	649
65°	490	480	465	452	444	484
75°	256	253	246	236	240	273
85°	62	61	60	55	53	70
90°	1	10	16	20	21	7
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	679	681	577
135°	801	814	821	829	828	619
145°	929	929	942	948	944	581
155°	1023	1016	1026	1030	1024	472
165°	1078	1074	1076	1082	1076	305
175°	1103	1097	1099	1105	1097	105
180°	1101	1101	1101	1101	1101	

TEST NUMBER: P916821

CATALOG NUMBER: DFN2DIP-PN4F0-050D040US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1586.2	1586.2	1586.2	1586.2	1586.2
2.5°	1595.4	1587.8	1571.0	1586.2	1583.3
5°	1586.2	1580.2	1563.3	1575.5	1572.6
7.5°	1575.5	1566.4	1549.6	1561.9	1558.9
10°	1558.9	1548.2	1529.9	1542.0	1537.5
12.5°	1535.9	1526.8	1508.5	1516.1	1513.0
15°	1509.9	1500.9	1481.0	1487.2	1479.5
17.5°	1477.9	1468.8	1448.9	1456.5	1448.9
20°	1442.8	1433.8	1412.4	1416.9	1411.0
22.5°	1407.9	1394.1	1374.2	1374.2	1371.1
25°	1366.6	1354.5	1328.5	1331.5	1328.5
27.5°	1320.8	1310.1	1290.4	1285.8	1278.2
30°	1275.1	1262.9	1240.1	1235.5	1229.4
32.5°	1226.3	1217.2	1192.8	1183.6	1177.5
35°	1179.0	1163.8	1139.4	1130.2	1122.6
37.5°	1125.6	1111.9	1087.4	1076.8	1069.2
40°	1070.8	1058.5	1034.0	1020.4	1014.3
42.5°	1017.4	1005.1	980.8	965.4	956.3
45°	959.4	948.8	925.8	909.1	902.9
47.5°	902.9	892.3	867.9	851.0	842.0
50°	843.4	835.8	814.5	793.1	785.5
52.5°	785.5	774.8	755.0	738.3	727.6
55°	726.1	716.9	698.5	680.3	672.7
57.5°	666.5	658.9	639.0	620.8	614.6
60°	607.0	601.0	579.7	562.8	558.3
62.5°	549.1	538.4	523.2	507.9	501.8
65°	489.7	480.5	465.2	451.5	443.8
67.5°	428.7	420.9	407.3	396.6	390.4
70°	372.2	366.1	352.3	341.6	335.7
72.5°	314.3	308.1	300.5	289.8	285.3
75°	256.2	253.2	245.5	236.4	239.5
77.5°	204.4	198.2	195.2	190.6	186.1
80°	152.6	151.0	147.9	143.4	140.3
82.5°	103.7	103.7	102.2	96.1	96.1
85°	62.5	61.0	59.5	54.9	53.4
87.5°	27.5	24.5	21.4	16.8	15.2
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.1	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	141.0	31.9	45.4	51.7	53.3
102.5°	193.5	192.0	47.0	55.7	58.1
105°	242.1	266.0	48.6	57.3	60.5
107.5°	298.6	318.5	50.2	58.9	62.1
110°	352.9	369.5	139.4	59.8	62.9

TEST NUMBER: P916821

CATALOG NUMBER: DFN2DIP-PN4F0-050D040US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.8	418.1	404.6	61.3	63.8
115°	457.9	471.4	491.4	122.6	65.4
117.5°	504.9	520.8	534.4	420.4	211.8
120°	557.5	569.4	583.8	593.4	485.8
122.5°	602.0	614.8	630.8	635.5	636.3
125°	647.4	657.9	672.9	678.6	680.9
127.5°	688.8	700.0	712.0	720.0	720.7
130°	727.9	740.7	749.3	758.1	757.4
132.5°	767.7	778.1	786.8	794.0	793.3
135°	801.2	814.0	821.1	829.1	827.5
137.5°	836.2	845.7	853.8	861.7	859.3
140°	870.4	876.9	885.6	892.8	888.8
142.5°	899.2	904.7	915.1	921.4	917.5
145°	929.4	928.6	942.1	947.7	943.7
147.5°	955.6	953.2	966.8	970.8	967.7
150°	981.1	975.6	988.4	993.1	989.1
152.5°	1002.7	996.3	1008.2	1013.0	1007.5
155°	1023.4	1016.3	1025.8	1030.5	1024.2
157.5°	1040.1	1033.7	1041.0	1046.5	1040.1
160°	1054.4	1049.6	1054.4	1059.2	1053.6
162.5°	1067.1	1062.4	1066.4	1072.0	1064.8
165°	1078.3	1073.6	1075.9	1081.5	1075.9
167.5°	1087.1	1082.2	1084.8	1090.3	1083.1
170°	1094.3	1089.5	1091.0	1096.7	1089.5
172.5°	1099.0	1094.3	1095.9	1101.5	1094.3
175°	1102.9	1097.4	1099.0	1104.6	1096.7
177.5°	1104.6	1099.0	1099.8	1105.5	1098.3
180°	1100.7	1100.7	1100.7	1100.7	1100.7

TEST NUMBER: P916821

CATALOG NUMBER: DFN2DIP-PN4F0-050D040US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.29	9.20	9.20	10.13	11.32	7.85	8.76	8.76	9.69	10.88
	3H	9.96	10.78	10.88	11.71	12.93	9.47	10.29	10.39	11.23	12.44
	4H	10.55	11.32	11.48	12.26	13.49	10.06	10.84	11.00	11.78	13.00
	6H	10.95	11.67	11.90	12.61	13.85	10.46	11.18	11.41	12.12	13.36
	8H	11.06	11.74	12.01	12.71	13.94	10.57	11.25	11.52	12.21	13.45
	12H	11.11	11.76	12.07	12.72	13.98	10.61	11.26	11.57	12.22	13.48
4H	2H	8.76	9.53	9.70	10.47	11.70	8.41	9.18	9.35	10.12	11.35
	3H	10.63	11.28	11.58	12.25	13.49	10.23	10.88	11.18	11.85	13.08
	4H	11.35	11.94	12.31	12.91	14.17	10.93	11.52	11.89	12.49	13.75
	6H	11.87	12.38	12.84	13.37	14.63	11.45	11.96	12.42	12.94	14.21
	8H	12.02	12.50	13.00	13.48	14.76	11.59	12.07	12.57	13.05	14.33
	12H	12.10	12.53	13.09	13.53	14.81	11.66	12.09	12.65	13.09	14.37
8H	4H	11.55	12.03	12.52	13.01	14.28	11.18	11.66	12.15	12.64	13.91
	6H	12.19	12.58	13.19	13.61	14.88	11.81	12.20	12.81	13.23	14.50
	8H	12.41	12.76	13.42	13.77	15.06	12.03	12.37	13.03	13.39	14.68
	12H	12.55	12.85	13.56	13.86	15.20	12.14	12.45	13.16	13.46	14.79
12H	4H	11.54	11.97	12.53	12.97	14.25	11.18	11.61	12.17	12.61	13.89
	6H	12.22	12.57	13.23	13.58	14.87	11.85	12.20	12.86	13.21	14.51
	8H	12.46	12.77	13.48	13.78	15.11	12.09	12.40	13.10	13.40	14.74