

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906083

Luminaire Tested: DFN2DIP-PN4F0-090D110US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906083
REPORT IS A COMBINATION OF REPORTS P901266 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-090D110US835-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18540.0 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 180
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906083

CATALOG NUMBER: DFN2DIP-PN4F0-090D110US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906083

CATALOG NUMBER: DFN2DIP-PN4F0-090D110US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	38	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	39	34	30	32	28	26	26	23	21
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	25	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2715	2715	2715
5°	2720	2673	2690
10°	2693	2620	2603
15°	2656	2534	2468
20°	2607	2415	2302
25°	2556	2282	2142
30°	2489	2145	1939
35°	2423	1997	1761
40°	2356	1845	1556
45°	2277	1676	1371
50°	2197	1505	1189
55°	2112	1323	1015
60°	2015	1132	836
65°	1902	938	753
70°	1766	757	682
75°	1595	668	622
80°	1348	561	541
85°	939	377	410

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2277 cd/sqm

TEST NUMBER: P906083

CATALOG NUMBER: DFN2DIP-PN4F0-090D110US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.6	1.9
10°-20°	957.0	5.2
20°-30°	1343.6	7.2
30°-40°	1464.6	7.9
40°-50°	1346.2	7.3
50°-60°	1057.2	5.7
60°-70°	688.1	3.7
70°-80°	354.2	1.9
80°-90°	97.0	0.5
90°-100°	122.4	0.7
100°-110°	456.3	2.5
110°-120°	1210.3	6.5
120°-130°	2007.3	10.8
130°-140°	2132.2	11.5
140°-150°	1981.7	10.7
150°-160°	1593.2	8.6
160°-170°	1026.6	5.5
170°-180°	353.3	1.9
0°-30°	2649.2	14.3
0°-40°	4113.9	22.2
0°-60°	6517.2	35.2
0°-90°	7656.5	41.3
90°-120°	1789.0	9.6
90°-150°	7910.3	42.7
90°-180°	10883.0	58.7
0°-180°	18540.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3720	3720	3720	3720	3720	
5°	3720	3703	3659	3689	3679	353
15°	3538	3501	3386	3322	3289	997
25°	3212	3104	2882	2744	2693	1477
35°	2767	2595	2299	2087	2013	1732
45°	2262	2036	1683	1444	1363	1747
55°	1720	1458	1094	892	828	1537
65°	1161	889	586	471	461	1151
75°	619	384	269	246	242	655
85°	145	74	64	64	64	166
90°	3	32	54	67	72	17
95°	174	86	105	118	116	207
105°	817	897	164	193	204	873
115°	1544	1590	1658	414	220	1521
125°	2184	2219	2270	2289	2297	1948
135°	2702	2746	2769	2797	2791	2088
145°	3135	3132	3178	3197	3183	1961
155°	3452	3428	3460	3476	3455	1591
165°	3637	3621	3629	3648	3629	1028
175°	3720	3702	3707	3726	3699	354
180°	3712	3712	3712	3712	3712	

TEST NUMBER: P906083

CATALOG NUMBER: DFN2DIP-PN4F0-090D110US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3719.7	3719.7	3719.7	3719.7	3719.7
2.5°	3736.5	3719.7	3682.5	3716.5	3709.7
5°	3719.7	3702.9	3659.0	3689.3	3679.3
7.5°	3689.3	3669.3	3622.2	3635.4	3618.6
10°	3649.0	3625.4	3558.3	3547.9	3527.9
12.5°	3598.6	3568.3	3477.2	3457.2	3420.0
15°	3537.9	3500.8	3386.5	3322.5	3289.0
17.5°	3467.2	3413.3	3271.8	3197.9	3144.0
20°	3386.5	3319.0	3150.7	3066.8	2992.5
22.5°	3299.0	3221.5	3026.1	2911.8	2861.5
25°	3211.5	3103.6	2881.5	2743.6	2692.9
27.5°	3107.2	2992.5	2746.8	2588.6	2511.1
30°	2996.1	2867.9	2598.6	2427.2	2336.1
32.5°	2888.2	2733.2	2457.5	2255.4	2171.1
35°	2767.2	2595.4	2299.3	2087.2	2012.9
37.5°	2649.3	2464.0	2151.1	1918.6	1834.7
40°	2524.7	2322.9	1996.1	1757.2	1669.7
42.5°	2396.8	2181.5	1841.4	1592.2	1508.2
45°	2262.2	2036.5	1683.2	1443.9	1363.2
47.5°	2134.3	1895.4	1531.8	1292.5	1218.6
50°	1992.9	1753.9	1383.6	1151.1	1080.7
52.5°	1854.7	1602.2	1242.2	1020.0	956.1
55°	1720.0	1457.5	1093.9	892.2	828.2
57.5°	1582.2	1312.9	962.9	774.3	720.4
60°	1440.7	1171.4	824.7	653.2	599.3
62.5°	1302.9	1033.6	706.8	545.4	518.6
65°	1161.4	888.6	585.7	471.4	461.1
67.5°	1026.8	753.9	471.4	413.9	403.9
70°	885.4	622.9	390.4	356.8	343.2
72.5°	750.7	501.4	326.4	299.6	292.9
75°	619.3	383.6	269.3	245.7	242.5
77.5°	488.2	272.5	212.1	198.6	191.8
80°	366.8	195.4	161.4	148.2	148.2
82.5°	255.7	131.4	111.1	104.3	104.3
85°	144.6	73.9	63.9	63.9	63.9
87.5°	53.9	26.8	26.8	23.6	23.6
90°	2.6	32.2	53.6	67.3	72.4
92.5°	67.3	56.5	64.4	69.9	72.4
95°	174.5	85.8	104.6	118.3	115.5
97.5°	314.2	94.1	136.8	145.1	147.7
100°	475.6	107.5	153.1	174.5	179.9
102.5°	652.6	647.5	158.5	187.9	196.2
105°	816.6	897.3	164.0	193.3	204.2
107.5°	1007.4	1074.3	169.4	198.7	209.6
110°	1190.1	1246.3	470.2	201.6	212.1

TEST NUMBER: P906083

CATALOG NUMBER: DFN2DIP-PN4F0-090D110US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1362.1	1410.2	1364.6	206.7	215.0
115°	1544.5	1590.1	1657.5	413.7	220.4
117.5°	1703.1	1756.7	1802.6	1418.2	714.5
120°	1880.4	1920.6	1969.1	2001.3	1638.6
122.5°	2030.7	2073.7	2127.6	2143.6	2146.5
125°	2183.8	2218.9	2269.9	2288.7	2296.7
127.5°	2323.5	2361.1	2401.6	2428.4	2431.0
130°	2455.2	2498.3	2527.6	2557.3	2554.8
132.5°	2589.5	2624.6	2654.0	2678.2	2675.7
135°	2702.5	2745.5	2769.4	2796.6	2791.1
137.5°	2820.5	2852.7	2879.8	2906.6	2898.6
140°	2936.0	2957.6	2987.0	3011.2	2997.8
142.5°	3032.9	3051.7	3086.5	3107.9	3094.5
145°	3135.0	3132.1	3177.7	3196.6	3183.2
147.5°	3223.4	3215.4	3261.0	3274.4	3263.9
150°	3309.5	3290.7	3333.7	3349.7	3336.3
152.5°	3381.9	3360.5	3400.7	3417.0	3398.2
155°	3451.8	3427.8	3460.0	3476.0	3454.6
157.5°	3508.2	3486.8	3511.1	3529.9	3508.2
160°	3556.7	3540.4	3556.7	3572.6	3553.8
162.5°	3599.4	3583.5	3596.9	3615.7	3591.5
165°	3637.1	3621.1	3629.1	3647.9	3629.1
167.5°	3666.7	3650.5	3658.8	3677.6	3653.4
170°	3691.0	3674.7	3680.1	3699.0	3674.7
172.5°	3706.9	3691.0	3696.4	3715.2	3691.0
175°	3720.3	3701.5	3706.9	3725.8	3699.0
177.5°	3725.8	3706.9	3709.8	3728.6	3704.4
180°	3712.4	3712.4	3712.4	3712.4	3712.4

TEST NUMBER: P906083

CATALOG NUMBER: DFN2DIP-PN4F0-090D110US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.75	10.52	10.79	11.56	12.95	5.72	6.48	6.75	7.52	8.91
	3H	11.43	12.11	12.47	13.16	14.57	6.90	7.59	7.95	8.63	10.04
	4H	12.04	12.68	13.09	13.73	15.15	7.35	8.00	8.41	9.05	10.47
	6H	12.46	13.05	13.52	14.10	15.54	7.67	8.26	8.74	9.32	10.75
	8H	12.58	13.15	13.65	14.22	15.64	7.76	8.32	8.83	9.39	10.82
	12H	12.64	13.18	13.72	14.24	15.69	7.80	8.34	8.88	9.40	10.85
4H	2H	9.76	10.41	10.83	11.46	12.88	6.31	6.95	7.37	8.00	9.42
	3H	11.59	12.13	12.66	13.20	14.64	7.65	8.19	8.72	9.27	10.70
	4H	12.28	12.78	13.36	13.84	15.30	8.20	8.69	9.28	9.76	11.21
	6H	12.80	13.22	13.88	14.31	15.76	8.62	9.04	9.70	10.13	11.58
	8H	12.97	13.37	14.06	14.45	15.91	8.74	9.14	9.83	10.22	11.68
	12H	13.07	13.42	14.17	14.52	15.99	8.81	9.16	9.91	10.26	11.73
8H	4H	12.25	12.64	13.33	13.72	15.19	8.48	8.87	9.56	9.95	11.42
	6H	12.81	13.14	13.92	14.26	15.72	8.99	9.32	10.10	10.44	11.90
	8H	13.03	13.32	14.14	14.42	15.90	9.19	9.47	10.30	10.58	12.06
	12H	13.17	13.42	14.29	14.52	16.04	9.30	9.55	10.42	10.65	12.17
12H	4H	12.19	12.55	13.30	13.65	15.12	8.48	8.83	9.58	9.93	11.40
	6H	12.79	13.07	13.90	14.18	15.66	9.04	9.33	10.16	10.44	11.92
	8H	13.01	13.26	14.12	14.36	15.88	9.25	9.50	10.37	10.60	12.12

END OF REPORT