

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906121

Luminaire Tested: DFN2DIP-PN4F0-100D120US835-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P906121  
REPORT IS A COMBINATION OF REPORTS P901285 AND P898053  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-100D120US835-FLLONL  
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 21780.0 lumens  
Efficiency: N/A  
Efficacy: 106.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 204.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9952  
Total Harmonic Distortion (THDi): 0.069  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P906121  
CATALOG NUMBER: DFN2DIP-PN4F0-100D120US835-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P906121  
 CATALOG NUMBER: DFN2DIP-PN4F0-100D120US835-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45	45	45	45
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38	38	38	38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	39	37	32	32	32	32
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	33	31	27	27	27	27
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23	23	23	23
5	67	56	48	42	62	52	45	39	43	38	34	36	32	29	29	26	24	20	20	20	20
6	62	50	42	36	57	46	39	34	39	34	30	32	28	25	26	23	21	18	18	18	18
7	57	45	37	32	53	42	35	30	35	30	26	30	25	22	24	21	18	16	16	16	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14	14	14	14
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13	13	13	13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14	12	12	12	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2840	2840	2840
5°	2845	2801	2820
10°	2822	2764	2782
15°	2780	2719	2723
20°	2724	2656	2663
25°	2668	2581	2593
30°	2599	2511	2503
35°	2532	2428	2409
40°	2451	2345	2319
45°	2369	2261	2227
50°	2281	2173	2121
55°	2187	2072	2023
60°	2082	1951	1911
65°	1968	1827	1779
70°	1821	1675	1637
75°	1619	1493	1507
80°	1375	1262	1257
85°	994	861	841

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2369 cd/sqm



TEST NUMBER: P906121

CATALOG NUMBER: DFN2DIP-PN4F0-100D120US835-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	366.2	1.7
10°-20°	1030.4	4.7
20°-30°	1514.3	7.0
30°-40°	1758.8	8.1
40°-50°	1756.6	8.1
50°-60°	1531.7	7.0
60°-70°	1132.3	5.2
70°-80°	640.6	2.9
80°-90°	176.2	0.8
90°-100°	133.5	0.6
100°-110°	497.8	2.3
110°-120°	1320.3	6.1
120°-130°	2189.8	10.1
130°-140°	2326.1	10.7
140°-150°	2161.8	9.9
150°-160°	1738.1	8.0
160°-170°	1119.9	5.1
170°-180°	385.5	1.8
0°-30°	2911.0	13.4
0°-40°	4669.7	21.4
0°-60°	7958.0	36.5
0°-90°	9907.1	45.5
90°-120°	1951.7	9.0
90°-150°	8629.4	39.6
90°-180°	11873.0	54.5
0°-180°	21780.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3891	3891	3891	3891	3891	
5°	3891	3876	3835	3865	3858	369
15°	3704	3682	3633	3648	3630	1043
25°	3352	3323	3259	3266	3259	1543
35°	2892	2855	2795	2772	2754	1806
45°	2354	2327	2271	2230	2215	1816
55°	1781	1759	1714	1669	1650	1592
65°	1201	1179	1141	1108	1089	1188
75°	628	621	602	580	588	671
85°	153	150	146	135	131	171
90°	3	35	58	73	79	20
95°	190	94	114	129	126	225
105°	891	979	179	211	223	952
115°	1685	1735	1808	451	240	1659
125°	2382	2421	2476	2497	2506	2125
135°	2948	2995	3021	3051	3045	2277
145°	3420	3417	3467	3487	3472	2139
155°	3766	3739	3775	3792	3769	1735
165°	3968	3950	3959	3980	3959	1121
175°	4058	4038	4044	4064	4035	386
180°	4050	4050	4050	4050	4050	



TEST NUMBER: P906121

CATALOG NUMBER: DFN2DIP-PN4F0-100D120US835-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3891.1	3891.1	3891.1	3891.1	3891.1
2.5°	3913.7	3895.0	3853.7	3891.1	3883.9
5°	3891.1	3876.4	3835.1	3864.9	3857.7
7.5°	3864.9	3842.6	3801.3	3831.5	3824.0
10°	3824.0	3797.8	3752.9	3782.7	3771.6
12.5°	3767.6	3745.4	3700.5	3719.2	3711.6
15°	3704.1	3681.9	3633.0	3648.1	3629.5
17.5°	3625.5	3603.3	3554.4	3573.1	3554.4
20°	3539.3	3517.1	3464.7	3475.8	3461.1
22.5°	3453.6	3419.9	3371.0	3371.0	3363.5
25°	3352.4	3322.6	3259.1	3266.2	3259.1
27.5°	3240.0	3213.8	3165.4	3154.3	3135.6
30°	3128.1	3097.9	3041.9	3030.8	3015.7
32.5°	3008.2	2986.0	2926.0	2903.4	2888.3
35°	2892.3	2855.0	2795.0	2772.4	2753.7
37.5°	2761.3	2727.5	2667.6	2641.4	2622.7
40°	2626.7	2596.5	2536.6	2503.3	2488.2
42.5°	2495.7	2465.5	2406.0	2368.3	2346.1
45°	2353.6	2327.4	2271.0	2230.1	2215.1
47.5°	2215.1	2188.9	2128.9	2087.6	2065.4
50°	2069.0	2050.3	1997.9	1945.5	1926.9
52.5°	1926.9	1900.7	1852.2	1811.0	1784.8
55°	1781.2	1758.6	1713.7	1668.8	1650.2
57.5°	1635.1	1616.4	1567.6	1522.8	1507.7
60°	1489.0	1474.3	1421.9	1380.6	1369.5
62.5°	1346.9	1320.7	1283.4	1246.1	1231.0
65°	1201.2	1178.6	1141.3	1107.5	1088.9
67.5°	1051.6	1032.5	999.2	973.0	957.9
70°	913.0	897.9	864.2	838.0	823.3
72.5°	770.9	755.8	737.2	711.0	699.8
75°	628.4	621.3	602.2	580.0	587.5
77.5°	501.4	486.3	478.7	467.6	456.5
80°	374.3	370.4	362.8	351.7	344.2
82.5°	254.5	254.5	250.9	235.8	235.8
85°	153.2	149.7	146.1	134.6	131.0
87.5°	67.5	59.9	52.4	41.3	37.3
90°	2.8	35.1	58.5	73.4	79.0
92.5°	73.4	61.6	70.3	76.2	79.0
95°	190.3	93.6	114.1	129.1	126.0
97.5°	342.8	102.7	149.3	158.3	161.1
100°	518.8	117.3	167.0	190.3	196.3
102.5°	712.0	706.4	172.9	205.0	214.0
105°	890.8	978.9	178.9	210.9	222.7
107.5°	1098.9	1172.0	184.8	216.8	228.6
110°	1298.3	1359.6	512.9	219.9	231.4



TEST NUMBER: P906121

CATALOG NUMBER: DFN2DIP-PN4F0-100D120US835-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1485.9	1538.4	1488.7	225.5	234.5
115°	1684.9	1734.7	1808.1	451.3	240.5
117.5°	1857.9	1916.4	1966.5	1547.1	779.5
120°	2051.4	2095.2	2148.1	2183.3	1787.6
122.5°	2215.3	2262.3	2321.1	2338.5	2341.6
125°	2382.3	2420.6	2476.3	2496.8	2505.5
127.5°	2534.7	2575.8	2620.0	2649.2	2652.0
130°	2678.4	2725.4	2757.4	2789.8	2787.0
132.5°	2824.9	2863.2	2895.2	2921.7	2918.9
135°	2948.1	2995.1	3021.2	3050.8	3044.9
137.5°	3076.9	3112.0	3141.6	3170.8	3162.1
140°	3202.9	3226.5	3258.5	3285.0	3270.4
142.5°	3308.6	3329.2	3367.1	3390.4	3375.8
145°	3420.0	3416.9	3466.6	3487.2	3472.5
147.5°	3516.4	3507.7	3557.5	3572.1	3560.6
150°	3610.3	3589.8	3636.8	3654.2	3639.6
152.5°	3689.3	3666.0	3709.9	3727.6	3707.1
155°	3765.5	3739.4	3774.6	3792.0	3768.7
157.5°	3827.1	3803.8	3830.3	3850.8	3827.1
160°	3880.0	3862.3	3880.0	3897.4	3876.9
162.5°	3926.7	3909.3	3923.9	3944.4	3918.0
165°	3967.7	3950.3	3959.0	3979.6	3959.0
167.5°	4000.1	3982.3	3991.4	4011.9	3985.5
170°	4026.5	4008.8	4014.7	4035.2	4008.8
172.5°	4043.9	4026.5	4032.5	4053.0	4026.5
175°	4058.5	4038.0	4043.9	4064.5	4035.2
177.5°	4064.5	4043.9	4047.1	4067.6	4041.2
180°	4049.9	4049.9	4049.9	4049.9	4049.9



TEST NUMBER: P906121  
 CATALOG NUMBER: DFN2DIP-PN4F0-100D120US835-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.47	11.30	11.47	12.30	13.64	10.03	10.86	11.03	11.86	13.20
	3H	12.13	12.87	13.14	13.89	15.24	11.65	12.39	12.66	13.40	14.76
	4H	12.72	13.42	13.74	14.44	15.80	12.23	12.93	13.25	13.95	15.31
	6H	13.12	13.76	14.15	14.79	16.16	12.63	13.27	13.66	14.30	15.67
	8H	13.23	13.84	14.26	14.88	16.25	12.73	13.35	13.77	14.39	15.76
	12H	13.27	13.86	14.31	14.89	16.29	12.77	13.36	13.81	14.39	15.79
4H	2H	10.93	11.63	11.96	12.65	14.01	10.58	11.28	11.60	12.30	13.66
	3H	12.80	13.38	13.83	14.43	15.80	12.39	12.98	13.43	14.02	15.40
	4H	13.51	14.04	14.55	15.08	16.48	13.09	13.63	14.13	14.67	16.06
	6H	14.03	14.49	15.08	15.55	16.94	13.60	14.06	14.65	15.12	16.52
	8H	14.18	14.61	15.23	15.66	17.07	13.75	14.18	14.80	15.23	16.64
	12H	14.25	14.64	15.32	15.71	17.12	13.81	14.20	14.88	15.27	16.68
8H	4H	13.70	14.13	14.76	15.19	16.60	13.33	13.76	14.38	14.82	16.23
	6H	14.34	14.69	15.41	15.79	17.20	13.96	14.32	15.04	15.41	16.82
	8H	14.56	14.87	15.64	15.95	17.38	14.18	14.49	15.26	15.57	16.99
	12H	14.69	14.97	15.78	16.04	17.51	14.29	14.56	15.38	15.64	17.11
12H	4H	13.69	14.08	14.76	15.15	16.56	13.33	13.71	14.40	14.78	16.20
	6H	14.37	14.68	15.45	15.76	17.19	14.00	14.31	15.08	15.39	16.82
	8H	14.61	14.88	15.70	15.96	17.43	14.24	14.51	15.32	15.59	17.05