

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917027

Luminaire Tested: DFN2DIP-PN4F0-100D100US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917027
REPORT IS A COMBINATION OF REPORTS P901250 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-100D100US930-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15001.5 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 175.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917027

CATALOG NUMBER: DFN2DIP-PN4F0-100D100US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917027

CATALOG NUMBER: DFN2DIP-PN4F0-100D100US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2460	2460	2460
5°	2464	2421	2437
10°	2439	2374	2358
15°	2406	2296	2236
20°	2361	2188	2086
25°	2316	2067	1941
30°	2255	1943	1757
35°	2195	1809	1595
40°	2134	1671	1410
45°	2063	1518	1242
50°	1990	1364	1077
55°	1914	1198	920
60°	1825	1025	758
65°	1723	849	682
70°	1600	685	618
75°	1445	605	563
80°	1221	509	490
85°	850	341	372

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2063 cd/sqm

TEST NUMBER: P917027

CATALOG NUMBER: DFN2DIP-PN4F0-100D100US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.8	2.1
10°-20°	866.9	5.8
20°-30°	1217.2	8.1
30°-40°	1326.8	8.8
40°-50°	1219.5	8.1
50°-60°	957.7	6.4
60°-70°	623.4	4.2
70°-80°	320.9	2.1
80°-90°	86.8	0.6
90°-100°	90.7	0.6
100°-110°	338.2	2.3
110°-120°	897.0	6.0
120°-130°	1487.8	9.9
130°-140°	1580.4	10.5
140°-150°	1468.8	9.8
150°-160°	1180.9	7.9
160°-170°	760.9	5.1
170°-180°	261.9	1.7
0°-30°	2399.9	16.0
0°-40°	3726.7	24.8
0°-60°	5903.9	39.4
0°-90°	6934.9	46.2
90°-120°	1326.0	8.8
90°-150°	5862.9	39.1
90°-180°	8067.0	53.8
0°-180°	15001.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3370	3370	3370	3370	3370	
5°	3370	3354	3315	3342	3333	320
15°	3205	3171	3068	3010	2979	903
25°	2909	2812	2610	2485	2440	1338
35°	2507	2351	2083	1891	1823	1569
45°	2049	1845	1525	1308	1235	1583
55°	1558	1320	991	808	750	1392
65°	1052	805	531	427	418	1043
75°	561	348	244	223	220	593
85°	131	67	58	58	58	150
90°	2	24	40	50	54	14
95°	129	64	78	88	86	153
105°	605	665	122	143	151	647
115°	1145	1179	1228	307	163	1127
125°	1619	1645	1682	1696	1702	1444
135°	2003	2035	2053	2073	2069	1547
145°	2324	2322	2355	2369	2359	1453
155°	2558	2541	2564	2576	2560	1179
165°	2696	2684	2690	2704	2690	762
175°	2757	2744	2748	2762	2742	262
180°	2752	2752	2752	2752	2752	

TEST NUMBER: P917027

CATALOG NUMBER: DFN2DIP-PN4F0-100D100US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3369.6	3369.6	3369.6	3369.6	3369.6
2.5°	3384.8	3369.6	3336.0	3366.7	3360.6
5°	3369.6	3354.4	3314.6	3342.2	3333.0
7.5°	3342.2	3324.0	3281.2	3293.2	3278.1
10°	3305.5	3284.2	3223.4	3214.0	3195.9
12.5°	3260.0	3232.4	3149.9	3131.8	3098.1
15°	3204.9	3171.3	3067.7	3009.8	2979.4
17.5°	3140.9	3092.0	2963.9	2896.9	2848.1
20°	3067.7	3006.6	2854.2	2778.2	2710.9
22.5°	2988.5	2918.3	2741.3	2637.8	2592.2
25°	2909.2	2811.6	2610.3	2485.4	2439.5
27.5°	2814.7	2710.9	2488.3	2345.0	2274.8
30°	2714.1	2597.9	2354.0	2198.8	2116.3
32.5°	2616.5	2476.0	2226.3	2043.1	1966.7
35°	2506.7	2351.2	2082.9	1890.8	1823.4
37.5°	2400.0	2232.0	1948.6	1738.1	1662.0
40°	2287.1	2104.3	1808.2	1591.8	1512.5
42.5°	2171.2	1976.1	1668.2	1442.3	1366.3
45°	2049.3	1844.8	1524.9	1308.1	1234.9
47.5°	1933.5	1717.0	1387.6	1170.8	1103.9
50°	1805.3	1588.9	1253.4	1042.8	979.0
52.5°	1680.1	1451.4	1125.3	924.0	866.1
55°	1558.1	1320.4	991.0	808.2	750.2
57.5°	1433.3	1189.3	872.3	701.4	652.6
60°	1305.1	1061.2	747.1	591.7	542.9
62.5°	1180.2	936.3	640.3	494.1	469.8
65°	1052.1	804.9	530.6	427.1	417.7
67.5°	930.2	683.0	427.1	375.0	365.9
70°	802.0	564.3	353.6	323.2	311.0
72.5°	680.0	454.2	295.7	271.4	265.3
75°	561.0	347.5	243.9	222.6	219.6
77.5°	442.3	246.9	192.2	179.9	173.7
80°	332.2	177.0	146.3	134.3	134.3
82.5°	231.6	119.0	100.6	94.5	94.5
85°	131.0	66.9	57.9	57.9	57.9
87.5°	48.8	24.3	24.3	21.4	21.4
90°	1.9	23.9	39.7	49.9	53.6
92.5°	49.9	41.8	47.8	51.8	53.6
95°	129.3	63.6	77.5	87.7	85.6
97.5°	232.8	69.7	101.4	107.5	109.5
100°	352.5	79.7	113.5	129.3	133.4
102.5°	483.7	480.0	117.5	139.3	145.4
105°	605.3	665.0	121.6	143.2	151.3
107.5°	746.7	796.3	125.6	147.3	155.3
110°	882.1	923.7	348.5	149.4	157.2



TEST NUMBER: P917027

CATALOG NUMBER: DFN2DIP-PN4F0-100D100US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1009.5	1045.2	1011.5	153.2	159.4
115°	1144.8	1178.6	1228.5	306.6	163.4
117.5°	1262.2	1302.0	1336.0	1051.2	529.6
120°	1393.8	1423.5	1459.5	1483.4	1214.5
122.5°	1505.1	1537.0	1576.9	1588.8	1590.9
125°	1618.6	1644.6	1682.4	1696.4	1702.3
127.5°	1722.2	1750.0	1780.0	1799.9	1801.8
130°	1819.7	1851.7	1873.5	1895.4	1893.5
132.5°	1919.3	1945.3	1967.1	1985.0	1983.1
135°	2003.0	2034.9	2052.7	2072.7	2068.7
137.5°	2090.5	2114.4	2134.5	2154.3	2148.4
140°	2176.0	2192.2	2213.9	2231.9	2221.9
142.5°	2247.9	2261.9	2287.6	2303.5	2293.6
145°	2323.6	2321.5	2355.3	2369.3	2359.3
147.5°	2389.1	2383.2	2417.0	2426.9	2419.2
150°	2452.9	2439.0	2470.9	2482.7	2472.8
152.5°	2506.6	2490.7	2520.6	2532.6	2518.6
155°	2558.4	2540.6	2564.5	2576.3	2560.5
157.5°	2600.2	2584.4	2602.4	2616.3	2600.2
160°	2636.2	2624.1	2636.2	2648.0	2634.1
162.5°	2667.8	2656.0	2665.9	2679.9	2661.9
165°	2695.7	2683.9	2689.8	2703.8	2689.8
167.5°	2717.7	2705.6	2711.8	2725.8	2707.8
170°	2735.7	2723.7	2727.7	2741.6	2723.7
172.5°	2747.5	2735.7	2739.7	2753.7	2735.7
175°	2757.4	2743.5	2747.5	2761.5	2741.6
177.5°	2761.5	2747.5	2749.7	2763.6	2745.6
180°	2751.6	2751.6	2751.6	2751.6	2751.6

TEST NUMBER: P917027

CATALOG NUMBER: DFN2DIP-PN4F0-100D100US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.92	10.72	10.91	11.72	13.05	5.88	6.68	6.88	7.69	9.01
	3H	11.60	12.31	12.60	13.32	14.67	7.07	7.79	8.08	8.80	10.14
	4H	12.21	12.88	13.22	13.90	15.25	7.52	8.20	8.54	9.21	10.57
	6H	12.63	13.25	13.66	14.27	15.64	7.84	8.46	8.87	9.48	10.85
	8H	12.75	13.35	13.79	14.38	15.75	7.93	8.52	8.96	9.56	10.92
	12H	12.82	13.38	13.86	14.41	15.80	7.97	8.54	9.01	9.56	10.95
4H	2H	9.93	10.61	10.96	11.62	12.98	6.48	7.15	7.50	8.17	9.52
	3H	11.76	12.33	12.80	13.37	14.74	7.82	8.39	8.86	9.43	10.80
	4H	12.46	12.97	13.50	14.01	15.40	8.37	8.89	9.41	9.92	11.31
	6H	12.97	13.41	14.02	14.47	15.86	8.79	9.23	9.84	10.29	11.68
	8H	13.15	13.56	14.20	14.61	16.01	8.92	9.33	9.97	10.38	11.79
	12H	13.24	13.62	14.31	14.68	16.09	8.98	9.36	10.05	10.42	11.83
8H	4H	12.42	12.83	13.47	13.88	15.29	8.65	9.06	9.70	10.12	11.52
	6H	12.99	13.33	14.06	14.42	15.82	9.17	9.51	10.24	10.60	12.00
	8H	13.21	13.51	14.29	14.58	16.00	9.36	9.66	10.44	10.74	12.16
	12H	13.35	13.61	14.43	14.68	16.14	9.48	9.74	10.57	10.82	12.28
12H	4H	12.37	12.74	13.44	13.81	15.22	8.66	9.03	9.72	10.09	11.50
	6H	12.96	13.26	14.05	14.34	15.76	9.22	9.52	10.30	10.60	12.02
	8H	13.19	13.45	14.27	14.52	15.98	9.43	9.69	10.52	10.77	12.23

END OF REPORT