

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917061

Luminaire Tested: DFN2DIP-PN4F0-110D100US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917061
REPORT IS A COMBINATION OF REPORTS P901251 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D100US930-FLLONL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16950.0 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 189.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917061

CATALOG NUMBER: DFN2DIP-PN4F0-110D100US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917061

CATALOG NUMBER: DFN2DIP-PN4F0-110D100US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	52	50	49
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	42
3	82	72	65	59	75	67	61	55	57	53	48	49	45	42	40	38	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23
7	58	46	38	33	54	43	36	31	37	32	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2547	2547	2547
5°	2551	2512	2529
10°	2531	2479	2495
15°	2493	2438	2442
20°	2443	2382	2388
25°	2393	2314	2325
30°	2330	2252	2245
35°	2271	2177	2160
40°	2198	2103	2080
45°	2125	2028	1997
50°	2045	1949	1902
55°	1962	1858	1814
60°	1867	1750	1714
65°	1765	1638	1595
70°	1634	1502	1468
75°	1452	1339	1351
80°	1234	1131	1127
85°	893	772	754

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2125 cd/sqm

TEST NUMBER: P917061

CATALOG NUMBER: DFN2DIP-PN4F0-110D100US930-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.4	1.9
10°-20°	924.1	5.5
20°-30°	1358.1	8.0
30°-40°	1577.3	9.3
40°-50°	1575.4	9.3
50°-60°	1373.7	8.1
60°-70°	1015.5	6.0
70°-80°	574.5	3.4
80°-90°	156.5	0.9
90°-100°	90.7	0.5
100°-110°	338.2	2.0
110°-120°	897.0	5.3
120°-130°	1487.8	8.8
130°-140°	1580.4	9.3
140°-150°	1468.8	8.7
150°-160°	1180.9	7.0
160°-170°	760.9	4.5
170°-180°	261.9	1.5
0°-30°	2610.6	15.4
0°-40°	4187.9	24.7
0°-60°	7137.0	42.1
0°-90°	8883.4	52.4
90°-120°	1326.0	7.8
90°-150°	5862.9	34.6
90°-180°	8067.0	47.6
0°-180°	16950.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3490	3490	3490	3490	3490	
5°	3490	3476	3439	3466	3460	331
15°	3322	3302	3258	3272	3255	936
25°	3006	2980	2923	2929	2923	1383
35°	2594	2560	2507	2486	2470	1620
45°	2111	2087	2037	2000	1987	1629
55°	1597	1577	1537	1497	1480	1428
65°	1077	1057	1024	993	977	1065
75°	564	557	540	520	527	602
85°	138	134	131	121	118	153
90°	2	24	40	50	54	16
95°	129	64	78	88	86	153
105°	605	665	122	143	151	647
115°	1145	1179	1228	307	163	1127
125°	1619	1645	1682	1696	1702	1444
135°	2003	2035	2053	2073	2069	1547
145°	2324	2322	2355	2369	2359	1453
155°	2558	2541	2564	2576	2560	1179
165°	2696	2684	2690	2704	2690	762
175°	2757	2744	2748	2762	2742	262
180°	2752	2752	2752	2752	2752	

TEST NUMBER: P917061

CATALOG NUMBER: DFN2DIP-PN4F0-110D100US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3489.6	3489.6	3489.6	3489.6	3489.6
2.5°	3509.9	3493.1	3456.1	3489.6	3483.2
5°	3489.6	3476.4	3439.4	3466.1	3459.7
7.5°	3466.1	3446.2	3409.2	3436.2	3429.5
10°	3429.5	3405.9	3365.7	3392.4	3382.4
12.5°	3378.9	3358.9	3318.8	3335.5	3328.7
15°	3321.9	3302.0	3258.2	3271.7	3255.0
17.5°	3251.4	3231.5	3187.7	3204.4	3187.7
20°	3174.2	3154.2	3107.3	3117.2	3104.1
22.5°	3097.3	3067.0	3023.2	3023.2	3016.4
25°	3006.5	2979.8	2922.8	2929.3	2922.8
27.5°	2905.7	2882.2	2838.8	2828.8	2812.1
30°	2805.4	2778.3	2728.1	2718.1	2704.6
32.5°	2697.8	2677.9	2624.1	2603.8	2590.3
35°	2593.9	2560.4	2506.6	2486.3	2469.6
37.5°	2476.4	2446.1	2392.4	2368.8	2352.1
40°	2355.7	2328.7	2274.9	2245.0	2231.5
42.5°	2238.2	2211.2	2157.8	2123.9	2104.0
45°	2110.8	2087.2	2036.7	2000.1	1986.6
47.5°	1986.6	1963.1	1909.3	1872.3	1852.3
50°	1855.5	1838.8	1791.8	1744.8	1728.1
52.5°	1728.1	1704.5	1661.2	1624.1	1600.6
55°	1597.4	1577.1	1536.9	1496.6	1479.9
57.5°	1466.4	1449.7	1405.9	1365.6	1352.1
60°	1335.4	1322.3	1275.2	1238.2	1228.2
62.5°	1207.9	1184.5	1151.0	1117.5	1104.0
65°	1077.3	1057.0	1023.5	993.3	976.6
67.5°	943.1	926.0	896.1	872.6	859.1
70°	818.8	805.3	775.0	751.5	738.3
72.5°	691.4	677.8	661.1	637.6	627.6
75°	563.5	557.2	540.1	520.2	526.9
77.5°	449.6	436.1	429.3	419.4	409.4
80°	335.7	332.2	325.4	315.4	308.7
82.5°	228.2	228.2	225.0	211.5	211.5
85°	137.5	134.2	131.0	120.7	117.5
87.5°	60.5	53.7	47.0	37.0	33.4
90°	1.9	23.9	39.7	49.9	53.6
92.5°	49.9	41.8	47.8	51.8	53.6
95°	129.3	63.6	77.5	87.7	85.6
97.5°	232.8	69.7	101.4	107.5	109.5
100°	352.5	79.7	113.5	129.3	133.4
102.5°	483.7	480.0	117.5	139.3	145.4
105°	605.3	665.0	121.6	143.2	151.3
107.5°	746.7	796.3	125.6	147.3	155.3
110°	882.1	923.7	348.5	149.4	157.2



TEST NUMBER: P917061

CATALOG NUMBER: DFN2DIP-PN4F0-110D100US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1009.5	1045.2	1011.5	153.2	159.4
115°	1144.8	1178.6	1228.5	306.6	163.4
117.5°	1262.2	1302.0	1336.0	1051.2	529.6
120°	1393.8	1423.5	1459.5	1483.4	1214.5
122.5°	1505.1	1537.0	1576.9	1588.8	1590.9
125°	1618.6	1644.6	1682.4	1696.4	1702.3
127.5°	1722.2	1750.0	1780.0	1799.9	1801.8
130°	1819.7	1851.7	1873.5	1895.4	1893.5
132.5°	1919.3	1945.3	1967.1	1985.0	1983.1
135°	2003.0	2034.9	2052.7	2072.7	2068.7
137.5°	2090.5	2114.4	2134.5	2154.3	2148.4
140°	2176.0	2192.2	2213.9	2231.9	2221.9
142.5°	2247.9	2261.9	2287.6	2303.5	2293.6
145°	2323.6	2321.5	2355.3	2369.3	2359.3
147.5°	2389.1	2383.2	2417.0	2426.9	2419.2
150°	2452.9	2439.0	2470.9	2482.7	2472.8
152.5°	2506.6	2490.7	2520.6	2532.6	2518.6
155°	2558.4	2540.6	2564.5	2576.3	2560.5
157.5°	2600.2	2584.4	2602.4	2616.3	2600.2
160°	2636.2	2624.1	2636.2	2648.0	2634.1
162.5°	2667.8	2656.0	2665.9	2679.9	2661.9
165°	2695.7	2683.9	2689.8	2703.8	2689.8
167.5°	2717.7	2705.6	2711.8	2725.8	2707.8
170°	2735.7	2723.7	2727.7	2741.6	2723.7
172.5°	2747.5	2735.7	2739.7	2753.7	2735.7
175°	2757.4	2743.5	2747.5	2761.5	2741.6
177.5°	2761.5	2747.5	2749.7	2763.6	2745.6
180°	2751.6	2751.6	2751.6	2751.6	2751.6

TEST NUMBER: P917061

CATALOG NUMBER: DFN2DIP-PN4F0-110D100US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.75	11.63	11.68	12.58	13.82	10.31	11.19	11.24	12.14	13.38
	3H	12.41	13.21	13.36	14.17	15.43	11.93	12.72	12.88	13.68	14.94
	4H	13.00	13.75	13.97	14.72	15.99	12.52	13.27	13.48	14.23	15.50
	6H	13.41	14.10	14.38	15.07	16.35	12.91	13.61	13.89	14.58	15.86
	8H	13.51	14.17	14.49	15.16	16.44	13.02	13.68	14.00	14.67	15.95
	12H	13.56	14.19	14.55	15.17	16.48	13.06	13.69	14.05	14.67	15.98
4H	2H	11.21	11.96	12.18	12.93	14.20	10.86	11.61	11.83	12.58	13.85
	3H	13.08	13.71	14.06	14.71	15.99	12.68	13.31	13.66	14.30	15.59
	4H	13.80	14.37	14.79	15.36	16.67	13.38	13.96	14.37	14.95	16.25
	6H	14.32	14.81	15.32	15.83	17.13	13.90	14.39	14.89	15.40	16.71
	8H	14.47	14.93	15.47	15.94	17.26	14.04	14.50	15.04	15.51	16.83
	12H	14.55	14.96	15.57	15.99	17.31	14.11	14.52	15.13	15.55	16.87
8H	4H	14.00	14.46	15.00	15.47	16.79	13.63	14.09	14.63	15.10	16.41
	6H	14.63	15.02	15.66	16.06	17.38	14.26	14.64	15.28	15.69	17.00
	8H	14.86	15.19	15.89	16.23	17.56	14.47	14.81	15.51	15.84	17.18
	12H	14.99	15.29	16.03	16.32	17.70	14.59	14.89	15.63	15.92	17.29
12H	4H	13.99	14.40	15.00	15.42	16.75	13.62	14.04	14.64	15.06	16.39
	6H	14.67	15.00	15.70	16.04	17.37	14.30	14.64	15.33	15.67	17.01
	8H	14.91	15.21	15.95	16.24	17.62	14.54	14.83	15.57	15.86	17.24

END OF REPORT