

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917095

Luminaire Tested: DFN2DIP-PN4F0-120D090US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917095
REPORT IS A COMBINATION OF REPORTS P901236 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-120D090US930-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15580.4 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 192.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917095

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917095

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		100	100	100	100		85	85	85		72	72	72		59	59	59
1	99	95	91	88		92	88	85	82		76	73	71		64	62	61		53	52	51
2	91	83	78	73		84	78	73	68		67	63	60		57	54	52		47	45	44
3	83	74	67	61		77	69	63	58		59	55	51		51	47	44		42	40	38
4	76	66	58	52		70	61	55	49		53	48	44		45	42	38		38	35	33
5	70	59	51	45		65	55	48	43		48	42	38		41	37	34		35	32	29
6	65	53	45	39		60	50	43	37		43	38	34		37	33	30		32	28	26
7	60	48	40	35		56	45	38	33		39	34	30		34	30	26		29	26	23
8	56	44	36	31		52	41	34	29		36	31	27		31	27	24		27	24	21
9	52	40	33	28		48	38	31	26		33	28	24		29	25	22		25	22	19
10	49	37	30	25		45	35	28	24		31	25	22		27	23	20		23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2952	2952	2952
5°	2956	2905	2924
10°	2927	2849	2829
15°	2887	2755	2683
20°	2833	2625	2503
25°	2779	2480	2329
30°	2706	2331	2108
35°	2634	2171	1914
40°	2561	2006	1692
45°	2476	1822	1490
50°	2388	1636	1293
55°	2296	1438	1104
60°	2190	1230	909
65°	2068	1019	819
70°	1920	823	742
75°	1734	726	676
80°	1465	610	588
85°	1021	410	446

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2476 cd/sqm

TEST NUMBER: P917095

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.0	2.4
10°-20°	1040.3	6.7
20°-30°	1460.6	9.4
30°-40°	1592.1	10.2
40°-50°	1463.4	9.4
50°-60°	1149.2	7.4
60°-70°	748.0	4.8
70°-80°	385.1	2.5
80°-90°	102.7	0.7
90°-100°	81.7	0.5
100°-110°	304.4	2.0
110°-120°	807.3	5.2
120°-130°	1339.0	8.6
130°-140°	1422.3	9.1
140°-150°	1321.9	8.5
150°-160°	1062.8	6.8
160°-170°	684.8	4.4
170°-180°	235.7	1.5
0°-30°	2879.9	18.5
0°-40°	4472.0	28.7
0°-60°	7084.6	45.5
0°-90°	8320.4	53.4
90°-120°	1193.4	7.7
90°-150°	5276.6	33.9
90°-180°	7260.0	46.6
0°-180°	15580.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4044	4044	4044	4044	4044	
5°	4044	4025	3978	4010	4000	383
15°	3846	3806	3681	3612	3575	1084
25°	3491	3374	3132	2982	2927	1606
35°	3008	2821	2500	2269	2188	1883
45°	2459	2214	1830	1570	1482	1899
55°	1870	1584	1189	970	900	1671
65°	1263	966	637	512	501	1252
75°	673	417	293	267	264	712
85°	157	80	70	70	70	181
90°	2	22	36	45	48	15
95°	116	57	70	79	77	138
105°	545	599	109	129	136	582
115°	1030	1061	1106	276	147	1014
125°	1457	1480	1514	1527	1532	1299
135°	1803	1831	1847	1866	1862	1393
145°	2091	2089	2120	2132	2123	1308
155°	2303	2287	2308	2319	2304	1061
165°	2426	2416	2421	2433	2421	685
175°	2482	2469	2473	2485	2467	236
180°	2476	2476	2476	2476	2476	

TEST NUMBER: P917095

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4043.6	4043.6	4043.6	4043.6	4043.6
2.5°	4061.8	4043.6	4003.2	4040.0	4032.6
5°	4043.6	4025.3	3977.5	4010.5	3999.7
7.5°	4010.5	3988.8	3937.6	3951.9	3933.7
10°	3966.7	3941.1	3868.0	3856.8	3835.1
12.5°	3911.9	3878.9	3779.9	3758.2	3717.8
15°	3845.9	3805.6	3681.3	3611.8	3575.3
17.5°	3769.0	3710.4	3556.7	3476.4	3417.7
20°	3681.3	3607.9	3425.1	3333.8	3253.0
22.5°	3586.2	3502.0	3289.6	3165.3	3110.6
25°	3491.1	3373.8	3132.3	2982.4	2927.3
27.5°	3377.7	3253.0	2985.9	2814.0	2729.7
30°	3257.0	3117.6	2824.8	2638.5	2539.5
32.5°	3139.7	2971.2	2671.5	2451.8	2360.1
35°	3008.1	2821.3	2499.5	2268.9	2188.1
37.5°	2880.0	2678.5	2338.4	2085.6	1994.4
40°	2744.5	2525.1	2169.9	1910.2	1815.0
42.5°	2605.4	2371.4	2001.8	1730.8	1639.6
45°	2459.1	2213.8	1829.8	1569.7	1481.9
47.5°	2320.1	2060.4	1665.2	1405.1	1324.7
50°	2166.4	1906.7	1504.1	1251.3	1174.8
52.5°	2016.2	1741.6	1350.3	1108.8	1039.3
55°	1869.8	1584.5	1189.2	969.8	900.3
57.5°	1719.9	1427.2	1046.7	841.7	783.1
60°	1566.2	1273.4	896.4	710.1	651.5
62.5°	1416.3	1123.6	768.3	592.9	563.7
65°	1262.6	966.0	636.7	512.5	501.2
67.5°	1116.2	819.5	512.5	450.0	439.1
70°	962.5	677.1	424.4	387.8	373.1
72.5°	816.1	545.1	354.8	325.7	318.4
75°	673.2	416.9	292.8	267.1	263.6
77.5°	530.8	296.2	230.6	215.9	208.5
80°	398.8	212.4	175.5	161.1	161.1
82.5°	278.0	142.8	120.7	113.3	113.3
85°	157.3	80.4	69.5	69.5	69.5
87.5°	58.6	29.1	29.1	25.6	25.6
90°	1.7	21.5	35.7	44.9	48.3
92.5°	44.9	37.7	43.0	46.6	48.3
95°	116.4	57.2	69.8	78.9	77.0
97.5°	209.6	62.8	91.3	96.8	98.5
100°	317.2	71.7	102.2	116.4	120.0
102.5°	435.4	431.9	105.7	125.3	130.9
105°	544.7	598.6	109.3	129.0	136.2
107.5°	672.0	716.6	113.0	132.6	139.8
110°	793.9	831.4	313.6	134.4	141.5



TEST NUMBER: P917095

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	908.6	940.7	910.3	137.9	143.4
115°	1030.3	1060.7	1105.6	276.0	147.0
117.5°	1136.0	1171.8	1202.4	946.1	476.6
120°	1254.3	1281.2	1313.5	1335.0	1093.1
122.5°	1354.6	1383.3	1419.3	1429.9	1431.8
125°	1456.7	1480.1	1514.2	1526.7	1532.0
127.5°	1549.9	1575.0	1602.1	1619.9	1621.6
130°	1637.8	1666.6	1686.1	1705.8	1704.2
132.5°	1727.4	1750.8	1770.3	1786.6	1784.9
135°	1802.7	1831.4	1847.4	1865.5	1861.9
137.5°	1881.5	1902.9	1921.0	1938.9	1933.6
140°	1958.4	1972.9	1992.5	2008.7	1999.8
142.5°	2023.2	2035.7	2058.9	2073.1	2064.3
145°	2091.2	2089.3	2119.8	2132.3	2123.4
147.5°	2150.2	2144.9	2175.3	2184.3	2177.2
150°	2207.7	2195.1	2223.8	2234.4	2225.5
152.5°	2255.9	2241.7	2268.5	2279.3	2266.8
155°	2302.6	2286.6	2308.0	2318.7	2304.4
157.5°	2340.2	2326.0	2342.1	2354.7	2340.2
160°	2372.5	2361.7	2372.5	2383.2	2370.6
162.5°	2401.1	2390.4	2399.3	2411.9	2395.8
165°	2426.2	2415.5	2420.9	2433.4	2420.9
167.5°	2446.0	2435.1	2440.6	2453.2	2437.0
170°	2462.1	2451.3	2454.9	2467.4	2451.3
172.5°	2472.8	2462.1	2465.7	2478.3	2462.1
175°	2481.7	2469.1	2472.8	2485.3	2467.4
177.5°	2485.3	2472.8	2474.7	2487.2	2471.1
180°	2476.4	2476.4	2476.4	2476.4	2476.4

TEST NUMBER: P917095

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.23	12.09	12.16	13.03	14.26	7.19	8.05	8.13	9.00	10.22
	3H	12.91	13.68	13.86	14.63	15.88	8.38	9.15	9.33	10.11	11.36
	4H	13.52	14.25	14.48	15.21	16.46	8.84	9.56	9.80	10.52	11.78
	6H	13.95	14.62	14.92	15.58	16.85	9.16	9.83	10.13	10.79	12.06
	8H	14.08	14.71	15.05	15.69	16.96	9.25	9.89	10.23	10.87	12.14
	12H	14.14	14.74	15.12	15.72	17.01	9.30	9.90	10.28	10.88	12.17
4H	2H	11.25	11.97	12.22	12.94	14.19	7.79	8.52	8.76	9.48	10.74
	3H	13.08	13.69	14.06	14.68	15.95	9.15	9.75	10.12	10.74	12.01
	4H	13.78	14.33	14.76	15.31	16.61	9.70	10.25	10.68	11.23	12.53
	6H	14.30	14.77	15.30	15.78	17.07	10.12	10.59	11.11	11.60	12.89
	8H	14.48	14.92	15.47	15.92	17.23	10.25	10.69	11.25	11.69	13.00
	12H	14.57	14.97	15.59	15.99	17.30	10.31	10.71	11.33	11.73	13.04
8H	4H	13.75	14.19	14.75	15.19	16.50	9.98	10.42	10.98	11.42	12.73
	6H	14.32	14.68	15.34	15.73	17.03	10.50	10.87	11.52	11.91	13.21
	8H	14.54	14.86	15.57	15.89	17.21	10.69	11.01	11.72	12.04	13.37
	12H	14.68	14.96	15.71	15.99	17.36	10.81	11.10	11.85	12.12	13.49
12H	4H	13.70	14.10	14.72	15.12	16.43	9.99	10.38	11.00	11.40	12.71
	6H	14.30	14.62	15.33	15.65	16.97	10.55	10.87	11.58	11.90	13.23
	8H	14.52	14.80	15.55	15.83	17.19	10.76	11.05	11.80	12.07	13.44