

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917105

Luminaire Tested: DFN2DIP-PN4F0-120D120US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917105
REPORT IS A COMBINATION OF REPORTS P901289 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-120D120US930-FLLONL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19371.5 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 229.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917105

CATALOG NUMBER: DFN2DIP-PN4F0-120D120US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917105

CATALOG NUMBER: DFN2DIP-PN4F0-120D120US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2779	2779	2779
5°	2783	2741	2759
10°	2761	2704	2722
15°	2720	2660	2664
20°	2665	2598	2605
25°	2611	2525	2536
30°	2542	2456	2449
35°	2478	2375	2357
40°	2398	2294	2269
45°	2318	2212	2179
50°	2231	2126	2075
55°	2140	2027	1979
60°	2037	1909	1870
65°	1925	1787	1741
70°	1782	1639	1602
75°	1584	1461	1474
80°	1346	1234	1229
85°	973	842	823

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2318 cd/sqm

TEST NUMBER: P917105

CATALOG NUMBER: DFN2DIP-PN4F0-120D120US930-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	358.3	1.8
10°-20°	1008.1	5.2
20°-30°	1481.5	7.6
30°-40°	1720.7	8.9
40°-50°	1718.6	8.9
50°-60°	1498.5	7.7
60°-70°	1107.8	5.7
70°-80°	626.7	3.2
80°-90°	171.2	0.9
90°-100°	108.9	0.6
100°-110°	405.9	2.1
110°-120°	1076.4	5.6
120°-130°	1785.3	9.2
130°-140°	1896.5	9.8
140°-150°	1762.5	9.1
150°-160°	1417.0	7.3
160°-170°	913.1	4.7
170°-180°	314.3	1.6
0°-30°	2848.0	14.7
0°-40°	4568.7	23.6
0°-60°	7785.8	40.2
0°-90°	9691.5	50.0
90°-120°	1591.2	8.2
90°-150°	7035.5	36.3
90°-180°	9680.0	50.0
0°-180°	19371.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3807	3807	3807	3807	3807	
5°	3807	3792	3752	3781	3774	361
15°	3624	3602	3554	3569	3551	1021
25°	3280	3251	3188	3196	3188	1509
35°	2830	2793	2734	2712	2694	1767
45°	2303	2277	2222	2182	2167	1777
55°	1743	1720	1677	1633	1614	1558
65°	1175	1153	1117	1084	1065	1162
75°	615	608	589	567	575	656
85°	150	146	143	132	128	167
90°	2	29	48	60	64	18
95°	155	76	93	105	103	184
105°	726	798	146	172	182	776
115°	1374	1414	1474	368	196	1352
125°	1942	1974	2019	2036	2043	1732
135°	2404	2442	2463	2487	2482	1857
145°	2788	2786	2826	2843	2831	1744
155°	3070	3049	3077	3092	3073	1415
165°	3235	3221	3228	3245	3228	914
175°	3309	3292	3297	3314	3290	315
180°	3302	3302	3302	3302	3302	

TEST NUMBER: P917105

CATALOG NUMBER: DFN2DIP-PN4F0-120D120US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3806.9	3806.9	3806.9	3806.9	3806.9
2.5°	3829.0	3810.7	3770.3	3806.9	3799.9
5°	3806.9	3792.4	3752.1	3781.2	3774.2
7.5°	3781.2	3759.4	3719.1	3748.6	3741.2
10°	3741.2	3715.6	3671.7	3700.8	3690.0
12.5°	3686.0	3664.3	3620.4	3638.7	3631.3
15°	3623.9	3602.2	3554.4	3569.1	3550.9
17.5°	3547.0	3525.3	3477.5	3495.8	3477.5
20°	3462.7	3441.0	3389.8	3400.6	3386.3
22.5°	3378.8	3345.8	3298.0	3298.0	3290.7
25°	3279.8	3250.7	3188.5	3195.6	3188.5
27.5°	3169.9	3144.3	3096.9	3086.0	3067.8
30°	3060.4	3030.9	2976.1	2965.2	2950.5
32.5°	2943.1	2921.4	2862.7	2840.6	2825.8
35°	2829.7	2793.2	2734.5	2712.4	2694.2
37.5°	2701.5	2668.6	2609.9	2584.3	2566.0
40°	2569.9	2540.4	2481.7	2449.1	2434.3
42.5°	2441.7	2412.2	2353.9	2317.1	2295.3
45°	2302.6	2277.0	2221.9	2181.9	2167.1
47.5°	2167.1	2141.5	2082.8	2042.5	2020.7
50°	2024.2	2006.0	1954.7	1903.4	1885.1
52.5°	1885.1	1859.5	1812.2	1771.7	1746.1
55°	1742.6	1720.5	1676.6	1632.7	1614.5
57.5°	1599.7	1581.4	1533.7	1489.8	1475.0
60°	1456.8	1442.4	1391.1	1350.8	1339.9
62.5°	1317.8	1292.1	1255.6	1219.1	1204.4
65°	1175.3	1153.1	1116.6	1083.5	1065.4
67.5°	1028.8	1010.2	977.5	951.9	937.2
70°	893.2	878.5	845.5	819.9	805.5
72.5°	754.2	739.5	721.2	695.6	684.7
75°	614.8	607.8	589.1	567.4	574.8
77.5°	490.5	475.7	468.4	457.5	446.6
80°	366.2	362.3	355.0	344.1	336.7
82.5°	248.9	248.9	245.5	230.7	230.7
85°	149.9	146.4	142.9	131.7	128.2
87.5°	66.0	58.6	51.3	40.4	36.5
90°	2.3	28.6	47.7	59.8	64.4
92.5°	59.8	50.2	57.3	62.1	64.4
95°	155.2	76.3	93.0	105.3	102.7
97.5°	279.5	83.7	121.7	129.1	131.3
100°	423.0	95.6	136.2	155.2	160.0
102.5°	580.5	575.9	141.0	167.1	174.5
105°	726.3	798.1	145.9	171.9	181.6
107.5°	895.9	955.5	150.7	176.8	186.4
110°	1058.5	1108.5	418.2	179.3	188.7



TEST NUMBER: P917105

CATALOG NUMBER: DFN2DIP-PN4F0-120D120US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1211.5	1254.3	1213.7	183.8	191.2
115°	1373.7	1414.3	1474.1	367.9	196.1
117.5°	1514.7	1562.4	1603.3	1261.3	635.5
120°	1672.5	1708.2	1751.3	1780.0	1457.4
122.5°	1806.1	1844.4	1892.4	1906.6	1909.1
125°	1942.3	1973.5	2018.9	2035.6	2042.7
127.5°	2066.5	2100.0	2136.1	2159.9	2162.2
130°	2183.7	2222.0	2248.1	2274.5	2272.2
132.5°	2303.1	2334.4	2360.5	2382.1	2379.8
135°	2403.6	2441.9	2463.2	2487.3	2482.5
137.5°	2508.6	2537.2	2561.3	2585.1	2578.1
140°	2611.3	2630.6	2656.6	2678.3	2666.4
142.5°	2697.5	2714.3	2745.2	2764.2	2752.3
145°	2788.3	2785.8	2826.3	2843.1	2831.1
147.5°	2866.9	2859.8	2900.4	2912.3	2903.0
150°	2943.5	2926.8	2965.1	2979.3	2967.4
152.5°	3007.9	2988.9	3024.7	3039.1	3022.4
155°	3070.0	3048.7	3077.4	3091.6	3072.6
157.5°	3120.2	3101.2	3122.8	3139.6	3120.2
160°	3163.4	3148.9	3163.4	3177.5	3160.8
162.5°	3201.4	3187.2	3199.1	3215.9	3194.3
165°	3234.9	3220.7	3227.8	3244.6	3227.8
167.5°	3261.3	3246.8	3254.2	3270.9	3249.4
170°	3282.8	3268.4	3273.2	3289.9	3268.4
172.5°	3297.0	3282.8	3287.7	3304.4	3282.8
175°	3308.9	3292.2	3297.0	3313.8	3289.9
177.5°	3313.8	3297.0	3299.6	3316.3	3294.8
180°	3301.9	3301.9	3301.9	3301.9	3301.9

TEST NUMBER: P917105

CATALOG NUMBER: DFN2DIP-PN4F0-120D120US930-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.83	11.69	11.79	12.67	13.94	10.39	11.25	11.35	12.23	13.50
	3H	12.50	13.27	13.46	14.25	15.54	12.01	12.78	12.98	13.77	15.06
	4H	13.09	13.82	14.07	14.80	16.10	12.60	13.33	13.58	14.32	15.62
	6H	13.49	14.16	14.48	15.15	16.47	13.00	13.67	13.99	14.66	15.97
	8H	13.59	14.24	14.59	15.24	16.55	13.10	13.74	14.10	14.75	16.06
	12H	13.64	14.25	14.65	15.25	16.59	13.14	13.75	14.15	14.75	16.09
4H	2H	11.29	12.03	12.28	13.01	14.31	10.94	11.67	11.93	12.66	13.96
	3H	13.16	13.77	14.16	14.79	16.10	12.76	13.37	13.76	14.39	15.70
	4H	13.88	14.44	14.89	15.45	16.78	13.46	14.02	14.47	15.03	16.37
	6H	14.40	14.88	15.41	15.91	17.25	13.97	14.45	14.99	15.49	16.82
	8H	14.55	15.00	15.57	16.02	17.37	14.12	14.57	15.14	15.59	16.94
	12H	14.62	15.03	15.66	16.07	17.42	14.18	14.59	15.22	15.63	16.98
8H	4H	14.08	14.53	15.09	15.55	16.90	13.71	14.16	14.72	15.18	16.53
	6H	14.71	15.08	15.75	16.15	17.50	14.34	14.71	15.38	15.77	17.12
	8H	14.93	15.26	15.98	16.31	17.68	14.55	14.88	15.60	15.93	17.30
	12H	15.07	15.36	16.12	16.40	17.81	14.67	14.95	15.72	16.00	17.41
12H	4H	14.06	14.47	15.10	15.51	16.86	13.70	14.11	14.74	15.15	16.50
	6H	14.74	15.07	15.79	16.12	17.49	14.38	14.70	15.43	15.76	17.12
	8H	14.99	15.27	16.04	16.32	17.73	14.61	14.90	15.67	15.95	17.36

END OF REPORT