

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919522

Luminaire Tested: DFN2DIP-PN4F0-040D060US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919522
REPORT IS A COMBINATION OF REPORTS P899646 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-040D060US935-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7499.3 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 78.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919522

CATALOG NUMBER: DFN2DIP-PN4F0-040D060US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P919522

CATALOG NUMBER: DFN2DIP-PN4F0-040D060US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1039	1039	1039
5°	1041	1023	1029
10°	1030	1003	996
15°	1016	970	944
20°	997	924	881
25°	978	873	820
30°	952	821	742
35°	927	764	674
40°	901	706	595
45°	871	641	525
50°	841	576	455
55°	808	506	388
60°	771	433	320
65°	728	359	288
70°	676	290	261
75°	610	256	238
80°	516	215	207
85°	360	144	157

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1279 cd/sqm

TEST NUMBER: P919522

CATALOG NUMBER: DFN2DIP-PN4F0-040D060US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.4	1.8
10°-20°	366.2	4.9
20°-30°	514.2	6.9
30°-40°	560.5	7.5
40°-50°	515.1	6.9
50°-60°	404.5	5.4
60°-70°	263.3	3.5
70°-80°	135.6	1.8
80°-90°	39.2	0.5
90°-100°	101.1	1.3
100°-110°	321.2	4.3
110°-120°	549.7	7.3
120°-130°	723.0	9.6
130°-140°	811.5	10.8
140°-150°	795.8	10.6
150°-160°	667.5	8.9
160°-170°	442.7	5.9
170°-180°	154.7	2.1
0°-30°	1013.8	13.5
0°-40°	1574.2	21.0
0°-60°	2493.9	33.3
0°-90°	2932.0	39.1
90°-120°	972.0	13.0
90°-150°	3302.3	44.0
90°-180°	4567.0	60.9
0°-180°	7499.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1423	1423	1423	1423	1423	
5°	1423	1417	1400	1412	1408	135
15°	1354	1340	1296	1271	1259	382
25°	1229	1188	1103	1050	1030	565
35°	1059	993	880	799	770	663
45°	866	779	644	553	522	668
55°	658	558	419	341	317	588
65°	444	340	224	180	176	441
75°	237	147	103	94	93	251
85°	55	28	24	24	24	64
90°	2	18	48	45	47	7
95°	72	86	88	88	86	80
105°	296	300	303	306	306	313
115°	552	560	557	556	552	546
125°	802	815	811	806	805	717
135°	1038	1053	1056	1055	1051	802
145°	1260	1270	1278	1279	1274	787
155°	1441	1445	1449	1456	1452	663
165°	1567	1566	1566	1576	1569	442
175°	1631	1627	1624	1634	1625	155
180°	1634	1634	1634	1634	1634	

TEST NUMBER: P919522

CATALOG NUMBER: DFN2DIP-PN4F0-040D060US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1423.4	1423.4	1423.4	1423.4	1423.4
2.5°	1429.9	1423.4	1409.2	1422.2	1419.5
5°	1423.4	1416.9	1400.2	1411.8	1408.0
7.5°	1411.8	1404.1	1386.1	1391.1	1384.7
10°	1396.4	1387.3	1361.6	1357.6	1350.0
12.5°	1377.1	1365.5	1330.6	1322.9	1308.7
15°	1353.8	1339.6	1295.9	1271.4	1258.6
17.5°	1326.8	1306.1	1252.0	1223.7	1203.1
20°	1295.9	1270.1	1205.7	1173.5	1145.1
22.5°	1262.4	1232.8	1158.0	1114.2	1095.0
25°	1228.9	1187.7	1102.6	1049.9	1030.4
27.5°	1189.0	1145.1	1051.1	990.6	960.9
30°	1146.5	1097.4	994.4	928.8	894.0
32.5°	1105.3	1045.9	940.4	863.1	830.8
35°	1058.9	993.2	879.9	798.7	770.2
37.5°	1013.8	942.9	823.1	734.2	702.1
40°	966.1	888.9	763.9	672.4	638.9
42.5°	917.1	834.7	704.6	609.2	577.1
45°	865.6	779.3	644.1	552.6	521.7
47.5°	816.7	725.3	586.2	494.6	466.3
50°	762.6	671.1	529.4	440.5	413.5
52.5°	709.7	613.1	475.4	390.3	365.8
55°	658.2	557.8	418.6	341.4	316.9
57.5°	605.5	502.4	368.4	296.3	275.7
60°	551.3	448.2	315.6	249.9	229.4
62.5°	498.6	395.5	270.4	208.7	198.5
65°	444.4	340.0	224.1	180.4	176.4
67.5°	393.0	288.5	180.4	158.4	154.5
70°	338.8	238.3	149.4	136.6	131.3
72.5°	287.3	191.9	124.9	114.7	112.1
75°	236.9	146.8	103.1	94.0	92.8
77.5°	186.8	104.3	81.2	76.0	73.4
80°	140.3	74.7	61.7	56.7	56.7
82.5°	97.9	50.3	42.5	39.9	39.9
85°	55.4	28.3	24.5	24.5	24.5
87.5°	20.7	10.2	10.2	9.0	9.0
90°	1.5	17.7	48.3	45.3	46.8
92.5°	30.6	41.4	42.9	44.3	44.3
95°	71.9	85.7	88.2	88.2	85.7
97.5°	119.7	132.5	137.9	137.9	137.9
100°	174.9	186.1	190.1	190.1	188.6
102.5°	233.0	241.3	246.8	248.2	246.8
105°	296.5	300.5	303.4	305.9	305.9
107.5°	359.6	365.5	365.5	366.4	359.6
110°	420.7	428.5	428.5	428.5	424.6

TEST NUMBER: P919522

CATALOG NUMBER: DFN2DIP-PN4F0-040D060US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	486.6	495.0	493.5	489.6	486.6
115°	551.6	559.6	557.1	555.6	551.6
117.5°	616.2	627.1	620.1	616.2	612.3
120°	681.2	692.1	681.2	681.2	676.7
122.5°	740.3	754.1	747.2	743.3	740.3
125°	802.4	814.7	810.7	806.3	804.9
127.5°	863.0	878.2	872.8	866.9	863.0
130°	919.6	937.4	934.9	931.9	926.5
132.5°	983.2	996.9	997.9	991.0	987.0
135°	1037.8	1053.1	1056.0	1054.6	1050.6
137.5°	1098.9	1111.2	1113.7	1112.7	1106.8
140°	1152.6	1164.9	1171.8	1171.8	1166.4
142.5°	1207.7	1220.0	1224.0	1225.5	1220.0
145°	1260.0	1269.8	1277.7	1279.2	1273.8
147.5°	1306.7	1319.0	1325.0	1327.4	1322.0
150°	1355.0	1363.4	1368.8	1373.2	1368.8
152.5°	1397.8	1406.3	1413.2	1418.6	1413.2
155°	1440.7	1444.7	1449.1	1456.0	1451.6
157.5°	1477.6	1480.7	1483.1	1493.0	1486.1
160°	1510.7	1513.6	1515.1	1523.4	1517.6
162.5°	1541.2	1541.2	1542.6	1552.0	1545.1
165°	1567.3	1565.8	1565.8	1575.7	1568.8
167.5°	1591.0	1586.6	1586.6	1596.4	1589.5
170°	1608.7	1604.7	1603.3	1613.1	1604.7
172.5°	1621.0	1617.0	1615.6	1625.4	1617.0
175°	1630.8	1626.9	1623.9	1633.8	1625.4
177.5°	1636.2	1632.4	1629.4	1637.7	1629.4
180°	1633.8	1633.8	1633.8	1633.8	1633.8

TEST NUMBER: P919522

CATALOG NUMBER: DFN2DIP-PN4F0-040D060US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.17	6.92	7.23	7.97	9.40	2.14	2.89	3.19	3.94	5.36
	3H	7.85	8.52	8.91	9.58	11.02	3.32	3.99	4.38	5.05	6.49
	4H	8.45	9.09	9.53	10.15	11.60	3.77	4.40	4.84	5.47	6.91
	6H	8.87	9.46	9.96	10.52	11.98	4.09	4.67	5.17	5.74	7.19
	8H	9.00	9.55	10.09	10.64	12.09	4.18	4.73	5.26	5.81	7.26
	12H	9.06	9.59	10.15	10.66	12.14	4.22	4.74	5.31	5.82	7.30
4H	2H	6.18	6.82	7.26	7.88	9.33	2.73	3.36	3.80	4.42	5.87
	3H	8.01	8.53	9.09	9.62	11.08	4.07	4.60	5.16	5.69	7.15
	4H	8.70	9.18	9.79	10.26	11.74	4.61	5.10	5.71	6.18	7.66
	6H	9.21	9.63	10.31	10.73	12.20	5.03	5.44	6.13	6.55	8.02
	8H	9.39	9.77	10.49	10.87	12.36	5.16	5.55	6.26	6.64	8.13
	12H	9.48	9.83	10.60	10.94	12.43	5.22	5.57	6.34	6.68	8.17
8H	4H	8.66	9.05	9.76	10.14	11.63	4.89	5.28	5.99	6.37	7.86
	6H	9.23	9.55	10.35	10.68	12.17	5.41	5.73	6.53	6.86	8.35
	8H	9.44	9.72	10.57	10.84	12.35	5.60	5.88	6.73	7.00	8.50
	12H	9.58	9.83	10.71	10.94	12.49	5.72	5.96	6.85	7.08	8.62
12H	4H	8.61	8.96	9.72	10.07	11.56	4.89	5.24	6.01	6.35	7.85
	6H	9.20	9.48	10.33	10.60	12.11	5.46	5.74	6.58	6.86	8.36
	8H	9.42	9.67	10.55	10.78	12.33	5.67	5.91	6.80	7.03	8.57

END OF REPORT