

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908790

Luminaire Tested: DFN2DIP-PN4F0-090D060US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908790
REPORT IS A COMBINATION OF REPORTS P899656 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-090D060US840-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13087.9 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 133.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908790

CATALOG NUMBER: DFN2DIP-PN4F0-090D060US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P908790

CATALOG NUMBER: DFN2DIP-PN4F0-090D060US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59		
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51		
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44		
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41	38		
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33		
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29		
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28	26		
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23		
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21		
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21	19		
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2742	2742	2742
5°	2746	2699	2716
10°	2719	2646	2628
15°	2682	2559	2492
20°	2632	2439	2325
25°	2582	2304	2163
30°	2513	2166	1958
35°	2447	2017	1778
40°	2379	1863	1572
45°	2300	1692	1384
50°	2218	1520	1201
55°	2133	1336	1025
60°	2035	1143	844
65°	1921	947	761
70°	1784	764	689
75°	1611	674	628
80°	1361	567	547
85°	948	380	414

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2300 cd/sqm

TEST NUMBER: P908790

CATALOG NUMBER: DFN2DIP-PN4F0-090D060US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.1	2.7
10°-20°	966.5	7.4
20°-30°	1356.9	10.4
30°-40°	1479.1	11.3
40°-50°	1359.4	10.4
50°-60°	1067.6	8.2
60°-70°	694.9	5.3
70°-80°	357.7	2.7
80°-90°	96.8	0.7
90°-100°	118.6	0.9
100°-110°	376.8	2.9
110°-120°	644.8	4.9
120°-130°	848.0	6.5
130°-140°	951.8	7.3
140°-150°	933.4	7.1
150°-160°	783.0	6.0
160°-170°	519.2	4.0
170°-180°	181.5	1.4
0°-30°	2675.4	20.4
0°-40°	4154.5	31.7
0°-60°	6581.5	50.3
0°-90°	7730.9	59.1
90°-120°	1140.1	8.7
90°-150°	3873.3	29.6
90°-180°	5357.0	40.9
0°-180°	13087.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3756	3756	3756	3756	3756	
5°	3756	3739	3695	3726	3716	356
15°	3573	3535	3420	3355	3321	1007
25°	3243	3134	2910	2771	2720	1492
35°	2794	2621	2322	2108	2033	1749
45°	2284	2057	1700	1458	1377	1764
55°	1737	1472	1105	901	836	1552
65°	1173	897	592	476	466	1163
75°	625	387	272	248	245	661
85°	146	75	64	64	64	168
90°	2	21	57	53	55	13
95°	84	100	103	103	100	94
105°	348	352	356	359	359	367
115°	647	656	653	652	647	640
125°	941	956	951	946	944	841
135°	1217	1235	1239	1237	1232	941
145°	1478	1489	1499	1500	1494	923
155°	1690	1694	1700	1708	1702	778
165°	1838	1836	1836	1848	1840	519
175°	1913	1908	1905	1916	1906	182
180°	1916	1916	1916	1916	1916	

TEST NUMBER: P908790

CATALOG NUMBER: DFN2DIP-PN4F0-090D060US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3756.4	3756.4	3756.4	3756.4	3756.4
2.5°	3773.4	3756.4	3718.8	3753.2	3746.3
5°	3756.4	3739.4	3695.1	3725.7	3715.6
7.5°	3725.7	3705.5	3657.9	3671.3	3654.3
10°	3685.0	3661.2	3593.4	3582.9	3562.7
12.5°	3634.1	3603.5	3511.5	3491.3	3453.7
15°	3572.8	3535.3	3419.9	3355.3	3321.4
17.5°	3501.4	3447.0	3304.1	3229.4	3175.0
20°	3419.9	3351.7	3181.8	3097.1	3022.0
22.5°	3331.5	3253.3	3056.0	2940.5	2889.7
25°	3243.2	3134.2	2909.9	2770.7	2719.5
27.5°	3137.9	3022.0	2773.9	2614.1	2535.9
30°	3025.7	2896.2	2624.2	2451.1	2359.1
32.5°	2916.7	2760.2	2481.7	2277.7	2192.5
35°	2794.5	2621.0	2322.0	2107.8	2032.8
37.5°	2675.4	2488.3	2172.3	1937.5	1852.8
40°	2549.6	2345.8	2015.8	1774.5	1686.2
42.5°	2420.4	2203.0	1859.6	1607.9	1523.1
45°	2284.5	2056.6	1699.8	1458.1	1376.6
47.5°	2155.4	1914.1	1546.9	1305.3	1230.6
50°	2012.6	1771.2	1397.2	1162.5	1091.4
52.5°	1873.0	1618.0	1254.5	1030.1	965.5
55°	1737.0	1471.9	1104.7	901.0	836.4
57.5°	1597.8	1325.9	972.4	781.9	727.5
60°	1454.9	1183.0	832.8	659.6	605.2
62.5°	1315.8	1043.8	713.8	550.8	523.7
65°	1172.9	897.4	591.5	476.1	465.6
67.5°	1036.9	761.3	476.1	418.0	407.9
70°	894.1	629.0	394.3	360.3	346.6
72.5°	758.1	506.3	329.6	302.6	295.8
75°	625.4	387.4	272.0	248.1	244.9
77.5°	493.0	275.2	214.2	200.6	193.7
80°	370.4	197.3	163.0	149.7	149.7
82.5°	258.2	132.7	112.2	105.3	105.3
85°	146.0	74.6	64.5	64.5	64.5
87.5°	54.4	27.1	27.1	23.8	23.8
90°	1.7	20.8	56.7	53.1	54.8
92.5°	35.9	48.6	50.3	52.0	52.0
95°	84.3	100.5	103.4	103.4	100.5
97.5°	140.4	155.4	161.8	161.8	161.8
100°	205.1	218.3	223.0	223.0	221.3
102.5°	273.3	283.1	289.4	291.1	289.4
105°	347.8	352.4	355.9	358.8	358.8
107.5°	421.7	428.7	428.7	429.8	421.7
110°	493.4	502.6	502.6	502.6	498.0

TEST NUMBER: P908790

CATALOG NUMBER: DFN2DIP-PN4F0-090D060US840-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	570.8	580.6	578.9	574.2	570.8
115°	647.0	656.3	653.4	651.7	647.0
117.5°	722.8	735.5	727.3	722.8	718.1
120°	799.0	811.7	799.0	799.0	793.8
122.5°	868.3	884.4	876.4	871.8	868.3
125°	941.1	955.5	950.9	945.7	944.0
127.5°	1012.2	1030.1	1023.7	1016.8	1012.2
130°	1078.6	1099.4	1096.5	1093.1	1086.7
132.5°	1153.2	1169.3	1170.4	1162.4	1157.7
135°	1217.3	1235.2	1238.6	1236.9	1232.2
137.5°	1288.9	1303.3	1306.3	1305.0	1298.2
140°	1351.9	1366.3	1374.4	1374.4	1368.1
142.5°	1416.5	1431.0	1435.6	1437.3	1431.0
145°	1477.8	1489.3	1498.6	1500.4	1494.0
147.5°	1532.7	1547.1	1554.1	1556.9	1550.5
150°	1589.3	1599.1	1605.5	1610.6	1605.5
152.5°	1639.5	1649.4	1657.5	1663.9	1657.5
155°	1689.8	1694.5	1699.6	1707.8	1702.5
157.5°	1733.1	1736.7	1739.5	1751.1	1743.0
160°	1771.9	1775.3	1777.1	1786.9	1780.0
162.5°	1807.7	1807.7	1809.4	1820.4	1812.3
165°	1838.3	1836.5	1836.5	1848.2	1840.1
167.5°	1866.0	1860.9	1860.9	1872.4	1864.3
170°	1886.8	1882.2	1880.5	1892.0	1882.2
172.5°	1901.3	1896.6	1894.9	1906.4	1896.6
175°	1912.8	1908.2	1904.7	1916.3	1906.4
177.5°	1919.1	1914.6	1911.1	1920.9	1911.1
180°	1916.3	1916.3	1916.3	1916.3	1916.3

TEST NUMBER: P908790

CATALOG NUMBER: DFN2DIP-PN4F0-090D060US840-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.46	12.38	12.35	13.27	14.41	7.43	8.34	8.31	9.24	10.38
	3H	13.15	13.97	14.05	14.87	16.04	8.62	9.44	9.52	10.35	11.51
	4H	13.77	14.53	14.68	15.45	16.62	9.08	9.85	9.99	10.76	11.94
	6H	14.19	14.90	15.12	15.82	17.01	9.41	10.11	10.33	11.03	12.22
	8H	14.32	15.00	15.25	15.93	17.12	9.50	10.17	10.43	11.11	12.29
	12H	14.39	15.03	15.32	15.96	17.17	9.55	10.19	10.48	11.12	12.33
4H	2H	11.49	12.26	12.41	13.17	14.35	8.04	8.80	8.95	9.72	10.89
	3H	13.33	13.97	14.26	14.92	16.10	9.39	10.03	10.32	10.98	12.17
	4H	14.03	14.61	14.97	15.55	16.76	9.95	10.53	10.88	11.47	12.68
	6H	14.55	15.05	15.50	16.02	17.23	10.37	10.87	11.32	11.83	13.05
	8H	14.73	15.20	15.68	16.15	17.38	10.50	10.97	11.45	11.93	13.15
	12H	14.83	15.25	15.80	16.23	17.46	10.57	10.99	11.54	11.97	13.20
8H	4H	14.00	14.47	14.96	15.43	16.66	10.23	10.70	11.19	11.66	12.89
	6H	14.58	14.96	15.55	15.96	17.19	10.76	11.14	11.73	12.14	13.37
	8H	14.79	15.14	15.78	16.12	17.37	10.95	11.29	11.94	12.28	13.52
	12H	14.94	15.24	15.93	16.22	17.51	11.07	11.37	12.06	12.35	13.65
12H	4H	13.96	14.38	14.93	15.35	16.59	10.24	10.66	11.21	11.64	12.87
	6H	14.55	14.89	15.54	15.88	17.13	10.81	11.15	11.79	12.14	13.38
	8H	14.78	15.08	15.77	16.06	17.35	11.02	11.32	12.01	12.30	13.60

END OF REPORT