

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908895

Luminaire Tested: DFN2DIP-PN4F0-120D050US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908895
REPORT IS A COMBINATION OF REPORTS P901164 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-120D050US840-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15299.4 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 163.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908895

CATALOG NUMBER: DFN2DIP-PN4F0-120D050US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908895

CATALOG NUMBER: DFN2DIP-PN4F0-120D050US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	98	94	91	96	93	89	86	83	80	78	73	71	70	65	63	62
2	94	86	80	75	88	82	77	72	73	69	66	65	62	59	58	55	53
3	86	77	69	64	81	73	66	61	65	60	56	58	54	51	52	49	46
4	79	68	61	55	74	65	58	52	58	53	48	52	48	44	47	43	40
5	73	61	53	47	69	58	51	46	53	47	42	47	43	39	42	39	36
6	67	55	47	42	63	53	45	40	48	42	37	43	38	34	39	35	32
7	63	50	42	37	59	48	41	36	44	38	33	39	35	31	36	32	28
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26
9	54	42	35	30	51	40	33	29	37	31	27	34	29	25	30	26	23
10	51	39	32	27	48	37	31	26	34	28	25	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3656	3656	3656
5°	3662	3598	3622
10°	3626	3528	3505
15°	3576	3412	3323
20°	3510	3252	3100
25°	3442	3072	2884
30°	3351	2888	2611
35°	3262	2689	2371
40°	3172	2484	2095
45°	3067	2257	1846
50°	2958	2027	1602
55°	2844	1781	1367
60°	2713	1524	1126
65°	2562	1263	1014
70°	2378	1019	919
75°	2148	899	837
80°	1815	756	728
85°	1264	507	552

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3067 cd/sqm

TEST NUMBER: P908895

CATALOG NUMBER: DFN2DIP-PN4F0-120D050US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	469.4	3.1
10°-20°	1288.6	8.4
20°-30°	1809.2	11.8
30°-40°	1972.1	12.9
40°-50°	1812.6	11.8
50°-60°	1423.5	9.3
60°-70°	926.6	6.1
70°-80°	476.9	3.1
80°-90°	124.8	0.8
90°-100°	56.2	0.4
100°-110°	209.5	1.4
110°-120°	555.6	3.6
120°-130°	921.4	6.0
130°-140°	978.8	6.4
140°-150°	909.7	5.9
150°-160°	731.3	4.8
160°-170°	471.2	3.1
170°-180°	162.2	1.1
0°-30°	3567.2	23.3
0°-40°	5539.3	36.2
0°-60°	8775.3	57.4
0°-90°	10303.6	67.3
90°-120°	821.2	5.4
90°-150°	3631.1	23.7
90°-180°	4996.0	32.7
0°-180°	15299.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5008	5008	5008	5008	5008	
5°	5008	4986	4927	4968	4954	475
15°	4764	4714	4560	4474	4429	1342
25°	4324	4179	3880	3694	3626	1989
35°	3726	3495	3096	2810	2710	2332
45°	3046	2742	2266	1944	1836	2352
55°	2316	1963	1473	1201	1115	2070
65°	1564	1196	789	635	621	1550
75°	834	516	363	331	326	882
85°	195	100	86	86	86	224
90°	1	15	25	31	33	15
95°	80	39	48	54	53	95
105°	375	412	75	89	94	401
115°	709	730	761	190	101	698
125°	1002	1019	1042	1051	1054	894
135°	1240	1260	1271	1284	1281	958
145°	1439	1438	1459	1467	1461	900
155°	1584	1574	1588	1596	1586	730
165°	1670	1662	1666	1674	1666	472
175°	1708	1699	1702	1710	1698	163
180°	1704	1704	1704	1704	1704	

TEST NUMBER: P908895

CATALOG NUMBER: DFN2DIP-PN4F0-120D050US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5008.5	5008.5	5008.5	5008.5	5008.5
2.5°	5031.2	5008.5	4958.5	5004.2	4995.0
5°	5008.5	4985.9	4926.7	4967.6	4954.2
7.5°	4967.6	4940.7	4877.2	4895.0	4872.4
10°	4913.3	4881.6	4791.1	4777.2	4750.3
12.5°	4845.4	4804.6	4681.9	4655.1	4605.1
15°	4763.7	4713.7	4559.8	4473.7	4428.6
17.5°	4668.5	4595.9	4405.4	4306.0	4233.4
20°	4559.8	4469.0	4242.4	4129.4	4029.4
22.5°	4442.0	4337.7	4074.6	3920.7	3852.9
25°	4324.2	4178.9	3879.8	3694.2	3625.9
27.5°	4183.8	4029.4	3698.5	3485.6	3381.1
30°	4034.2	3861.6	3499.0	3268.1	3145.5
32.5°	3889.0	3680.3	3309.0	3036.9	2923.4
35°	3726.0	3494.6	3095.9	2810.4	2710.3
37.5°	3567.2	3317.7	2896.4	2583.3	2470.3
40°	3399.4	3127.8	2687.8	2366.0	2248.2
42.5°	3227.2	2937.3	2479.5	2143.8	2030.8
45°	3046.0	2742.1	2266.4	1944.3	1835.5
47.5°	2873.8	2552.1	2062.5	1740.4	1640.8
50°	2683.4	2361.7	1863.0	1549.9	1455.2
52.5°	2497.3	2157.3	1672.5	1373.4	1287.4
55°	2316.0	1962.6	1473.0	1201.2	1115.2
57.5°	2130.3	1767.8	1296.5	1042.6	970.0
60°	1940.0	1577.3	1110.3	879.6	807.0
62.5°	1754.3	1391.7	951.7	734.4	698.2
65°	1563.9	1196.5	788.7	634.8	620.9
67.5°	1382.6	1015.1	634.8	557.3	543.9
70°	1192.1	838.7	525.6	480.4	462.1
72.5°	1010.9	675.2	439.5	403.4	394.4
75°	833.8	516.4	362.6	330.8	326.5
77.5°	657.4	366.9	285.7	267.4	258.2
80°	493.9	263.1	217.3	199.5	199.5
82.5°	344.4	176.9	149.6	140.4	140.4
85°	194.8	99.6	86.0	86.0	86.0
87.5°	72.6	36.1	36.1	31.7	31.7
90°	1.2	14.7	24.6	30.9	33.2
92.5°	30.9	26.0	29.6	32.1	33.2
95°	80.1	39.4	48.1	54.3	53.0
97.5°	144.2	43.2	62.8	66.7	67.8
100°	218.3	49.4	70.3	80.1	82.6
102.5°	299.6	297.2	72.8	86.2	90.1
105°	374.9	411.9	75.2	88.8	93.7
107.5°	462.4	493.1	77.8	91.2	96.2
110°	546.3	572.1	215.8	92.5	97.4



TEST NUMBER: P908895

CATALOG NUMBER: DFN2DIP-PN4F0-120D050US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	625.2	647.3	626.4	94.9	98.7
115°	709.0	729.9	760.8	190.0	101.2
117.5°	781.7	806.4	827.5	651.0	328.0
120°	863.1	881.6	903.8	918.7	752.1
122.5°	932.1	951.9	976.6	984.0	985.3
125°	1002.4	1018.6	1042.0	1050.6	1054.3
127.5°	1066.5	1083.8	1102.5	1114.7	1115.9
130°	1127.0	1146.8	1160.2	1173.9	1172.8
132.5°	1188.7	1204.8	1218.2	1229.4	1228.2
135°	1240.5	1260.3	1271.2	1283.7	1281.2
137.5°	1294.6	1309.5	1321.9	1334.2	1330.6
140°	1347.7	1357.7	1371.1	1382.2	1376.1
142.5°	1392.2	1400.9	1416.8	1426.6	1420.5
145°	1439.1	1437.7	1458.6	1467.3	1461.2
147.5°	1479.7	1475.9	1496.9	1503.1	1498.2
150°	1519.1	1510.6	1530.2	1537.6	1531.5
152.5°	1552.4	1542.6	1561.1	1568.5	1559.8
155°	1584.5	1573.5	1588.2	1595.6	1585.8
157.5°	1610.3	1600.5	1611.6	1620.3	1610.3
160°	1632.6	1625.2	1632.6	1639.9	1631.3
162.5°	1652.2	1645.0	1651.0	1659.7	1648.6
165°	1669.5	1662.2	1665.9	1674.5	1665.9
167.5°	1683.1	1675.7	1679.5	1688.1	1677.0
170°	1694.3	1686.8	1689.3	1697.9	1686.8
172.5°	1701.6	1694.3	1696.8	1705.4	1694.3
175°	1707.8	1699.1	1701.6	1710.2	1697.9
177.5°	1710.2	1701.6	1702.9	1711.5	1700.4
180°	1704.0	1704.0	1704.0	1704.0	1704.0

TEST NUMBER: P908895

CATALOG NUMBER: DFN2DIP-PN4F0-120D050US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.14	14.14	13.94	14.95	15.96	9.11	10.10	9.91	10.92	11.92
	3H	14.84	15.73	15.65	16.55	17.58	10.31	11.20	11.12	12.03	13.06
	4H	15.45	16.29	16.28	17.13	18.17	10.77	11.61	11.60	12.44	13.48
	6H	15.89	16.66	16.73	17.50	18.56	11.10	11.87	11.94	12.71	13.77
	8H	16.02	16.75	16.87	17.61	18.67	11.19	11.93	12.04	12.79	13.85
	12H	16.09	16.79	16.94	17.64	18.72	11.24	11.94	12.10	12.80	13.88
4H	2H	13.18	14.02	14.02	14.85	15.90	9.72	10.56	10.56	11.40	12.44
	3H	15.03	15.72	15.87	16.59	17.65	11.09	11.79	11.94	12.66	13.71
	4H	15.73	16.36	16.59	17.23	18.31	11.65	12.28	12.50	13.14	14.23
	6H	16.26	16.80	17.13	17.69	18.78	12.07	12.62	12.95	13.51	14.60
	8H	16.44	16.95	17.31	17.83	18.93	12.21	12.72	13.08	13.60	14.70
	12H	16.54	17.00	17.44	17.90	19.01	12.28	12.74	13.18	13.64	14.75
8H	4H	15.71	16.22	16.59	17.10	18.21	11.94	12.45	12.82	13.33	14.44
	6H	16.28	16.71	17.19	17.63	18.73	12.46	12.89	13.37	13.81	14.91
	8H	16.50	16.88	17.42	17.80	18.92	12.66	13.03	13.57	13.95	15.07
	12H	16.65	16.98	17.57	17.89	19.06	12.78	13.11	13.70	14.02	15.20
12H	4H	15.67	16.13	16.56	17.03	18.14	11.95	12.41	12.85	13.31	14.42
	6H	16.26	16.63	17.17	17.55	18.67	12.52	12.89	13.43	13.81	14.93
	8H	16.49	16.82	17.41	17.73	18.90	12.73	13.06	13.65	13.97	15.15