

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919612

Luminaire Tested: DFN2DIP-PN4F0-060D110US935-FLLFLL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P919612  
REPORT IS A COMBINATION OF REPORTS P899739 AND P896497  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-060D110US935-FLLFLL  
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13496.1 lumens  
Efficiency: N/A  
Efficacy: 92.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: Semi-Indirect

Input Watts (W): 146.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9933  
Total Harmonic Distortion (THDi): 0.066  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P919612  
CATALOG NUMBER: DFN2DIP-PN4F0-060D110US935-FLLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P919612

CATALOG NUMBER: DFN2DIP-PN4F0-060D110US935-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				38
1	95	91	87	84	86	83	79	76	67	65	63	53	51	50	40	39	38	32				32
2	87	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32	27				27
3	79	70	62	57	71	63	57	52	52	47	44	41	38	35	31	29	27	23				23
4	72	62	54	48	65	56	49	44	46	41	37	37	33	30	28	25	23	19				19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17				17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15				15
7	56	44	36	31	51	41	34	29	33	28	24	27	23	20	21	18	16	13				13
8	52	40	32	27	47	37	30	25	30	25	22	25	21	18	19	16	14	12				12
9	48	37	29	24	44	34	27	23	28	23	19	23	19	16	17	15	13	11				11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	14	12	10				10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1467	1467	1467
5°	1470	1447	1457
10°	1458	1428	1437
15°	1436	1404	1407
20°	1407	1372	1376
25°	1379	1333	1339
30°	1342	1297	1293
35°	1308	1254	1244
40°	1266	1211	1198
45°	1224	1168	1151
50°	1178	1123	1096
55°	1130	1070	1045
60°	1076	1008	987
65°	1016	944	919
70°	941	865	846
75°	836	771	778
80°	711	652	649
85°	513	444	434

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 2346 cd/sqm



TEST NUMBER: P919612

CATALOG NUMBER: DFN2DIP-PN4F0-060D110US935-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.2	1.4
10°-20°	532.3	3.9
20°-30°	782.3	5.8
30°-40°	908.6	6.7
40°-50°	907.5	6.7
50°-60°	791.3	5.9
60°-70°	584.9	4.3
70°-80°	330.9	2.5
80°-90°	95.9	0.7
90°-100°	185.3	1.4
100°-110°	588.9	4.4
110°-120°	1007.8	7.5
120°-130°	1325.4	9.8
130°-140°	1487.7	11.0
140°-150°	1458.9	10.8
150°-160°	1223.8	9.1
160°-170°	811.6	6.0
170°-180°	283.7	2.1
0°-30°	1503.8	11.1
0°-40°	2412.4	17.9
0°-60°	4111.1	30.5
0°-90°	5122.8	38.0
90°-120°	1782.1	13.2
90°-150°	6054.2	44.9
90°-180°	8373.0	62.0
0°-180°	13496.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2010	2010	2010	2010	2010	
5°	2010	2002	1981	1997	1993	191
15°	1914	1902	1877	1885	1875	539
25°	1732	1716	1684	1687	1684	797
35°	1494	1475	1444	1432	1422	933
45°	1216	1202	1173	1152	1144	938
55°	920	908	885	862	852	823
65°	620	609	590	572	562	614
75°	325	321	311	300	304	347
85°	79	77	75	70	68	88
90°	3	32	88	83	86	13
95°	132	157	162	162	157	147
105°	544	551	556	561	561	574
115°	1011	1026	1021	1019	1011	1000
125°	1471	1494	1486	1478	1476	1315
135°	1903	1931	1936	1933	1926	1471
145°	2310	2328	2342	2345	2335	1443
155°	2641	2648	2657	2669	2661	1216
165°	2873	2871	2871	2889	2876	811
175°	2990	2983	2977	2995	2980	284
180°	2995	2995	2995	2995	2995	



TEST NUMBER: P919612

CATALOG NUMBER: DFN2DIP-PN4F0-060D110US935-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2010.1	2010.1	2010.1	2010.1	2010.1
2.5°	2021.8	2012.2	1990.8	2010.1	2006.4
5°	2010.1	2002.5	1981.2	1996.6	1992.9
7.5°	1996.6	1985.1	1963.8	1979.3	1975.5
10°	1975.5	1962.0	1938.7	1954.1	1948.4
12.5°	1946.4	1934.8	1911.7	1921.3	1917.4
15°	1913.5	1902.0	1876.8	1884.6	1875.0
17.5°	1872.9	1861.5	1836.3	1845.8	1836.3
20°	1828.4	1817.0	1789.8	1795.6	1788.0
22.5°	1784.2	1766.7	1741.5	1741.5	1737.6
25°	1731.8	1716.5	1683.6	1687.3	1683.6
27.5°	1673.8	1660.3	1635.2	1629.5	1619.9
30°	1616.0	1600.3	1571.5	1565.7	1557.9
32.5°	1554.0	1542.6	1511.6	1499.9	1492.1
35°	1494.2	1474.9	1443.9	1432.2	1422.5
37.5°	1426.5	1409.0	1378.1	1364.5	1354.9
40°	1356.9	1341.3	1310.4	1293.2	1285.4
42.5°	1289.3	1273.7	1242.9	1223.5	1211.9
45°	1215.9	1202.3	1173.2	1152.1	1144.3
47.5°	1144.3	1130.7	1099.8	1078.5	1066.9
50°	1068.8	1059.2	1032.2	1005.0	995.4
52.5°	995.4	981.9	956.8	935.6	922.0
55°	920.1	908.4	885.3	862.1	852.5
57.5°	844.7	835.1	809.9	786.7	778.9
60°	769.2	761.6	734.6	713.3	707.5
62.5°	695.8	682.3	663.0	643.7	635.9
65°	620.5	608.9	589.6	572.1	562.5
67.5°	543.2	533.4	516.2	502.7	494.8
70°	471.7	463.9	446.4	432.9	425.3
72.5°	398.2	390.5	380.8	367.3	361.5
75°	324.6	321.0	311.1	299.6	303.5
77.5°	259.0	251.2	247.3	241.6	235.8
80°	193.4	191.3	187.4	181.7	177.8
82.5°	131.5	131.5	129.6	121.8	121.8
85°	79.1	77.3	75.4	69.5	67.7
87.5°	34.9	31.0	27.0	21.4	19.3
90°	2.7	32.5	88.5	83.1	85.8
92.5°	56.0	75.9	78.5	81.3	81.3
95°	131.8	157.1	161.6	161.6	157.1
97.5°	219.5	242.9	252.9	252.9	252.9
100°	320.5	341.3	348.5	348.5	345.9
102.5°	427.1	442.5	452.5	455.1	452.5
105°	543.6	550.9	556.3	560.8	560.8
107.5°	659.2	670.0	670.0	671.8	659.2
110°	771.2	785.7	785.7	785.7	778.4



TEST NUMBER: P919612

CATALOG NUMBER: DFN2DIP-PN4F0-060D110US935-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	892.2	907.5	904.8	897.6	892.2
115°	1011.4	1025.8	1021.3	1018.6	1011.4
117.5°	1129.7	1149.5	1136.9	1129.7	1122.5
120°	1248.9	1268.8	1248.9	1248.9	1240.8
122.5°	1357.3	1382.5	1369.8	1362.6	1357.3
125°	1471.0	1493.6	1486.3	1478.2	1475.5
127.5°	1582.1	1610.1	1600.2	1589.3	1582.1
130°	1685.9	1718.5	1713.9	1708.5	1698.6
132.5°	1802.4	1827.7	1829.5	1816.9	1809.6
135°	1902.6	1930.6	1936.0	1933.4	1926.1
137.5°	2014.6	2037.2	2041.7	2039.9	2029.1
140°	2113.1	2135.6	2148.3	2148.3	2138.4
142.5°	2214.2	2236.8	2244.0	2246.7	2236.8
145°	2309.9	2328.0	2342.4	2345.1	2335.2
147.5°	2395.7	2418.3	2429.1	2433.6	2423.7
150°	2484.2	2499.6	2509.5	2517.6	2509.5
152.5°	2562.8	2578.1	2590.7	2600.7	2590.7
155°	2641.4	2648.5	2656.7	2669.4	2661.2
157.5°	2709.0	2714.5	2718.9	2737.0	2724.4
160°	2769.6	2775.0	2777.7	2793.1	2782.2
162.5°	2825.5	2825.5	2828.3	2845.4	2832.8
165°	2873.4	2870.7	2870.7	2888.7	2876.1
167.5°	2916.7	2908.6	2908.6	2926.7	2914.0
170°	2949.3	2942.0	2939.4	2957.4	2942.0
172.5°	2971.8	2964.6	2961.9	2980.0	2964.6
175°	2989.9	2982.7	2977.2	2995.3	2980.0
177.5°	2999.8	2992.6	2987.1	3002.6	2987.1
180°	2995.3	2995.3	2995.3	2995.3	2995.3



TEST NUMBER: P919612  
 CATALOG NUMBER: DFN2DIP-PN4F0-060D110US935-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.38	8.14	8.44	9.20	10.64	6.94	7.70	8.00	8.76	10.20
	3H	9.04	9.72	10.10	10.79	12.24	8.55	9.24	9.62	10.30	11.75
	4H	9.62	10.27	10.70	11.34	12.80	9.13	9.78	10.21	10.85	12.31
	6H	10.02	10.62	11.10	11.69	13.16	9.53	10.12	10.61	11.20	12.67
	8H	10.12	10.69	11.21	11.78	13.24	9.63	10.20	10.72	11.29	12.75
	12H	10.17	10.71	11.26	11.79	13.28	9.67	10.21	10.76	11.29	12.78
4H	2H	7.83	8.48	8.91	9.55	11.01	7.48	8.13	8.56	9.20	10.65
	3H	9.69	10.23	10.78	11.33	12.80	9.29	9.83	10.38	10.92	12.40
	4H	10.40	10.90	11.50	11.99	13.48	9.99	10.48	11.08	11.57	13.06
	6H	10.92	11.34	12.02	12.45	13.94	10.49	10.92	11.59	12.03	13.51
	8H	11.06	11.46	12.17	12.56	14.07	10.64	11.03	11.74	12.13	13.64
	12H	11.13	11.49	12.25	12.61	14.12	10.69	11.05	11.81	12.17	13.68
8H	4H	10.59	10.99	11.69	12.09	13.59	10.22	10.62	11.32	11.72	13.22
	6H	11.22	11.55	12.35	12.69	14.19	10.85	11.17	11.97	12.32	13.82
	8H	11.44	11.73	12.57	12.86	14.38	11.06	11.35	12.19	12.47	13.99
	12H	11.57	11.83	12.71	12.95	14.50	11.17	11.42	12.31	12.54	14.10
12H	4H	10.57	10.93	11.69	12.05	13.55	10.21	10.57	11.33	11.68	13.19
	6H	11.25	11.54	12.38	12.66	14.18	10.89	11.17	12.02	12.30	13.82
	8H	11.49	11.74	12.63	12.87	14.42	11.12	11.37	12.25	12.49	14.05