

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911359

Luminaire Tested: DFN2DIP-PN4F0-040D110US850-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911359
REPORT IS A COMBINATION OF REPORTS P901256 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-040D110US850-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15847.6 lumens
Efficiency: N/A
Efficacy: 126.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 125
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911359

CATALOG NUMBER: DFN2DIP-PN4F0-040D110US850-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P911359

CATALOG NUMBER: DFN2DIP-PN4F0-040D110US850-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	27
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	25	24	23
3	77	68	61	56	68	61	55	50	47	43	40	34	32	30	23	21	20
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	20	19	18
5	64	53	46	40	57	48	41	37	37	33	29	28	25	22	19	17	15
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	30	26	22	23	20	17	15	14	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	36	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	32	26	21	39	29	23	19	23	19	16	18	15	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1338	1338	1338
5°	1340	1317	1326
10°	1327	1292	1283
15°	1309	1249	1216
20°	1285	1190	1135
25°	1260	1125	1056
30°	1227	1057	956
35°	1194	985	868
40°	1161	909	767
45°	1123	826	676
50°	1083	742	586
55°	1041	652	500
60°	993	558	412
65°	938	462	371
70°	871	373	336
75°	786	329	307
80°	664	276	267
85°	463	186	202

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2195 cd/sqm

TEST NUMBER: P911359

CATALOG NUMBER: DFN2DIP-PN4F0-040D110US850-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.8	1.1
10°-20°	471.7	3.0
20°-30°	662.3	4.2
30°-40°	721.9	4.6
40°-50°	663.5	4.2
50°-60°	521.1	3.3
60°-70°	339.2	2.1
70°-80°	174.6	1.1
80°-90°	51.8	0.3
90°-100°	135.7	0.9
100°-110°	506.1	3.2
110°-120°	1342.2	8.5
120°-130°	2226.1	14.0
130°-140°	2364.7	14.9
140°-150°	2197.7	13.9
150°-160°	1766.9	11.1
160°-170°	1138.5	7.2
170°-180°	391.9	2.5
0°-30°	1305.8	8.2
0°-40°	2027.7	12.8
0°-60°	3212.2	20.3
0°-90°	3777.8	23.8
90°-120°	1984.0	12.5
90°-150°	8772.5	55.4
90°-180°	12070.0	76.2
0°-180°	15847.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1833	1833	1833	1833	1833	
5°	1833	1825	1804	1818	1814	174
15°	1744	1726	1669	1638	1621	491
25°	1583	1530	1420	1352	1327	728
35°	1364	1279	1133	1029	992	854
45°	1115	1004	830	712	672	861
55°	848	718	539	440	408	758
65°	572	438	289	232	227	568
75°	305	189	133	121	120	323
85°	71	36	32	32	32	82
90°	3	36	59	75	80	15
95°	194	95	116	131	128	229
105°	906	995	182	214	226	968
115°	1713	1763	1838	459	244	1686
125°	2422	2461	2517	2538	2547	2160
135°	2997	3045	3071	3101	3095	2315
145°	3477	3474	3524	3545	3530	2174
155°	3828	3801	3837	3855	3831	1764
165°	4034	4016	4025	4046	4025	1140
175°	4126	4105	4111	4132	4102	393
180°	4117	4117	4117	4117	4117	

TEST NUMBER: P911359

CATALOG NUMBER: DFN2DIP-PN4F0-040D110US850-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1833.4	1833.4	1833.4	1833.4	1833.4
2.5°	1841.7	1833.4	1815.1	1831.8	1828.4
5°	1833.4	1825.1	1803.5	1818.4	1813.5
7.5°	1818.4	1808.6	1785.4	1791.8	1783.6
10°	1798.6	1786.9	1753.8	1748.7	1738.9
12.5°	1773.7	1758.8	1713.8	1704.0	1685.7
15°	1743.8	1725.5	1669.2	1637.7	1621.1
17.5°	1709.0	1682.4	1612.6	1576.2	1549.6
20°	1669.2	1635.9	1552.9	1511.6	1475.0
22.5°	1626.0	1587.9	1491.5	1435.2	1410.4
25°	1582.9	1529.8	1420.2	1352.3	1327.3
27.5°	1531.5	1475.0	1353.9	1275.9	1237.6
30°	1476.7	1413.5	1280.8	1196.3	1151.5
32.5°	1423.6	1347.2	1211.2	1111.7	1070.1
35°	1364.0	1279.2	1133.3	1028.7	992.1
37.5°	1305.8	1214.5	1060.2	945.6	904.3
40°	1244.4	1144.9	983.9	866.1	823.0
42.5°	1181.3	1075.2	907.6	784.7	743.4
45°	1115.0	1003.8	829.6	711.8	671.9
47.5°	1052.0	934.2	755.0	637.1	600.6
50°	982.2	864.5	681.9	567.4	532.7
52.5°	914.1	789.7	612.3	502.7	471.2
55°	847.8	718.4	539.2	439.7	408.2
57.5°	779.8	647.1	474.5	381.6	355.1
60°	710.1	577.3	406.4	321.9	295.4
62.5°	642.2	509.5	348.3	268.8	255.6
65°	572.5	437.9	288.7	232.3	227.2
67.5°	506.1	371.6	232.3	204.1	199.1
70°	436.4	307.0	192.4	175.9	169.1
72.5°	370.1	247.2	160.9	147.7	144.4
75°	305.2	189.1	132.7	121.1	119.6
77.5°	240.7	134.3	104.6	97.9	94.5
80°	180.8	96.3	79.5	73.1	73.1
82.5°	126.1	64.8	54.8	51.3	51.3
85°	71.3	36.5	31.5	31.5	31.5
87.5°	26.6	13.2	13.2	11.6	11.6
90°	2.9	35.7	59.4	74.6	80.3
92.5°	74.6	62.7	71.4	77.5	80.3
95°	193.5	95.2	116.0	131.2	128.1
97.5°	348.4	104.4	151.7	160.9	163.8
100°	527.4	119.2	169.8	193.5	199.5
102.5°	723.7	718.1	175.8	208.4	217.6
105°	905.6	995.1	181.9	214.4	226.5
107.5°	1117.2	1191.4	187.9	220.4	232.4
110°	1319.8	1382.1	521.5	223.6	235.2

TEST NUMBER: P911359

CATALOG NUMBER: DFN2DIP-PN4F0-040D110US850-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1510.6	1563.9	1513.3	229.2	238.4
115°	1712.9	1763.4	1838.2	458.8	244.4
117.5°	1888.7	1948.2	1999.1	1572.8	792.4
120°	2085.4	2129.9	2183.7	2219.4	1817.2
122.5°	2252.0	2299.7	2359.5	2377.3	2380.5
125°	2421.8	2460.8	2517.3	2538.2	2547.0
127.5°	2576.8	2618.5	2663.4	2693.1	2696.0
130°	2722.8	2770.6	2803.1	2836.0	2833.3
132.5°	2871.8	2910.7	2943.3	2970.1	2967.4
135°	2997.1	3044.8	3071.3	3101.4	3095.3
137.5°	3127.9	3163.6	3193.7	3223.4	3214.5
140°	3256.0	3280.0	3312.6	3339.4	3324.6
142.5°	3363.5	3384.3	3422.9	3446.7	3431.8
145°	3476.7	3473.5	3524.1	3545.0	3530.2
147.5°	3574.8	3565.9	3616.4	3631.3	3619.7
150°	3670.2	3649.4	3697.1	3714.8	3700.0
152.5°	3750.5	3726.8	3771.4	3789.5	3768.6
155°	3828.0	3801.4	3837.1	3854.9	3831.2
157.5°	3890.6	3866.9	3893.8	3914.7	3890.6
160°	3944.4	3926.3	3944.4	3962.0	3941.2
162.5°	3991.7	3974.1	3989.0	4009.8	3983.0
165°	4033.5	4015.8	4024.7	4045.5	4024.7
167.5°	4066.4	4048.4	4057.6	4078.5	4051.6
170°	4093.3	4075.2	4081.2	4102.2	4075.2
172.5°	4111.0	4093.3	4099.3	4120.2	4093.3
175°	4125.8	4105.0	4111.0	4131.9	4102.2
177.5°	4131.9	4111.0	4114.2	4135.0	4108.2
180°	4117.1	4117.1	4117.1	4117.1	4117.1

TEST NUMBER: P911359

CATALOG NUMBER: DFN2DIP-PN4F0-040D110US850-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.01	5.66	6.16	6.80	8.40	0.97	1.62	2.13	2.77	4.37
	3H	6.67	7.26	7.84	8.41	10.02	2.15	2.73	3.31	3.88	5.50
	4H	7.27	7.83	8.45	8.98	10.60	2.59	3.14	3.76	4.29	5.92
	6H	7.69	8.20	8.87	9.35	10.99	2.90	3.41	4.08	4.56	6.20
	8H	7.81	8.30	9.00	9.46	11.09	2.99	3.47	4.17	4.64	6.26
	12H	7.87	8.33	9.06	9.49	11.14	3.03	3.49	4.21	4.65	6.29
4H	2H	5.00	5.56	6.18	6.71	8.33	1.54	2.10	2.73	3.25	4.87
	3H	6.82	7.28	8.00	8.46	10.09	2.88	3.34	4.07	4.52	6.15
	4H	7.51	7.93	8.69	9.09	10.75	3.42	3.85	4.61	5.01	6.66
	6H	8.01	8.38	9.20	9.56	11.21	3.83	4.20	5.02	5.38	7.03
	8H	8.19	8.53	9.38	9.70	11.36	3.96	4.30	5.15	5.48	7.13
	12H	8.28	8.58	9.48	9.77	11.44	4.02	4.32	5.22	5.51	7.18
8H	4H	7.46	7.80	8.65	8.98	10.64	3.69	4.03	4.88	5.21	6.87
	6H	8.02	8.30	9.23	9.52	11.18	4.20	4.48	5.41	5.70	7.36
	8H	8.24	8.48	9.45	9.68	11.36	4.40	4.64	5.61	5.83	7.51
	12H	8.37	8.59	9.59	9.78	11.49	4.51	4.72	5.72	5.91	7.62
12H	4H	7.40	7.71	8.61	8.90	10.56	3.69	4.00	4.89	5.18	6.85
	6H	8.00	8.24	9.21	9.44	11.11	4.25	4.50	5.47	5.69	7.37
	8H	8.21	8.43	9.43	9.62	11.33	4.46	4.67	5.67	5.87	7.57

END OF REPORT