

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919687

Luminaire Tested: DFN2DIP-PN4F0-080D110US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919687
REPORT IS A COMBINATION OF REPORTS P901264 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-080D110US935-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15231.0 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 168.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919687

CATALOG NUMBER: DFN2DIP-PN4F0-080D110US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P919687

CATALOG NUMBER: DFN2DIP-PN4F0-080D110US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39
2	87	80	74	70	79	73	68	64	60	56	53	48	45	43	36	35	34
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	33	31	29
4	73	63	55	50	66	58	51	46	47	43	39	38	35	32	29	27	25
5	67	56	48	43	61	51	45	40	43	38	34	34	31	28	27	24	22
6	62	50	43	37	56	46	39	35	38	33	30	31	27	25	24	22	20
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18
8	53	41	34	29	48	38	32	27	32	27	23	26	22	20	20	18	16
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2078	2078	2078
5°	2081	2045	2059
10°	2061	2006	1992
15°	2032	1939	1889
20°	1995	1848	1762
25°	1956	1746	1640
30°	1905	1641	1484
35°	1854	1529	1348
40°	1803	1412	1191
45°	1743	1283	1049
50°	1681	1152	910
55°	1617	1012	777
60°	1542	866	640
65°	1456	717	576
70°	1352	579	522
75°	1221	511	476
80°	1031	430	414
85°	719	288	314

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1743 cd/sqm

TEST NUMBER: P919687

CATALOG NUMBER: DFN2DIP-PN4F0-080D110US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.8	1.8
10°-20°	732.4	4.8
20°-30°	1028.3	6.8
30°-40°	1120.9	7.4
40°-50°	1030.3	6.8
50°-60°	809.1	5.3
60°-70°	526.6	3.5
70°-80°	271.1	1.8
80°-90°	74.8	0.5
90°-100°	105.4	0.7
100°-110°	392.9	2.6
110°-120°	1042.0	6.8
120°-130°	1728.3	11.3
130°-140°	1835.9	12.1
140°-150°	1706.2	11.2
150°-160°	1371.8	9.0
160°-170°	883.9	5.8
170°-180°	304.2	2.0
0°-30°	2027.6	13.3
0°-40°	3148.5	20.7
0°-60°	4987.8	32.7
0°-90°	5860.4	38.5
90°-120°	1540.3	10.1
90°-150°	6810.7	44.7
90°-180°	9371.0	61.5
0°-180°	15231.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2847	2847	2847	2847	2847	
5°	2847	2834	2800	2824	2816	270
15°	2708	2679	2592	2543	2517	763
25°	2458	2375	2205	2100	2061	1130
35°	2118	1986	1760	1597	1540	1326
45°	1731	1559	1288	1105	1043	1337
55°	1316	1116	837	683	634	1176
65°	889	680	448	361	353	881
75°	474	294	206	188	186	501
85°	111	57	49	49	49	127
90°	2	28	46	58	62	14
95°	150	74	90	102	99	178
105°	703	773	141	166	176	751
115°	1330	1369	1427	356	190	1309
125°	1880	1910	1954	1971	1978	1677
135°	2327	2364	2384	2408	2403	1797
145°	2699	2697	2736	2752	2741	1688
155°	2972	2951	2979	2993	2974	1370
165°	3132	3118	3125	3141	3125	885
175°	3203	3187	3192	3208	3185	305
180°	3196	3196	3196	3196	3196	

TEST NUMBER: P919687

CATALOG NUMBER: DFN2DIP-PN4F0-080D110US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2846.8	2846.8	2846.8	2846.8	2846.8
2.5°	2859.6	2846.8	2818.4	2844.3	2839.1
5°	2846.8	2834.0	2800.3	2823.6	2815.9
7.5°	2823.6	2808.2	2772.2	2782.3	2769.4
10°	2792.6	2774.7	2723.3	2715.3	2700.0
12.5°	2754.2	2730.9	2661.2	2645.8	2617.4
15°	2707.7	2679.3	2591.8	2542.9	2517.1
17.5°	2653.5	2612.3	2504.0	2447.5	2406.1
20°	2591.8	2540.1	2411.4	2347.2	2290.3
22.5°	2524.8	2465.5	2316.0	2228.5	2189.9
25°	2457.8	2375.3	2205.3	2099.8	2061.0
27.5°	2378.0	2290.3	2102.2	1981.2	1921.8
30°	2293.0	2194.9	1988.8	1857.6	1787.9
32.5°	2210.4	2091.9	1880.8	1726.1	1661.6
35°	2117.8	1986.3	1759.7	1597.4	1540.5
37.5°	2027.6	1885.8	1646.3	1468.3	1404.1
40°	1932.3	1777.8	1527.7	1344.8	1277.8
42.5°	1834.4	1669.6	1409.3	1218.6	1154.3
45°	1731.3	1558.6	1288.2	1105.1	1043.4
47.5°	1633.5	1450.6	1172.3	989.2	932.6
50°	1525.2	1342.4	1058.9	881.0	827.1
52.5°	1419.4	1226.1	950.6	780.7	731.8
55°	1316.4	1115.5	837.2	682.8	633.9
57.5°	1210.9	1004.8	736.9	592.6	551.3
60°	1102.6	896.6	631.1	499.9	458.7
62.5°	997.1	791.0	541.0	417.4	396.9
65°	888.9	680.0	448.2	360.8	352.8
67.5°	785.8	577.0	360.8	316.8	309.2
70°	677.6	476.7	298.8	273.0	262.7
72.5°	574.5	383.7	249.9	229.4	224.1
75°	474.0	293.6	206.1	188.0	185.6
77.5°	373.7	208.5	162.4	152.0	146.8
80°	280.7	149.6	123.6	113.4	113.4
82.5°	195.7	100.6	85.0	79.8	79.8
85°	110.7	56.6	48.9	48.9	48.9
87.5°	41.2	20.5	20.5	18.1	18.1
90°	2.2	27.7	46.1	57.9	62.3
92.5°	57.9	48.6	55.4	60.2	62.3
95°	150.2	73.9	90.1	101.9	99.4
97.5°	270.5	81.0	117.8	124.9	127.2
100°	409.5	92.6	131.8	150.2	154.9
102.5°	561.9	557.5	136.5	161.8	168.9
105°	703.1	772.6	141.2	166.4	175.8
107.5°	867.4	925.0	145.9	171.1	180.5
110°	1024.7	1073.1	404.8	173.6	182.6

TEST NUMBER: P919687

CATALOG NUMBER: DFN2DIP-PN4F0-080D110US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1172.8	1214.2	1174.9	178.0	185.1
115°	1329.8	1369.1	1427.1	356.2	189.8
117.5°	1466.4	1512.5	1552.0	1221.1	615.2
120°	1619.0	1653.6	1695.4	1723.1	1410.8
122.5°	1748.4	1785.5	1831.9	1845.6	1848.1
125°	1880.2	1910.5	1954.4	1970.6	1977.5
127.5°	2000.5	2032.9	2067.8	2090.8	2093.1
130°	2113.9	2151.0	2176.3	2201.8	2199.7
132.5°	2229.6	2259.8	2285.1	2305.9	2303.8
135°	2326.8	2363.9	2384.4	2407.9	2403.1
137.5°	2428.4	2456.2	2479.5	2502.6	2495.7
140°	2527.9	2546.5	2571.8	2592.6	2581.1
142.5°	2611.3	2627.5	2657.5	2675.9	2664.4
145°	2699.2	2696.7	2736.0	2752.3	2740.7
147.5°	2775.3	2768.5	2807.7	2819.3	2810.2
150°	2849.5	2833.3	2870.3	2884.1	2872.5
152.5°	2911.8	2893.4	2928.0	2942.0	2925.8
155°	2972.0	2951.3	2979.1	2992.8	2974.4
157.5°	3020.6	3002.1	3023.0	3039.2	3020.6
160°	3062.3	3048.3	3062.3	3076.0	3059.8
162.5°	3099.1	3085.4	3096.9	3113.1	3092.3
165°	3131.5	3117.8	3124.6	3140.8	3124.6
167.5°	3157.0	3143.1	3150.2	3166.4	3145.6
170°	3177.9	3163.9	3168.6	3184.8	3163.9
172.5°	3191.6	3177.9	3182.6	3198.8	3177.9
175°	3203.2	3187.0	3191.6	3207.9	3184.8
177.5°	3207.9	3191.6	3194.1	3210.3	3189.5
180°	3196.4	3196.4	3196.4	3196.4	3196.4

TEST NUMBER: P919687

CATALOG NUMBER: DFN2DIP-PN4F0-080D110US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.52	9.26	9.57	10.32	11.74	4.48	5.22	5.54	6.28	7.71
	3H	10.19	10.85	11.25	11.92	13.37	5.66	6.33	6.73	7.39	8.84
	4H	10.80	11.43	11.87	12.49	13.95	6.11	6.74	7.19	7.81	9.26
	6H	11.22	11.79	12.30	12.86	14.33	6.43	7.01	7.51	8.08	9.54
	8H	11.34	11.89	12.43	12.98	14.44	6.52	7.07	7.61	8.15	9.61
	12H	11.40	11.92	12.50	13.00	14.49	6.56	7.08	7.65	8.16	9.64
4H	2H	8.52	9.15	9.61	10.22	11.67	5.07	5.70	6.15	6.76	8.22
	3H	10.35	10.87	11.44	11.97	13.43	6.41	6.93	7.50	8.03	9.49
	4H	11.04	11.52	12.13	12.60	14.09	6.95	7.44	8.05	8.52	10.01
	6H	11.55	11.96	12.65	13.07	14.55	7.37	7.78	8.47	8.89	10.37
	8H	11.73	12.11	12.83	13.21	14.71	7.50	7.88	8.60	8.98	10.48
	12H	11.82	12.17	12.94	13.28	14.78	7.56	7.91	8.68	9.02	10.52
8H	4H	11.00	11.38	12.10	12.48	13.98	7.23	7.61	8.33	8.71	10.21
	6H	11.57	11.88	12.69	13.02	14.52	7.75	8.06	8.87	9.21	10.70
	8H	11.78	12.06	12.92	13.18	14.70	7.94	8.22	9.07	9.34	10.85
	12H	11.92	12.17	13.06	13.28	14.84	8.05	8.30	9.19	9.42	10.97
12H	4H	10.95	11.30	12.07	12.41	13.91	7.23	7.58	8.35	8.69	10.19
	6H	11.54	11.82	12.67	12.94	14.46	7.80	8.07	8.93	9.20	10.71
	8H	11.76	12.00	12.89	13.12	14.67	8.00	8.25	9.14	9.37	10.92