

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919710

Luminaire Tested: DFN2DIP-PN4F0-090D080US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919710
REPORT IS A COMBINATION OF REPORTS P899692 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-090D080US935-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12682.5 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 146.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919710

CATALOG NUMBER: DFN2DIP-PN4F0-090D080US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P919710

CATALOG NUMBER: DFN2DIP-PN4F0-090D080US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	84	84	84	71	71	71	58	58	58
1	99	95	91	88	91	88	84	82	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43
3	83	74	66	61	76	68	62	57	59	54	50	50	46	44	42	39	37
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	37	35	32
5	70	59	51	45	65	55	48	42	47	42	38	40	36	33	34	31	28
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25
7	60	48	40	35	55	45	38	33	39	33	29	34	29	26	28	25	23
8	56	44	36	31	51	41	34	29	36	30	26	31	27	23	26	23	21
9	52	40	33	28	48	37	31	26	33	27	24	28	24	21	24	21	19
10	49	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2338	2338	2338
5°	2342	2301	2316
10°	2318	2256	2241
15°	2286	2182	2125
20°	2244	2079	1982
25°	2201	1964	1844
30°	2143	1847	1670
35°	2086	1720	1516
40°	2028	1589	1340
45°	1961	1443	1180
50°	1891	1296	1024
55°	1819	1139	874
60°	1735	975	720
65°	1638	807	649
70°	1521	651	588
75°	1374	575	536
80°	1160	483	466
85°	808	324	353

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1961 cd/sqm

TEST NUMBER: P919710

CATALOG NUMBER: DFN2DIP-PN4F0-090D080US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.2	2.4
10°-20°	824.0	6.5
20°-30°	1156.9	9.1
30°-40°	1261.0	9.9
40°-50°	1159.0	9.1
50°-60°	910.3	7.2
60°-70°	592.5	4.7
70°-80°	305.0	2.4
80°-90°	84.0	0.7
90°-100°	134.8	1.1
100°-110°	428.3	3.4
110°-120°	733.0	5.8
120°-130°	964.0	7.6
130°-140°	1082.0	8.5
140°-150°	1061.0	8.4
150°-160°	890.1	7.0
160°-170°	590.3	4.7
170°-180°	206.3	1.6
0°-30°	2281.0	18.0
0°-40°	3542.0	27.9
0°-60°	5611.3	44.2
0°-90°	6592.8	52.0
90°-120°	1296.1	10.2
90°-150°	4403.1	34.7
90°-180°	6090.0	48.0
0°-180°	12682.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3203	3203	3203	3203	3203	
5°	3203	3188	3150	3176	3168	304
15°	3046	3014	2916	2861	2832	858
25°	2765	2672	2481	2362	2319	1272
35°	2383	2235	1980	1797	1733	1491
45°	1948	1753	1449	1243	1174	1504
55°	1481	1255	942	768	713	1323
65°	1000	765	504	406	397	991
75°	533	330	232	212	209	564
85°	124	64	55	55	55	143
90°	2	24	64	60	62	12
95°	96	114	118	118	114	107
105°	395	401	405	408	408	417
115°	736	746	743	741	736	728
125°	1070	1086	1081	1075	1073	956
135°	1384	1404	1408	1406	1401	1070
145°	1680	1693	1704	1706	1698	1050
155°	1921	1926	1932	1941	1935	884
165°	2090	2088	2088	2101	2092	590
175°	2174	2169	2165	2178	2167	207
180°	2178	2178	2178	2178	2178	

TEST NUMBER: P919710

CATALOG NUMBER: DFN2DIP-PN4F0-090D080US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3202.7	3202.7	3202.7	3202.7	3202.7
2.5°	3217.1	3202.7	3170.6	3199.9	3194.0
5°	3202.7	3188.2	3150.4	3176.5	3167.9
7.5°	3176.5	3159.3	3118.7	3130.1	3115.6
10°	3141.8	3121.5	3063.7	3054.7	3037.5
12.5°	3098.4	3072.3	2993.9	2976.6	2944.6
15°	3046.1	3014.2	2915.8	2860.7	2831.8
17.5°	2985.3	2938.8	2817.0	2753.4	2707.0
20°	2915.8	2857.7	2712.7	2640.5	2576.5
22.5°	2840.4	2773.7	2605.5	2507.1	2463.7
25°	2765.1	2672.2	2481.0	2362.2	2318.6
27.5°	2675.3	2576.5	2365.0	2228.8	2162.1
30°	2579.6	2469.3	2237.4	2089.8	2011.4
32.5°	2486.7	2353.3	2115.9	1941.9	1869.3
35°	2382.6	2234.6	1979.7	1797.1	1733.1
37.5°	2281.0	2121.5	1852.1	1651.9	1579.7
40°	2173.8	2000.0	1718.6	1512.9	1437.6
42.5°	2063.6	1878.3	1585.4	1370.9	1298.6
45°	1947.7	1753.4	1449.2	1243.2	1173.7
47.5°	1837.6	1631.9	1318.9	1112.8	1049.2
50°	1715.9	1510.1	1191.3	991.1	930.5
52.5°	1596.9	1379.5	1069.5	878.2	823.2
55°	1480.9	1254.9	941.8	768.2	713.1
57.5°	1362.3	1130.4	829.1	666.7	620.3
60°	1240.4	1008.6	710.1	562.4	516.0
62.5°	1121.8	889.9	608.6	469.6	446.5
65°	1000.0	765.1	504.3	405.9	397.0
67.5°	884.1	649.1	405.9	356.4	347.8
70°	762.3	536.3	336.1	307.2	295.5
72.5°	646.4	431.7	281.0	258.0	252.2
75°	533.2	330.3	231.9	211.5	208.8
77.5°	420.3	234.6	182.6	171.0	165.1
80°	315.8	168.2	139.0	127.6	127.6
82.5°	220.2	113.1	95.7	89.8	89.8
85°	124.5	63.6	55.0	55.0	55.0
87.5°	46.4	23.1	23.1	20.3	20.3
90°	2.0	23.7	64.4	60.4	62.4
92.5°	40.7	55.2	57.2	59.1	59.1
95°	95.9	114.3	117.5	117.5	114.3
97.5°	159.6	176.7	183.9	183.9	183.9
100°	233.2	248.2	253.5	253.5	251.5
102.5°	310.6	321.8	329.0	331.0	329.0
105°	395.4	400.6	404.6	407.9	407.9
107.5°	479.4	487.3	487.3	488.6	479.4
110°	560.9	571.4	571.4	571.4	566.1

TEST NUMBER: P919710

CATALOG NUMBER: DFN2DIP-PN4F0-090D080US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	648.8	660.0	658.1	652.8	648.8
115°	735.6	746.1	742.8	740.8	735.6
117.5°	821.6	836.0	826.8	821.6	816.3
120°	908.3	922.7	908.3	908.3	902.3
122.5°	987.0	1005.5	996.3	991.0	987.0
125°	1069.8	1086.2	1081.0	1075.0	1073.1
127.5°	1150.6	1171.0	1163.7	1155.9	1150.6
130°	1226.1	1249.7	1246.5	1242.6	1235.4
132.5°	1310.9	1329.2	1330.6	1321.4	1316.1
135°	1383.7	1404.1	1408.1	1406.1	1400.8
137.5°	1465.2	1481.6	1484.9	1483.6	1475.7
140°	1536.8	1553.2	1562.4	1562.4	1555.1
142.5°	1610.3	1626.8	1632.0	1634.0	1626.8
145°	1680.0	1693.1	1703.6	1705.6	1698.3
147.5°	1742.3	1758.8	1766.6	1770.0	1762.7
150°	1806.7	1817.8	1825.1	1831.0	1825.1
152.5°	1863.8	1875.0	1884.2	1891.4	1884.2
155°	1921.0	1926.2	1932.2	1941.3	1935.4
157.5°	1970.2	1974.2	1977.5	1990.5	1981.4
160°	2014.2	2018.2	2020.2	2031.3	2023.4
162.5°	2054.9	2054.9	2056.9	2069.4	2060.2
165°	2089.7	2087.7	2087.7	2100.9	2091.7
167.5°	2121.2	2115.4	2115.4	2128.5	2119.3
170°	2144.9	2139.7	2137.7	2150.9	2139.7
172.5°	2161.4	2156.1	2154.1	2167.2	2156.1
175°	2174.5	2169.2	2165.2	2178.4	2167.2
177.5°	2181.7	2176.4	2172.5	2183.7	2172.5
180°	2178.4	2178.4	2178.4	2178.4	2178.4

TEST NUMBER: P919710

CATALOG NUMBER: DFN2DIP-PN4F0-090D080US935-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.29	11.13	11.23	12.09	13.34	6.25	7.10	7.20	8.06	9.30
	3H	11.97	12.73	12.93	13.69	14.96	7.44	8.20	8.40	9.17	10.44
	4H	12.58	13.30	13.55	14.27	15.54	7.89	8.61	8.87	9.58	10.86
	6H	13.00	13.66	13.99	14.64	15.93	8.22	8.88	9.20	9.85	11.14
	8H	13.13	13.76	14.12	14.75	16.04	8.31	8.93	9.30	9.93	11.22
	12H	13.20	13.79	14.19	14.78	16.09	8.35	8.95	9.35	9.94	11.25
4H	2H	10.31	11.02	11.29	11.99	13.27	6.85	7.57	7.83	8.54	9.82
	3H	12.14	12.74	13.13	13.74	15.03	8.20	8.80	9.19	9.80	11.09
	4H	12.84	13.38	13.83	14.37	15.69	8.75	9.30	9.75	10.29	11.61
	6H	13.35	13.82	14.36	14.84	16.15	9.17	9.64	10.18	10.66	11.97
	8H	13.53	13.97	14.54	14.98	16.31	9.30	9.74	10.31	10.75	12.08
	12H	13.63	14.02	14.66	15.05	16.38	9.37	9.76	10.40	10.79	12.12
8H	4H	12.81	13.24	13.81	14.25	15.58	9.04	9.47	10.04	10.48	11.81
	6H	13.38	13.73	14.41	14.79	16.11	9.56	9.92	10.59	10.97	12.29
	8H	13.59	13.91	14.63	14.95	16.29	9.75	10.07	10.79	11.10	12.45
	12H	13.74	14.01	14.78	15.05	16.43	9.87	10.15	10.91	11.18	12.57
12H	4H	12.76	13.15	13.78	14.18	15.51	9.04	9.44	10.07	10.46	11.79
	6H	13.35	13.67	14.39	14.71	16.05	9.61	9.92	10.65	10.96	12.31
	8H	13.57	13.85	14.62	14.89	16.27	9.82	10.10	10.86	11.13	12.52

END OF REPORT