

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919719

Luminaire Tested: DFN2DIP-PN4F0-090D100US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919719
REPORT IS A COMBINATION OF REPORTS P901248 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-090D100US935-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15110.6 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 163.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919719

CATALOG NUMBER: DFN2DIP-PN4F0-090D100US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P919719

CATALOG NUMBER: DFN2DIP-PN4F0-090D100US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	106	106	106	106	97	97	97	97		80	80	80		64	64	64		50	50	50
1	97	93	89	86	88	85	82	79		71	68	66		57	56	54		45	44	43
2	88	81	76	71	81	75	70	65		62	59	56		51	48	46		40	39	37
3	81	72	65	59	74	66	60	55		55	51	47		45	42	39		36	34	32
4	74	64	56	50	68	59	52	47		49	44	41		41	37	34		32	30	28
5	68	57	49	43	62	53	46	41		44	39	35		37	33	30		29	27	25
6	63	51	43	38	58	47	41	36		40	35	31		33	29	26		27	24	22
7	58	46	39	33	53	43	36	31		36	31	27		30	26	23		25	22	20
8	54	42	35	30	50	39	32	28		33	28	24		28	24	21		23	20	18
9	50	39	31	26	46	36	29	25		31	25	22		26	22	19		21	18	16
10	47	35	28	24	43	33	27	22		28	23	20		24	20	17		20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2338	2338	2338
5°	2342	2301	2316
10°	2318	2256	2241
15°	2286	2182	2125
20°	2244	2079	1982
25°	2201	1964	1844
30°	2143	1847	1670
35°	2086	1720	1516
40°	2028	1589	1340
45°	1961	1443	1180
50°	1891	1296	1024
55°	1819	1139	874
60°	1735	975	720
65°	1638	807	649
70°	1521	651	588
75°	1374	575	536
80°	1160	483	466
85°	808	324	353

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1961 cd/sqm

TEST NUMBER: P919719

CATALOG NUMBER: DFN2DIP-PN4F0-090D100US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.2	2.0
10°-20°	824.0	5.5
20°-30°	1156.9	7.7
30°-40°	1261.0	8.3
40°-50°	1159.0	7.7
50°-60°	910.3	6.0
60°-70°	592.5	3.9
70°-80°	305.0	2.0
80°-90°	83.0	0.5
90°-100°	95.8	0.6
100°-110°	357.2	2.4
110°-120°	947.3	6.3
120°-130°	1571.2	10.4
130°-140°	1669.0	11.0
140°-150°	1551.1	10.3
150°-160°	1247.1	8.3
160°-170°	803.6	5.3
170°-180°	276.6	1.8
0°-30°	2281.0	15.1
0°-40°	3542.0	23.4
0°-60°	5611.3	37.1
0°-90°	6591.8	43.6
90°-120°	1400.3	9.3
90°-150°	6191.6	41.0
90°-180°	8519.0	56.4
0°-180°	15110.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3203	3203	3203	3203	3203	
5°	3203	3188	3150	3176	3168	304
15°	3046	3014	2916	2861	2832	858
25°	2765	2672	2481	2362	2319	1272
35°	2383	2235	1980	1797	1733	1491
45°	1948	1753	1449	1243	1174	1504
55°	1481	1255	942	768	713	1323
65°	1000	765	504	406	397	991
75°	533	330	232	212	209	564
85°	124	64	55	55	55	143
90°	2	25	42	53	57	14
95°	137	67	82	93	90	162
105°	639	702	128	151	160	683
115°	1209	1245	1297	324	172	1190
125°	1709	1737	1777	1792	1798	1524
135°	2115	2149	2168	2189	2185	1634
145°	2454	2452	2487	2502	2492	1535
155°	2702	2683	2708	2721	2704	1245
165°	2847	2834	2841	2855	2841	804
175°	2912	2897	2902	2916	2895	277
180°	2906	2906	2906	2906	2906	

TEST NUMBER: P919719

CATALOG NUMBER: DFN2DIP-PN4F0-090D100US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3202.7	3202.7	3202.7	3202.7	3202.7
2.5°	3217.1	3202.7	3170.6	3199.9	3194.0
5°	3202.7	3188.2	3150.4	3176.5	3167.9
7.5°	3176.5	3159.3	3118.7	3130.1	3115.6
10°	3141.8	3121.5	3063.7	3054.7	3037.5
12.5°	3098.4	3072.3	2993.9	2976.6	2944.6
15°	3046.1	3014.2	2915.8	2860.7	2831.8
17.5°	2985.3	2938.8	2817.0	2753.4	2707.0
20°	2915.8	2857.7	2712.7	2640.5	2576.5
22.5°	2840.4	2773.7	2605.5	2507.1	2463.7
25°	2765.1	2672.2	2481.0	2362.2	2318.6
27.5°	2675.3	2576.5	2365.0	2228.8	2162.1
30°	2579.6	2469.3	2237.4	2089.8	2011.4
32.5°	2486.7	2353.3	2115.9	1941.9	1869.3
35°	2382.6	2234.6	1979.7	1797.1	1733.1
37.5°	2281.0	2121.5	1852.1	1651.9	1579.7
40°	2173.8	2000.0	1718.6	1512.9	1437.6
42.5°	2063.6	1878.3	1585.4	1370.9	1298.6
45°	1947.7	1753.4	1449.2	1243.2	1173.7
47.5°	1837.6	1631.9	1318.9	1112.8	1049.2
50°	1715.9	1510.1	1191.3	991.1	930.5
52.5°	1596.9	1379.5	1069.5	878.2	823.2
55°	1480.9	1254.9	941.8	768.2	713.1
57.5°	1362.3	1130.4	829.1	666.7	620.3
60°	1240.4	1008.6	710.1	562.4	516.0
62.5°	1121.8	889.9	608.6	469.6	446.5
65°	1000.0	765.1	504.3	405.9	397.0
67.5°	884.1	649.1	405.9	356.4	347.8
70°	762.3	536.3	336.1	307.2	295.5
72.5°	646.4	431.7	281.0	258.0	252.2
75°	533.2	330.3	231.9	211.5	208.8
77.5°	420.3	234.6	182.6	171.0	165.1
80°	315.8	168.2	139.0	127.6	127.6
82.5°	220.2	113.1	95.7	89.8	89.8
85°	124.5	63.6	55.0	55.0	55.0
87.5°	46.4	23.1	23.1	20.3	20.3
90°	2.0	25.2	41.9	52.7	56.7
92.5°	52.7	44.2	50.5	54.7	56.7
95°	136.6	67.2	81.9	92.6	90.4
97.5°	245.9	73.6	107.1	113.6	115.6
100°	372.3	84.1	119.9	136.6	140.9
102.5°	510.8	506.9	124.1	147.1	153.5
105°	639.2	702.3	128.4	151.3	159.8
107.5°	788.5	840.9	132.6	155.6	164.0
110°	931.5	975.5	368.0	157.8	166.0

TEST NUMBER: P919719

CATALOG NUMBER: DFN2DIP-PN4F0-090D100US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1066.1	1103.8	1068.2	161.8	168.3
115°	1208.9	1244.7	1297.4	323.8	172.5
117.5°	1333.0	1375.0	1410.9	1110.1	559.3
120°	1471.9	1503.3	1541.3	1566.5	1282.6
122.5°	1589.5	1623.2	1665.3	1677.8	1680.1
125°	1709.3	1736.8	1776.8	1791.5	1797.7
127.5°	1818.7	1848.1	1879.8	1900.8	1902.8
130°	1921.7	1955.5	1978.5	2001.6	1999.7
132.5°	2026.9	2054.3	2077.3	2096.3	2094.3
135°	2115.3	2149.0	2167.7	2188.9	2184.7
137.5°	2207.7	2232.9	2254.1	2275.1	2268.8
140°	2298.0	2315.1	2338.0	2357.0	2346.5
142.5°	2373.9	2388.7	2415.9	2432.6	2422.2
145°	2453.8	2451.6	2487.3	2502.1	2491.6
147.5°	2523.0	2516.8	2552.4	2562.9	2554.8
150°	2590.4	2575.7	2609.4	2621.9	2611.4
152.5°	2647.1	2630.3	2661.9	2674.5	2659.8
155°	2701.8	2683.0	2708.3	2720.8	2704.0
157.5°	2746.0	2729.3	2748.2	2762.9	2746.0
160°	2784.0	2771.2	2784.0	2796.4	2781.7
162.5°	2817.4	2804.9	2815.4	2830.1	2811.2
165°	2846.8	2834.3	2840.6	2855.3	2840.6
167.5°	2870.1	2857.3	2863.9	2878.6	2859.5
170°	2889.0	2876.3	2880.6	2895.3	2876.3
172.5°	2901.5	2889.0	2893.3	2908.0	2889.0
175°	2912.0	2897.3	2901.5	2916.3	2895.3
177.5°	2916.3	2901.5	2903.8	2918.5	2899.5
180°	2905.8	2905.8	2905.8	2905.8	2905.8

TEST NUMBER: P919719

CATALOG NUMBER: DFN2DIP-PN4F0-090D100US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.48	10.26	10.50	11.28	12.64	5.44	6.22	6.46	7.25	8.61
	3H	11.16	11.85	12.18	12.88	14.27	6.63	7.33	7.66	8.36	9.74
	4H	11.76	12.42	12.80	13.46	14.85	7.08	7.74	8.12	8.77	10.16
	6H	12.19	12.79	13.23	13.83	15.23	7.40	8.00	8.45	9.04	10.44
	8H	12.31	12.89	13.37	13.94	15.34	7.49	8.06	8.54	9.12	10.51
	12H	12.37	12.92	13.43	13.97	15.39	7.53	8.08	8.59	9.12	10.55
4H	2H	9.49	10.15	10.54	11.18	12.57	6.03	6.70	7.08	7.73	9.12
	3H	11.32	11.87	12.37	12.93	14.33	7.38	7.93	8.43	8.99	10.39
	4H	12.01	12.51	13.07	13.57	14.99	7.93	8.43	8.99	9.48	10.91
	6H	12.53	12.96	13.60	14.03	15.45	8.35	8.78	9.41	9.85	11.27
	8H	12.70	13.10	13.77	14.17	15.61	8.47	8.88	9.54	9.94	11.38
	12H	12.80	13.16	13.88	14.24	15.68	8.54	8.90	9.62	9.98	11.42
8H	4H	11.98	12.38	13.04	13.45	14.88	8.21	8.61	9.28	9.68	11.11
	6H	12.54	12.87	13.63	13.98	15.42	8.72	9.06	9.82	10.17	11.60
	8H	12.76	13.05	13.86	14.15	15.60	8.92	9.21	10.01	10.30	11.75
	12H	12.90	13.16	14.00	14.24	15.74	9.03	9.29	10.14	10.38	11.87
12H	4H	11.93	12.29	13.01	13.37	14.81	8.21	8.57	9.30	9.65	11.09
	6H	12.52	12.81	13.62	13.90	15.35	8.77	9.07	9.87	10.16	11.61
	8H	12.74	13.00	13.84	14.08	15.57	8.98	9.24	10.09	10.33	11.82

END OF REPORT