

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919779

Luminaire Tested: DFN2DIP-PN4F0-110D070US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919779
REPORT IS A COMBINATION OF REPORTS P901198 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D070US935-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14017.1 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 166.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919779

CATALOG NUMBER: DFN2DIP-PN4F0-110D070US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P919779

CATALOG NUMBER: DFN2DIP-PN4F0-110D070US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		75	75	75		63	63	63
1	100	96	92	89		93	89	86	83		78	75	73		67	65	63		57	55	54
2	92	84	78	73		85	79	74	69		69	65	61		59	56	54		50	48	47
3	84	75	68	62		78	70	64	59		61	56	52		53	49	46		45	43	40
4	77	66	59	53		72	62	56	50		55	49	45		47	43	40		41	38	35
5	71	60	52	46		66	56	49	44		49	44	39		43	39	35		37	34	31
6	66	54	46	40		61	51	43	38		45	39	35		39	35	31		34	30	28
7	61	49	41	35		57	46	39	34		41	35	31		36	31	28		31	27	25
8	57	44	37	32		53	42	35	30		37	32	28		33	28	25		29	25	22
9	53	41	33	28		49	38	32	27		34	29	25		30	26	23		27	23	20
10	49	37	30	26		46	35	29	25		32	26	23		28	24	21		25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2857	2857	2857
5°	2862	2812	2831
10°	2834	2758	2739
15°	2794	2667	2597
20°	2743	2541	2423
25°	2690	2401	2254
30°	2619	2257	2041
35°	2550	2102	1853
40°	2479	1942	1638
45°	2397	1764	1442
50°	2312	1584	1252
55°	2223	1392	1068
60°	2120	1191	880
65°	2002	987	793
70°	1859	796	718
75°	1679	703	655
80°	1418	591	570
85°	988	396	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2397 cd/sqm

TEST NUMBER: P919779

CATALOG NUMBER: DFN2DIP-PN4F0-110D070US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.9	2.6
10°-20°	1007.1	7.2
20°-30°	1413.9	10.1
30°-40°	1541.3	11.0
40°-50°	1416.6	10.1
50°-60°	1112.5	7.9
60°-70°	724.2	5.2
70°-80°	372.8	2.7
80°-90°	98.7	0.7
90°-100°	67.1	0.5
100°-110°	250.0	1.8
110°-120°	663.1	4.7
120°-130°	1099.8	7.8
130°-140°	1168.3	8.3
140°-150°	1085.8	7.7
150°-160°	872.9	6.2
160°-170°	562.5	4.0
170°-180°	193.6	1.4
0°-30°	2787.9	19.9
0°-40°	4329.1	30.9
0°-60°	6858.3	48.9
0°-90°	8053.9	57.5
90°-120°	980.2	7.0
90°-150°	4334.1	30.9
90°-180°	5963.0	42.5
0°-180°	14017.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3914	3914	3914	3914	3914	
5°	3914	3897	3850	3882	3872	371
15°	3723	3684	3564	3496	3461	1049
25°	3380	3266	3032	2887	2834	1554
35°	2912	2731	2420	2196	2118	1823
45°	2381	2143	1771	1520	1435	1838
55°	1810	1534	1151	939	872	1617
65°	1222	935	616	496	485	1212
75°	652	404	283	259	255	689
85°	152	78	67	67	67	175
90°	1	18	29	37	40	13
95°	96	47	57	65	63	113
105°	448	492	90	106	112	478
115°	846	871	908	227	121	833
125°	1196	1216	1244	1254	1258	1067
135°	1481	1504	1517	1532	1529	1144
145°	1718	1716	1741	1751	1744	1074
155°	1891	1878	1896	1904	1893	872
165°	1993	1984	1988	1999	1988	563
175°	2038	2028	2031	2041	2027	194
180°	2034	2034	2034	2034	2034	

TEST NUMBER: P919779

CATALOG NUMBER: DFN2DIP-PN4F0-110D070US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3914.4	3914.4	3914.4	3914.4	3914.4
2.5°	3932.0	3914.4	3875.3	3911.0	3903.9
5°	3914.4	3896.7	3850.5	3882.4	3871.9
7.5°	3882.4	3861.3	3811.7	3825.7	3807.9
10°	3840.0	3815.1	3744.5	3733.5	3712.5
12.5°	3786.9	3755.0	3659.2	3638.1	3599.0
15°	3723.0	3684.0	3563.7	3496.4	3461.0
17.5°	3648.7	3591.9	3443.0	3365.2	3308.5
20°	3563.7	3492.6	3315.6	3227.3	3149.1
22.5°	3471.6	3390.0	3184.5	3064.2	3011.2
25°	3379.5	3266.0	3032.3	2887.2	2833.8
27.5°	3269.8	3149.1	2890.5	2724.0	2642.5
30°	3152.9	3018.0	2734.6	2554.2	2458.3
32.5°	3039.4	2876.2	2586.1	2373.4	2284.7
35°	2912.0	2731.2	2419.7	2196.4	2118.2
37.5°	2788.0	2592.9	2263.6	2019.0	1930.7
40°	2656.8	2444.5	2100.6	1849.1	1757.0
42.5°	2522.2	2295.6	1937.8	1675.5	1587.2
45°	2380.6	2143.0	1771.3	1519.5	1434.6
47.5°	2246.0	1994.6	1612.0	1360.1	1282.4
50°	2097.1	1845.7	1456.0	1211.3	1137.3
52.5°	1951.7	1686.0	1307.2	1073.4	1006.1
55°	1810.0	1533.8	1151.2	938.8	871.6
57.5°	1665.0	1381.6	1013.2	814.8	758.0
60°	1516.1	1232.8	867.8	687.4	630.7
62.5°	1371.1	1087.7	743.8	573.9	545.7
65°	1222.2	935.0	616.4	496.1	485.2
67.5°	1080.6	793.4	496.1	435.6	425.1
70°	931.7	655.5	410.8	375.5	361.2
72.5°	790.0	527.7	343.5	315.3	308.2
75°	651.7	403.6	283.4	258.6	255.2
77.5°	513.8	286.8	223.3	209.0	201.8
80°	386.0	205.6	169.9	156.0	156.0
82.5°	269.1	138.3	116.9	109.8	109.8
85°	152.2	77.8	67.2	67.2	67.2
87.5°	56.7	28.2	28.2	24.8	24.8
90°	1.4	17.7	29.4	36.9	39.7
92.5°	36.9	30.9	35.3	38.3	39.7
95°	95.6	47.0	57.3	64.8	63.3
97.5°	172.1	51.6	75.0	79.6	80.9
100°	260.6	58.9	83.9	95.6	98.6
102.5°	357.6	354.8	86.9	103.0	107.5
105°	447.5	491.6	89.8	105.9	111.8
107.5°	551.9	588.7	92.8	108.9	114.9
110°	652.1	682.9	257.6	110.5	116.2



TEST NUMBER: P919779

CATALOG NUMBER: DFN2DIP-PN4F0-110D070US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	746.3	772.7	747.7	113.2	117.8
115°	846.3	871.2	908.1	226.7	120.8
117.5°	933.1	962.5	987.7	777.1	391.5
120°	1030.3	1052.3	1078.9	1096.6	897.8
122.5°	1112.6	1136.2	1165.8	1174.5	1176.0
125°	1196.5	1215.7	1243.7	1254.0	1258.3
127.5°	1273.1	1293.6	1315.9	1330.6	1332.0
130°	1345.2	1368.8	1384.9	1401.2	1399.8
132.5°	1418.8	1438.0	1454.1	1467.4	1466.0
135°	1480.7	1504.2	1517.4	1532.2	1529.3
137.5°	1545.3	1563.1	1577.9	1592.6	1588.2
140°	1608.6	1620.5	1636.6	1649.8	1642.5
142.5°	1661.7	1672.1	1691.1	1702.8	1695.5
145°	1717.7	1716.1	1741.1	1751.4	1744.1
147.5°	1766.1	1761.8	1786.7	1794.1	1788.3
150°	1813.3	1803.0	1826.6	1835.3	1828.0
152.5°	1853.0	1841.2	1863.3	1872.2	1861.9
155°	1891.3	1878.1	1895.7	1904.5	1892.8
157.5°	1922.2	1910.5	1923.7	1934.1	1922.2
160°	1948.8	1939.8	1948.8	1957.5	1947.1
162.5°	1972.2	1963.4	1970.7	1981.1	1967.8
165°	1992.8	1984.1	1988.4	1998.7	1988.4
167.5°	2009.1	2000.1	2004.7	2015.0	2001.7
170°	2022.3	2013.4	2016.4	2026.7	2013.4
172.5°	2031.1	2022.3	2025.3	2035.6	2022.3
175°	2038.4	2028.1	2031.1	2041.3	2026.7
177.5°	2041.3	2031.1	2032.6	2043.0	2029.6
180°	2034.0	2034.0	2034.0	2034.0	2034.0

TEST NUMBER: P919779

CATALOG NUMBER: DFN2DIP-PN4F0-110D070US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.47	12.37	12.37	13.28	14.44	7.44	8.33	8.33	9.24	10.41
	3H	13.16	13.96	14.07	14.88	16.07	8.63	9.43	9.54	10.35	11.54
	4H	13.77	14.53	14.70	15.45	16.65	9.08	9.84	10.01	10.77	11.97
	6H	14.20	14.89	15.13	15.83	17.04	9.41	10.11	10.35	11.04	12.25
	8H	14.33	14.99	15.27	15.94	17.15	9.50	10.16	10.45	11.11	12.32
	12H	14.39	15.02	15.34	15.97	17.20	9.55	10.18	10.50	11.12	12.36
4H	2H	11.50	12.25	12.43	13.18	14.38	8.04	8.80	8.97	9.72	10.92
	3H	13.34	13.96	14.28	14.92	16.13	9.40	10.03	10.34	10.98	12.20
	4H	14.03	14.60	14.98	15.56	16.80	9.95	10.52	10.90	11.47	12.71
	6H	14.55	15.05	15.52	16.02	17.26	10.37	10.87	11.34	11.84	13.08
	8H	14.73	15.19	15.70	16.16	17.41	10.50	10.96	11.47	11.93	13.18
	12H	14.83	15.25	15.82	16.23	17.49	10.57	10.99	11.56	11.97	13.23
8H	4H	14.01	14.47	14.97	15.43	16.69	10.24	10.70	11.20	11.67	12.92
	6H	14.58	14.96	15.57	15.97	17.22	10.76	11.14	11.75	12.15	13.40
	8H	14.80	15.13	15.80	16.13	17.40	10.95	11.29	11.95	12.29	13.55
	12H	14.94	15.23	15.94	16.23	17.54	11.07	11.37	12.08	12.36	13.68
12H	4H	13.96	14.37	14.94	15.36	16.62	10.24	10.66	11.23	11.65	12.90
	6H	14.55	14.89	15.55	15.89	17.16	10.81	11.14	11.81	12.14	13.41
	8H	14.78	15.07	15.78	16.07	17.38	11.02	11.32	12.03	12.31	13.63

END OF REPORT