

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919788

Luminaire Tested: DFN2DIP-PN4F0-110D100US935-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P919788  
REPORT IS A COMBINATION OF REPORTS P899731 AND P896497  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-110D100US935-FLLFLL  
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 16996.1 lumens  
Efficiency: N/A  
Efficacy: 89.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 189.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.996  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P919788  
CATALOG NUMBER: DFN2DIP-PN4F0-110D100US935-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P919788

CATALOG NUMBER: DFN2DIP-PN4F0-110D100US935-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	51	46
2	90	83	76	71	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	70	60	53	47	52	46	42	45	40	37	38	34	32	28
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	30	28	25
6	64	51	43	37	59	48	41	36	42	36	32	36	32	28	31	27	24	22
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2690	2690	2690
5°	2694	2653	2671
10°	2673	2618	2635
15°	2633	2575	2579
20°	2580	2515	2522
25°	2527	2444	2456
30°	2461	2378	2371
35°	2398	2300	2281
40°	2321	2221	2196
45°	2244	2142	2109
50°	2160	2058	2009
55°	2072	1962	1916
60°	1972	1848	1810
65°	1863	1730	1685
70°	1725	1586	1550
75°	1533	1414	1427
80°	1303	1195	1190
85°	943	816	796

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2244 cd/sqm



TEST NUMBER: P919788

CATALOG NUMBER: DFN2DIP-PN4F0-110D100US935-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	346.9	2.0
10°-20°	975.9	5.7
20°-30°	1434.2	8.4
30°-40°	1665.7	9.8
40°-50°	1663.7	9.8
50°-60°	1450.7	8.5
60°-70°	1072.4	6.3
70°-80°	606.7	3.6
80°-90°	167.9	1.0
90°-100°	168.5	1.0
100°-110°	535.4	3.2
110°-120°	916.2	5.4
120°-130°	1204.9	7.1
130°-140°	1352.5	8.0
140°-150°	1326.3	7.8
150°-160°	1112.6	6.5
160°-170°	737.8	4.3
170°-180°	257.9	1.5
0°-30°	2757.0	16.2
0°-40°	4422.7	26.0
0°-60°	7537.0	44.3
0°-90°	9384.0	55.2
90°-120°	1620.1	9.5
90°-150°	5503.8	32.4
90°-180°	7612.0	44.8
0°-180°	16996.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3685	3685	3685	3685	3685	
5°	3685	3671	3632	3660	3654	350
15°	3508	3487	3441	3455	3437	988
25°	3175	3147	3087	3094	3087	1461
35°	2739	2704	2647	2626	2608	1711
45°	2229	2204	2151	2112	2098	1720
55°	1687	1666	1623	1580	1563	1508
65°	1138	1116	1081	1049	1031	1125
75°	595	588	570	549	556	635
85°	145	142	138	127	124	162
90°	2	30	80	76	78	16
95°	120	143	147	147	143	133
105°	494	501	506	510	510	522
115°	920	932	928	926	920	909
125°	1337	1358	1351	1344	1341	1195
135°	1730	1755	1760	1758	1751	1337
145°	2100	2116	2130	2132	2123	1312
155°	2401	2408	2415	2427	2419	1105
165°	2612	2610	2610	2626	2615	737
175°	2718	2712	2707	2723	2709	258
180°	2723	2723	2723	2723	2723	



TEST NUMBER: P919788

CATALOG NUMBER: DFN2DIP-PN4F0-110D100US935-FLLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3685.2	3685.2	3685.2	3685.2	3685.2
2.5°	3706.6	3688.9	3649.9	3685.2	3678.4
5°	3685.2	3671.3	3632.2	3660.4	3653.6
7.5°	3660.4	3639.4	3600.3	3628.8	3621.7
10°	3621.7	3596.8	3554.4	3582.5	3572.0
12.5°	3568.3	3547.2	3504.8	3522.4	3515.3
15°	3508.1	3487.0	3440.8	3455.1	3437.4
17.5°	3433.7	3412.7	3366.4	3384.1	3366.4
20°	3352.1	3331.0	3281.4	3291.9	3278.1
22.5°	3270.9	3238.9	3192.7	3192.7	3185.5
25°	3175.0	3146.9	3086.7	3093.5	3086.7
27.5°	3068.6	3043.8	2997.9	2987.4	2969.8
30°	2962.6	2934.0	2881.0	2870.5	2856.2
32.5°	2849.0	2828.0	2771.2	2749.8	2735.5
35°	2739.3	2704.0	2647.1	2625.7	2608.0
37.5°	2615.2	2583.3	2526.5	2501.6	2484.0
40°	2487.8	2459.2	2402.4	2370.8	2356.6
42.5°	2363.7	2335.1	2278.7	2243.0	2222.0
45°	2229.1	2204.2	2150.9	2112.2	2097.9
47.5°	2097.9	2073.1	2016.3	1977.2	1956.1
50°	1959.5	1941.9	1892.2	1842.6	1825.0
52.5°	1825.0	1800.1	1754.3	1715.1	1690.3
55°	1687.0	1665.5	1623.1	1580.5	1562.9
57.5°	1548.6	1530.9	1484.7	1442.2	1427.9
60°	1410.2	1396.4	1346.7	1307.6	1297.1
62.5°	1275.7	1250.9	1215.5	1180.2	1165.9
65°	1137.6	1116.2	1080.9	1049.0	1031.3
67.5°	995.9	977.9	946.3	921.5	907.2
70°	864.7	850.4	818.5	793.7	779.7
72.5°	730.1	715.8	698.2	673.4	662.8
75°	595.1	588.4	570.3	549.3	556.5
77.5°	474.8	460.5	453.4	442.9	432.4
80°	354.6	350.8	343.6	333.1	326.0
82.5°	241.0	241.0	237.6	223.3	223.3
85°	145.2	141.7	138.4	127.4	124.1
87.5°	63.9	56.7	49.6	39.1	35.3
90°	2.5	29.5	80.4	75.5	78.0
92.5°	50.9	69.0	71.5	73.9	73.9
95°	119.9	142.8	147.0	147.0	142.8
97.5°	199.5	220.8	229.9	229.9	229.9
100°	291.4	310.3	316.8	316.8	314.4
102.5°	388.3	402.3	411.3	413.7	411.3
105°	494.2	500.8	505.7	509.8	509.8
107.5°	599.3	609.2	609.2	610.8	599.3
110°	701.1	714.2	714.2	714.2	707.7



TEST NUMBER: P919788

CATALOG NUMBER: DFN2DIP-PN4F0-110D100US935-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	811.1	825.0	822.6	816.0	811.1
115°	919.5	932.5	928.5	926.0	919.5
117.5°	1027.0	1045.1	1033.5	1027.0	1020.4
120°	1135.3	1153.4	1135.3	1135.3	1128.0
122.5°	1233.8	1256.8	1245.3	1238.8	1233.8
125°	1337.3	1357.8	1351.3	1343.8	1341.4
127.5°	1438.3	1463.7	1454.7	1444.8	1438.3
130°	1532.7	1562.2	1558.1	1553.2	1544.2
132.5°	1638.6	1661.6	1663.2	1651.7	1645.1
135°	1729.7	1755.1	1760.1	1757.6	1751.0
137.5°	1831.5	1852.0	1856.1	1854.5	1844.6
140°	1921.0	1941.5	1953.0	1953.0	1944.0
142.5°	2012.9	2033.4	2040.0	2042.5	2033.4
145°	2099.9	2116.3	2129.5	2131.9	2122.9
147.5°	2177.9	2198.5	2208.3	2212.4	2203.4
150°	2258.4	2272.3	2281.4	2288.7	2281.4
152.5°	2329.8	2343.7	2355.3	2364.3	2355.3
155°	2401.2	2407.8	2415.2	2426.6	2419.2
157.5°	2462.8	2467.7	2471.8	2488.2	2476.7
160°	2517.8	2522.7	2525.1	2539.1	2529.3
162.5°	2568.7	2568.7	2571.1	2586.7	2575.2
165°	2612.2	2609.7	2609.7	2626.1	2614.7
167.5°	2651.6	2644.2	2644.2	2660.7	2649.1
170°	2681.1	2674.6	2672.1	2688.6	2674.6
172.5°	2701.6	2695.1	2692.6	2709.0	2695.1
175°	2718.1	2711.5	2706.6	2723.0	2709.0
177.5°	2727.1	2720.6	2715.6	2729.5	2715.6
180°	2723.0	2723.0	2723.0	2723.0	2723.0



TEST NUMBER: P919788  
 CATALOG NUMBER: DFN2DIP-PN4F0-110D100US935-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.18	12.09	12.09	13.02	14.22	10.74	11.65	11.65	12.58	13.78
	3H	12.85	13.67	13.77	14.61	15.83	12.37	13.18	13.29	14.12	15.34
	4H	13.44	14.22	14.38	15.16	16.39	12.96	13.73	13.89	14.67	15.90
	6H	13.85	14.56	14.80	15.51	16.75	13.36	14.07	14.30	15.02	16.26
	8H	13.95	14.63	14.91	15.60	16.84	13.46	14.14	14.42	15.11	16.35
	12H	14.01	14.65	14.97	15.61	16.88	13.51	14.15	14.47	15.11	16.38
4H	2H	11.65	12.42	12.59	13.37	14.60	11.30	12.07	12.24	13.02	14.25
	3H	13.53	14.17	14.48	15.14	16.39	13.12	13.77	14.08	14.74	15.98
	4H	14.24	14.83	15.21	15.80	17.07	13.83	14.42	14.79	15.38	16.65
	6H	14.76	15.27	15.74	16.26	17.53	14.34	14.85	15.32	15.84	17.11
	8H	14.92	15.39	15.89	16.38	17.66	14.49	14.96	15.47	15.95	17.23
	12H	14.99	15.42	15.99	16.42	17.71	14.55	14.98	15.55	15.98	17.27
8H	4H	14.44	14.92	15.42	15.90	17.19	14.07	14.55	15.05	15.53	16.81
	6H	15.08	15.47	16.08	16.50	17.78	14.70	15.10	15.71	16.13	17.40
	8H	15.30	15.65	16.32	16.67	17.96	14.92	15.27	15.93	16.28	17.58
	12H	15.44	15.75	16.46	16.75	18.10	15.04	15.34	16.05	16.35	17.69
12H	4H	14.43	14.86	15.43	15.86	17.15	14.07	14.50	15.07	15.50	16.79
	6H	15.11	15.46	16.12	16.47	17.77	14.75	15.09	15.76	16.11	17.41
	8H	15.36	15.66	16.37	16.67	18.01	14.99	15.29	16.00	16.30	17.64