

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911550

Luminaire Tested: DFN2DIP-PN4F0-100D050US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911550
REPORT IS A COMBINATION OF REPORTS P899640 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-100D050US850-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14333.8 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 138.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911550
CATALOG NUMBER: DFN2DIP-PN4F0-100D050US850-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P911550

CATALOG NUMBER: DFN2DIP-PN4F0-100D050US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66			66
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61	57			57
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52	49			49
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45	42			42
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40	36			36
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35	32			32
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31	29			29
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28	26			26
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25	23			23
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23	21			21
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19			19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3346	3346	3346
5°	3351	3293	3314
10°	3318	3229	3207
15°	3272	3123	3041
20°	3212	2976	2837
25°	3150	2811	2640
30°	3067	2643	2389
35°	2985	2461	2170
40°	2903	2274	1918
45°	2806	2065	1689
50°	2707	1855	1466
55°	2603	1630	1251
60°	2483	1395	1030
65°	2344	1155	928
70°	2176	932	841
75°	1966	823	766
80°	1660	692	667
85°	1157	464	505

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2806 cd/sqm



TEST NUMBER: P911550

CATALOG NUMBER: DFN2DIP-PN4F0-100D050US850-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	429.6	3.0
10°-20°	1179.3	8.2
20°-30°	1655.6	11.6
30°-40°	1804.7	12.6
40°-50°	1658.8	11.6
50°-60°	1302.7	9.1
60°-70°	847.9	5.9
70°-80°	436.5	3.0
80°-90°	116.4	0.8
90°-100°	108.5	0.8
100°-110°	344.8	2.4
110°-120°	590.1	4.1
120°-130°	776.0	5.4
130°-140°	871.0	6.1
140°-150°	854.2	6.0
150°-160°	716.5	5.0
160°-170°	475.2	3.3
170°-180°	166.1	1.2
0°-30°	3264.5	22.8
0°-40°	5069.2	35.4
0°-60°	8030.6	56.0
0°-90°	9431.5	65.8
90°-120°	1043.4	7.3
90°-150°	3544.6	24.7
90°-180°	4902.0	34.2
0°-180°	14333.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4584	4584	4584	4584	4584	
5°	4584	4563	4509	4546	4534	435
15°	4360	4314	4173	4094	4053	1228
25°	3957	3824	3551	3381	3318	1820
35°	3410	3198	2833	2572	2480	2134
45°	2788	2509	2074	1779	1680	2153
55°	2119	1796	1348	1099	1020	1894
65°	1431	1095	722	581	568	1419
75°	763	473	332	303	299	807
85°	178	91	79	79	79	205
90°	2	19	52	49	50	14
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1371	1373	1367	845
155°	1546	1551	1555	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	



TEST NUMBER: P911550

CATALOG NUMBER: DFN2DIP-PN4F0-100D050US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4583.5	4583.5	4583.5	4583.5	4583.5
2.5°	4604.1	4583.5	4537.7	4579.5	4571.2
5°	4583.5	4562.8	4508.6	4546.1	4533.7
7.5°	4546.1	4521.4	4463.3	4479.6	4459.0
10°	4496.3	4467.3	4384.5	4371.8	4347.2
12.5°	4434.3	4396.9	4284.6	4260.0	4214.2
15°	4359.5	4313.7	4172.8	4094.1	4052.7
17.5°	4272.3	4205.9	4031.7	3940.5	3874.1
20°	4172.8	4089.7	3882.4	3779.0	3687.4
22.5°	4065.0	3969.6	3728.8	3588.1	3526.0
25°	3957.2	3824.4	3550.6	3380.7	3318.2
27.5°	3828.7	3687.4	3384.7	3189.7	3094.2
30°	3691.9	3533.8	3202.0	2990.9	2878.6
32.5°	3559.0	3367.9	3028.2	2779.2	2675.2
35°	3409.7	3198.1	2833.3	2571.9	2480.3
37.5°	3264.6	3036.1	2650.6	2364.2	2260.7
40°	3111.0	2862.3	2459.7	2165.2	2057.4
42.5°	2953.4	2688.0	2269.1	1961.9	1858.5
45°	2787.5	2509.3	2074.2	1779.3	1679.8
47.5°	2630.0	2335.6	1887.5	1592.6	1501.6
50°	2455.7	2161.2	1704.9	1418.4	1331.7
52.5°	2285.3	1974.2	1530.6	1256.8	1178.1
55°	2119.4	1796.0	1348.0	1099.4	1020.5
57.5°	1949.6	1617.7	1186.5	954.1	887.6
60°	1775.3	1443.5	1016.2	804.9	738.5
62.5°	1605.4	1273.6	870.9	672.1	639.0
65°	1431.2	1094.9	721.7	580.9	568.1
67.5°	1265.3	929.0	580.9	510.0	497.7
70°	1090.9	767.5	481.0	439.6	423.0
72.5°	925.0	617.8	402.2	369.2	360.9
75°	763.1	472.7	331.8	302.8	298.8
77.5°	601.6	335.8	261.4	244.6	236.3
80°	451.9	240.8	199.0	182.7	182.7
82.5°	315.1	161.9	136.9	128.5	128.5
85°	178.2	91.0	78.7	78.7	78.7
87.5°	66.4	33.0	33.0	29.1	29.1
90°	1.6	19.1	51.8	48.7	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.6	94.6	92.0
97.5°	128.4	142.2	148.1	148.1	148.1
100°	187.6	199.8	204.1	204.1	202.5
102.5°	250.1	259.1	264.8	266.5	264.8
105°	318.3	322.5	325.7	328.3	328.3
107.5°	385.9	392.3	392.3	393.4	385.9
110°	451.5	460.0	460.0	460.0	455.7



TEST NUMBER: P911550

CATALOG NUMBER: DFN2DIP-PN4F0-100D050US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.3	531.3	529.8	525.6	522.3
115°	592.1	600.6	598.0	596.4	592.1
117.5°	661.4	673.1	665.6	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.0	797.8	794.6
125°	861.2	874.4	870.2	865.5	863.9
127.5°	926.2	942.6	936.9	930.5	926.2
130°	987.1	1006.1	1003.4	1000.3	994.4
132.5°	1055.3	1070.1	1071.2	1063.8	1059.5
135°	1114.0	1130.3	1133.5	1132.0	1127.7
137.5°	1179.5	1192.7	1195.4	1194.3	1188.0
140°	1237.1	1250.4	1257.7	1257.7	1252.0
142.5°	1296.3	1309.6	1313.8	1315.4	1309.6
145°	1352.4	1363.0	1371.4	1373.1	1367.2
147.5°	1402.7	1415.9	1422.2	1424.8	1419.0
150°	1454.5	1463.4	1469.2	1474.0	1469.2
152.5°	1500.5	1509.5	1516.8	1522.7	1516.8
155°	1546.4	1550.6	1555.4	1562.8	1558.0
157.5°	1586.1	1589.2	1591.9	1602.5	1595.1
160°	1621.5	1624.7	1626.2	1635.2	1628.9
162.5°	1654.3	1654.3	1655.8	1665.9	1658.5
165°	1682.4	1680.7	1680.7	1691.3	1683.9
167.5°	1707.6	1702.9	1702.9	1713.5	1706.1
170°	1726.7	1722.5	1720.9	1731.5	1722.5
172.5°	1739.9	1735.7	1734.1	1744.7	1735.7
175°	1750.6	1746.2	1743.1	1753.7	1744.7
177.5°	1756.3	1752.1	1748.9	1757.9	1748.9
180°	1753.7	1753.7	1753.7	1753.7	1753.7



TEST NUMBER: P911550
 CATALOG NUMBER: DFN2DIP-PN4F0-100D050US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.71	13.69	13.53	14.52	15.55	8.67	9.65	9.49	10.49	11.52
	3H	14.40	15.28	15.23	16.12	17.18	9.88	10.75	10.70	11.59	12.65
	4H	15.02	15.84	15.87	16.69	17.76	10.33	11.16	11.18	12.01	13.08
	6H	15.45	16.21	16.31	17.07	18.15	10.66	11.42	11.52	12.28	13.36
	8H	15.58	16.31	16.45	17.18	18.26	10.76	11.48	11.62	12.36	13.44
	12H	15.65	16.34	16.52	17.21	18.31	10.81	11.49	11.68	12.36	13.47
4H	2H	12.75	13.57	13.60	14.42	15.49	9.29	10.12	10.14	10.97	12.03
	3H	14.59	15.28	15.45	16.16	17.24	10.65	11.34	11.52	12.22	13.31
	4H	15.29	15.92	16.17	16.80	17.91	11.21	11.83	12.08	12.71	13.82
	6H	15.82	16.36	16.71	17.26	18.37	11.64	12.17	12.53	13.08	14.19
	8H	16.00	16.50	16.89	17.40	18.52	11.77	12.27	12.66	13.17	14.30
	12H	16.10	16.55	17.01	17.47	18.60	11.84	12.29	12.75	13.21	14.34
8H	4H	15.27	15.77	16.16	16.67	17.80	11.50	12.00	12.39	12.90	14.03
	6H	15.85	16.26	16.76	17.20	18.33	12.03	12.44	12.95	13.38	14.51
	8H	16.06	16.43	16.99	17.37	18.51	12.22	12.59	13.15	13.52	14.66
	12H	16.21	16.54	17.14	17.46	18.66	12.35	12.67	13.28	13.59	14.79
12H	4H	15.23	15.68	16.14	16.60	17.73	11.51	11.96	12.42	12.88	14.01
	6H	15.82	16.19	16.75	17.12	18.27	12.08	12.44	13.01	13.38	14.52
	8H	16.05	16.37	16.98	17.30	18.49	12.30	12.62	13.23	13.54	14.74