

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911553

Luminaire Tested: DFN2DIP-PN4F0-100D060US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911553
REPORT IS A COMBINATION OF REPORTS P901177 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-100D060US850-FLLONL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17566.5 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 146.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911553

CATALOG NUMBER: DFN2DIP-PN4F0-100D060US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P911553

CATALOG NUMBER: DFN2DIP-PN4F0-100D060US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	86	79	73	69	69	65	62	61	58	55	53	50	48
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	38	32	40	34	30	35	31	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	40	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3150	3150	3150
5°	3155	3106	3128
10°	3129	3065	3086
15°	3083	3015	3020
20°	3021	2945	2953
25°	2959	2862	2875
30°	2882	2784	2776
35°	2808	2693	2671
40°	2718	2600	2572
45°	2628	2508	2470
50°	2529	2410	2352
55°	2426	2298	2244
60°	2309	2164	2119
65°	2182	2026	1973
70°	2020	1857	1815
75°	1795	1656	1671
80°	1525	1399	1394
85°	1103	955	932

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2628 cd/sqm

TEST NUMBER: P911553

CATALOG NUMBER: DFN2DIP-PN4F0-100D060US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.1	2.3
10°-20°	1142.7	6.5
20°-30°	1679.4	9.6
30°-40°	1950.5	11.1
40°-50°	1948.1	11.1
50°-60°	1698.7	9.7
60°-70°	1255.7	7.1
70°-80°	710.4	4.0
80°-90°	191.5	1.1
90°-100°	74.1	0.4
100°-110°	276.0	1.6
110°-120°	732.1	4.2
120°-130°	1214.2	6.9
130°-140°	1289.8	7.3
140°-150°	1198.7	6.8
150°-160°	963.8	5.5
160°-170°	621.0	3.5
170°-180°	213.7	1.2
0°-30°	3228.3	18.4
0°-40°	5178.7	29.5
0°-60°	8825.5	50.2
0°-90°	10983.1	62.5
90°-120°	1082.2	6.2
90°-150°	4785.0	27.2
90°-180°	6583.0	37.5
0°-180°	17566.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4315	4315	4315	4315	4315	
5°	4315	4299	4253	4286	4278	410
15°	4108	4083	4029	4046	4025	1157
25°	3718	3685	3614	3622	3614	1711
35°	3208	3166	3100	3075	3054	2003
45°	2610	2581	2518	2473	2456	2014
55°	1975	1950	1900	1851	1830	1766
65°	1332	1307	1266	1228	1208	1317
75°	697	689	668	643	652	744
85°	170	166	162	149	145	190
90°	2	20	32	41	44	16
95°	106	52	63	72	70	125
105°	494	543	99	117	124	528
115°	934	962	1003	250	133	920
125°	1321	1342	1373	1384	1389	1178
135°	1635	1661	1675	1692	1688	1263
145°	1896	1895	1922	1934	1926	1186
155°	2088	2074	2093	2103	2090	962
165°	2200	2190	2195	2207	2195	622
175°	2250	2239	2242	2254	2238	214
180°	2246	2246	2246	2246	2246	

TEST NUMBER: P911553

CATALOG NUMBER: DFN2DIP-PN4F0-100D060US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4315.2	4315.2	4315.2	4315.2	4315.2
2.5°	4340.3	4319.6	4273.8	4315.2	4307.2
5°	4315.2	4298.9	4253.1	4286.2	4278.2
7.5°	4286.2	4261.4	4215.6	4249.1	4240.8
10°	4240.8	4211.8	4162.0	4195.0	4182.7
12.5°	4178.3	4153.6	4103.9	4124.6	4116.2
15°	4107.8	4083.2	4029.0	4045.7	4025.1
17.5°	4020.7	3996.1	3941.8	3962.6	3941.8
20°	3925.1	3900.5	3842.4	3854.7	3838.4
22.5°	3830.0	3792.7	3738.4	3738.4	3730.1
25°	3717.8	3684.8	3614.3	3622.2	3614.3
27.5°	3593.2	3564.1	3510.4	3498.1	3477.4
30°	3469.1	3435.6	3373.5	3361.2	3344.4
32.5°	3336.1	3311.5	3244.9	3219.9	3203.1
35°	3207.6	3166.2	3099.7	3074.6	3053.9
37.5°	3062.3	3024.8	2958.4	2929.3	2908.6
40°	2913.0	2879.5	2813.1	2776.2	2759.4
42.5°	2767.7	2734.2	2668.3	2626.4	2601.8
45°	2610.1	2581.1	2518.5	2473.2	2456.5
47.5°	2456.5	2427.5	2361.0	2315.1	2290.5
50°	2294.5	2273.8	2215.7	2157.6	2136.9
52.5°	2136.9	2107.9	2054.1	2008.4	1979.3
55°	1975.4	1950.3	1900.5	1850.7	1830.1
57.5°	1813.3	1792.6	1738.5	1688.8	1672.0
60°	1651.3	1635.0	1576.9	1531.1	1518.8
62.5°	1493.7	1464.7	1423.3	1381.9	1365.2
65°	1332.1	1307.1	1265.7	1228.2	1207.6
67.5°	1166.2	1145.0	1108.1	1079.1	1062.3
70°	1012.5	995.8	958.4	929.3	913.0
72.5°	854.9	838.2	817.6	788.5	776.1
75°	696.9	689.0	667.8	643.2	651.5
77.5°	556.1	539.3	530.9	518.6	506.3
80°	415.1	410.8	402.3	390.0	381.7
82.5°	282.2	282.2	278.2	261.5	261.5
85°	169.9	166.0	162.0	149.3	145.3
87.5°	74.9	66.4	58.1	45.8	41.4
90°	1.6	19.5	32.4	40.7	43.8
92.5°	40.7	34.2	38.9	42.3	43.8
95°	105.6	51.9	63.3	71.6	69.9
97.5°	190.1	56.9	82.7	87.8	89.4
100°	287.7	65.0	92.6	105.6	108.8
102.5°	394.8	391.7	95.9	113.7	118.7
105°	493.9	542.7	99.1	116.9	123.5
107.5°	609.4	649.9	102.5	120.2	126.8
110°	720.0	753.9	284.5	122.0	128.3

TEST NUMBER: P911553

CATALOG NUMBER: DFN2DIP-PN4F0-100D060US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	823.9	853.0	825.4	125.0	130.1
115°	934.3	961.9	1002.6	250.3	133.3
117.5°	1030.2	1062.6	1090.4	857.9	432.2
120°	1137.5	1161.8	1191.2	1210.6	991.2
122.5°	1228.3	1254.4	1287.0	1296.6	1298.4
125°	1321.0	1342.2	1373.1	1384.5	1389.2
127.5°	1405.5	1428.3	1452.8	1469.0	1470.5
130°	1485.2	1511.2	1529.0	1546.9	1545.4
132.5°	1566.5	1587.6	1605.4	1620.0	1618.5
135°	1634.8	1660.8	1675.3	1691.7	1688.3
137.5°	1706.1	1725.6	1742.0	1758.2	1753.4
140°	1776.0	1789.1	1806.9	1821.5	1813.4
142.5°	1834.6	1846.0	1867.1	1880.0	1871.9
145°	1896.4	1894.6	1922.2	1933.7	1925.6
147.5°	1949.8	1945.0	1972.6	1980.7	1974.4
150°	2002.0	1990.5	2016.6	2026.3	2018.2
152.5°	2045.8	2032.8	2057.1	2067.0	2055.5
155°	2088.0	2073.5	2093.0	2102.7	2089.7
157.5°	2122.2	2109.2	2123.8	2135.3	2122.2
160°	2151.5	2141.6	2151.5	2161.1	2149.8
162.5°	2177.3	2167.7	2175.7	2187.2	2172.5
165°	2200.1	2190.5	2195.3	2206.7	2195.3
167.5°	2218.0	2208.2	2213.2	2224.7	2209.9
170°	2232.7	2222.9	2226.2	2237.5	2222.9
172.5°	2242.4	2232.7	2236.0	2247.4	2232.7
175°	2250.5	2239.1	2242.4	2253.7	2237.5
177.5°	2253.7	2242.4	2244.1	2255.5	2240.8
180°	2245.6	2245.6	2245.6	2245.6	2245.6

TEST NUMBER: P911553

CATALOG NUMBER: DFN2DIP-PN4F0-100D060US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.35	13.33	13.19	14.20	15.28	11.91	12.89	12.75	13.76	14.84
	3H	14.02	14.90	14.87	15.78	16.89	13.53	14.42	14.39	15.29	16.40
	4H	14.61	15.45	15.48	16.33	17.45	14.13	14.96	15.00	15.84	16.96
	6H	15.02	15.79	15.91	16.68	17.81	14.53	15.30	15.41	16.19	17.32
	8H	15.13	15.87	16.02	16.77	17.90	14.64	15.38	15.53	16.28	17.41
	12H	15.19	15.89	16.08	16.79	17.94	14.69	15.39	15.58	16.29	17.44
4H	2H	12.82	13.66	13.70	14.54	15.66	12.47	13.31	13.35	14.19	15.31
	3H	14.70	15.40	15.59	16.31	17.45	14.30	15.00	15.19	15.91	17.04
	4H	15.43	16.06	16.32	16.97	18.13	15.01	15.64	15.91	16.55	17.71
	6H	15.95	16.50	16.86	17.43	18.59	15.53	16.08	16.44	17.01	18.17
	8H	16.10	16.62	17.02	17.55	18.72	15.68	16.19	16.59	17.12	18.29
	12H	16.19	16.65	17.12	17.59	18.77	15.75	16.21	16.68	17.15	18.33
8H	4H	15.63	16.15	16.55	17.07	18.25	15.26	15.78	16.18	16.70	17.88
	6H	16.27	16.70	17.21	17.67	18.84	15.90	16.32	16.84	17.29	18.46
	8H	16.50	16.87	17.45	17.83	19.02	16.11	16.49	17.06	17.45	18.64
	12H	16.64	16.97	17.59	17.92	19.16	16.23	16.57	17.19	17.52	18.76
12H	4H	15.62	16.09	16.56	17.03	18.21	15.26	15.73	16.20	16.67	17.85
	6H	16.30	16.68	17.26	17.64	18.83	15.94	16.32	16.89	17.27	18.47
	8H	16.55	16.89	17.51	17.84	19.08	16.18	16.51	17.14	17.46	18.71