

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911610

Luminaire Tested: DFN2DIP-PN4F0-110D110US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911610
REPORT IS A COMBINATION OF REPORTS P899750 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D110US850-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21165.2 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 205.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911610

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911610

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3680	3680	3680
5°	3686	3622	3646
10°	3650	3552	3528
15°	3599	3435	3345
20°	3533	3274	3121
25°	3465	3093	2904
30°	3373	2907	2628
35°	3284	2707	2387
40°	3193	2501	2109
45°	3087	2272	1858
50°	2977	2040	1612
55°	2863	1793	1376
60°	2731	1534	1133
65°	2579	1271	1021
70°	2394	1025	925
75°	2162	905	843
80°	1827	761	734
85°	1273	510	556

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3087 cd/sqm

TEST NUMBER: P911610

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	472.5	2.2
10°-20°	1297.2	6.1
20°-30°	1821.2	8.6
30°-40°	1985.2	9.4
40°-50°	1824.6	8.6
50°-60°	1433.0	6.8
60°-70°	932.7	4.4
70°-80°	480.1	2.3
80°-90°	133.5	0.6
90°-100°	238.7	1.1
100°-110°	758.6	3.6
110°-120°	1298.1	6.1
120°-130°	1707.2	8.1
130°-140°	1916.3	9.1
140°-150°	1879.1	8.9
150°-160°	1576.3	7.4
160°-170°	1045.4	4.9
170°-180°	365.4	1.7
0°-30°	3590.9	17.0
0°-40°	5576.1	26.3
0°-60°	8833.7	41.7
0°-90°	10380.1	49.0
90°-120°	2295.4	10.8
90°-150°	7798.0	36.8
90°-180°	10785.0	51.0
0°-180°	21165.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5042	5042	5042	5042	5042	
5°	5042	5019	4960	5001	4987	478
15°	4795	4745	4590	4504	4458	1351
25°	4353	4207	3906	3719	3650	2002
35°	3751	3518	3117	2829	2728	2348
45°	3066	2760	2282	1957	1848	2368
55°	2331	1976	1483	1209	1123	2083
65°	1574	1204	794	639	625	1561
75°	839	520	365	333	329	888
85°	196	100	87	87	87	225
90°	3	42	114	107	110	21
95°	170	202	208	208	202	189
105°	700	710	716	722	722	739
115°	1303	1321	1316	1312	1303	1288
125°	1895	1924	1914	1904	1900	1693
135°	2451	2487	2494	2490	2481	1894
145°	2975	2998	3017	3021	3008	1859
155°	3402	3411	3422	3438	3428	1566
165°	3701	3698	3698	3721	3704	1044
175°	3851	3842	3835	3858	3838	366
180°	3858	3858	3858	3858	3858	

TEST NUMBER: P911610

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5041.8	5041.8	5041.8	5041.8	5041.8
2.5°	5064.6	5041.8	4991.5	5037.5	5028.3
5°	5041.8	5019.1	4959.6	5000.7	4987.2
7.5°	5000.7	4973.5	4909.7	4927.6	4904.8
10°	4946.0	4914.0	4823.0	4809.0	4781.9
12.5°	4877.7	4836.6	4713.1	4686.0	4635.6
15°	4795.4	4745.1	4590.2	4503.5	4458.0
17.5°	4699.6	4626.5	4434.8	4334.5	4261.4
20°	4590.2	4498.7	4270.6	4156.9	4056.2
22.5°	4471.6	4366.5	4101.7	3946.8	3878.5
25°	4352.9	4206.8	3905.7	3718.8	3650.1
27.5°	4211.6	4056.2	3723.1	3508.7	3403.6
30°	4061.0	3887.3	3522.3	3289.8	3166.4
32.5°	3914.9	3704.7	3331.0	3057.1	2942.8
35°	3750.7	3517.9	3116.6	2829.1	2728.4
37.5°	3591.1	3339.8	2915.7	2600.5	2486.8
40°	3422.0	3148.6	2705.6	2381.7	2263.1
42.5°	3248.7	2956.8	2496.0	2158.1	2044.3
45°	3066.3	2760.3	2281.5	1957.2	1847.8
47.5°	2892.9	2569.1	2076.3	1751.9	1651.7
50°	2701.2	2377.4	1875.4	1560.3	1464.9
52.5°	2513.9	2171.6	1683.7	1382.6	1295.9
55°	2331.3	1975.6	1482.7	1209.3	1122.6
57.5°	2144.6	1779.5	1305.1	1049.6	976.4
60°	1952.8	1587.9	1117.8	885.4	812.3
62.5°	1766.0	1401.0	958.1	739.3	702.9
65°	1574.2	1204.4	793.9	639.0	624.9
67.5°	1391.8	1021.9	639.0	561.0	547.5
70°	1200.0	844.3	529.1	483.6	465.2
72.5°	1017.5	679.7	442.5	406.1	396.9
75°	839.4	519.9	365.0	333.0	328.7
77.5°	661.7	369.4	287.6	269.2	259.9
80°	497.2	264.8	218.8	201.0	201.0
82.5°	346.6	178.1	150.6	141.4	141.4
85°	196.1	100.3	86.6	86.6	86.6
87.5°	73.1	36.3	36.3	31.9	31.9
90°	3.4	41.9	114.0	107.0	110.5
92.5°	72.1	97.7	101.1	104.7	104.7
95°	169.8	202.4	208.2	208.2	202.4
97.5°	282.7	312.8	325.7	325.7	325.7
100°	412.9	439.6	448.9	448.9	445.5
102.5°	550.2	569.9	582.8	586.2	582.8
105°	700.2	709.5	716.5	722.3	722.3
107.5°	849.1	863.0	863.0	865.4	849.1
110°	993.3	1012.0	1012.0	1012.0	1002.6

TEST NUMBER: P911610

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1149.1	1168.9	1165.4	1156.1	1149.1
115°	1302.7	1321.3	1315.5	1312.1	1302.7
117.5°	1455.1	1480.6	1464.3	1455.1	1445.8
120°	1608.6	1634.2	1608.6	1608.6	1598.2
122.5°	1748.2	1780.7	1764.4	1755.1	1748.2
125°	1894.7	1923.8	1914.5	1904.0	1900.5
127.5°	2037.8	2073.8	2061.1	2047.1	2037.8
130°	2171.5	2213.5	2207.6	2200.6	2187.8
132.5°	2321.6	2354.2	2356.5	2340.2	2330.9
135°	2450.7	2486.7	2493.7	2490.3	2480.9
137.5°	2594.9	2624.0	2629.8	2627.4	2613.6
140°	2721.7	2750.8	2767.1	2767.1	2754.3
142.5°	2852.0	2881.1	2890.4	2893.8	2881.1
145°	2975.2	2998.5	3017.1	3020.6	3007.8
147.5°	3085.8	3114.8	3128.8	3134.6	3121.8
150°	3199.8	3219.5	3232.3	3242.8	3232.3
152.5°	3300.9	3320.7	3337.0	3349.8	3337.0
155°	3402.2	3411.4	3421.9	3438.2	3427.7
157.5°	3489.4	3496.3	3502.1	3525.4	3509.1
160°	3567.3	3574.3	3577.7	3597.6	3583.6
162.5°	3639.4	3639.4	3643.0	3665.0	3648.7
165°	3701.1	3697.5	3697.5	3720.8	3704.5
167.5°	3756.8	3746.4	3746.4	3769.7	3753.4
170°	3798.8	3789.5	3786.0	3809.2	3789.5
172.5°	3827.8	3818.5	3815.1	3838.4	3818.5
175°	3851.1	3841.8	3834.8	3858.1	3838.4
177.5°	3863.9	3854.6	3847.6	3867.4	3847.6
180°	3858.1	3858.1	3858.1	3858.1	3858.1

TEST NUMBER: P911610

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.59	12.41	12.56	13.39	14.68	7.55	8.38	8.53	9.36	10.65
	3H	13.27	14.00	14.25	14.99	16.30	8.74	9.48	9.73	10.47	11.78
	4H	13.88	14.57	14.88	15.57	16.89	9.19	9.89	10.19	10.88	12.20
	6H	14.30	14.94	15.31	15.94	17.27	9.52	10.16	10.52	11.15	12.48
	8H	14.43	15.04	15.44	16.05	17.38	9.61	10.21	10.62	11.23	12.56
	12H	14.49	15.07	15.51	16.08	17.43	9.65	10.23	10.67	11.24	12.59
4H	2H	11.61	12.30	12.61	13.30	14.61	8.15	8.85	9.15	9.84	11.16
	3H	13.44	14.02	14.45	15.04	16.37	9.50	10.08	10.51	11.10	12.43
	4H	14.13	14.66	15.15	15.68	17.03	10.05	10.58	11.07	11.59	12.95
	6H	14.65	15.10	15.68	16.14	17.49	10.47	10.92	11.50	11.96	13.31
	8H	14.83	15.25	15.86	16.28	17.65	10.60	11.02	11.63	12.05	13.42
	12H	14.92	15.31	15.97	16.35	17.72	10.66	11.05	11.71	12.09	13.46
8H	4H	14.10	14.52	15.13	15.56	16.92	10.33	10.75	11.36	11.79	13.15
	6H	14.67	15.02	15.72	16.09	17.46	10.85	11.20	11.90	12.27	13.64
	8H	14.89	15.19	15.95	16.25	17.64	11.04	11.35	12.10	12.41	13.79
	12H	15.03	15.30	16.09	16.35	17.78	11.16	11.43	12.23	12.49	13.91
12H	4H	14.05	14.43	15.10	15.48	16.85	10.34	10.72	11.38	11.76	13.14
	6H	14.64	14.95	15.71	16.01	17.39	10.90	11.21	11.96	12.27	13.65
	8H	14.87	15.14	15.93	16.19	17.62	11.11	11.38	12.18	12.44	13.86

END OF REPORT