

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911642

Luminaire Tested: DFN2DIP-PN4F0-120D100US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911642
REPORT IS A COMBINATION OF REPORTS P899734 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-120D100US850-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21126.4 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 201.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911642

CATALOG NUMBER: DFN2DIP-PN4F0-120D100US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911642

CATALOG NUMBER: DFN2DIP-PN4F0-120D100US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38
4	76	66	58	52	71	61	55	49	53	48	44	46	42	38	38	36	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4015	4015	4015
5°	4021	3952	3977
10°	3981	3875	3849
15°	3927	3747	3649
20°	3854	3571	3404
25°	3780	3374	3168
30°	3680	3171	2867
35°	3583	2954	2604
40°	3483	2728	2301
45°	3368	2478	2027
50°	3248	2226	1759
55°	3124	1956	1501
60°	2979	1673	1237
65°	2813	1386	1114
70°	2612	1119	1009
75°	2359	987	919
80°	1993	830	800
85°	1388	557	606

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3368 cd/sqm

TEST NUMBER: P911642

CATALOG NUMBER: DFN2DIP-PN4F0-120D100US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	515.5	2.4
10°-20°	1415.1	6.7
20°-30°	1986.8	9.4
30°-40°	2165.7	10.3
40°-50°	1990.5	9.4
50°-60°	1563.2	7.4
60°-70°	1017.5	4.8
70°-80°	523.8	2.5
80°-90°	143.7	0.7
90°-100°	217.0	1.0
100°-110°	689.6	3.3
110°-120°	1180.1	5.6
120°-130°	1552.0	7.3
130°-140°	1742.1	8.2
140°-150°	1708.3	8.1
150°-160°	1433.0	6.8
160°-170°	950.4	4.5
170°-180°	332.2	1.6
0°-30°	3917.3	18.5
0°-40°	6083.0	28.8
0°-60°	9636.8	45.6
0°-90°	11321.7	53.6
90°-120°	2086.7	9.9
90°-150°	7089.1	33.6
90°-180°	9805.0	46.4
0°-180°	21126.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5500	5500	5500	5500	5500	
5°	5500	5475	5410	5455	5440	522
15°	5231	5176	5008	4913	4863	1474
25°	4749	4589	4261	4057	3982	2184
35°	4092	3838	3400	3086	2976	2561
45°	3345	3011	2489	2135	2016	2583
55°	2543	2155	1618	1319	1225	2273
65°	1717	1314	866	697	682	1703
75°	916	567	398	363	358	969
85°	214	109	94	94	94	246
90°	3	38	104	97	100	21
95°	154	184	189	189	184	172
105°	637	645	651	657	657	672
115°	1184	1201	1196	1193	1184	1171
125°	1722	1749	1740	1731	1728	1539
135°	2228	2261	2267	2264	2255	1722
145°	2705	2726	2743	2746	2734	1690
155°	3093	3101	3111	3126	3116	1424
165°	3365	3361	3361	3383	3368	949
175°	3501	3493	3486	3507	3489	333
180°	3507	3507	3507	3507	3507	

TEST NUMBER: P911642

CATALOG NUMBER: DFN2DIP-PN4F0-120D100US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5500.2	5500.2	5500.2	5500.2	5500.2
2.5°	5525.0	5500.2	5445.3	5495.4	5485.3
5°	5500.2	5475.4	5410.4	5455.3	5440.5
7.5°	5455.3	5425.7	5356.0	5375.5	5350.7
10°	5395.6	5360.8	5261.4	5246.1	5216.6
12.5°	5321.1	5276.3	5141.5	5112.0	5057.2
15°	5231.4	5176.5	5007.5	4912.9	4863.3
17.5°	5126.8	5047.1	4837.9	4728.7	4648.9
20°	5007.5	4907.7	4658.9	4534.8	4424.9
22.5°	4878.0	4763.5	4474.6	4305.6	4231.2
25°	4748.7	4589.2	4260.7	4056.8	3981.9
27.5°	4594.5	4424.9	4061.6	3827.7	3713.0
30°	4430.2	4240.7	3842.5	3588.9	3454.3
32.5°	4270.8	4041.5	3633.9	3335.0	3210.3
35°	4091.8	3837.7	3399.9	3086.2	2976.3
37.5°	3917.4	3643.4	3180.7	2836.9	2712.8
40°	3733.1	3434.8	2951.6	2598.3	2468.9
42.5°	3544.0	3225.6	2722.9	2354.3	2230.2
45°	3345.0	3011.3	2488.9	2135.2	2015.7
47.5°	3155.9	2802.7	2265.0	1911.3	1801.9
50°	2946.8	2593.5	2045.9	1702.1	1598.1
52.5°	2742.4	2369.0	1836.7	1508.2	1413.8
55°	2543.4	2155.2	1617.6	1319.2	1224.7
57.5°	2339.4	1941.3	1423.7	1144.9	1065.2
60°	2130.4	1732.1	1219.3	965.9	886.2
62.5°	1926.6	1528.3	1045.1	806.5	766.8
65°	1717.4	1313.9	866.1	697.1	681.8
67.5°	1518.3	1114.8	697.1	612.1	597.3
70°	1309.2	921.0	577.2	527.6	507.5
72.5°	1110.1	741.5	482.6	443.0	433.1
75°	915.7	567.1	398.2	363.3	358.5
77.5°	722.0	402.9	313.7	293.7	283.6
80°	542.4	288.9	238.7	219.1	219.1
82.5°	378.2	194.3	164.2	154.2	154.2
85°	213.9	109.3	94.5	94.5	94.5
87.5°	79.7	39.6	39.6	34.8	34.8
90°	3.2	38.0	103.6	97.3	100.5
92.5°	65.5	88.8	92.0	95.2	95.2
95°	154.4	184.0	189.3	189.3	184.0
97.5°	257.0	284.5	296.1	296.1	296.1
100°	375.4	399.7	408.1	408.1	405.0
102.5°	500.2	518.1	529.8	532.9	529.8
105°	636.6	645.0	651.3	656.6	656.6
107.5°	771.9	784.6	784.6	786.7	771.9
110°	903.1	919.9	919.9	919.9	911.5

TEST NUMBER: P911642

CATALOG NUMBER: DFN2DIP-PN4F0-120D100US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1044.7	1062.6	1059.5	1051.0	1044.7
115°	1184.3	1201.2	1195.9	1192.7	1184.3
117.5°	1322.8	1346.1	1331.2	1322.8	1314.3
120°	1462.3	1485.6	1462.3	1462.3	1452.9
122.5°	1589.2	1618.8	1604.1	1595.6	1589.2
125°	1722.5	1748.9	1740.5	1730.9	1727.8
127.5°	1852.6	1885.3	1873.7	1861.0	1852.6
130°	1974.1	2012.2	2007.0	2000.5	1989.0
132.5°	2110.5	2140.1	2142.3	2127.5	2119.0
135°	2227.9	2260.7	2267.0	2263.9	2255.4
137.5°	2359.1	2385.5	2390.8	2388.7	2375.9
140°	2474.3	2500.7	2515.5	2515.5	2503.9
142.5°	2592.7	2619.1	2627.6	2630.8	2619.1
145°	2704.7	2725.9	2742.9	2746.0	2734.4
147.5°	2805.2	2831.7	2844.4	2849.7	2838.0
150°	2908.9	2926.9	2938.5	2947.9	2938.5
152.5°	3000.8	3018.8	3033.7	3045.3	3033.7
155°	3092.9	3101.3	3110.9	3125.6	3116.1
157.5°	3172.2	3178.5	3183.8	3204.9	3190.1
160°	3243.0	3249.4	3252.5	3270.4	3257.8
162.5°	3308.6	3308.6	3311.7	3331.8	3317.0
165°	3364.6	3361.4	3361.4	3382.6	3367.8
167.5°	3415.4	3405.8	3405.8	3427.0	3412.2
170°	3453.4	3445.0	3441.8	3463.0	3445.0
172.5°	3479.8	3471.4	3468.2	3489.4	3471.4
175°	3501.0	3492.6	3486.3	3507.3	3489.4
177.5°	3512.6	3504.2	3497.8	3515.8	3497.8
180°	3507.3	3507.3	3507.3	3507.3	3507.3

TEST NUMBER: P911642

CATALOG NUMBER: DFN2DIP-PN4F0-120D100US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.31	13.17	13.24	14.12	15.34	8.28	9.14	9.21	10.08	11.30
	3H	13.99	14.76	14.94	15.72	16.96	9.47	10.24	10.41	11.19	12.44
	4H	14.61	15.33	15.56	16.29	17.55	9.92	10.65	10.88	11.61	12.86
	6H	15.03	15.70	16.00	16.67	17.93	10.24	10.91	11.21	11.88	13.14
	8H	15.16	15.80	16.14	16.78	18.04	10.34	10.97	11.31	11.95	13.22
	12H	15.22	15.83	16.21	16.80	18.09	10.38	10.99	11.36	11.96	13.25
4H	2H	12.33	13.06	13.30	14.02	15.27	8.88	9.60	9.84	10.56	11.82
	3H	14.17	14.77	15.14	15.76	17.03	10.23	10.84	11.20	11.82	13.09
	4H	14.86	15.42	15.85	16.40	17.69	10.78	11.33	11.76	12.31	13.61
	6H	15.38	15.86	16.38	16.86	18.16	11.20	11.68	12.20	12.68	13.97
	8H	15.56	16.00	16.56	17.00	18.31	11.33	11.78	12.33	12.77	14.08
	12H	15.66	16.06	16.67	17.07	18.38	11.40	11.80	12.41	12.81	14.12
8H	4H	14.83	15.28	15.83	16.28	17.58	11.07	11.51	12.06	12.51	13.81
	6H	15.40	15.77	16.43	16.81	18.11	11.59	11.95	12.61	12.99	14.30
	8H	15.62	15.95	16.65	16.97	18.30	11.78	12.10	12.81	13.13	14.45
	12H	15.77	16.05	16.80	17.07	18.44	11.90	12.18	12.93	13.20	14.57
12H	4H	14.79	15.19	15.80	16.20	17.51	11.07	11.47	12.09	12.49	13.80
	6H	15.38	15.70	16.41	16.73	18.05	11.64	11.96	12.66	12.99	14.31
	8H	15.60	15.89	16.64	16.91	18.28	11.85	12.13	12.88	13.15	14.52

END OF REPORT