

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922348

Luminaire Tested: DFN2DIP-PN4F0-070D040US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922348
REPORT IS A COMBINATION OF REPORTS P899615 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-070D040US940-FLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9336.3 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 97
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922348
CATALOG NUMBER: DFN2DIP-PN4F0-070D040US940-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P922348

CATALOG NUMBER: DFN2DIP-PN4F0-070D040US940-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66				66
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	61	60	56				56
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	55	53	51	47				47
3	84	75	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	40				40
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37	34				34
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	32	30				30
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	29	26				26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	25	23				23
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21				21
9	53	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19				19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17				17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1773	1773	1773
5°	1776	1748	1760
10°	1761	1725	1737
15°	1735	1697	1700
20°	1700	1658	1662
25°	1666	1611	1618
30°	1622	1567	1563
35°	1581	1516	1504
40°	1530	1463	1448
45°	1479	1411	1390
50°	1424	1357	1324
55°	1365	1293	1263
60°	1300	1218	1193
65°	1228	1140	1110
70°	1137	1045	1022
75°	1011	932	941
80°	858	788	784
85°	621	538	525

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1479 cd/sqm



TEST NUMBER: P922348

CATALOG NUMBER: DFN2DIP-PN4F0-070D040US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.6	2.4
10°-20°	643.2	6.9
20°-30°	945.2	10.1
30°-40°	1097.8	11.8
40°-50°	1096.5	11.7
50°-60°	956.1	10.2
60°-70°	706.8	7.6
70°-80°	399.9	4.3
80°-90°	108.8	1.2
90°-100°	69.8	0.7
100°-110°	221.8	2.4
110°-120°	379.5	4.1
120°-130°	499.2	5.3
130°-140°	560.3	6.0
140°-150°	549.4	5.9
150°-160°	460.9	4.9
160°-170°	305.7	3.3
170°-180°	106.8	1.1
0°-30°	1817.0	19.5
0°-40°	2914.9	31.2
0°-60°	4967.4	53.2
0°-90°	6182.8	66.2
90°-120°	671.2	7.2
90°-150°	2280.1	24.4
90°-180°	3153.0	33.8
0°-180°	9336.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2429	2429	2429	2429	2429	
5°	2429	2420	2394	2412	2408	231
15°	2312	2298	2268	2277	2266	651
25°	2093	2074	2034	2039	2034	963
35°	1805	1782	1745	1730	1719	1127
45°	1469	1453	1418	1392	1383	1134
55°	1112	1098	1070	1042	1030	994
65°	750	736	712	691	680	741
75°	392	388	376	362	367	419
85°	96	94	91	84	82	107
90°	1	12	33	31	32	9
95°	50	59	61	61	59	55
105°	205	207	210	211	211	216
115°	381	386	385	384	381	377
125°	554	562	560	557	556	495
135°	717	727	729	728	725	554
145°	870	877	882	883	880	544
155°	995	998	1000	1005	1002	458
165°	1082	1081	1081	1088	1083	305
175°	1126	1123	1121	1128	1122	107
180°	1128	1128	1128	1128	1128	



TEST NUMBER: P922348

CATALOG NUMBER: DFN2DIP-PN4F0-070D040US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2428.8	2428.8	2428.8	2428.8	2428.8
2.5°	2442.9	2431.2	2405.5	2428.8	2424.3
5°	2428.8	2419.7	2393.9	2412.4	2408.0
7.5°	2412.4	2398.5	2372.8	2391.7	2386.9
10°	2386.9	2370.5	2342.5	2361.2	2354.2
12.5°	2351.7	2337.9	2309.9	2321.5	2316.8
15°	2312.1	2298.2	2267.7	2277.2	2265.5
17.5°	2263.0	2249.2	2218.7	2230.3	2218.7
20°	2209.2	2195.4	2162.7	2169.6	2160.4
22.5°	2155.7	2134.7	2104.2	2104.2	2099.4
25°	2092.6	2073.9	2034.3	2038.8	2034.3
27.5°	2022.4	2006.1	1975.9	1968.9	1957.2
30°	1952.6	1933.7	1898.8	1891.9	1882.4
32.5°	1877.7	1863.9	1826.4	1812.3	1802.9
35°	1805.4	1782.1	1744.6	1730.5	1718.9
37.5°	1723.6	1702.5	1665.1	1648.8	1637.1
40°	1639.6	1620.8	1583.3	1562.5	1553.1
42.5°	1557.8	1539.0	1501.8	1478.3	1464.4
45°	1469.1	1452.8	1417.6	1392.0	1382.6
47.5°	1382.6	1366.3	1328.8	1303.1	1289.2
50°	1291.5	1279.8	1247.1	1214.4	1202.7
52.5°	1202.7	1186.4	1156.2	1130.4	1114.0
55°	1111.8	1097.7	1069.7	1041.7	1030.0
57.5°	1020.7	1009.0	978.5	950.5	941.1
60°	929.4	920.2	887.6	861.8	854.9
62.5°	840.7	824.4	801.1	777.8	768.4
65°	749.8	735.7	712.4	691.3	679.7
67.5°	656.4	644.5	623.7	607.3	597.9
70°	569.9	560.5	539.4	523.1	513.9
72.5°	481.2	471.8	460.1	443.8	436.8
75°	392.3	387.8	375.9	362.0	366.8
77.5°	313.0	303.5	298.8	291.9	285.0
80°	233.6	231.2	226.5	219.5	214.8
82.5°	158.8	158.8	156.6	147.2	147.2
85°	95.7	93.5	91.2	84.0	81.8
87.5°	42.1	37.5	32.7	25.8	23.3
90°	1.0	12.2	33.3	31.3	32.3
92.5°	21.0	28.5	29.6	30.6	30.6
95°	49.7	59.2	60.9	60.9	59.2
97.5°	82.7	91.5	95.2	95.2	95.2
100°	120.7	128.6	131.3	131.3	130.3
102.5°	160.9	166.7	170.4	171.4	170.4
105°	204.7	207.4	209.5	211.2	211.2
107.5°	248.3	252.4	252.4	253.0	248.3
110°	290.4	295.9	295.9	295.9	293.2



TEST NUMBER: P922348

CATALOG NUMBER: DFN2DIP-PN4F0-070D040US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	336.0	341.8	340.7	338.0	336.0
115°	380.8	386.4	384.6	383.6	380.8
117.5°	425.4	432.9	428.2	425.4	422.8
120°	470.4	477.8	470.4	470.4	467.3
122.5°	511.1	520.7	515.9	513.2	511.1
125°	554.0	562.5	559.8	556.7	555.7
127.5°	595.8	606.4	602.6	598.5	595.8
130°	634.9	647.2	645.5	643.5	639.7
132.5°	678.8	688.3	689.0	684.2	681.5
135°	716.6	727.1	729.2	728.1	725.4
137.5°	758.8	767.2	768.9	768.2	764.2
140°	795.8	804.3	809.0	809.0	805.3
142.5°	833.9	842.4	845.1	846.1	842.4
145°	870.0	876.7	882.2	883.2	879.5
147.5°	902.2	910.7	914.8	916.5	912.8
150°	935.6	941.4	945.1	948.2	945.1
152.5°	965.2	970.9	975.7	979.5	975.7
155°	994.7	997.5	1000.5	1005.3	1002.2
157.5°	1020.3	1022.3	1024.0	1030.8	1026.0
160°	1043.0	1045.1	1046.1	1051.9	1047.8
162.5°	1064.1	1064.1	1065.1	1071.6	1066.8
165°	1082.2	1081.1	1081.1	1087.9	1083.2
167.5°	1098.5	1095.4	1095.4	1102.2	1097.4
170°	1110.7	1108.0	1107.0	1113.7	1108.0
172.5°	1119.2	1116.5	1115.4	1122.3	1116.5
175°	1126.1	1123.3	1121.2	1128.0	1122.3
177.5°	1129.8	1127.0	1125.0	1130.8	1125.0
180°	1128.0	1128.0	1128.0	1128.0	1128.0



TEST NUMBER: P922348
 CATALOG NUMBER: DFN2DIP-PN4F0-070D040US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.64	11.67	11.45	12.50	13.52	10.20	11.23	11.01	12.06	13.08
	3H	12.32	13.24	13.14	14.08	15.13	11.84	12.76	12.65	13.60	14.64
	4H	12.92	13.79	13.75	14.63	15.69	12.43	13.30	13.26	14.15	15.20
	6H	13.33	14.13	14.17	14.98	16.06	12.84	13.64	13.68	14.49	15.56
	8H	13.44	14.21	14.29	15.08	16.15	12.95	13.71	13.80	14.58	15.66
	12H	13.49	14.22	14.35	15.09	16.19	12.99	13.72	13.85	14.59	15.69
4H	2H	11.13	12.00	11.96	12.84	13.90	10.77	11.65	11.61	12.49	13.55
	3H	13.01	13.74	13.86	14.62	15.69	12.61	13.34	13.46	14.21	15.29
	4H	13.73	14.40	14.60	15.27	16.37	13.32	13.98	14.18	14.85	15.95
	6H	14.26	14.83	15.14	15.73	16.84	13.84	14.41	14.71	15.31	16.41
	8H	14.42	14.95	15.30	15.85	16.96	13.99	14.52	14.87	15.42	16.53
	12H	14.50	14.98	15.40	15.89	17.02	14.06	14.54	14.96	15.45	16.58
8H	4H	13.94	14.48	14.83	15.37	16.49	13.57	14.11	14.45	15.00	16.12
	6H	14.59	15.03	15.49	15.96	17.08	14.21	14.65	15.12	15.59	16.71
	8H	14.81	15.20	15.73	16.13	17.27	14.42	14.82	15.34	15.75	16.88
	12H	14.95	15.30	15.87	16.22	17.40	14.55	14.90	15.47	15.82	17.00
12H	4H	13.94	14.42	14.84	15.33	16.46	13.57	14.06	14.48	14.97	16.09
	6H	14.62	15.01	15.54	15.94	17.07	14.25	14.65	15.17	15.57	16.71
	8H	14.87	15.22	15.79	16.14	17.32	14.50	14.84	15.42	15.76	16.95