

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922378

Luminaire Tested: DFN2DIP-PN4F0-070D110US940-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P922378  
REPORT IS A COMBINATION OF REPORTS P899742 AND P896497  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-070D110US940-RLLFLL  
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13986.4 lumens  
Efficiency: N/A  
Efficacy: 88.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 158.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9789  
Total Harmonic Distortion (THDi): 0.074  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P922378  
CATALOG NUMBER: DFN2DIP-PN4F0-070D110US940-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P922378

CATALOG NUMBER: DFN2DIP-PN4F0-070D110US940-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				38
1	95	91	88	84	87	83	80	77	68	66	64	53	52	51	40	40	39	33				33
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28				28
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24				24
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21				21
5	67	56	48	43	61	51	45	40	42	37	34	34	30	28	26	24	22	19				19
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	20	16				16
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15				15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13				13
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12				12
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13	11				11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1883	1883	1883
5°	1886	1854	1865
10°	1868	1817	1805
15°	1842	1758	1712
20°	1808	1675	1597
25°	1773	1582	1486
30°	1726	1487	1345
35°	1680	1385	1221
40°	1634	1280	1079
45°	1580	1162	951
50°	1524	1044	825
55°	1465	917	704
60°	1397	785	580
65°	1319	650	522
70°	1225	525	473
75°	1106	463	431
80°	935	389	375
85°	651	261	284

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 2428 cd/sqm



TEST NUMBER: P922378

CATALOG NUMBER: DFN2DIP-PN4F0-070D110US940-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	241.8	1.7
10°-20°	663.7	4.7
20°-30°	931.9	6.7
30°-40°	1015.8	7.3
40°-50°	933.6	6.7
50°-60°	733.2	5.2
60°-70°	477.3	3.4
70°-80°	245.7	1.8
80°-90°	71.5	0.5
90°-100°	192.0	1.4
100°-110°	609.9	4.4
110°-120°	1043.8	7.5
120°-130°	1372.7	9.8
130°-140°	1540.8	11.0
140°-150°	1511.0	10.8
150°-160°	1267.5	9.1
160°-170°	840.6	6.0
170°-180°	293.8	2.1
0°-30°	1837.4	13.1
0°-40°	2853.2	20.4
0°-60°	4520.0	32.3
0°-90°	5314.5	38.0
90°-120°	1845.7	13.2
90°-150°	6270.1	44.8
90°-180°	8672.0	62.0
0°-180°	13986.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2580	2580	2580	2580	2580	
5°	2580	2568	2538	2559	2552	245
15°	2454	2428	2349	2304	2281	691
25°	2227	2152	1998	1903	1868	1024
35°	1919	1800	1595	1448	1396	1201
45°	1569	1412	1167	1002	946	1212
55°	1193	1011	759	619	574	1066
65°	806	616	406	327	320	799
75°	430	266	187	170	168	454
85°	100	51	44	44	44	115
90°	3	34	92	86	89	14
95°	136	163	167	167	163	152
105°	563	570	576	581	581	594
115°	1048	1062	1058	1055	1048	1036
125°	1524	1547	1539	1531	1528	1361
135°	1970	2000	2005	2002	1995	1523
145°	2392	2411	2426	2429	2418	1495
155°	2736	2743	2752	2765	2756	1259
165°	2976	2973	2973	2992	2979	840
175°	3097	3089	3083	3102	3086	294
180°	3102	3102	3102	3102	3102	



TEST NUMBER: P922378

CATALOG NUMBER: DFN2DIP-PN4F0-070D110US940-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2579.8	2579.8	2579.8	2579.8	2579.8
2.5°	2591.4	2579.8	2554.0	2577.6	2572.9
5°	2579.8	2568.1	2537.7	2558.8	2551.8
7.5°	2558.8	2544.9	2512.2	2521.3	2509.7
10°	2530.8	2514.4	2467.8	2460.7	2446.8
12.5°	2495.8	2474.8	2411.6	2397.7	2371.9
15°	2453.7	2427.9	2348.7	2304.4	2281.1
17.5°	2404.7	2367.3	2269.2	2217.9	2180.5
20°	2348.7	2301.9	2185.2	2127.0	2075.5
22.5°	2288.0	2234.3	2098.7	2019.5	1984.6
25°	2227.3	2152.5	1998.4	1902.8	1867.7
27.5°	2155.0	2075.5	1905.1	1795.4	1741.6
30°	2078.0	1989.0	1802.2	1683.4	1620.2
32.5°	2003.1	1895.7	1704.4	1564.2	1505.7
35°	1919.1	1800.0	1594.7	1447.6	1396.1
37.5°	1837.5	1708.9	1491.9	1330.6	1272.5
40°	1751.0	1611.1	1384.4	1218.7	1158.0
42.5°	1662.3	1513.0	1277.1	1104.2	1046.1
45°	1569.0	1412.4	1167.4	1001.5	945.5
47.5°	1480.2	1314.6	1062.4	896.4	845.2
50°	1382.2	1216.5	959.6	798.3	749.6
52.5°	1286.3	1111.2	861.5	707.4	663.1
55°	1192.9	1010.8	758.7	618.8	574.4
57.5°	1097.3	910.5	667.8	537.0	499.6
60°	999.3	812.4	571.9	453.1	415.6
62.5°	903.6	716.8	490.2	378.3	359.6
65°	805.5	616.3	406.3	327.0	319.8
67.5°	712.1	522.9	327.0	287.0	280.2
70°	614.0	431.9	270.7	247.4	238.0
72.5°	520.7	347.8	226.4	207.9	203.1
75°	429.5	266.0	186.7	170.4	168.2
77.5°	338.6	189.0	147.1	137.7	133.0
80°	254.4	135.5	112.0	102.8	102.8
82.5°	177.4	91.1	77.0	72.3	72.3
85°	100.3	51.3	44.3	44.3	44.3
87.5°	37.4	18.5	18.5	16.3	16.3
90°	2.8	33.7	91.7	86.1	88.8
92.5°	58.0	78.6	81.3	84.2	84.2
95°	136.5	162.7	167.4	167.4	162.7
97.5°	227.3	251.6	261.9	261.9	261.9
100°	332.0	353.5	361.0	361.0	358.2
102.5°	442.4	458.2	468.6	471.4	468.6
105°	563.0	570.5	576.1	580.8	580.8
107.5°	682.7	693.9	693.9	695.8	682.7
110°	798.7	813.7	813.7	813.7	806.2



TEST NUMBER: P922378

CATALOG NUMBER: DFN2DIP-PN4F0-070D110US940-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	924.0	939.9	937.1	929.6	924.0
115°	1047.5	1062.4	1057.7	1055.0	1047.5
117.5°	1170.0	1190.5	1177.4	1170.0	1162.5
120°	1293.4	1314.0	1293.4	1293.4	1285.0
122.5°	1405.7	1431.8	1418.7	1411.2	1405.7
125°	1523.5	1546.8	1539.4	1531.0	1528.1
127.5°	1638.5	1667.5	1657.2	1646.0	1638.5
130°	1746.1	1779.8	1775.0	1769.4	1759.2
132.5°	1866.7	1892.9	1894.8	1881.7	1874.2
135°	1970.5	1999.5	2005.1	2002.3	1994.8
137.5°	2086.5	2109.9	2114.5	2112.6	2101.5
140°	2188.4	2211.8	2224.9	2224.9	2214.7
142.5°	2293.2	2316.6	2324.1	2326.8	2316.6
145°	2392.3	2411.0	2426.0	2428.8	2418.5
147.5°	2481.2	2504.5	2515.8	2520.4	2510.2
150°	2572.9	2588.7	2599.0	2607.5	2599.0
152.5°	2654.2	2670.0	2683.2	2693.5	2683.2
155°	2735.6	2743.0	2751.5	2764.6	2756.1
157.5°	2805.7	2811.3	2815.9	2834.7	2821.5
160°	2868.4	2874.0	2876.7	2892.7	2881.5
162.5°	2926.3	2926.3	2929.2	2946.9	2933.8
165°	2975.9	2973.1	2973.1	2991.8	2978.7
167.5°	3020.8	3012.4	3012.4	3031.1	3018.0
170°	3054.5	3047.0	3044.2	3062.8	3047.0
172.5°	3077.8	3070.3	3067.6	3086.3	3070.3
175°	3096.6	3089.1	3083.4	3102.2	3086.3
177.5°	3106.8	3099.3	3093.7	3109.7	3093.7
180°	3102.2	3102.2	3102.2	3102.2	3102.2



TEST NUMBER: P922378  
 CATALOG NUMBER: DFN2DIP-PN4F0-070D110US940-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.12	8.86	9.18	9.92	11.35	4.08	4.82	5.14	5.88	7.32
	3H	9.79	10.45	10.86	11.52	12.97	5.26	5.93	6.33	6.99	8.45
	4H	10.40	11.02	11.48	12.09	13.55	5.71	6.34	6.79	7.41	8.87
	6H	10.82	11.39	11.90	12.47	13.94	6.03	6.60	7.12	7.68	9.15
	8H	10.94	11.49	12.03	12.58	14.04	6.12	6.66	7.21	7.75	9.22
	12H	11.00	11.52	12.10	12.60	14.09	6.16	6.68	7.25	7.76	9.25
4H	2H	8.12	8.75	9.21	9.82	11.28	4.67	5.29	5.75	6.36	7.82
	3H	9.95	10.47	11.04	11.57	13.04	6.01	6.53	7.10	7.63	9.10
	4H	10.64	11.12	11.74	12.20	13.70	6.55	7.03	7.65	8.12	9.61
	6H	11.15	11.56	12.26	12.67	14.16	6.97	7.38	8.08	8.49	9.98
	8H	11.33	11.71	12.43	12.81	14.31	7.10	7.48	8.20	8.58	10.09
	12H	11.42	11.77	12.54	12.88	14.39	7.16	7.51	8.28	8.62	10.13
8H	4H	10.60	10.98	11.71	12.08	13.59	6.83	7.21	7.94	8.32	9.82
	6H	11.17	11.48	12.29	12.63	14.13	7.35	7.66	8.47	8.81	10.31
	8H	11.38	11.66	12.52	12.79	14.31	7.54	7.81	8.67	8.94	10.46
	12H	11.52	11.76	12.66	12.88	14.44	7.65	7.90	8.79	9.02	10.58
12H	4H	10.55	10.89	11.67	12.01	13.52	6.83	7.18	7.95	8.29	9.80
	6H	11.14	11.42	12.27	12.54	14.06	7.40	7.67	8.53	8.80	10.32
	8H	11.36	11.60	12.50	12.72	14.28	7.60	7.85	8.74	8.97	10.53