

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914250

Luminaire Tested: DFN2DIP-PN4F0-090D070US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914250
REPORT IS A COMBINATION OF REPORTS P899674 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-090D070US927-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10967.8 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 140.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914250
CATALOG NUMBER: DFN2DIP-PN4F0-090D070US927-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P914250
 CATALOG NUMBER: DFN2DIP-PN4F0-090D070US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	92	88	92	89	86	83	76	74	72	65	63	62	55	54	53	48
2	91	84	78	73	84	78	73	69	68	64	60	58	55	53	49	47	45	41
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39	35
4	77	66	58	52	71	62	55	50	54	49	44	46	42	39	39	36	34	31
5	71	59	51	45	65	55	48	43	48	43	39	42	38	34	36	33	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27	24
7	60	48	41	35	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	44	36	31	52	41	35	30	37	31	27	32	28	24	28	24	22	19
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	22	20	18
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2151	2151	2151
5°	2154	2117	2131
10°	2133	2076	2062
15°	2104	2008	1955
20°	2065	1913	1824
25°	2025	1807	1697
30°	1972	1699	1536
35°	1919	1582	1395
40°	1866	1462	1233
45°	1804	1328	1086
50°	1740	1192	942
55°	1673	1048	804
60°	1596	897	663
65°	1507	743	597
70°	1399	599	541
75°	1264	529	493
80°	1068	445	429
85°	743	298	325

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1804 cd/sqm



TEST NUMBER: P914250

CATALOG NUMBER: DFN2DIP-PN4F0-090D070US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.2	2.5
10°-20°	758.1	6.9
20°-30°	1064.4	9.7
30°-40°	1160.3	10.6
40°-50°	1066.4	9.7
50°-60°	837.5	7.6
60°-70°	545.1	5.0
70°-80°	280.6	2.6
80°-90°	76.6	0.7
90°-100°	108.5	1.0
100°-110°	344.8	3.1
110°-120°	590.1	5.4
120°-130°	776.1	7.1
130°-140°	871.1	7.9
140°-150°	854.2	7.8
150°-160°	716.6	6.5
160°-170°	475.2	4.3
170°-180°	166.1	1.5
0°-30°	2098.7	19.1
0°-40°	3258.9	29.7
0°-60°	5162.8	47.1
0°-90°	6065.2	55.3
90°-120°	1043.4	9.5
90°-150°	3544.8	32.3
90°-180°	4903.0	44.7
0°-180°	10967.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2947	2947	2947	2947	2947	
5°	2947	2933	2899	2923	2915	279
15°	2803	2773	2683	2632	2606	790
25°	2544	2459	2283	2173	2133	1170
35°	2192	2056	1822	1653	1595	1372
45°	1792	1613	1333	1144	1080	1384
55°	1363	1155	867	707	656	1218
65°	920	704	464	373	365	912
75°	491	304	213	195	192	519
85°	114	58	51	51	51	132
90°	2	19	52	49	50	11
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1372	1373	1367	845
155°	1546	1551	1556	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	



TEST NUMBER: P914250

CATALOG NUMBER: DFN2DIP-PN4F0-090D070US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2946.7	2946.7	2946.7	2946.7	2946.7
2.5°	2960.0	2946.7	2917.2	2944.1	2938.8
5°	2946.7	2933.4	2898.6	2922.6	2914.7
7.5°	2922.6	2906.8	2869.4	2879.9	2866.6
10°	2890.7	2872.0	2818.8	2810.6	2794.7
12.5°	2850.7	2826.7	2754.6	2738.7	2709.3
15°	2802.7	2773.3	2682.7	2632.0	2605.5
17.5°	2746.7	2704.0	2591.9	2533.3	2490.6
20°	2682.7	2629.2	2495.9	2429.5	2370.6
22.5°	2613.4	2552.0	2397.2	2306.7	2266.8
25°	2544.1	2458.6	2282.7	2173.4	2133.3
27.5°	2461.5	2370.6	2176.0	2050.6	1989.2
30°	2373.5	2271.9	2058.6	1922.8	1850.6
32.5°	2288.0	2165.2	1946.8	1786.7	1719.9
35°	2192.1	2056.0	1821.5	1653.4	1594.6
37.5°	2098.7	1951.9	1704.1	1519.9	1453.4
40°	2000.0	1840.2	1581.3	1392.0	1322.7
42.5°	1898.7	1728.1	1458.7	1261.3	1194.8
45°	1792.1	1613.3	1333.4	1143.8	1079.9
47.5°	1690.8	1501.5	1213.5	1023.9	965.4
50°	1578.7	1389.4	1096.1	911.9	856.1
52.5°	1469.3	1269.2	984.0	808.0	757.4
55°	1362.6	1154.6	866.6	706.8	656.1
57.5°	1253.4	1040.1	762.8	613.4	570.7
60°	1141.3	928.0	653.3	517.5	474.8
62.5°	1032.1	818.8	559.9	432.1	410.8
65°	920.0	703.9	464.0	373.4	365.3
67.5°	813.4	597.2	373.4	327.9	320.0
70°	701.4	493.4	309.3	282.7	271.9
72.5°	594.7	397.2	258.6	237.3	232.0
75°	490.6	303.9	213.3	194.6	192.1
77.5°	386.7	215.9	168.0	157.3	151.9
80°	290.6	154.8	127.9	117.4	117.4
82.5°	202.6	104.1	88.0	82.6	82.6
85°	114.5	58.5	50.6	50.6	50.6
87.5°	42.7	21.2	21.2	18.7	18.7
90°	1.6	19.0	51.8	48.6	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.7	94.7	92.0
97.5°	128.5	142.2	148.1	148.1	148.1
100°	187.7	199.9	204.1	204.1	202.5
102.5°	250.1	259.0	264.9	266.5	264.9
105°	318.3	322.5	325.7	328.4	328.4
107.5°	386.0	392.3	392.3	393.4	386.0
110°	451.5	460.0	460.0	460.0	455.7



TEST NUMBER: P914250

CATALOG NUMBER: DFN2DIP-PN4F0-090D070US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.4	531.4	529.8	525.5	522.4
115°	592.2	600.6	598.0	596.4	592.2
117.5°	661.4	673.0	665.7	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.1	797.8	794.6
125°	861.3	874.5	870.3	865.5	864.0
127.5°	926.3	942.7	936.9	930.6	926.3
130°	987.1	1006.1	1003.5	1000.4	994.5
132.5°	1055.3	1070.2	1071.2	1063.8	1059.5
135°	1114.0	1130.4	1133.6	1131.9	1127.7
137.5°	1179.6	1192.8	1195.4	1194.4	1188.0
140°	1237.2	1250.5	1257.8	1257.8	1252.0
142.5°	1296.4	1309.6	1313.8	1315.4	1309.6
145°	1352.5	1363.0	1371.5	1373.1	1367.3
147.5°	1402.7	1415.9	1422.3	1424.9	1419.1
150°	1454.5	1463.5	1469.3	1474.1	1469.3
152.5°	1500.5	1509.5	1516.9	1522.7	1516.9
155°	1546.5	1550.7	1555.5	1562.9	1558.1
157.5°	1586.2	1589.4	1592.0	1602.6	1595.1
160°	1621.6	1624.8	1626.3	1635.3	1629.0
162.5°	1654.4	1654.4	1656.0	1666.0	1658.6
165°	1682.4	1680.8	1680.8	1691.4	1683.9
167.5°	1707.8	1703.0	1703.0	1713.6	1706.2
170°	1726.8	1722.6	1721.0	1731.5	1722.6
172.5°	1740.0	1735.7	1734.2	1744.8	1735.7
175°	1750.6	1746.4	1743.2	1753.7	1744.8
177.5°	1756.4	1752.1	1749.0	1758.0	1749.0
180°	1753.7	1753.7	1753.7	1753.7	1753.7



TEST NUMBER: P914250
 CATALOG NUMBER: DFN2DIP-PN4F0-090D070US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.30	11.17	11.21	12.10	13.30	6.26	7.14	7.18	8.07	9.26
	3H	11.98	12.76	12.91	13.70	14.92	7.45	8.24	8.38	9.18	10.40
	4H	12.59	13.33	13.54	14.28	15.51	7.91	8.65	8.85	9.59	10.82
	6H	13.02	13.70	13.97	14.65	15.89	8.23	8.91	9.19	9.86	11.10
	8H	13.15	13.79	14.11	14.76	16.00	8.32	8.97	9.28	9.94	11.18
	12H	13.21	13.83	14.18	14.79	16.05	8.37	8.98	9.33	9.94	11.21
4H	2H	10.32	11.06	11.27	12.00	13.23	6.86	7.60	7.81	8.55	9.78
	3H	12.16	12.77	13.11	13.75	14.99	8.22	8.83	9.18	9.81	11.05
	4H	12.85	13.41	13.82	14.38	15.65	8.77	9.33	9.74	10.30	11.57
	6H	13.37	13.85	14.35	14.85	16.12	9.19	9.67	10.17	10.67	11.93
	8H	13.55	14.00	14.53	14.99	16.27	9.32	9.77	10.30	10.76	12.04
	12H	13.65	14.05	14.65	15.06	16.34	9.39	9.79	10.39	10.80	12.08
8H	4H	12.82	13.27	13.81	14.26	15.54	9.05	9.50	10.04	10.49	11.77
	6H	13.39	13.77	14.40	14.79	16.07	9.58	9.95	10.58	10.98	12.25
	8H	13.61	13.94	14.63	14.96	16.25	9.77	10.09	10.78	11.11	12.41
	12H	13.76	14.04	14.77	15.05	16.40	9.89	10.18	10.91	11.19	12.53
12H	4H	12.78	13.18	13.78	14.19	15.47	9.06	9.47	10.06	10.47	11.76
	6H	13.37	13.70	14.39	14.71	16.01	9.63	9.95	10.64	10.97	12.27
	8H	13.59	13.88	14.61	14.89	16.24	9.84	10.13	10.86	11.14	12.48