

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914255

Luminaire Tested: DFN2DIP-PN4F0-090D080US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914255
REPORT IS A COMBINATION OF REPORTS P901212 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-090D080US927-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12334.2 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 146.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914255

CATALOG NUMBER: DFN2DIP-PN4F0-090D080US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P914255

CATALOG NUMBER: DFN2DIP-PN4F0-090D080US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		55
1	98	94	90	87	90	87	84	81	73	71	69		61	59	58		50
2	90	83	77	72	82	76	71	67	65	61	58		54	52	49		44
3	82	73	66	60	75	68	62	57	58	53	49		48	45	42		40
4	75	65	57	51	69	60	54	48	51	46	42		43	40	37		36
5	69	58	50	44	64	54	47	42	46	41	37		39	35	32		32
6	64	52	44	39	59	49	42	37	42	36	32		36	31	28		30
7	59	47	40	34	55	44	37	32	38	33	29		32	28	25		27
8	55	43	36	30	51	40	33	29	35	29	26		30	26	23		25
9	51	39	32	27	47	37	30	26	32	27	23		28	23	20		23
10	48	36	29	24	44	34	28	23	30	24	21		25	21	19		22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2151	2151	2151
5°	2154	2117	2131
10°	2133	2076	2062
15°	2104	2008	1955
20°	2065	1913	1824
25°	2025	1807	1697
30°	1972	1699	1536
35°	1919	1582	1395
40°	1866	1462	1233
45°	1804	1328	1086
50°	1740	1192	942
55°	1673	1048	804
60°	1596	897	663
65°	1507	743	597
70°	1399	599	541
75°	1264	529	493
80°	1068	445	429
85°	743	298	325

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1804 cd/sqm

TEST NUMBER: P914255

CATALOG NUMBER: DFN2DIP-PN4F0-090D080US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.2	2.2
10°-20°	758.1	6.1
20°-30°	1064.4	8.6
30°-40°	1160.3	9.4
40°-50°	1066.4	8.6
50°-60°	837.5	6.8
60°-70°	545.1	4.4
70°-80°	280.6	2.3
80°-90°	75.4	0.6
90°-100°	70.5	0.6
100°-110°	262.9	2.1
110°-120°	697.3	5.7
120°-130°	1156.5	9.4
130°-140°	1228.4	10.0
140°-150°	1141.7	9.3
150°-160°	917.9	7.4
160°-170°	591.5	4.8
170°-180°	203.6	1.7
0°-30°	2098.7	17.0
0°-40°	3258.9	26.4
0°-60°	5162.8	41.9
0°-90°	6064.0	49.2
90°-120°	1030.7	8.4
90°-150°	4557.3	36.9
90°-180°	6270.0	50.8
0°-180°	12334.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2947	2947	2947	2947	2947	
5°	2947	2933	2899	2923	2915	279
15°	2803	2773	2683	2632	2606	790
25°	2544	2459	2283	2173	2133	1170
35°	2192	2056	1822	1653	1595	1372
45°	1792	1613	1333	1144	1080	1384
55°	1363	1155	867	707	656	1218
65°	920	704	464	373	365	912
75°	491	304	213	195	192	519
85°	114	58	51	51	51	132
90°	2	18	31	39	42	12
95°	100	49	60	68	66	119
105°	470	517	94	111	118	503
115°	890	916	955	238	127	876
125°	1258	1278	1308	1319	1323	1122
135°	1557	1582	1596	1611	1608	1203
145°	1806	1804	1831	1842	1834	1130
155°	1989	1975	1993	2003	1990	916
165°	2096	2086	2091	2102	2091	592
175°	2143	2133	2136	2146	2131	204
180°	2139	2139	2139	2139	2139	

TEST NUMBER: P914255

CATALOG NUMBER: DFN2DIP-PN4F0-090D080US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2946.7	2946.7	2946.7	2946.7	2946.7
2.5°	2960.0	2946.7	2917.2	2944.1	2938.8
5°	2946.7	2933.4	2898.6	2922.6	2914.7
7.5°	2922.6	2906.8	2869.4	2879.9	2866.6
10°	2890.7	2872.0	2818.8	2810.6	2794.7
12.5°	2850.7	2826.7	2754.6	2738.7	2709.3
15°	2802.7	2773.3	2682.7	2632.0	2605.5
17.5°	2746.7	2704.0	2591.9	2533.3	2490.6
20°	2682.7	2629.2	2495.9	2429.5	2370.6
22.5°	2613.4	2552.0	2397.2	2306.7	2266.8
25°	2544.1	2458.6	2282.7	2173.4	2133.3
27.5°	2461.5	2370.6	2176.0	2050.6	1989.2
30°	2373.5	2271.9	2058.6	1922.8	1850.6
32.5°	2288.0	2165.2	1946.8	1786.7	1719.9
35°	2192.1	2056.0	1821.5	1653.4	1594.6
37.5°	2098.7	1951.9	1704.1	1519.9	1453.4
40°	2000.0	1840.2	1581.3	1392.0	1322.7
42.5°	1898.7	1728.1	1458.7	1261.3	1194.8
45°	1792.1	1613.3	1333.4	1143.8	1079.9
47.5°	1690.8	1501.5	1213.5	1023.9	965.4
50°	1578.7	1389.4	1096.1	911.9	856.1
52.5°	1469.3	1269.2	984.0	808.0	757.4
55°	1362.6	1154.6	866.6	706.8	656.1
57.5°	1253.4	1040.1	762.8	613.4	570.7
60°	1141.3	928.0	653.3	517.5	474.8
62.5°	1032.1	818.8	559.9	432.1	410.8
65°	920.0	703.9	464.0	373.4	365.3
67.5°	813.4	597.2	373.4	327.9	320.0
70°	701.4	493.4	309.3	282.7	271.9
72.5°	594.7	397.2	258.6	237.3	232.0
75°	490.6	303.9	213.3	194.6	192.1
77.5°	386.7	215.9	168.0	157.3	151.9
80°	290.6	154.8	127.9	117.4	117.4
82.5°	202.6	104.1	88.0	82.6	82.6
85°	114.5	58.5	50.6	50.6	50.6
87.5°	42.7	21.2	21.2	18.7	18.7
90°	1.5	18.5	30.9	38.7	41.7
92.5°	38.7	32.6	37.2	40.2	41.7
95°	100.5	49.4	60.3	68.2	66.5
97.5°	181.0	54.2	78.8	83.7	85.1
100°	274.0	61.9	88.2	100.5	103.6
102.5°	376.0	373.0	91.3	108.2	113.0
105°	470.5	517.0	94.4	111.4	117.6
107.5°	580.4	618.9	97.6	114.5	120.7
110°	685.7	718.0	270.9	116.1	122.2

TEST NUMBER: P914255

CATALOG NUMBER: DFN2DIP-PN4F0-090D080US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	784.7	812.5	786.2	119.1	123.9
115°	889.9	916.2	954.9	238.4	127.0
117.5°	981.2	1012.1	1038.5	817.1	411.7
120°	1083.4	1106.5	1134.5	1153.0	944.0
122.5°	1169.9	1194.8	1225.8	1235.0	1236.7
125°	1258.1	1278.3	1307.7	1318.6	1323.2
127.5°	1338.6	1360.3	1383.7	1399.1	1400.6
130°	1414.5	1439.3	1456.3	1473.4	1471.9
132.5°	1491.9	1512.1	1529.1	1543.0	1541.5
135°	1557.0	1581.7	1595.5	1611.2	1608.0
137.5°	1625.0	1643.5	1659.1	1674.6	1670.0
140°	1691.5	1704.0	1720.9	1734.9	1727.1
142.5°	1747.4	1758.2	1778.2	1790.6	1782.8
145°	1806.2	1804.5	1830.8	1841.7	1833.9
147.5°	1857.1	1852.5	1878.7	1886.5	1880.4
150°	1906.7	1895.8	1920.6	1929.8	1922.1
152.5°	1948.4	1936.1	1959.2	1968.6	1957.8
155°	1988.7	1974.9	1993.4	2002.6	1990.4
157.5°	2021.2	2008.9	2022.8	2033.7	2021.2
160°	2049.1	2039.8	2049.1	2058.3	2047.5
162.5°	2073.8	2064.6	2072.3	2083.1	2069.2
165°	2095.5	2086.3	2090.9	2101.7	2090.9
167.5°	2112.5	2103.2	2107.9	2118.8	2104.8
170°	2126.5	2117.1	2120.3	2131.1	2117.1
172.5°	2135.7	2126.5	2129.6	2140.5	2126.5
175°	2143.4	2132.6	2135.7	2146.5	2131.1
177.5°	2146.5	2135.7	2137.3	2148.2	2134.2
180°	2138.8	2138.8	2138.8	2138.8	2138.8

TEST NUMBER: P914255

CATALOG NUMBER: DFN2DIP-PN4F0-090D080US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.74	10.56	10.71	11.54	12.83	5.70	6.52	6.67	7.51	8.79
	3H	11.42	12.15	12.40	13.14	14.45	6.89	7.63	7.87	8.62	9.92
	4H	12.03	12.72	13.02	13.72	15.03	7.34	8.04	8.34	9.03	10.35
	6H	12.45	13.09	13.46	14.09	15.42	7.66	8.30	8.67	9.30	10.63
	8H	12.58	13.19	13.59	14.20	15.53	7.75	8.36	8.76	9.38	10.70
	12H	12.64	13.22	13.66	14.23	15.58	7.80	8.38	8.81	9.38	10.73
4H	2H	9.75	10.45	10.76	11.44	12.76	6.30	6.99	7.30	7.99	9.30
	3H	11.59	12.16	12.60	13.19	14.52	7.65	8.23	8.66	9.25	10.58
	4H	12.28	12.81	13.30	13.82	15.18	8.20	8.73	9.21	9.74	11.09
	6H	12.80	13.25	13.83	14.29	15.64	8.62	9.07	9.65	10.11	11.46
	8H	12.97	13.40	14.00	14.43	15.79	8.75	9.17	9.78	10.20	11.56
	12H	13.07	13.45	14.12	14.50	15.87	8.81	9.19	9.86	10.24	11.61
8H	4H	12.25	12.67	13.28	13.70	15.07	8.48	8.90	9.51	9.93	11.30
	6H	12.82	13.17	13.87	14.24	15.60	9.00	9.35	10.05	10.42	11.78
	8H	13.03	13.34	14.10	14.40	15.78	9.19	9.50	10.25	10.55	11.94
	12H	13.18	13.45	14.24	14.50	15.92	9.31	9.58	10.37	10.63	12.06
12H	4H	12.20	12.58	13.25	13.63	15.00	8.48	8.87	9.53	9.91	11.28
	6H	12.79	13.10	13.85	14.16	15.54	9.05	9.36	10.11	10.41	11.79
	8H	13.01	13.28	14.08	14.34	15.76	9.26	9.53	10.32	10.58	12.01