

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922389

Luminaire Tested: DFN2DIP-PN4F0-080D050US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922389
REPORT IS A COMBINATION OF REPORTS P901155 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-080D050US940-FLLONL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11476.4 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 114.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922389

CATALOG NUMBER: DFN2DIP-PN4F0-080D050US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P922389

CATALOG NUMBER: DFN2DIP-PN4F0-080D050US940-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	56
2	91	84	78	72	85	79	73	69	69	65	61	60	57	54	52	50	48
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	38	35
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21
9	52	39	32	27	49	37	30	26	33	28	23	30	25	21	26	22	19
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2026	2026	2026
5°	2029	1998	2012
10°	2013	1972	1985
15°	1983	1939	1943
20°	1943	1895	1900
25°	1904	1841	1850
30°	1854	1791	1786
35°	1806	1732	1718
40°	1748	1673	1654
45°	1690	1613	1589
50°	1627	1550	1513
55°	1560	1478	1443
60°	1485	1392	1363
65°	1404	1303	1269
70°	1299	1195	1168
75°	1155	1065	1075
80°	981	900	896
85°	709	614	600

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1690 cd/sqm

TEST NUMBER: P922389

CATALOG NUMBER: DFN2DIP-PN4F0-080D050US940-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.3	2.3
10°-20°	735.1	6.4
20°-30°	1080.3	9.4
30°-40°	1254.7	10.9
40°-50°	1253.1	10.9
50°-60°	1092.7	9.5
60°-70°	807.7	7.0
70°-80°	457.0	4.0
80°-90°	123.3	1.1
90°-100°	49.6	0.4
100°-110°	185.0	1.6
110°-120°	490.6	4.3
120°-130°	813.6	7.1
130°-140°	864.3	7.5
140°-150°	803.2	7.0
150°-160°	645.8	5.6
160°-170°	416.1	3.6
170°-180°	143.2	1.2
0°-30°	2076.6	18.1
0°-40°	3331.3	29.0
0°-60°	5677.0	49.5
0°-90°	7065.0	61.6
90°-120°	725.2	6.3
90°-150°	3206.2	27.9
90°-180°	4411.0	38.4
0°-180°	11476.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2776	2776	2776	2776	2776	
5°	2776	2765	2736	2757	2752	263
15°	2642	2626	2592	2602	2589	744
25°	2392	2370	2325	2330	2325	1100
35°	2063	2037	1994	1978	1964	1288
45°	1679	1660	1620	1591	1580	1296
55°	1271	1254	1222	1190	1177	1136
65°	857	841	814	790	777	847
75°	448	443	430	414	419	479
85°	109	107	104	96	94	122
90°	1	13	22	27	29	11
95°	71	35	42	48	47	84
105°	331	364	66	78	83	354
115°	626	644	672	168	89	616
125°	885	899	920	928	931	789
135°	1095	1113	1122	1134	1131	846
145°	1271	1270	1288	1296	1290	795
155°	1399	1389	1402	1409	1400	645
165°	1474	1468	1471	1478	1471	416
175°	1508	1500	1502	1510	1499	144
180°	1505	1505	1505	1505	1505	

TEST NUMBER: P922389

CATALOG NUMBER: DFN2DIP-PN4F0-080D050US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2775.7	2775.7	2775.7	2775.7	2775.7
2.5°	2791.9	2778.6	2749.1	2775.7	2770.6
5°	2775.7	2765.3	2735.9	2757.1	2752.0
7.5°	2757.1	2741.2	2711.8	2733.3	2727.9
10°	2727.9	2709.2	2677.2	2698.4	2690.6
12.5°	2687.7	2671.8	2639.8	2653.1	2647.8
15°	2642.4	2626.5	2591.7	2602.5	2589.2
17.5°	2586.3	2570.4	2535.6	2549.0	2535.6
20°	2524.9	2509.0	2471.6	2479.6	2469.1
22.5°	2463.7	2439.6	2404.8	2404.8	2399.4
25°	2391.5	2370.3	2325.0	2330.0	2325.0
27.5°	2311.3	2292.7	2258.1	2250.1	2236.9
30°	2231.5	2209.9	2170.1	2162.1	2151.3
32.5°	2146.0	2130.1	2087.3	2071.2	2060.5
35°	2063.2	2036.7	1993.9	1977.7	1964.4
37.5°	1969.8	1945.7	1903.0	1884.3	1871.0
40°	1873.8	1852.3	1809.5	1785.7	1774.9
42.5°	1780.4	1758.8	1716.4	1689.4	1673.7
45°	1679.0	1660.3	1620.1	1590.9	1580.2
47.5°	1580.2	1561.5	1518.7	1489.2	1473.4
50°	1476.0	1462.7	1425.2	1387.9	1374.6
52.5°	1374.6	1355.8	1321.3	1291.9	1273.2
55°	1270.6	1254.5	1222.5	1190.5	1177.1
57.5°	1166.4	1153.2	1118.3	1086.3	1075.5
60°	1062.2	1051.8	1014.3	984.9	977.0
62.5°	960.8	942.2	915.5	888.9	878.2
65°	856.9	840.8	814.1	790.1	776.8
67.5°	750.1	736.6	712.7	694.1	683.3
70°	651.3	640.5	616.5	597.8	587.3
72.5°	549.9	539.2	525.8	507.2	499.3
75°	448.3	443.2	429.6	413.8	419.1
77.5°	357.7	346.9	341.5	333.6	325.7
80°	267.1	264.2	258.9	250.9	245.5
82.5°	181.6	181.6	179.0	168.2	168.2
85°	109.3	106.7	104.2	96.0	93.5
87.5°	48.2	42.8	37.4	29.4	26.7
90°	1.1	13.0	21.8	27.3	29.3
92.5°	27.3	22.9	26.1	28.4	29.3
95°	70.7	34.8	42.4	48.0	46.8
97.5°	127.3	38.2	55.5	58.9	59.8
100°	192.8	43.6	62.1	70.7	72.9
102.5°	264.6	262.4	64.3	76.2	79.5
105°	331.0	363.7	66.4	78.4	82.8
107.5°	408.3	435.4	68.7	80.5	85.0
110°	482.4	505.2	190.6	81.7	86.0

TEST NUMBER: P922389

CATALOG NUMBER: DFN2DIP-PN4F0-080D050US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	552.1	571.6	553.1	83.8	87.1
115°	626.1	644.5	671.8	167.7	89.3
117.5°	690.3	712.0	730.7	574.8	289.6
120°	762.1	778.5	798.1	811.2	664.1
122.5°	823.0	840.5	862.4	868.9	870.0
125°	885.1	899.4	920.1	927.6	930.9
127.5°	941.7	957.0	973.5	984.3	985.3
130°	995.1	1012.6	1024.5	1036.5	1035.5
132.5°	1049.6	1063.8	1075.7	1085.6	1084.5
135°	1095.4	1112.9	1122.5	1133.5	1131.3
137.5°	1143.2	1156.3	1167.2	1178.1	1174.9
140°	1190.0	1198.8	1210.7	1220.5	1215.1
142.5°	1229.3	1237.0	1251.1	1259.7	1254.3
145°	1270.7	1269.5	1288.0	1295.7	1290.2
147.5°	1306.5	1303.2	1321.8	1327.2	1322.9
150°	1341.4	1333.8	1351.2	1357.7	1352.3
152.5°	1370.7	1362.1	1378.4	1385.0	1377.3
155°	1399.1	1389.4	1402.4	1408.9	1400.3
157.5°	1421.9	1413.3	1423.1	1430.7	1421.9
160°	1441.6	1435.0	1441.6	1448.0	1440.5
162.5°	1458.9	1452.5	1457.9	1465.5	1455.7
165°	1474.2	1467.8	1471.0	1478.5	1471.0
167.5°	1486.2	1479.6	1483.0	1490.6	1480.8
170°	1496.0	1489.4	1491.7	1499.2	1489.4
172.5°	1502.5	1496.0	1498.3	1505.8	1496.0
175°	1508.0	1500.3	1502.5	1510.1	1499.2
177.5°	1510.1	1502.5	1503.7	1511.3	1501.5
180°	1504.7	1504.7	1504.7	1504.7	1504.7

TEST NUMBER: P922389

CATALOG NUMBER: DFN2DIP-PN4F0-080D050US940-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.74	11.71	11.59	12.58	13.68	10.30	11.27	11.15	12.14	13.24
	3H	12.41	13.28	13.27	14.17	15.29	11.92	12.80	12.79	13.68	14.80
	4H	13.00	13.83	13.88	14.72	15.85	12.51	13.34	13.39	14.23	15.36
	6H	13.41	14.17	14.30	15.07	16.22	12.92	13.68	13.81	14.58	15.72
	8H	13.52	14.25	14.42	15.16	16.31	13.03	13.75	13.93	14.67	15.81
	12H	13.57	14.27	14.48	15.17	16.34	13.07	13.77	13.98	14.67	15.84
4H	2H	11.21	12.04	12.10	12.93	14.06	10.86	11.69	11.74	12.58	13.71
	3H	13.09	13.78	13.99	14.70	15.85	12.69	13.38	13.58	14.30	15.45
	4H	13.81	14.44	14.72	15.36	16.53	13.39	14.02	14.30	14.94	16.11
	6H	14.34	14.88	15.26	15.82	17.00	13.91	14.46	14.83	15.40	16.57
	8H	14.49	15.00	15.41	15.93	17.12	14.06	14.57	14.99	15.50	16.69
	12H	14.57	15.03	15.51	15.98	17.18	14.13	14.59	15.07	15.54	16.74
8H	4H	14.02	14.53	14.94	15.46	16.65	13.65	14.16	14.57	15.09	16.28
	6H	14.66	15.08	15.61	16.05	17.24	14.28	14.70	15.23	15.68	16.87
	8H	14.88	15.25	15.84	16.22	17.43	14.50	14.87	15.46	15.84	17.04
	12H	15.02	15.35	15.98	16.31	17.56	14.62	14.95	15.58	15.91	17.16
12H	4H	14.01	14.47	14.95	15.42	16.61	13.65	14.11	14.59	15.06	16.25
	6H	14.69	15.06	15.65	16.03	17.23	14.32	14.70	15.28	15.66	16.87
	8H	14.94	15.27	15.90	16.23	17.48	14.57	14.89	15.53	15.85	17.11

END OF REPORT