

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914308

Luminaire Tested: DFN2DIP-PN4F0-110D040US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914308
REPORT IS A COMBINATION OF REPORTS P899623 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D040US927-FLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11431.2 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 144.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914308

CATALOG NUMBER: DFN2DIP-PN4F0-110D040US927-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P914308

CATALOG NUMBER: DFN2DIP-PN4F0-110D040US927-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	80	80	80
1	104	99	95	91	98	94	91	88	86	83	80	78	76	74	70	69	67
2	94	87	80	75	89	83	77	72	75	71	67	68	65	62	62	59	57
3	86	76	68	62	82	73	66	60	66	61	56	60	56	52	55	51	48
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42
5	73	60	52	46	69	58	50	44	53	46	42	48	43	39	44	40	36
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	36	32
7	62	49	41	35	59	47	40	34	44	37	32	40	34	30	37	32	29
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2475	2475	2475
5°	2479	2441	2457
10°	2459	2408	2425
15°	2423	2369	2373
20°	2374	2314	2320
25°	2325	2249	2259
30°	2264	2188	2181
35°	2207	2116	2099
40°	2136	2043	2021
45°	2065	1970	1941
50°	1987	1894	1848
55°	1906	1805	1763
60°	1814	1700	1665
65°	1715	1592	1550
70°	1587	1459	1426
75°	1411	1301	1313
80°	1199	1099	1095
85°	867	750	733

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2065 cd/sqm

TEST NUMBER: P914308

CATALOG NUMBER: DFN2DIP-PN4F0-110D040US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.1	2.8
10°-20°	897.9	7.9
20°-30°	1319.6	11.5
30°-40°	1532.6	13.4
40°-50°	1530.7	13.4
50°-60°	1334.7	11.7
60°-70°	986.7	8.6
70°-80°	558.2	4.9
80°-90°	150.2	1.3
90°-100°	62.0	0.5
100°-110°	197.0	1.7
110°-120°	337.2	2.9
120°-130°	443.5	3.9
130°-140°	497.8	4.4
140°-150°	488.1	4.3
150°-160°	409.5	3.6
160°-170°	271.5	2.4
170°-180°	94.9	0.8
0°-30°	2536.6	22.2
0°-40°	4069.2	35.6
0°-60°	6934.6	60.7
0°-90°	8629.7	75.5
90°-120°	596.2	5.2
90°-150°	2025.6	17.7
90°-180°	2801.0	24.5
0°-180°	11431.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3391	3391	3391	3391	3391	
5°	3391	3378	3342	3368	3362	322
15°	3228	3208	3166	3179	3163	909
25°	2921	2895	2840	2846	2840	1344
35°	2520	2488	2436	2416	2400	1574
45°	2051	2028	1979	1943	1930	1583
55°	1552	1532	1493	1454	1438	1388
65°	1047	1027	994	965	949	1035
75°	548	541	525	505	512	585
85°	134	130	127	117	114	149
90°	1	11	30	28	29	11
95°	44	53	54	54	53	49
105°	182	184	186	188	188	192
115°	338	343	342	341	338	335
125°	492	500	497	495	494	440
135°	637	646	648	647	644	492
145°	773	779	784	785	781	483
155°	884	886	889	893	890	407
165°	961	960	960	966	962	271
175°	1000	998	996	1002	997	95
180°	1002	1002	1002	1002	1002	

TEST NUMBER: P914308

CATALOG NUMBER: DFN2DIP-PN4F0-110D040US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3390.7	3390.7	3390.7	3390.7	3390.7
2.5°	3410.3	3394.1	3358.1	3390.7	3384.4
5°	3390.7	3377.9	3341.9	3367.8	3361.6
7.5°	3367.8	3348.5	3312.5	3338.8	3332.2
10°	3332.2	3309.3	3270.3	3296.2	3286.5
12.5°	3283.1	3263.7	3224.7	3240.9	3234.3
15°	3227.7	3208.3	3165.8	3178.9	3162.7
17.5°	3159.2	3139.9	3097.3	3113.6	3097.3
20°	3084.2	3064.8	3019.2	3028.8	3016.1
22.5°	3009.5	2980.0	2937.5	2937.5	2930.9
25°	2921.2	2895.3	2840.0	2846.2	2840.0
27.5°	2823.3	2800.5	2758.3	2748.6	2732.4
30°	2725.8	2699.5	2650.7	2641.1	2627.9
32.5°	2621.3	2602.0	2549.7	2530.0	2516.8
35°	2520.3	2487.8	2435.6	2415.8	2399.6
37.5°	2406.2	2376.8	2324.6	2301.7	2285.4
40°	2288.9	2262.6	2210.4	2181.4	2168.2
42.5°	2174.8	2148.5	2096.6	2063.7	2044.4
45°	2051.0	2028.1	1978.9	1943.4	1930.2
47.5°	1930.2	1907.4	1855.1	1819.2	1799.8
50°	1802.9	1786.7	1741.0	1695.3	1679.1
52.5°	1679.1	1656.2	1614.1	1578.0	1555.2
55°	1552.1	1532.4	1493.3	1454.2	1438.0
57.5°	1424.8	1408.6	1366.0	1326.9	1313.8
60°	1297.5	1284.8	1239.1	1203.1	1193.4
62.5°	1173.7	1150.9	1118.3	1085.8	1072.7
65°	1046.7	1027.0	994.5	965.1	948.9
67.5°	916.3	899.8	870.7	847.9	834.7
70°	795.6	782.4	753.0	730.2	717.4
72.5°	671.8	658.6	642.4	619.6	609.8
75°	547.6	541.4	524.7	505.4	512.0
77.5°	436.9	423.7	417.2	407.5	397.8
80°	326.2	322.7	316.2	306.5	299.9
82.5°	221.7	221.7	218.6	205.5	205.5
85°	133.6	130.4	127.3	117.2	114.2
87.5°	58.8	52.2	45.6	36.0	32.5
90°	0.9	10.9	29.6	27.8	28.7
92.5°	18.7	25.3	26.3	27.2	27.2
95°	44.1	52.6	54.1	54.1	52.6
97.5°	73.4	81.3	84.6	84.6	84.6
100°	107.3	114.2	116.6	116.6	115.7
102.5°	142.9	148.1	151.4	152.3	151.4
105°	181.9	184.3	186.1	187.6	187.6
107.5°	220.5	224.2	224.2	224.7	220.5
110°	258.0	262.8	262.8	262.8	260.5

TEST NUMBER: P914308

CATALOG NUMBER: DFN2DIP-PN4F0-110D040US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	298.5	303.6	302.7	300.3	298.5
115°	338.3	343.3	341.7	340.8	338.3
117.5°	377.9	384.6	380.4	377.9	375.6
120°	417.9	424.5	417.9	417.9	415.1
122.5°	454.1	462.6	458.4	455.9	454.1
125°	492.2	499.7	497.3	494.6	493.7
127.5°	529.3	538.7	535.4	531.7	529.3
130°	564.0	575.0	573.5	571.6	568.3
132.5°	603.0	611.5	612.1	607.8	605.5
135°	636.6	645.9	647.8	646.8	644.4
137.5°	674.1	681.6	683.1	682.5	678.9
140°	706.9	714.5	718.7	718.7	715.4
142.5°	740.8	748.4	750.8	751.7	748.4
145°	772.9	778.9	783.7	784.7	781.3
147.5°	801.5	809.1	812.7	814.2	810.9
150°	831.2	836.3	839.6	842.3	839.6
152.5°	857.5	862.5	866.8	870.1	866.8
155°	883.7	886.1	888.8	893.1	890.3
157.5°	906.4	908.2	909.7	915.8	911.5
160°	926.6	928.4	929.3	934.5	930.8
162.5°	945.3	945.3	946.3	952.0	947.8
165°	961.4	960.4	960.4	966.5	962.3
167.5°	975.9	973.1	973.1	979.2	974.9
170°	986.7	984.3	983.4	989.4	984.3
172.5°	994.3	991.9	990.9	997.0	991.9
175°	1000.4	997.9	996.1	1002.1	997.0
177.5°	1003.7	1001.2	999.4	1004.6	999.4
180°	1002.1	1002.1	1002.1	1002.1	1002.1

TEST NUMBER: P914308

CATALOG NUMBER: DFN2DIP-PN4F0-110D040US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.51	13.66	13.21	14.38	15.23	12.07	13.22	12.77	13.94	14.79
	3H	14.19	15.23	14.91	15.96	16.84	13.71	14.74	14.43	15.47	16.36
	4H	14.80	15.77	15.53	16.51	17.41	14.31	15.28	15.04	16.03	16.92
	6H	15.21	16.11	15.96	16.86	17.78	14.72	15.62	15.47	16.37	17.29
	8H	15.33	16.18	16.08	16.96	17.87	14.83	15.69	15.59	16.46	17.38
	12H	15.39	16.20	16.15	16.97	17.91	14.89	15.70	15.65	16.47	17.41
4H	2H	13.00	13.98	13.74	14.72	15.62	12.65	13.63	13.39	14.37	15.27
	3H	14.90	15.71	15.65	16.49	17.41	14.50	15.31	15.25	16.09	17.01
	4H	15.63	16.37	16.39	17.15	18.09	15.21	15.95	15.98	16.73	17.67
	6H	16.16	16.80	16.95	17.61	18.56	15.74	16.38	16.52	17.18	18.13
	8H	16.32	16.92	17.11	17.72	18.68	15.89	16.49	16.68	17.29	18.25
	12H	16.41	16.95	17.22	17.77	18.74	15.97	16.51	16.78	17.33	18.30
8H	4H	15.85	16.45	16.64	17.25	18.21	15.48	16.08	16.26	16.88	17.84
	6H	16.49	16.99	17.31	17.83	18.80	16.12	16.61	16.93	17.46	18.42
	8H	16.72	17.16	17.55	18.00	18.98	16.33	16.78	17.16	17.62	18.60
	12H	16.87	17.26	17.70	18.09	19.13	16.46	16.85	17.30	17.68	18.72
12H	4H	15.85	16.39	16.66	17.21	18.18	15.48	16.02	16.29	16.85	17.82
	6H	16.53	16.97	17.36	17.81	18.79	16.16	16.60	16.99	17.44	18.43
	8H	16.78	17.17	17.62	18.00	19.04	16.41	16.80	17.24	17.63	18.67