

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914372

Luminaire Tested: DFN2DIP-PN4F0-120D110US927-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P914372  
REPORT IS A COMBINATION OF REPORTS P899751 AND P896497  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-120D110US927-FLLFLL  
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 17123.0 lumens  
Efficiency: N/A  
Efficacy: 78.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 217.9  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9781  
Total Harmonic Distortion (THDi): 0.075  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P914372  
CATALOG NUMBER: DFN2DIP-PN4F0-120D110US927-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P914372

CATALOG NUMBER: DFN2DIP-PN4F0-120D110US927-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	87	92	88	85	81	76	73	71	64	62	61	54	52	51	46
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	25
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24	22
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2700	2700	2700
5°	2704	2663	2681
10°	2682	2627	2645
15°	2643	2584	2589
20°	2590	2525	2531
25°	2537	2453	2465
30°	2470	2387	2380
35°	2407	2308	2290
40°	2330	2229	2204
45°	2252	2149	2117
50°	2168	2066	2016
55°	2079	1970	1923
60°	1979	1855	1817
65°	1870	1737	1691
70°	1732	1592	1556
75°	1539	1419	1432
80°	1307	1199	1195
85°	946	819	799

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2252 cd/sqm



TEST NUMBER: P914372

CATALOG NUMBER: DFN2DIP-PN4F0-120D110US927-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	348.1	2.0
10°-20°	979.5	5.7
20°-30°	1439.5	8.4
30°-40°	1671.9	9.8
40°-50°	1669.9	9.8
50°-60°	1456.0	8.5
60°-70°	1076.3	6.3
70°-80°	609.0	3.6
80°-90°	168.6	1.0
90°-100°	170.5	1.0
100°-110°	541.8	3.2
110°-120°	927.3	5.4
120°-130°	1219.5	7.1
130°-140°	1368.8	8.0
140°-150°	1342.3	7.8
150°-160°	1126.0	6.6
160°-170°	746.7	4.4
170°-180°	261.0	1.5
0°-30°	2767.2	16.2
0°-40°	4439.1	25.9
0°-60°	7565.0	44.2
0°-90°	9418.9	55.0
90°-120°	1639.7	9.6
90°-150°	5570.3	32.5
90°-180°	7704.0	45.0
0°-180°	17123.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3699	3699	3699	3699	3699	
5°	3699	3685	3646	3674	3667	351
15°	3521	3500	3454	3468	3450	992
25°	3187	3158	3098	3105	3098	1466
35°	2749	2714	2657	2636	2618	1717
45°	2237	2212	2159	2120	2106	1727
55°	1693	1672	1629	1586	1569	1514
65°	1142	1120	1085	1053	1035	1129
75°	597	591	572	551	558	638
85°	146	142	139	128	124	162
90°	2	30	81	76	79	17
95°	121	145	149	149	145	135
105°	500	507	512	516	516	528
115°	931	944	940	937	931	920
125°	1353	1374	1368	1360	1358	1209
135°	1751	1776	1781	1779	1772	1353
145°	2125	2142	2155	2158	2149	1328
155°	2430	2437	2444	2456	2448	1119
165°	2644	2641	2641	2658	2646	746
175°	2751	2744	2739	2756	2742	261
180°	2756	2756	2756	2756	2756	



TEST NUMBER: P914372

CATALOG NUMBER: DFN2DIP-PN4F0-120D110US927-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3698.9	3698.9	3698.9	3698.9	3698.9
2.5°	3720.4	3702.7	3663.4	3698.9	3692.1
5°	3698.9	3684.9	3645.7	3674.0	3667.2
7.5°	3674.0	3652.8	3613.6	3642.3	3635.2
10°	3635.2	3610.2	3567.6	3595.9	3585.3
12.5°	3581.5	3560.4	3517.8	3535.5	3528.3
15°	3521.2	3500.0	3453.6	3467.9	3450.2
17.5°	3446.5	3425.3	3378.9	3396.6	3378.9
20°	3364.6	3343.4	3293.7	3304.2	3290.2
22.5°	3283.0	3251.0	3204.5	3204.5	3197.4
25°	3186.8	3158.5	3098.1	3105.0	3098.1
27.5°	3080.0	3055.1	3009.1	2998.5	2980.8
30°	2973.6	2944.9	2891.7	2881.2	2866.8
32.5°	2859.6	2838.5	2781.5	2760.0	2745.7
35°	2749.4	2714.0	2657.0	2635.5	2617.8
37.5°	2624.9	2592.9	2535.9	2511.0	2493.2
40°	2497.0	2468.4	2411.3	2379.6	2365.3
42.5°	2372.5	2343.8	2287.2	2251.4	2230.2
45°	2237.4	2212.5	2158.9	2120.0	2105.7
47.5°	2105.7	2080.7	2023.8	1984.6	1963.4
50°	1966.8	1949.1	1899.3	1849.4	1831.7
52.5°	1831.7	1806.8	1760.8	1721.5	1696.6
55°	1693.2	1671.7	1629.0	1586.4	1568.7
57.5°	1554.3	1536.6	1490.2	1447.6	1433.2
60°	1415.5	1401.5	1351.7	1312.5	1301.9
62.5°	1280.4	1255.4	1220.0	1184.5	1170.2
65°	1141.9	1120.4	1084.9	1052.8	1035.1
67.5°	999.7	981.5	949.8	925.0	910.6
70°	867.9	853.6	821.5	796.6	782.7
72.5°	732.8	718.5	700.8	675.9	665.3
75°	597.4	590.6	572.4	551.4	558.5
77.5°	476.6	462.2	455.1	444.5	434.0
80°	355.8	352.0	344.9	334.4	327.2
82.5°	241.9	241.9	238.5	224.2	224.2
85°	145.7	142.3	138.9	127.9	124.5
87.5°	64.2	57.0	49.8	39.2	35.5
90°	2.5	29.9	81.4	76.4	78.9
92.5°	51.5	69.8	72.2	74.8	74.8
95°	121.3	144.6	148.7	148.7	144.6
97.5°	201.9	223.5	232.7	232.7	232.7
100°	294.9	314.0	320.7	320.7	318.2
102.5°	393.0	407.1	416.3	418.7	416.3
105°	500.2	506.8	511.8	515.9	515.9
107.5°	606.5	616.5	616.5	618.1	606.5
110°	709.6	722.9	722.9	722.9	716.2



TEST NUMBER: P914372

CATALOG NUMBER: DFN2DIP-PN4F0-120D110US927-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	820.9	835.0	832.5	825.8	820.9
115°	930.6	943.8	939.7	937.2	930.6
117.5°	1039.4	1057.6	1046.0	1039.4	1032.8
120°	1149.1	1167.4	1149.1	1149.1	1141.6
122.5°	1248.8	1272.0	1260.4	1253.7	1248.8
125°	1353.4	1374.2	1367.5	1360.1	1357.6
127.5°	1455.6	1481.4	1472.3	1462.3	1455.6
130°	1551.2	1581.1	1576.9	1571.9	1562.8
132.5°	1658.4	1681.6	1683.3	1671.7	1665.0
135°	1750.6	1776.3	1781.3	1778.8	1772.2
137.5°	1853.6	1874.4	1878.5	1876.8	1866.9
140°	1944.2	1964.9	1976.6	1976.6	1967.5
142.5°	2037.3	2058.0	2064.7	2067.1	2058.0
145°	2125.3	2141.9	2155.2	2157.7	2148.6
147.5°	2204.2	2225.0	2235.0	2239.1	2230.0
150°	2285.7	2299.8	2308.9	2316.4	2308.9
152.5°	2357.9	2372.0	2383.7	2392.9	2383.7
155°	2430.3	2436.8	2444.4	2456.0	2448.5
157.5°	2492.5	2497.5	2501.6	2518.3	2506.6
160°	2548.2	2553.2	2555.7	2569.8	2559.9
162.5°	2599.7	2599.7	2602.2	2618.0	2606.4
165°	2643.7	2641.2	2641.2	2657.8	2646.2
167.5°	2683.6	2676.1	2676.1	2692.8	2681.1
170°	2713.5	2706.9	2704.4	2721.0	2706.9
172.5°	2734.3	2727.6	2725.2	2741.8	2727.6
175°	2750.9	2744.3	2739.3	2755.9	2741.8
177.5°	2760.0	2753.4	2748.4	2762.6	2748.4
180°	2755.9	2755.9	2755.9	2755.9	2755.9



TEST NUMBER: P914372  
 CATALOG NUMBER: DFN2DIP-PN4F0-120D110US927-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.18	12.09	12.09	13.02	14.22	10.74	11.65	11.65	12.58	13.78
	3H	12.85	13.66	13.77	14.60	15.82	12.36	13.18	13.29	14.12	15.34
	4H	13.44	14.21	14.38	15.15	16.39	12.95	13.72	13.89	14.67	15.90
	6H	13.84	14.55	14.79	15.50	16.75	13.35	14.06	14.30	15.01	16.26
	8H	13.95	14.63	14.91	15.60	16.84	13.46	14.13	14.41	15.10	16.34
	12H	14.00	14.64	14.96	15.61	16.87	13.50	14.14	14.46	15.11	16.37
4H	2H	11.65	12.42	12.59	13.36	14.59	11.30	12.07	12.24	13.01	14.24
	3H	13.52	14.16	14.47	15.14	16.38	13.12	13.76	14.07	14.74	15.98
	4H	14.24	14.83	15.20	15.80	17.07	13.82	14.41	14.79	15.38	16.65
	6H	14.76	15.27	15.74	16.26	17.53	14.33	14.84	15.31	15.84	17.10
	8H	14.91	15.38	15.89	16.37	17.66	14.48	14.96	15.46	15.94	17.23
	12H	14.99	15.42	15.99	16.42	17.71	14.55	14.98	15.55	15.98	17.27
8H	4H	14.44	14.91	15.42	15.90	17.18	14.07	14.54	15.05	15.53	16.81
	6H	15.08	15.47	16.08	16.50	17.78	14.70	15.09	15.70	16.12	17.40
	8H	15.30	15.64	16.31	16.66	17.96	14.91	15.26	15.93	16.28	17.58
	12H	15.43	15.74	16.45	16.75	18.09	15.03	15.34	16.05	16.35	17.69
12H	4H	14.43	14.85	15.43	15.86	17.15	14.06	14.49	15.06	15.50	16.78
	6H	15.11	15.45	16.12	16.47	17.77	14.74	15.09	15.75	16.10	17.40
	8H	15.35	15.66	16.37	16.67	18.01	14.98	15.28	16.00	16.30	17.64