

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922446

Luminaire Tested: DFN2DIP-PN4F0-090D100US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922446
REPORT IS A COMBINATION OF REPORTS P899728 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-090D100US940-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14713.2 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 163.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922446
CATALOG NUMBER: DFN2DIP-PN4F0-090D100US940-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P922446

CATALOG NUMBER: DFN2DIP-PN4F0-090D100US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46			46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45	40			40
2	89	82	76	71	82	76	71	66	64	60	57	52	50	48	42	41	39	34			34
3	82	72	65	60	75	67	61	56	56	52	48	47	44	41	38	36	34	30			30
4	75	64	57	51	69	60	53	48	50	45	41	42	38	35	34	32	29	26			26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23			23
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20			20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18			18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16			16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15			15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	15	13			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2421	2421	2421
5°	2425	2383	2398
10°	2401	2337	2321
15°	2368	2260	2201
20°	2324	2154	2053
25°	2279	2035	1910
30°	2219	1912	1729
35°	2160	1781	1570
40°	2100	1645	1388
45°	2031	1494	1222
50°	1959	1342	1061
55°	1884	1179	905
60°	1797	1009	746
65°	1696	836	672
70°	1575	675	608
75°	1423	595	554
80°	1202	500	483
85°	837	336	366

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2209 cd/sqm



TEST NUMBER: P922446

CATALOG NUMBER: DFN2DIP-PN4F0-090D100US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.9	2.1
10°-20°	853.4	5.8
20°-30°	1198.1	8.1
30°-40°	1306.0	8.9
40°-50°	1200.4	8.2
50°-60°	942.7	6.4
60°-70°	613.6	4.2
70°-80°	315.9	2.1
80°-90°	88.7	0.6
90°-100°	174.5	1.2
100°-110°	554.5	3.8
110°-120°	948.9	6.4
120°-130°	1247.9	8.5
130°-140°	1400.8	9.5
140°-150°	1373.6	9.3
150°-160°	1152.3	7.8
160°-170°	764.1	5.2
170°-180°	267.1	1.8
0°-30°	2362.4	16.1
0°-40°	3668.4	24.9
0°-60°	5811.5	39.5
0°-90°	6829.6	46.4
90°-120°	1677.9	11.4
90°-150°	5700.1	38.7
90°-180°	7884.0	53.6
0°-180°	14713.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3317	3317	3317	3317	3317	
5°	3317	3302	3263	3290	3281	315
15°	3155	3122	3020	2963	2933	889
25°	2864	2768	2570	2446	2401	1317
35°	2468	2314	2050	1861	1795	1544
45°	2017	1816	1501	1288	1216	1558
55°	1534	1300	975	796	738	1371
65°	1036	792	522	420	411	1027
75°	552	342	240	219	216	584
85°	129	66	57	57	57	148
90°	3	31	83	78	81	15
95°	124	148	152	152	148	138
105°	512	519	524	528	528	540
115°	952	966	962	959	952	942
125°	1385	1406	1400	1392	1389	1238
135°	1791	1818	1823	1820	1814	1385
145°	2175	2192	2206	2208	2199	1359
155°	2487	2494	2501	2513	2506	1145
165°	2705	2703	2703	2720	2708	763
175°	2815	2808	2803	2820	2806	267
180°	2820	2820	2820	2820	2820	



TEST NUMBER: P922446

CATALOG NUMBER: DFN2DIP-PN4F0-090D100US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3316.9	3316.9	3316.9	3316.9	3316.9
2.5°	3331.9	3316.9	3283.7	3314.0	3308.0
5°	3316.9	3301.9	3262.8	3289.8	3280.9
7.5°	3289.8	3272.0	3230.0	3241.7	3226.7
10°	3253.9	3232.8	3173.0	3163.7	3145.9
12.5°	3208.9	3181.9	3100.7	3082.8	3049.6
15°	3154.8	3121.7	3019.8	2962.7	2932.8
17.5°	3091.7	3043.7	2917.5	2851.6	2803.5
20°	3019.8	2959.6	2809.5	2734.7	2668.4
22.5°	2941.8	2872.6	2698.4	2596.5	2551.6
25°	2863.7	2767.5	2569.5	2446.5	2401.3
27.5°	2770.7	2668.4	2449.4	2308.3	2239.2
30°	2671.7	2557.3	2317.2	2164.4	2083.1
32.5°	2575.4	2437.2	2191.4	2011.2	1936.0
35°	2467.5	2314.3	2050.3	1861.2	1794.9
37.5°	2362.4	2197.2	1918.2	1710.8	1636.0
40°	2251.3	2071.4	1779.9	1566.9	1488.9
42.5°	2137.3	1945.3	1642.0	1419.8	1344.9
45°	2017.2	1816.0	1500.9	1287.5	1215.6
47.5°	1903.2	1690.1	1365.9	1152.5	1086.6
50°	1777.1	1564.0	1233.8	1026.4	963.7
52.5°	1653.9	1428.7	1107.7	909.5	852.6
55°	1533.7	1299.7	975.4	795.6	738.5
57.5°	1410.9	1170.7	858.6	690.5	642.4
60°	1284.7	1044.5	735.4	582.5	534.4
62.5°	1161.8	921.7	630.3	486.3	462.4
65°	1035.6	792.4	522.3	420.4	411.2
67.5°	915.6	672.3	420.4	369.1	360.2
70°	789.5	555.4	348.1	318.2	306.0
72.5°	669.4	447.1	291.1	267.2	261.2
75°	552.2	342.1	240.1	219.1	216.2
77.5°	435.3	243.0	189.1	177.1	171.0
80°	327.1	174.2	143.9	132.2	132.2
82.5°	228.0	117.2	99.1	93.0	93.0
85°	128.9	65.9	57.0	57.0	57.0
87.5°	48.1	23.9	23.9	21.0	21.0
90°	2.6	30.6	83.3	78.2	80.8
92.5°	52.7	71.4	74.0	76.5	76.5
95°	124.1	147.9	152.2	152.2	147.9
97.5°	206.6	228.7	238.1	238.1	238.1
100°	301.8	321.4	328.1	328.1	325.7
102.5°	402.2	416.6	426.0	428.5	426.0
105°	511.8	518.6	523.7	528.0	528.0
107.5°	620.6	630.9	630.9	632.6	620.6
110°	726.1	739.7	739.7	739.7	732.9



TEST NUMBER: P922446

CATALOG NUMBER: DFN2DIP-PN4F0-090D100US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	840.0	854.4	851.9	845.1	840.0
115°	952.3	965.8	961.6	959.0	952.3
117.5°	1063.6	1082.4	1070.4	1063.6	1056.8
120°	1175.8	1194.5	1175.8	1175.8	1168.2
122.5°	1277.8	1301.6	1289.8	1283.0	1277.8
125°	1385.0	1406.2	1399.5	1391.8	1389.3
127.5°	1489.6	1515.9	1506.5	1496.4	1489.6
130°	1587.3	1617.9	1613.7	1608.6	1599.3
132.5°	1697.0	1720.8	1722.5	1710.7	1703.8
135°	1791.4	1817.8	1822.8	1820.3	1813.5
137.5°	1896.8	1918.1	1922.3	1920.7	1910.4
140°	1989.5	2010.7	2022.7	2022.7	2013.3
142.5°	2084.7	2106.0	2112.7	2115.3	2106.0
145°	2174.8	2191.8	2205.5	2208.0	2198.6
147.5°	2255.6	2276.9	2287.1	2291.3	2282.0
150°	2339.0	2353.4	2362.8	2370.3	2362.8
152.5°	2412.3	2427.3	2439.3	2448.6	2439.3
155°	2486.9	2493.7	2501.3	2513.2	2505.5
157.5°	2550.6	2555.7	2560.0	2577.0	2565.1
160°	2607.6	2612.7	2615.2	2629.7	2619.5
162.5°	2660.3	2660.3	2662.8	2679.0	2667.1
165°	2705.4	2702.8	2702.8	2719.8	2707.9
167.5°	2746.2	2738.5	2738.5	2755.6	2743.6
170°	2776.8	2770.0	2767.4	2784.5	2770.0
172.5°	2798.0	2791.2	2788.6	2805.7	2791.2
175°	2815.0	2808.3	2803.2	2820.1	2805.7
177.5°	2824.4	2817.6	2812.5	2826.9	2812.5
180°	2820.1	2820.1	2820.1	2820.1	2820.1



TEST NUMBER: P922446
 CATALOG NUMBER: DFN2DIP-PN4F0-090D100US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.88	10.68	10.87	11.68	13.01	5.85	6.65	6.84	7.65	8.97
	3H	11.56	12.28	12.56	13.29	14.63	7.03	7.75	8.04	8.76	10.10
	4H	12.17	12.85	13.18	13.86	15.21	7.48	8.16	8.50	9.17	10.53
	6H	12.59	13.21	13.62	14.23	15.60	7.80	8.43	8.83	9.44	10.81
	8H	12.72	13.31	13.75	14.34	15.71	7.89	8.49	8.93	9.52	10.88
	12H	12.78	13.34	13.82	14.37	15.76	7.94	8.50	8.97	9.53	10.91
4H	2H	9.89	10.57	10.92	11.59	12.94	6.44	7.12	7.46	8.13	9.48
	3H	11.72	12.29	12.76	13.33	14.70	7.79	8.35	8.82	9.39	10.76
	4H	12.42	12.93	13.46	13.97	15.36	8.34	8.85	9.37	9.88	11.27
	6H	12.93	13.38	13.98	14.43	15.82	8.75	9.20	9.80	10.25	11.64
	8H	13.11	13.52	14.16	14.57	15.97	8.88	9.30	9.93	10.35	11.75
	12H	13.21	13.58	14.27	14.64	16.05	8.95	9.32	10.01	10.38	11.79
8H	4H	12.38	12.80	13.43	13.85	15.25	8.61	9.03	9.66	10.08	11.48
	6H	12.95	13.29	14.02	14.38	15.78	9.13	9.47	10.21	10.57	11.96
	8H	13.17	13.47	14.25	14.55	15.96	9.33	9.62	10.41	10.70	12.12
	12H	13.31	13.57	14.39	14.64	16.10	9.44	9.71	10.53	10.78	12.24
12H	4H	12.33	12.71	13.40	13.77	15.18	8.62	8.99	9.69	10.06	11.46
	6H	12.93	13.23	14.01	14.30	15.72	9.18	9.48	10.26	10.56	11.98
	8H	13.15	13.41	14.23	14.48	15.94	9.39	9.66	10.48	10.73	12.19