

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922544

Luminaire Tested: DFN2DIP-PN4F0-120D080US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922544
REPORT IS A COMBINATION OF REPORTS P899697 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-120D080US940-FLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16906.8 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 184.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922544
CATALOG NUMBER: DFN2DIP-PN4F0-120D080US940-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P922544

CATALOG NUMBER: DFN2DIP-PN4F0-120D080US940-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	60	59	57	53
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48	53	50	48	44
3	84	74	66	60	78	70	63	58	61	56	52	54	50	46	47	44	41	47	44	41	37
4	77	66	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	38	34	31	28
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	34	30	27	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	31	27	24	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	29	25	22	20
9	52	40	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3039	3039	3039
5°	3044	2997	3018
10°	3019	2957	2977
15°	2975	2909	2914
20°	2915	2842	2849
25°	2855	2761	2774
30°	2781	2686	2679
35°	2710	2598	2578
40°	2623	2509	2481
45°	2535	2419	2383
50°	2440	2326	2269
55°	2341	2217	2165
60°	2228	2088	2045
65°	2106	1955	1904
70°	1949	1792	1752
75°	1732	1598	1612
80°	1472	1350	1345
85°	1065	921	900

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2535 cd/sqm



TEST NUMBER: P922544

CATALOG NUMBER: DFN2DIP-PN4F0-120D080US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.9	2.3
10°-20°	1102.6	6.5
20°-30°	1620.4	9.6
30°-40°	1882.0	11.1
40°-50°	1879.7	11.1
50°-60°	1639.0	9.7
60°-70°	1211.6	7.2
70°-80°	685.5	4.1
80°-90°	187.3	1.1
90°-100°	139.6	0.8
100°-110°	443.6	2.6
110°-120°	759.1	4.5
120°-130°	998.3	5.9
130°-140°	1120.6	6.6
140°-150°	1098.9	6.5
150°-160°	921.8	5.5
160°-170°	611.3	3.6
170°-180°	213.7	1.3
0°-30°	3114.9	18.4
0°-40°	4996.9	29.6
0°-60°	8515.5	50.4
0°-90°	10599.9	62.7
90°-120°	1342.3	7.9
90°-150°	4560.1	27.0
90°-180°	6307.0	37.3
0°-180°	16906.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4164	4164	4164	4164	4164	
5°	4164	4148	4104	4136	4128	395
15°	3964	3940	3888	3904	3884	1116
25°	3587	3555	3487	3495	3487	1651
35°	3095	3055	2991	2967	2947	1933
45°	2518	2490	2430	2386	2370	1944
55°	1906	1882	1834	1786	1766	1704
65°	1285	1261	1221	1185	1165	1271
75°	672	665	644	621	629	718
85°	164	160	156	144	140	183
90°	2	24	67	63	65	16
95°	99	118	122	122	118	111
105°	410	415	419	422	422	432
115°	762	773	769	767	762	753
125°	1108	1125	1120	1113	1111	990
135°	1433	1454	1458	1456	1451	1108
145°	1740	1754	1764	1766	1759	1087
155°	1990	1995	2001	2010	2004	916
165°	2164	2162	2162	2176	2166	611
175°	2252	2247	2242	2256	2244	214
180°	2256	2256	2256	2256	2256	



TEST NUMBER: P922544

CATALOG NUMBER: DFN2DIP-PN4F0-120D080US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4163.7	4163.7	4163.7	4163.7	4163.7
2.5°	4187.8	4167.9	4123.7	4163.7	4156.0
5°	4163.7	4147.9	4103.7	4135.6	4127.9
7.5°	4135.6	4111.8	4067.6	4099.9	4091.9
10°	4091.9	4063.8	4015.8	4047.7	4035.8
12.5°	4031.5	4007.7	3959.7	3979.7	3971.6
15°	3963.6	3939.8	3887.5	3903.6	3883.7
17.5°	3879.5	3855.7	3803.4	3823.4	3803.4
20°	3787.3	3763.5	3707.5	3719.3	3703.6
22.5°	3695.5	3659.4	3607.1	3607.1	3599.1
25°	3587.2	3555.3	3487.4	3495.1	3487.4
27.5°	3467.0	3439.0	3387.2	3375.2	3355.3
30°	3347.2	3314.9	3255.0	3243.2	3227.0
32.5°	3218.9	3195.2	3131.0	3106.8	3090.7
35°	3094.9	3055.0	2990.8	2966.6	2946.7
37.5°	2954.7	2918.7	2854.5	2826.5	2806.5
40°	2810.8	2778.5	2714.3	2678.6	2662.5
42.5°	2670.6	2638.3	2574.5	2534.2	2510.4
45°	2518.5	2490.5	2430.1	2386.4	2370.3
47.5°	2370.3	2342.2	2278.1	2233.9	2210.1
50°	2213.9	2194.0	2137.9	2081.8	2061.8
52.5°	2061.8	2033.8	1982.0	1937.8	1909.8
55°	1905.9	1881.8	1833.7	1785.7	1765.8
57.5°	1749.6	1729.7	1677.4	1629.4	1613.3
60°	1593.3	1577.6	1521.5	1477.4	1465.4
62.5°	1441.3	1413.2	1373.3	1333.4	1317.2
65°	1285.4	1261.1	1221.2	1185.1	1165.2
67.5°	1125.2	1104.8	1069.2	1041.2	1025.0
70°	977.0	960.8	924.7	896.7	881.0
72.5°	824.9	808.8	788.8	760.8	748.9
75°	672.4	664.8	644.3	620.6	628.7
77.5°	536.5	520.3	512.3	500.3	488.5
80°	400.6	396.3	388.3	376.4	368.3
82.5°	272.2	272.2	268.5	252.4	252.4
85°	164.0	160.2	156.3	144.0	140.2
87.5°	72.2	64.1	56.1	44.1	39.9
90°	2.1	24.5	66.7	62.6	64.6
92.5°	42.2	57.2	59.2	61.2	61.2
95°	99.3	118.3	121.7	121.7	118.3
97.5°	165.3	183.0	190.5	190.5	190.5
100°	241.5	257.1	262.5	262.5	260.5
102.5°	321.7	333.3	340.7	342.8	340.7
105°	409.5	414.9	419.0	422.4	422.4
107.5°	496.5	504.7	504.7	506.0	496.5
110°	580.9	591.7	591.7	591.7	586.3



TEST NUMBER: P922544

CATALOG NUMBER: DFN2DIP-PN4F0-120D080US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	672.0	683.6	681.5	676.1	672.0
115°	761.8	772.7	769.3	767.2	761.8
117.5°	850.9	865.9	856.3	850.9	845.4
120°	940.7	955.6	940.7	940.7	934.5
122.5°	1022.3	1041.3	1031.8	1026.4	1022.3
125°	1108.0	1125.0	1119.5	1113.4	1111.4
127.5°	1191.7	1212.7	1205.2	1197.1	1191.7
130°	1269.9	1294.3	1290.9	1286.9	1279.4
132.5°	1357.6	1376.6	1378.0	1368.5	1363.1
135°	1433.1	1454.2	1458.3	1456.3	1450.8
137.5°	1517.4	1534.5	1537.8	1536.5	1528.3
140°	1591.6	1608.6	1618.1	1618.1	1610.6
142.5°	1667.8	1684.8	1690.2	1692.3	1684.8
145°	1739.9	1753.5	1764.3	1766.4	1758.9
147.5°	1804.5	1821.5	1829.6	1833.1	1825.6
150°	1871.2	1882.7	1890.2	1896.3	1890.2
152.5°	1930.3	1941.9	1951.4	1958.9	1951.4
155°	1989.5	1994.9	2001.1	2010.5	2004.5
157.5°	2040.5	2044.6	2048.0	2061.5	2052.1
160°	2086.1	2090.2	2092.2	2103.7	2095.6
162.5°	2128.2	2128.2	2130.3	2143.2	2133.7
165°	2164.3	2162.2	2162.2	2175.9	2166.3
167.5°	2196.9	2190.8	2190.8	2204.4	2194.9
170°	2221.4	2216.0	2213.9	2227.6	2216.0
172.5°	2238.5	2233.0	2231.0	2244.5	2233.0
175°	2252.0	2246.6	2242.5	2256.1	2244.5
177.5°	2259.5	2254.1	2250.0	2261.6	2250.0
180°	2256.1	2256.1	2256.1	2256.1	2256.1



TEST NUMBER: P922544
 CATALOG NUMBER: DFN2DIP-PN4F0-120D080US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.24	13.22	13.08	14.09	15.16	11.80	12.78	12.64	13.65	14.72
	3H	13.91	14.80	14.76	15.67	16.77	13.42	14.31	14.28	15.18	16.29
	4H	14.50	15.34	15.37	16.22	17.34	14.02	14.85	14.89	15.73	16.85
	6H	14.91	15.69	15.79	16.57	17.70	14.42	15.19	15.30	16.08	17.21
	8H	15.02	15.76	15.91	16.66	17.79	14.53	15.27	15.42	16.17	17.30
	12H	15.08	15.78	15.97	16.67	17.83	14.58	15.28	15.47	16.17	17.33
4H	2H	12.71	13.55	13.59	14.43	15.54	12.36	13.20	13.23	14.08	15.19
	3H	14.59	15.29	15.48	16.20	17.33	14.19	14.89	15.08	15.80	16.93
	4H	15.31	15.95	16.21	16.86	18.02	14.90	15.54	15.79	16.44	17.60
	6H	15.84	16.39	16.75	17.32	18.48	15.42	15.97	16.33	16.90	18.06
	8H	15.99	16.51	16.91	17.43	18.61	15.57	16.08	16.48	17.01	18.18
	12H	16.07	16.54	17.01	17.48	18.66	15.63	16.10	16.57	17.04	18.22
8H	4H	15.52	16.04	16.44	16.96	18.13	15.15	15.67	16.06	16.59	17.76
	6H	16.16	16.59	17.10	17.55	18.73	15.79	16.21	16.73	17.18	18.35
	8H	16.39	16.76	17.34	17.72	18.91	16.00	16.38	16.95	17.34	18.53
	12H	16.52	16.86	17.48	17.81	19.05	16.12	16.46	17.08	17.41	18.64
12H	4H	15.51	15.98	16.45	16.92	18.10	15.15	15.62	16.08	16.56	17.74
	6H	16.19	16.57	17.14	17.53	18.72	15.83	16.21	16.78	17.16	18.35
	8H	16.44	16.78	17.40	17.73	18.96	16.07	16.40	17.02	17.35	18.59