

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916893

Luminaire Tested: DFN2DIP-PN4F0-070D040US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916893
REPORT IS A COMBINATION OF REPORTS P901135 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-070D040US930-FLLONL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8878.6 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 97
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916893

CATALOG NUMBER: DFN2DIP-PN4F0-070D040US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P916893

CATALOG NUMBER: DFN2DIP-PN4F0-070D040US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91		79	79	79		69
1	101	96	92	89	94	91	87	84	80	77	75		70	68	66		61
2	92	84	78	73	86	79	74	69	70	66	62		61	58	55		53
3	84	74	67	61	78	70	63	58	62	57	52		54	50	47		47
4	77	66	58	51	72	62	55	49	55	49	45		48	44	40		42
5	71	59	50	44	66	55	48	42	49	43	39		44	39	35		38
6	65	53	44	38	61	50	42	37	44	38	34		39	34	31		35
7	60	48	39	34	56	45	38	32	40	34	30		36	31	27		32
8	56	43	35	30	52	41	34	29	37	31	27		33	28	24		29
9	52	40	32	27	49	38	31	26	34	28	24		30	25	22		27
10	49	36	29	24	46	35	28	23	31	26	22		28	23	20		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1621	1621	1621
5°	1624	1599	1609
10°	1610	1577	1588
15°	1587	1552	1554
20°	1555	1516	1520
25°	1523	1473	1480
30°	1483	1433	1429
35°	1445	1386	1375
40°	1399	1338	1323
45°	1352	1290	1271
50°	1302	1240	1210
55°	1248	1182	1155
60°	1188	1114	1091
65°	1123	1043	1015
70°	1040	956	934
75°	924	852	860
80°	785	720	717
85°	568	492	480

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1352 cd/sqm

TEST NUMBER: P916893

CATALOG NUMBER: DFN2DIP-PN4F0-070D040US930-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.0	2.4
10°-20°	588.1	6.6
20°-30°	864.2	9.7
30°-40°	1003.7	11.3
40°-50°	1002.5	11.3
50°-60°	874.2	9.8
60°-70°	646.2	7.3
70°-80°	365.6	4.1
80°-90°	98.4	1.1
90°-100°	36.3	0.4
100°-110°	135.3	1.5
110°-120°	358.8	4.0
120°-130°	595.1	6.7
130°-140°	632.1	7.1
140°-150°	587.5	6.6
150°-160°	472.3	5.3
160°-170°	304.4	3.4
170°-180°	104.8	1.2
0°-30°	1661.3	18.7
0°-40°	2665.1	30.0
0°-60°	4541.7	51.2
0°-90°	5652.0	63.7
90°-120°	530.4	6.0
90°-150°	2345.2	26.4
90°-180°	3227.0	36.3
0°-180°	8878.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2221	2221	2221	2221	2221	
5°	2221	2212	2189	2206	2202	211
15°	2114	2101	2073	2082	2071	595
25°	1913	1896	1860	1864	1860	880
35°	1651	1629	1595	1582	1572	1031
45°	1343	1328	1296	1273	1264	1037
55°	1016	1004	978	952	942	909
65°	686	673	651	632	621	678
75°	359	355	344	331	335	383
85°	88	85	83	77	75	98
90°	1	10	16	20	21	8
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	679	681	577
135°	801	814	821	829	828	619
145°	929	929	942	948	944	581
155°	1023	1016	1026	1030	1024	472
165°	1078	1074	1076	1082	1076	305
175°	1103	1097	1099	1105	1097	105
180°	1101	1101	1101	1101	1101	

TEST NUMBER: P916893

CATALOG NUMBER: DFN2DIP-PN4F0-070D040US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2220.6	2220.6	2220.6	2220.6	2220.6
2.5°	2233.6	2222.9	2199.3	2220.6	2216.6
5°	2220.6	2212.3	2188.7	2205.7	2201.6
7.5°	2205.7	2193.0	2169.4	2186.7	2182.4
10°	2182.4	2167.4	2141.8	2158.8	2152.5
12.5°	2150.2	2137.5	2111.9	2122.5	2118.2
15°	2114.0	2101.3	2073.4	2082.0	2071.3
17.5°	2069.1	2056.4	2028.5	2039.2	2028.5
20°	2019.9	2007.3	1977.3	1983.7	1975.3
22.5°	1971.0	1951.7	1923.9	1923.9	1919.5
25°	1913.3	1896.2	1860.0	1864.1	1860.0
27.5°	1849.1	1834.2	1806.5	1800.2	1789.5
30°	1785.3	1768.0	1736.1	1729.7	1721.1
32.5°	1716.8	1704.1	1669.9	1657.0	1648.4
35°	1650.7	1629.4	1595.1	1582.2	1571.6
37.5°	1575.9	1556.6	1522.4	1507.5	1496.8
40°	1499.1	1481.9	1447.6	1428.6	1420.0
42.5°	1424.3	1407.1	1373.1	1351.6	1338.9
45°	1343.2	1328.3	1296.1	1272.8	1264.1
47.5°	1264.1	1249.2	1215.0	1191.4	1178.8
50°	1180.8	1170.1	1140.2	1110.4	1099.7
52.5°	1099.7	1084.8	1057.1	1033.6	1018.6
55°	1016.5	1003.6	978.0	952.4	941.8
57.5°	933.2	922.5	894.6	869.0	860.5
60°	849.8	841.4	811.5	788.0	781.6
62.5°	768.7	753.7	732.5	711.2	702.5
65°	685.6	672.6	651.3	632.1	621.4
67.5°	600.1	589.3	570.2	555.3	546.7
70°	521.1	512.5	493.2	478.3	469.9
72.5°	439.9	431.4	420.7	405.8	399.4
75°	358.6	354.6	343.6	331.0	335.3
77.5°	286.2	277.5	273.2	266.8	260.6
80°	213.6	211.4	207.1	200.7	196.4
82.5°	145.2	145.2	143.2	134.6	134.6
85°	87.5	85.4	83.4	76.8	74.8
87.5°	38.5	34.2	29.9	23.6	21.3
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.1	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	141.0	31.9	45.4	51.7	53.3
102.5°	193.5	192.0	47.0	55.7	58.1
105°	242.1	266.0	48.6	57.3	60.5
107.5°	298.6	318.5	50.2	58.9	62.1
110°	352.9	369.5	139.4	59.8	62.9

TEST NUMBER: P916893

CATALOG NUMBER: DFN2DIP-PN4F0-070D040US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.8	418.1	404.6	61.3	63.8
115°	457.9	471.4	491.4	122.6	65.4
117.5°	504.9	520.8	534.4	420.4	211.8
120°	557.5	569.4	583.8	593.4	485.8
122.5°	602.0	614.8	630.8	635.5	636.3
125°	647.4	657.9	672.9	678.6	680.9
127.5°	688.8	700.0	712.0	720.0	720.7
130°	727.9	740.7	749.3	758.1	757.4
132.5°	767.7	778.1	786.8	794.0	793.3
135°	801.2	814.0	821.1	829.1	827.5
137.5°	836.2	845.7	853.8	861.7	859.3
140°	870.4	876.9	885.6	892.8	888.8
142.5°	899.2	904.7	915.1	921.4	917.5
145°	929.4	928.6	942.1	947.7	943.7
147.5°	955.6	953.2	966.8	970.8	967.7
150°	981.1	975.6	988.4	993.1	989.1
152.5°	1002.7	996.3	1008.2	1013.0	1007.5
155°	1023.4	1016.3	1025.8	1030.5	1024.2
157.5°	1040.1	1033.7	1041.0	1046.5	1040.1
160°	1054.4	1049.6	1054.4	1059.2	1053.6
162.5°	1067.1	1062.4	1066.4	1072.0	1064.8
165°	1078.3	1073.6	1075.9	1081.5	1075.9
167.5°	1087.1	1082.2	1084.8	1090.3	1083.1
170°	1094.3	1089.5	1091.0	1096.7	1089.5
172.5°	1099.0	1094.3	1095.9	1101.5	1094.3
175°	1102.9	1097.4	1099.0	1104.6	1096.7
177.5°	1104.6	1099.0	1099.8	1105.5	1098.3
180°	1100.7	1100.7	1100.7	1100.7	1100.7

TEST NUMBER: P916893

CATALOG NUMBER: DFN2DIP-PN4F0-070D040US930-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.13	11.13	10.96	11.98	13.04	9.69	10.69	10.52	11.54	12.60
	3H	11.80	12.70	12.65	13.56	14.65	11.32	12.22	12.16	13.08	14.17
	4H	12.40	13.25	13.26	14.12	15.22	11.91	12.76	12.77	13.63	14.73
	6H	12.81	13.59	13.68	14.47	15.58	12.32	13.10	13.19	13.97	15.09
	8H	12.92	13.66	13.80	14.56	15.67	12.43	13.17	13.31	14.07	15.18
	12H	12.97	13.68	13.86	14.57	15.71	12.47	13.18	13.36	14.07	15.21
4H	2H	10.61	11.46	11.47	12.32	13.42	10.26	11.10	11.12	11.97	13.07
	3H	12.49	13.20	13.37	14.10	15.21	12.09	12.79	12.96	13.70	14.81
	4H	13.21	13.86	14.10	14.76	15.90	12.79	13.44	13.68	14.34	15.48
	6H	13.74	14.30	14.64	15.22	16.36	13.31	13.87	14.22	14.79	15.94
	8H	13.89	14.41	14.80	15.33	16.49	13.46	13.98	14.37	14.90	16.06
	12H	13.97	14.44	14.90	15.38	16.54	13.53	14.00	14.46	14.94	16.10
8H	4H	13.42	13.94	14.33	14.86	16.01	13.05	13.57	13.95	14.49	15.64
	6H	14.06	14.49	14.99	15.45	16.61	13.68	14.12	14.62	15.07	16.23
	8H	14.28	14.67	15.23	15.62	16.79	13.90	14.28	14.84	15.23	16.41
	12H	14.42	14.76	15.37	15.70	16.93	14.02	14.36	14.97	15.30	16.53
12H	4H	13.41	13.88	14.34	14.82	15.98	13.05	13.52	13.97	14.45	15.62
	6H	14.09	14.47	15.03	15.42	16.60	13.73	14.11	14.67	15.06	16.23
	8H	14.34	14.68	15.29	15.62	16.85	13.97	14.31	14.92	15.25	16.47