

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922550

Luminaire Tested: DFN2DIP-PN4F0-120D090US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922550
REPORT IS A COMBINATION OF REPORTS P899716 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-120D090US940-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16197.9 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 192.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922550
CATALOG NUMBER: DFN2DIP-PN4F0-120D090US940-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P922550

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56	56	56	56
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53	48	48	48	48
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46	41	41	41	41
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40	36	36	36	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31	31	31	31
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30	27	27	27	27
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27	24	24	24	24
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24	22	22	22	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20	20	20	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20	18	18	18	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3228	3228	3228
5°	3233	3177	3198
10°	3201	3115	3094
15°	3157	3013	2934
20°	3099	2871	2737
25°	3039	2713	2547
30°	2959	2550	2306
35°	2881	2375	2093
40°	2801	2194	1850
45°	2708	1993	1630
50°	2612	1790	1414
55°	2511	1572	1207
60°	2395	1345	994
65°	2262	1115	896
70°	2100	899	811
75°	1897	794	739
80°	1602	667	643
85°	1116	448	488

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2708 cd/sqm



TEST NUMBER: P922550

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.5	2.6
10°-20°	1137.8	7.0
20°-30°	1597.5	9.9
30°-40°	1741.4	10.8
40°-50°	1600.5	9.9
50°-60°	1256.9	7.8
60°-70°	818.2	5.1
70°-80°	421.2	2.6
80°-90°	114.7	0.7
90°-100°	157.1	1.0
100°-110°	499.0	3.1
110°-120°	854.0	5.3
120°-130°	1123.1	6.9
130°-140°	1260.7	7.8
140°-150°	1236.2	7.6
150°-160°	1037.0	6.4
160°-170°	687.7	4.2
170°-180°	240.4	1.5
0°-30°	3149.8	19.4
0°-40°	4891.2	30.2
0°-60°	7748.6	47.8
0°-90°	9102.6	56.2
90°-120°	1510.1	9.3
90°-150°	5130.1	31.7
90°-180°	7095.0	43.8
0°-180°	16197.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4422	4422	4422	4422	4422	
5°	4422	4403	4350	4386	4375	419
15°	4206	4162	4026	3950	3910	1185
25°	3818	3690	3426	3262	3202	1756
35°	3290	3086	2734	2482	2393	2059
45°	2690	2421	2001	1717	1621	2077
55°	2045	1733	1301	1061	985	1827
65°	1381	1056	696	560	548	1369
75°	736	456	320	292	288	779
85°	172	88	76	76	76	197
90°	2	28	75	70	73	16
95°	112	133	137	137	133	124
105°	461	467	471	475	475	486
115°	857	869	865	863	857	848
125°	1246	1266	1260	1253	1250	1114
135°	1612	1636	1641	1638	1632	1246
145°	1957	1973	1985	1987	1979	1223
155°	2238	2244	2251	2262	2255	1030
165°	2435	2432	2432	2448	2437	687
175°	2534	2527	2523	2538	2525	241
180°	2538	2538	2538	2538	2538	



TEST NUMBER: P922550

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4422.5	4422.5	4422.5	4422.5	4422.5
2.5°	4442.5	4422.5	4378.4	4418.7	4410.6
5°	4422.5	4402.6	4350.3	4386.4	4374.6
7.5°	4386.4	4362.6	4306.6	4322.3	4302.3
10°	4338.4	4310.4	4230.5	4218.2	4194.5
12.5°	4278.5	4242.5	4134.1	4110.4	4066.3
15°	4206.4	4162.2	4026.3	3950.3	3910.4
17.5°	4122.3	4058.2	3890.0	3802.2	3738.0
20°	4026.3	3946.1	3746.1	3646.3	3557.9
22.5°	3922.3	3830.2	3597.9	3462.0	3402.1
25°	3818.3	3690.0	3425.9	3262.0	3201.7
27.5°	3694.3	3557.9	3265.8	3077.7	2985.5
30°	3562.2	3409.8	3089.6	2885.8	2777.5
32.5°	3434.0	3249.7	2921.9	2681.6	2581.3
35°	3290.1	3085.8	2733.7	2481.5	2393.2
37.5°	3149.9	2929.5	2557.5	2281.1	2181.3
40°	3001.7	2761.8	2373.3	2089.2	1985.1
42.5°	2849.6	2593.6	2189.4	1893.0	1793.2
45°	2689.6	2421.3	2001.3	1716.8	1620.8
47.5°	2537.5	2253.5	1821.2	1536.8	1448.9
50°	2369.5	2085.4	1645.0	1368.6	1285.0
52.5°	2205.1	1904.9	1476.9	1212.7	1136.8
55°	2045.0	1732.9	1300.6	1060.7	984.7
57.5°	1881.1	1560.9	1144.8	920.6	856.5
60°	1713.0	1392.8	980.4	776.7	712.6
62.5°	1549.1	1228.9	840.3	648.5	616.5
65°	1380.9	1056.5	696.4	560.5	548.2
67.5°	1220.8	896.3	560.5	492.1	480.3
70°	1052.7	740.6	464.1	424.2	408.0
72.5°	892.6	596.2	388.1	356.2	348.2
75°	736.3	456.0	320.2	292.1	288.3
77.5°	580.5	324.0	252.3	236.1	228.0
80°	436.1	232.3	191.9	176.2	176.2
82.5°	304.1	156.2	132.1	123.9	123.9
85°	172.0	87.9	76.0	76.0	76.0
87.5°	64.1	31.8	31.8	28.0	28.0
90°	2.3	27.6	75.0	70.4	72.7
92.5°	47.4	64.3	66.6	68.8	68.8
95°	111.7	133.1	137.0	137.0	133.1
97.5°	185.9	205.8	214.3	214.3	214.3
100°	271.6	289.3	295.3	295.3	293.1
102.5°	361.9	375.0	383.3	385.7	383.3
105°	460.7	466.7	471.4	475.2	475.2
107.5°	558.6	567.8	567.8	569.3	558.6
110°	653.4	665.8	665.8	665.8	659.6



TEST NUMBER: P922550

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	756.0	769.0	766.7	760.6	756.0
115°	857.0	869.2	865.4	863.2	857.0
117.5°	957.3	974.1	963.4	957.3	951.1
120°	1058.3	1075.0	1058.3	1058.3	1051.3
122.5°	1150.0	1171.5	1160.8	1154.7	1150.0
125°	1246.5	1265.6	1259.5	1252.6	1250.4
127.5°	1340.6	1364.3	1355.9	1346.8	1340.6
130°	1428.6	1456.2	1452.3	1447.7	1439.3
132.5°	1527.3	1548.7	1550.2	1539.5	1533.5
135°	1612.2	1635.9	1640.6	1638.3	1632.2
137.5°	1707.1	1726.3	1730.1	1728.6	1719.4
140°	1790.6	1809.6	1820.3	1820.3	1812.0
142.5°	1876.2	1895.3	1901.5	1903.8	1895.3
145°	1957.4	1972.6	1984.9	1987.2	1978.8
147.5°	2030.1	2049.2	2058.3	2062.2	2053.8
150°	2105.1	2118.1	2126.5	2133.3	2126.5
152.5°	2171.6	2184.6	2195.3	2203.8	2195.3
155°	2238.2	2244.3	2251.2	2261.9	2255.0
157.5°	2295.5	2300.2	2304.0	2319.2	2308.5
160°	2346.8	2351.4	2353.8	2366.7	2357.5
162.5°	2394.2	2394.2	2396.6	2411.1	2400.4
165°	2434.8	2432.5	2432.5	2447.8	2437.1
167.5°	2471.6	2464.7	2464.7	2479.9	2469.2
170°	2499.1	2493.0	2490.7	2506.0	2493.0
172.5°	2518.2	2512.1	2509.8	2525.1	2512.1
175°	2533.5	2527.4	2522.8	2538.2	2525.1
177.5°	2541.9	2535.8	2531.2	2544.2	2531.2
180°	2538.2	2538.2	2538.2	2538.2	2538.2



TEST NUMBER: P922550
 CATALOG NUMBER: DFN2DIP-PN4F0-120D090US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.78	12.67	12.69	13.59	14.77	7.75	8.63	8.66	9.56	10.74
	3H	13.47	14.26	14.39	15.19	16.40	8.94	9.73	9.86	10.67	11.87
	4H	14.08	14.83	15.02	15.77	16.98	9.40	10.14	10.33	11.08	12.30
	6H	14.51	15.20	15.46	16.14	17.37	9.72	10.41	10.67	11.35	12.58
	8H	14.64	15.29	15.59	16.25	17.48	9.81	10.47	10.77	11.43	12.65
	12H	14.70	15.32	15.66	16.28	17.53	9.86	10.48	10.82	11.43	12.69
4H	2H	11.81	12.56	12.75	13.49	14.71	8.35	9.10	9.29	10.04	11.25
	3H	13.65	14.27	14.60	15.23	16.47	9.71	10.33	10.66	11.30	12.53
	4H	14.34	14.91	15.30	15.87	17.13	10.26	10.83	11.22	11.79	13.04
	6H	14.86	15.35	15.84	16.34	17.59	10.68	11.17	11.66	12.16	13.41
	8H	15.04	15.50	16.02	16.48	17.74	10.81	11.27	11.79	12.25	13.52
	12H	15.14	15.55	16.13	16.55	17.82	10.88	11.29	11.87	12.29	13.56
8H	4H	14.31	14.77	15.29	15.75	17.02	10.55	11.00	11.52	11.98	13.25
	6H	14.89	15.26	15.89	16.28	17.55	11.07	11.44	12.07	12.46	13.73
	8H	15.10	15.44	16.11	16.45	17.73	11.26	11.59	12.27	12.60	13.89
	12H	15.25	15.54	16.26	16.54	17.87	11.38	11.67	12.39	12.68	14.01
12H	4H	14.27	14.68	15.26	15.67	16.95	10.55	10.96	11.55	11.96	13.23
	6H	14.86	15.19	15.87	16.20	17.49	11.12	11.45	12.13	12.46	13.74
	8H	15.09	15.38	16.10	16.38	17.71	11.33	11.62	12.34	12.63	13.96