

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922551

Luminaire Tested: DFN2DIP-PN4F0-120D090US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922551
REPORT IS A COMBINATION OF REPORTS P901236 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-120D090US940-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17040.6 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 192.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922551

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P922551

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		100	100	100	100		85	85	85		72	72	72		59	59	59
1	99	95	91	88		92	88	85	82		76	73	71		64	62	61		53	52	51
2	91	83	78	73		84	78	73	68		67	63	60		57	54	52		47	45	44
3	83	74	67	61		77	69	63	58		59	55	51		51	47	44		42	40	38
4	76	66	58	52		70	61	55	49		53	48	44		45	42	38		38	35	33
5	70	59	51	45		65	55	48	43		48	42	38		41	37	34		35	32	29
6	65	53	45	39		60	50	43	37		43	38	34		37	33	30		32	28	26
7	60	48	40	35		56	45	38	33		39	34	30		34	30	26		29	26	23
8	56	44	36	31		52	41	34	29		36	31	27		31	27	24		27	24	21
9	52	40	33	28		48	38	31	26		33	28	24		29	25	22		25	22	19
10	49	37	30	25		45	35	28	24		31	25	22		27	23	20		23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3228	3228	3228
5°	3233	3177	3198
10°	3201	3115	3094
15°	3157	3013	2934
20°	3099	2871	2737
25°	3039	2713	2547
30°	2959	2550	2306
35°	2881	2375	2093
40°	2801	2194	1850
45°	2708	1993	1630
50°	2612	1790	1414
55°	2511	1572	1207
60°	2395	1345	994
65°	2262	1115	896
70°	2100	899	811
75°	1897	794	739
80°	1602	667	643
85°	1116	448	488

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2708 cd/sqm

TEST NUMBER: P922551

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.5	2.4
10°-20°	1137.8	6.7
20°-30°	1597.5	9.4
30°-40°	1741.4	10.2
40°-50°	1600.5	9.4
50°-60°	1256.9	7.4
60°-70°	818.2	4.8
70°-80°	421.2	2.5
80°-90°	112.3	0.7
90°-100°	89.3	0.5
100°-110°	332.9	2.0
110°-120°	883.0	5.2
120°-130°	1464.5	8.6
130°-140°	1555.6	9.1
140°-150°	1445.8	8.5
150°-160°	1162.4	6.8
160°-170°	749.0	4.4
170°-180°	257.8	1.5
0°-30°	3149.8	18.5
0°-40°	4891.2	28.7
0°-60°	7748.6	45.5
0°-90°	9100.2	53.4
90°-120°	1305.2	7.7
90°-150°	5771.2	33.9
90°-180°	7940.0	46.6
0°-180°	17040.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4422	4422	4422	4422	4422	
5°	4422	4403	4350	4386	4375	419
15°	4206	4162	4026	3950	3910	1185
25°	3818	3690	3426	3262	3202	1756
35°	3290	3086	2734	2482	2393	2059
45°	2690	2421	2001	1717	1621	2077
55°	2045	1733	1301	1061	985	1827
65°	1381	1056	696	560	548	1369
75°	736	456	320	292	288	779
85°	172	88	76	76	76	197
90°	2	24	39	49	53	16
95°	127	63	76	86	84	151
105°	596	655	120	141	149	637
115°	1127	1160	1209	302	161	1109
125°	1593	1619	1656	1670	1676	1421
135°	1972	2003	2020	2040	2036	1523
145°	2287	2285	2318	2332	2322	1431
155°	2518	2501	2524	2536	2520	1161
165°	2654	2642	2648	2662	2648	750
175°	2714	2700	2705	2718	2699	258
180°	2708	2708	2708	2708	2708	

TEST NUMBER: P922551

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4422.5	4422.5	4422.5	4422.5	4422.5
2.5°	4442.5	4422.5	4378.4	4418.7	4410.6
5°	4422.5	4402.6	4350.3	4386.4	4374.6
7.5°	4386.4	4362.6	4306.6	4322.3	4302.3
10°	4338.4	4310.4	4230.5	4218.2	4194.5
12.5°	4278.5	4242.5	4134.1	4110.4	4066.3
15°	4206.4	4162.2	4026.3	3950.3	3910.4
17.5°	4122.3	4058.2	3890.0	3802.2	3738.0
20°	4026.3	3946.1	3746.1	3646.3	3557.9
22.5°	3922.3	3830.2	3597.9	3462.0	3402.1
25°	3818.3	3690.0	3425.9	3262.0	3201.7
27.5°	3694.3	3557.9	3265.8	3077.7	2985.5
30°	3562.2	3409.8	3089.6	2885.8	2777.5
32.5°	3434.0	3249.7	2921.9	2681.6	2581.3
35°	3290.1	3085.8	2733.7	2481.5	2393.2
37.5°	3149.9	2929.5	2557.5	2281.1	2181.3
40°	3001.7	2761.8	2373.3	2089.2	1985.1
42.5°	2849.6	2593.6	2189.4	1893.0	1793.2
45°	2689.6	2421.3	2001.3	1716.8	1620.8
47.5°	2537.5	2253.5	1821.2	1536.8	1448.9
50°	2369.5	2085.4	1645.0	1368.6	1285.0
52.5°	2205.1	1904.9	1476.9	1212.7	1136.8
55°	2045.0	1732.9	1300.6	1060.7	984.7
57.5°	1881.1	1560.9	1144.8	920.6	856.5
60°	1713.0	1392.8	980.4	776.7	712.6
62.5°	1549.1	1228.9	840.3	648.5	616.5
65°	1380.9	1056.5	696.4	560.5	548.2
67.5°	1220.8	896.3	560.5	492.1	480.3
70°	1052.7	740.6	464.1	424.2	408.0
72.5°	892.6	596.2	388.1	356.2	348.2
75°	736.3	456.0	320.2	292.1	288.3
77.5°	580.5	324.0	252.3	236.1	228.0
80°	436.1	232.3	191.9	176.2	176.2
82.5°	304.1	156.2	132.1	123.9	123.9
85°	172.0	87.9	76.0	76.0	76.0
87.5°	64.1	31.8	31.8	28.0	28.0
90°	1.9	23.5	39.1	49.1	52.8
92.5°	49.1	41.2	47.0	51.0	52.8
95°	127.3	62.6	76.3	86.3	84.3
97.5°	229.3	68.7	99.9	105.8	107.7
100°	347.0	78.5	111.7	127.3	131.3
102.5°	476.2	472.4	115.7	137.1	143.1
105°	595.8	654.7	119.6	141.1	148.9
107.5°	734.9	783.8	123.6	145.0	152.9
110°	868.3	909.3	343.0	147.0	154.8

TEST NUMBER: P922551

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	993.7	1028.9	995.6	150.8	156.9
115°	1126.9	1160.1	1209.2	301.8	160.8
117.5°	1242.5	1281.7	1315.1	1034.7	521.3
120°	1371.9	1401.2	1436.6	1460.1	1195.5
122.5°	1481.6	1513.0	1552.3	1563.9	1566.0
125°	1593.2	1618.8	1656.1	1669.8	1675.6
127.5°	1695.1	1722.6	1752.2	1771.7	1773.6
130°	1791.3	1822.7	1844.1	1865.7	1863.9
132.5°	1889.3	1914.9	1936.3	1954.0	1952.1
135°	1971.7	2003.0	2020.5	2040.3	2036.4
137.5°	2057.8	2081.3	2101.0	2120.6	2114.8
140°	2142.0	2157.8	2179.3	2196.9	2187.2
142.5°	2212.8	2226.5	2251.8	2267.4	2257.7
145°	2287.2	2285.1	2318.4	2332.2	2322.4
147.5°	2351.7	2345.9	2379.2	2389.0	2381.2
150°	2414.6	2400.8	2432.2	2443.8	2434.1
152.5°	2467.4	2451.8	2481.1	2493.0	2479.2
155°	2518.4	2500.9	2524.3	2536.0	2520.4
157.5°	2559.6	2544.0	2561.6	2575.3	2559.6
160°	2594.9	2583.0	2594.9	2606.6	2592.8
162.5°	2626.1	2614.4	2624.2	2637.9	2620.3
165°	2653.6	2641.9	2647.8	2661.5	2647.8
167.5°	2675.2	2663.4	2669.3	2683.1	2665.4
170°	2692.9	2681.0	2684.9	2698.7	2681.0
172.5°	2704.6	2692.9	2696.8	2710.5	2692.9
175°	2714.3	2700.5	2704.6	2718.2	2698.7
177.5°	2718.2	2704.6	2706.6	2720.3	2702.7
180°	2708.5	2708.5	2708.5	2708.5	2708.5

TEST NUMBER: P922551

CATALOG NUMBER: DFN2DIP-PN4F0-120D090US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.54	12.40	12.47	13.34	14.57	7.50	8.36	8.44	9.31	10.53
	3H	13.22	13.99	14.17	14.94	16.19	8.69	9.46	9.64	10.42	11.67
	4H	13.83	14.56	14.79	15.52	16.78	9.15	9.87	10.11	10.83	12.09
	6H	14.26	14.93	15.23	15.89	17.16	9.47	10.14	10.44	11.10	12.37
	8H	14.39	15.02	15.37	16.01	17.27	9.56	10.20	10.54	11.18	12.45
	12H	14.45	15.06	15.43	16.03	17.32	9.61	10.21	10.59	11.19	12.48
4H	2H	11.56	12.29	12.53	13.25	14.50	8.10	8.83	9.07	9.79	11.05
	3H	13.40	14.00	14.37	14.99	16.26	9.46	10.06	10.43	11.05	12.32
	4H	14.09	14.64	15.07	15.62	16.92	10.01	10.56	10.99	11.54	12.84
	6H	14.61	15.08	15.61	16.09	17.38	10.43	10.90	11.43	11.91	13.20
	8H	14.79	15.23	15.79	16.23	17.54	10.56	11.00	11.56	12.00	13.31
	12H	14.89	15.28	15.90	16.30	17.61	10.63	11.02	11.64	12.04	13.35
8H	4H	14.06	14.50	15.06	15.50	16.81	10.29	10.73	11.29	11.73	13.04
	6H	14.63	15.00	15.65	16.04	17.34	10.81	11.18	11.83	12.22	13.53
	8H	14.85	15.17	15.88	16.20	17.52	11.00	11.33	12.03	12.35	13.68
	12H	14.99	15.27	16.03	16.30	17.67	11.13	11.41	12.16	12.43	13.80
12H	4H	14.01	14.41	15.03	15.43	16.74	10.30	10.70	11.31	11.71	13.03
	6H	14.61	14.93	15.64	15.96	17.28	10.86	11.18	11.89	12.21	13.54
	8H	14.83	15.11	15.86	16.14	17.51	11.08	11.36	12.11	12.38	13.75

END OF REPORT