

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924987

Luminaire Tested: DFN2DIP-PN4F0-040D080US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924987
REPORT IS A COMBINATION OF REPORTS P901202 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-040D080US950-RLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10799.3 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 91.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924987
CATALOG NUMBER: DFN2DIP-PN4F0-040D080US950-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P924987
 CATALOG NUMBER: DFN2DIP-PN4F0-040D080US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	38	38	38	30
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32	34	33	32	26
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28	30	29	28	22
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	24	22	21	17
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	20	18	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15	18	16	15	12
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13	17	15	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	16	13	12	10
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11	14	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1151	1151	1151
5°	1153	1133	1140
10°	1142	1111	1104
15°	1126	1075	1046
20°	1105	1024	976
25°	1084	967	908
30°	1055	909	822
35°	1027	847	747
40°	999	782	660
45°	966	711	581
50°	931	638	504
55°	896	561	431
60°	854	480	355
65°	807	397	319
70°	749	321	289
75°	676	283	264
80°	571	238	230
85°	398	160	174

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1375 cd/sqm



TEST NUMBER: P924987

CATALOG NUMBER: DFN2DIP-PN4F0-040D080US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.8	1.4
10°-20°	405.8	3.8
20°-30°	569.7	5.3
30°-40°	621.0	5.8
40°-50°	570.8	5.3
50°-60°	448.2	4.2
60°-70°	291.8	2.7
70°-80°	150.2	1.4
80°-90°	42.9	0.4
90°-100°	84.9	0.8
100°-110°	316.6	2.9
110°-120°	839.7	7.8
120°-130°	1392.7	12.9
130°-140°	1479.4	13.7
140°-150°	1374.9	12.7
150°-160°	1105.4	10.2
160°-170°	712.3	6.6
170°-180°	245.2	2.3
0°-30°	1123.3	10.4
0°-40°	1744.3	16.2
0°-60°	2763.3	25.6
0°-90°	3248.1	30.1
90°-120°	1241.3	11.5
90°-150°	5488.3	50.8
90°-180°	7551.0	69.9
0°-180°	10799.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1577	1577	1577	1577	1577	
5°	1577	1570	1551	1564	1560	150
15°	1500	1484	1436	1409	1395	423
25°	1362	1316	1222	1163	1142	626
35°	1173	1100	975	885	853	734
45°	959	864	714	612	578	741
55°	729	618	464	378	351	652
65°	492	377	248	200	196	488
75°	262	163	114	104	103	278
85°	61	31	27	27	27	70
90°	2	22	37	47	50	10
95°	121	60	73	82	80	143
105°	567	623	114	134	142	605
115°	1072	1103	1150	287	153	1055
125°	1515	1540	1575	1588	1594	1351
135°	1875	1905	1922	1940	1936	1448
145°	2175	2173	2205	2218	2208	1360
155°	2395	2378	2401	2412	2397	1104
165°	2524	2512	2518	2531	2518	713
175°	2581	2568	2572	2585	2566	246
180°	2576	2576	2576	2576	2576	



TEST NUMBER: P924987

CATALOG NUMBER: DFN2DIP-PN4F0-040D080US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1577.2	1577.2	1577.2	1577.2	1577.2
2.5°	1584.3	1577.2	1561.4	1575.8	1572.9
5°	1577.2	1570.0	1551.4	1564.3	1560.1
7.5°	1564.3	1555.8	1535.8	1541.4	1534.3
10°	1547.2	1537.2	1508.7	1504.3	1495.9
12.5°	1525.8	1512.9	1474.3	1465.8	1450.1
15°	1500.1	1484.3	1435.9	1408.8	1394.6
17.5°	1470.1	1447.2	1387.2	1355.9	1333.0
20°	1435.9	1407.2	1335.9	1300.3	1268.8
22.5°	1398.8	1365.9	1283.0	1234.6	1213.3
25°	1361.6	1315.9	1221.7	1163.3	1141.7
27.5°	1317.5	1268.8	1164.6	1097.6	1064.7
30°	1270.3	1216.0	1101.8	1029.1	990.5
32.5°	1224.6	1158.9	1042.0	956.3	920.5
35°	1173.3	1100.4	974.9	884.9	853.4
37.5°	1123.3	1044.7	912.0	813.5	777.9
40°	1070.5	984.9	846.4	745.1	708.0
42.5°	1016.2	924.9	780.8	675.1	639.5
45°	959.2	863.5	713.7	612.3	578.0
47.5°	905.0	803.6	649.5	548.1	516.7
50°	845.0	743.6	586.6	488.1	458.2
52.5°	786.4	679.3	526.7	432.4	405.4
55°	729.3	618.0	463.8	378.3	351.2
57.5°	670.9	556.7	408.2	328.3	305.5
60°	610.8	496.7	349.6	276.9	254.1
62.5°	552.5	438.3	299.7	231.2	219.9
65°	492.5	376.7	248.3	199.9	195.5
67.5°	435.4	319.7	199.9	175.5	171.2
70°	375.4	264.1	165.5	151.3	145.5
72.5°	318.3	212.6	138.4	127.1	124.2
75°	262.5	162.7	114.2	104.2	102.8
77.5°	207.0	115.5	90.0	84.2	81.3
80°	155.5	82.8	68.4	62.9	62.9
82.5°	108.5	55.7	47.1	44.2	44.2
85°	61.3	31.4	27.1	27.1	27.1
87.5°	22.9	11.4	11.4	10.0	10.0
90°	1.8	22.3	37.2	46.7	50.3
92.5°	46.7	39.2	44.7	48.5	50.3
95°	121.1	59.5	72.6	82.1	80.1
97.5°	218.0	65.3	94.9	100.7	102.5
100°	330.0	74.6	106.3	121.1	124.8
102.5°	452.9	449.2	110.0	130.3	136.1
105°	566.6	622.6	113.7	134.1	141.7
107.5°	698.9	745.4	117.5	137.9	145.4
110°	825.8	864.7	326.3	139.9	147.2



TEST NUMBER: P924987

CATALOG NUMBER: DFN2DIP-PN4F0-040D080US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	945.0	978.4	946.8	143.4	149.2
115°	1071.6	1103.3	1150.0	287.1	152.9
117.5°	1181.6	1218.8	1250.7	984.0	495.8
120°	1304.7	1332.5	1366.2	1388.5	1136.9
122.5°	1408.9	1438.8	1476.2	1487.3	1489.3
125°	1515.1	1539.5	1574.9	1587.9	1593.5
127.5°	1612.1	1638.2	1666.4	1684.9	1686.7
130°	1703.5	1733.3	1753.7	1774.3	1772.5
132.5°	1796.7	1821.0	1841.4	1858.2	1856.4
135°	1875.0	1904.9	1921.5	1940.3	1936.5
137.5°	1956.9	1979.3	1998.1	2016.7	2011.1
140°	2037.0	2052.1	2072.5	2089.3	2079.9
142.5°	2104.3	2117.3	2141.4	2156.3	2147.0
145°	2175.1	2173.1	2204.8	2217.9	2208.5
147.5°	2236.5	2230.9	2262.5	2271.9	2264.5
150°	2296.2	2283.1	2313.0	2324.0	2314.8
152.5°	2346.5	2331.6	2359.4	2370.8	2357.7
155°	2394.9	2378.3	2400.6	2411.7	2396.9
157.5°	2434.0	2419.2	2436.0	2449.1	2434.0
160°	2467.7	2456.5	2467.7	2478.8	2465.7
162.5°	2497.4	2486.3	2495.6	2508.6	2491.8
165°	2523.5	2512.5	2518.0	2531.0	2518.0
167.5°	2544.0	2532.8	2538.5	2551.6	2534.8
170°	2560.9	2549.6	2553.4	2566.5	2549.6
172.5°	2572.0	2560.9	2564.6	2577.7	2560.9
175°	2581.2	2568.2	2572.0	2585.0	2566.5
177.5°	2585.0	2572.0	2573.9	2587.0	2570.2
180°	2575.7	2575.7	2575.7	2575.7	2575.7



TEST NUMBER: P924987
 CATALOG NUMBER: DFN2DIP-PN4F0-040D080US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.42	6.11	6.54	7.22	8.75	1.39	2.08	2.50	3.18	4.72
	3H	7.09	7.71	8.22	8.83	10.37	2.57	3.18	3.69	4.30	5.85
	4H	7.70	8.28	8.83	9.40	10.95	3.01	3.60	4.14	4.71	6.27
	6H	8.11	8.65	9.25	9.77	11.34	3.32	3.86	4.47	4.98	6.55
	8H	8.24	8.75	9.38	9.88	11.44	3.41	3.92	4.56	5.06	6.62
	12H	8.30	8.78	9.44	9.91	11.49	3.45	3.94	4.60	5.06	6.65
4H	2H	5.42	6.01	6.57	7.13	8.68	1.97	2.55	3.11	3.67	5.22
	3H	7.24	7.73	8.39	8.87	10.44	3.30	3.79	4.45	4.93	6.50
	4H	7.93	8.38	9.08	9.51	11.10	3.85	4.30	5.00	5.43	7.01
	6H	8.44	8.82	9.60	9.98	11.56	4.26	4.64	5.42	5.80	7.38
	8H	8.62	8.97	9.77	10.12	11.71	4.39	4.75	5.54	5.89	7.48
	12H	8.71	9.03	9.88	10.19	11.79	4.45	4.77	5.62	5.93	7.53
8H	4H	7.89	8.25	9.04	9.39	10.99	4.12	4.48	5.27	5.62	7.22
	6H	8.45	8.75	9.63	9.94	11.53	4.63	4.93	5.81	6.12	7.71
	8H	8.67	8.93	9.85	10.10	11.70	4.83	5.08	6.01	6.25	7.86
	12H	8.81	9.03	9.99	10.20	11.84	4.94	5.17	6.12	6.33	7.97
12H	4H	7.83	8.16	9.01	9.32	10.91	4.12	4.44	5.29	5.60	7.20
	6H	8.43	8.69	9.61	9.85	11.46	4.68	4.94	5.86	6.11	7.72
	8H	8.64	8.87	9.83	10.03	11.68	4.89	5.12	6.07	6.28	7.92