

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917070

Luminaire Tested: DFN2DIP-PN4F0-110D120US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917070
REPORT IS A COMBINATION OF REPORTS P899768 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D120US930-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16281.5 lumens
Efficiency: N/A
Efficacy: 74.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 217.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917070

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P917070

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53
1	98	93	90	86	90	86	83	80	72	70	68	59	58	57	48	47	46
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	26	23
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2706	2706	2706
5°	2710	2663	2680
10°	2683	2611	2594
15°	2646	2525	2459
20°	2597	2407	2294
25°	2547	2274	2135
30°	2480	2137	1932
35°	2414	1990	1755
40°	2347	1839	1551
45°	2269	1670	1366
50°	2189	1500	1185
55°	2105	1318	1012
60°	2008	1128	833
65°	1896	934	751
70°	1760	754	680
75°	1590	665	620
80°	1343	559	539
85°	935	375	409

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2422 cd/sqm

TEST NUMBER: P917070

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.4	2.1
10°-20°	953.6	5.9
20°-30°	1338.9	8.2
30°-40°	1459.5	9.0
40°-50°	1341.4	8.2
50°-60°	1053.5	6.5
60°-70°	685.7	4.2
70°-80°	353.0	2.2
80°-90°	98.9	0.6
90°-100°	191.5	1.2
100°-110°	608.3	3.7
110°-120°	1041.1	6.4
120°-130°	1369.2	8.4
130°-140°	1536.9	9.4
140°-150°	1507.1	9.3
150°-160°	1264.2	7.8
160°-170°	838.4	5.1
170°-180°	293.0	1.8
0°-30°	2639.9	16.2
0°-40°	4099.4	25.2
0°-60°	6494.2	39.9
0°-90°	7631.8	46.9
90°-120°	1840.9	11.3
90°-150°	6254.0	38.4
90°-180°	8650.0	53.1
0°-180°	16281.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3707	3707	3707	3707	3707	
5°	3707	3690	3646	3676	3666	351
15°	3525	3488	3374	3311	3277	993
25°	3200	3093	2871	2734	2683	1472
35°	2757	2586	2291	2080	2006	1726
45°	2254	2029	1677	1439	1358	1741
55°	1714	1452	1090	889	825	1532
65°	1157	885	584	470	459	1147
75°	617	382	268	245	242	653
85°	144	74	64	64	64	165
90°	3	34	91	86	89	16
95°	136	162	167	167	162	152
105°	562	569	575	579	579	593
115°	1045	1060	1055	1052	1045	1033
125°	1520	1543	1536	1527	1524	1358
135°	1965	1994	2000	1997	1990	1519
145°	2386	2405	2420	2423	2412	1491
155°	2728	2736	2744	2757	2749	1256
165°	2968	2966	2966	2984	2971	837
175°	3089	3081	3076	3094	3078	293
180°	3094	3094	3094	3094	3094	



TEST NUMBER: P917070

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3706.6	3706.6	3706.6	3706.6	3706.6
2.5°	3723.3	3706.6	3669.6	3703.4	3696.6
5°	3706.6	3689.9	3646.1	3676.3	3666.4
7.5°	3676.3	3656.4	3609.4	3622.6	3605.8
10°	3636.1	3612.6	3545.7	3535.4	3515.5
12.5°	3585.9	3555.7	3464.9	3445.0	3407.9
15°	3525.4	3488.4	3374.5	3310.8	3277.3
17.5°	3455.0	3401.3	3260.3	3186.6	3132.9
20°	3374.5	3307.3	3139.6	3056.0	2982.0
22.5°	3287.4	3210.1	3015.5	2901.6	2851.3
25°	3200.1	3092.7	2871.3	2733.9	2683.4
27.5°	3096.3	2982.0	2737.1	2579.4	2502.2
30°	2985.5	2857.8	2589.5	2418.6	2327.8
32.5°	2878.1	2723.6	2448.8	2247.5	2163.5
35°	2757.4	2586.2	2291.2	2079.8	2005.8
37.5°	2640.0	2455.3	2143.5	1911.8	1828.2
40°	2515.8	2314.7	1989.1	1750.9	1663.8
42.5°	2388.3	2173.7	1835.0	1586.6	1502.9
45°	2254.2	2029.3	1677.3	1438.8	1358.4
47.5°	2126.8	1888.7	1526.4	1287.9	1214.3
50°	1985.8	1747.8	1378.8	1147.0	1076.9
52.5°	1848.1	1596.5	1237.8	1016.4	952.7
55°	1713.9	1452.4	1090.1	889.0	825.3
57.5°	1576.6	1308.2	959.4	771.6	717.8
60°	1435.7	1167.3	821.7	650.9	597.2
62.5°	1298.3	1030.0	704.3	543.5	516.7
65°	1157.3	885.4	583.7	469.8	459.4
67.5°	1023.2	751.3	469.8	412.5	402.5
70°	882.2	620.7	389.0	355.6	342.0
72.5°	748.0	499.7	325.3	298.6	291.8
75°	617.1	382.2	268.3	244.8	241.7
77.5°	486.5	271.6	211.4	197.9	191.1
80°	365.5	194.7	160.9	147.7	147.7
82.5°	254.8	130.9	110.7	104.0	104.0
85°	144.1	73.7	63.7	63.7	63.7
87.5°	53.7	26.7	26.7	23.5	23.5
90°	2.8	33.6	91.4	85.9	88.6
92.5°	57.8	78.4	81.1	84.0	84.0
95°	136.2	162.3	167.0	167.0	162.3
97.5°	226.7	250.9	261.2	261.2	261.2
100°	331.2	352.6	360.0	360.0	357.3
102.5°	441.2	457.1	467.3	470.2	467.3
105°	561.6	569.0	574.6	579.3	579.3
107.5°	680.9	692.2	692.2	694.0	680.9
110°	796.6	811.5	811.5	811.5	804.1



TEST NUMBER: P917070

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	921.6	937.5	934.7	927.2	921.6
115°	1044.7	1059.7	1055.0	1052.2	1044.7
117.5°	1166.9	1187.5	1174.4	1166.9	1159.5
120°	1290.1	1310.6	1290.1	1290.1	1281.7
122.5°	1402.1	1428.2	1415.1	1407.6	1402.1
125°	1519.6	1542.9	1535.5	1527.1	1524.2
127.5°	1634.3	1663.2	1652.9	1641.8	1634.3
130°	1741.6	1775.1	1770.5	1764.9	1754.6
132.5°	1861.9	1888.1	1889.9	1876.8	1869.4
135°	1965.4	1994.4	2000.0	1997.2	1989.7
137.5°	2081.1	2104.4	2109.1	2107.2	2096.1
140°	2182.8	2206.1	2219.2	2219.2	2208.9
142.5°	2287.3	2310.6	2318.1	2320.8	2310.6
145°	2386.1	2404.8	2419.7	2422.6	2412.3
147.5°	2474.8	2498.1	2509.3	2514.0	2503.7
150°	2566.2	2582.0	2592.3	2600.7	2592.3
152.5°	2647.4	2663.2	2676.3	2686.6	2676.3
155°	2728.5	2736.0	2744.4	2757.4	2749.0
157.5°	2798.5	2804.1	2808.7	2827.4	2814.3
160°	2861.0	2866.6	2869.4	2885.3	2874.0
162.5°	2918.8	2918.8	2921.6	2939.3	2926.3
165°	2968.3	2965.5	2965.5	2984.1	2971.0
167.5°	3013.0	3004.6	3004.6	3023.3	3010.2
170°	3046.6	3039.1	3036.3	3055.0	3039.1
172.5°	3069.9	3062.4	3059.7	3078.3	3062.4
175°	3088.6	3081.1	3075.5	3094.1	3078.3
177.5°	3098.9	3091.4	3085.7	3101.6	3085.7
180°	3094.1	3094.1	3094.1	3094.1	3094.1

TEST NUMBER: P917070

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.31	11.12	11.30	12.11	13.43	6.28	7.08	7.27	8.08	9.40
	3H	11.99	12.71	12.99	13.72	15.06	7.46	8.18	8.46	9.19	10.53
	4H	12.60	13.28	13.61	14.29	15.64	7.91	8.59	8.93	9.60	10.95
	6H	13.02	13.65	14.05	14.66	16.02	8.23	8.86	9.26	9.88	11.23
	8H	13.15	13.74	14.18	14.78	16.13	8.32	8.92	9.35	9.95	11.31
	12H	13.21	13.78	14.24	14.80	16.18	8.37	8.93	9.40	9.96	11.34
4H	2H	10.33	11.01	11.35	12.02	13.36	6.87	7.55	7.89	8.56	9.91
	3H	12.16	12.72	13.18	13.76	15.12	8.22	8.79	9.25	9.82	11.18
	4H	12.85	13.37	13.88	14.40	15.78	8.77	9.28	9.80	10.32	11.70
	6H	13.37	13.81	14.41	14.86	16.24	9.19	9.63	10.23	10.68	12.06
	8H	13.54	13.96	14.59	15.00	16.40	9.31	9.73	10.36	10.78	12.17
	12H	13.64	14.01	14.70	15.07	16.47	9.38	9.75	10.44	10.82	12.21
8H	4H	12.82	13.23	13.86	14.28	15.67	9.05	9.46	10.09	10.51	11.90
	6H	13.38	13.73	14.45	14.82	16.21	9.57	9.91	10.64	11.00	12.39
	8H	13.60	13.90	14.68	14.98	16.39	9.76	10.06	10.83	11.13	12.54
	12H	13.74	14.01	14.82	15.07	16.53	9.88	10.14	10.96	11.21	12.66
12H	4H	12.77	13.14	13.83	14.20	15.60	9.05	9.43	10.11	10.49	11.89
	6H	13.36	13.66	14.44	14.73	16.14	9.62	9.92	10.69	10.99	12.40
	8H	13.58	13.85	14.66	14.91	16.37	9.83	10.09	10.91	11.16	12.61

END OF REPORT