

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925286

Luminaire Tested: DFN2DIP-PN4F0-120D110US950-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P925286  
REPORT IS A COMBINATION OF REPORTS P899752 AND P896497  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-120D110US950-RLLFLL  
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 19018.0 lumens  
Efficiency: N/A  
Efficacy: 87.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 217.9  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9781  
Total Harmonic Distortion (THDi): 0.075  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P925286  
CATALOG NUMBER: DFN2DIP-PN4F0-120D110US950-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P925286

CATALOG NUMBER: DFN2DIP-PN4F0-120D110US950-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42	38
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	37	33
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32	28
5	70	58	51	45	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	31	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3454	3454	3454
5°	3459	3399	3421
10°	3425	3333	3311
15°	3378	3223	3139
20°	3316	3072	2928
25°	3252	2902	2725
30°	3166	2728	2467
35°	3082	2541	2240
40°	2996	2347	1979
45°	2897	2132	1743
50°	2794	1915	1513
55°	2687	1682	1291
60°	2563	1439	1064
65°	2420	1193	958
70°	2247	962	868
75°	2029	849	791
80°	1714	714	688
85°	1194	479	522

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2897 cd/sqm



TEST NUMBER: P925286

CATALOG NUMBER: DFN2DIP-PN4F0-120D110US950-RLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	443.4	2.3
10°-20°	1217.3	6.4
20°-30°	1709.1	9.0
30°-40°	1863.0	9.8
40°-50°	1712.3	9.0
50°-60°	1344.7	7.1
60°-70°	875.3	4.6
70°-80°	450.6	2.4
80°-90°	124.5	0.7
90°-100°	205.4	1.1
100°-110°	652.5	3.4
110°-120°	1116.7	5.9
120°-130°	1468.6	7.7
130°-140°	1648.4	8.7
140°-150°	1616.5	8.5
150°-160°	1356.0	7.1
160°-170°	899.3	4.7
170°-180°	314.3	1.7
0°-30°	3369.8	17.7
0°-40°	5232.8	27.5
0°-60°	8289.9	43.6
0°-90°	9740.2	51.2
90°-120°	1974.6	10.4
90°-150°	6708.2	35.3
90°-180°	9278.0	48.8
0°-180°	19018.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4732	4732	4732	4732	4732	
5°	4732	4710	4654	4693	4680	449
15°	4500	4453	4308	4226	4184	1268
25°	4085	3948	3665	3490	3425	1879
35°	3520	3301	2925	2655	2560	2203
45°	2878	2590	2141	1837	1734	2222
55°	2188	1854	1392	1135	1054	1955
65°	1477	1130	745	600	586	1465
75°	788	488	343	312	308	833
85°	184	94	81	81	81	211
90°	3	36	98	92	95	19
95°	146	174	179	179	174	163
105°	602	610	616	621	621	636
115°	1121	1137	1132	1129	1121	1108
125°	1630	1655	1647	1638	1635	1457
135°	2108	2139	2145	2142	2134	1630
145°	2559	2579	2596	2598	2587	1599
155°	2927	2935	2944	2958	2949	1347
165°	3184	3181	3181	3201	3187	898
175°	3313	3305	3299	3319	3302	315
180°	3319	3319	3319	3319	3319	



TEST NUMBER: P925286

CATALOG NUMBER: DFN2DIP-PN4F0-120D110US950-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4731.5	4731.5	4731.5	4731.5	4731.5
2.5°	4752.8	4731.5	4684.2	4727.4	4718.7
5°	4731.5	4710.1	4654.2	4692.8	4680.1
7.5°	4692.8	4667.3	4607.4	4624.2	4602.9
10°	4641.5	4611.5	4526.1	4512.9	4487.5
12.5°	4577.4	4538.8	4422.9	4397.6	4350.3
15°	4500.2	4453.0	4307.6	4226.2	4183.6
17.5°	4410.2	4341.7	4161.7	4067.8	3999.2
20°	4307.6	4221.7	4007.8	3901.0	3806.5
22.5°	4196.3	4097.7	3849.2	3703.8	3639.8
25°	4085.0	3947.7	3665.2	3489.8	3425.3
27.5°	3952.3	3806.5	3493.9	3292.7	3194.1
30°	3811.0	3648.0	3305.4	3087.3	2971.5
32.5°	3673.9	3476.7	3126.0	2868.9	2761.6
35°	3519.9	3301.3	2924.7	2654.9	2560.3
37.5°	3369.9	3134.2	2736.2	2440.4	2333.7
40°	3211.4	2954.7	2539.1	2235.1	2123.8
42.5°	3048.7	2774.8	2342.4	2025.2	1918.5
45°	2877.5	2590.4	2141.1	1836.7	1734.0
47.5°	2714.8	2410.9	1948.4	1644.1	1550.1
50°	2535.0	2231.0	1759.9	1464.2	1374.7
52.5°	2359.1	2037.9	1580.0	1297.4	1216.2
55°	2187.9	1854.0	1391.5	1134.8	1053.5
57.5°	2012.5	1670.0	1224.7	984.9	916.3
60°	1832.6	1490.1	1048.9	830.9	762.3
62.5°	1657.3	1314.7	899.0	693.7	659.6
65°	1477.4	1130.3	745.1	599.7	586.5
67.5°	1306.1	959.0	599.7	526.5	513.8
70°	1126.2	792.3	496.6	453.8	436.6
72.5°	955.0	637.8	415.2	381.1	372.5
75°	787.7	487.9	342.6	312.5	308.4
77.5°	621.1	346.6	269.9	252.6	243.9
80°	466.6	248.5	205.3	188.5	188.5
82.5°	325.3	167.1	141.3	132.6	132.6
85°	184.0	94.1	81.3	81.3	81.3
87.5°	68.6	34.1	34.1	30.0	30.0
90°	3.0	36.1	98.1	92.1	95.0
92.5°	62.0	84.0	87.0	90.1	90.1
95°	146.1	174.1	179.1	179.1	174.1
97.5°	243.2	269.1	280.2	280.2	280.2
100°	355.2	378.2	386.2	386.2	383.2
102.5°	473.3	490.3	501.3	504.3	501.3
105°	602.4	610.4	616.4	621.3	621.3
107.5°	730.4	742.4	742.4	744.4	730.4
110°	854.5	870.5	870.5	870.5	862.5



TEST NUMBER: P925286

CATALOG NUMBER: DFN2DIP-PN4F0-120D110US950-RLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	988.5	1005.5	1002.6	994.5	988.5
115°	1120.7	1136.6	1131.6	1128.7	1120.7
117.5°	1251.7	1273.7	1259.7	1251.7	1243.7
120°	1383.8	1405.8	1383.8	1383.8	1374.8
122.5°	1503.9	1531.8	1517.8	1509.8	1503.9
125°	1629.9	1654.9	1646.9	1637.9	1634.9
127.5°	1753.0	1784.0	1773.0	1761.0	1753.0
130°	1868.0	1904.1	1899.0	1893.0	1882.1
132.5°	1997.1	2025.2	2027.2	2013.1	2005.1
135°	2108.1	2139.2	2145.2	2142.2	2134.2
137.5°	2232.3	2257.3	2262.2	2260.2	2248.3
140°	2341.3	2366.3	2380.3	2380.3	2369.4
142.5°	2453.4	2478.4	2486.4	2489.4	2478.4
145°	2559.4	2579.4	2595.5	2598.4	2587.4
147.5°	2654.5	2679.5	2691.5	2696.5	2685.5
150°	2752.6	2769.6	2780.5	2789.6	2780.5
152.5°	2839.6	2856.6	2870.6	2881.7	2870.6
155°	2926.7	2934.6	2943.7	2957.7	2948.6
157.5°	3001.7	3007.7	3012.6	3032.7	3018.6
160°	3068.7	3074.7	3077.7	3094.8	3082.8
162.5°	3130.7	3130.7	3133.8	3152.8	3138.8
165°	3183.8	3180.7	3180.7	3200.8	3186.7
167.5°	3231.8	3222.8	3222.8	3242.8	3228.8
170°	3267.8	3259.8	3256.9	3276.8	3259.8
172.5°	3292.8	3284.8	3281.9	3301.9	3284.8
175°	3312.9	3304.8	3298.8	3318.9	3301.9
177.5°	3323.8	3315.8	3309.8	3326.9	3309.8
180°	3318.9	3318.9	3318.9	3318.9	3318.9



TEST NUMBER: P925286  
 CATALOG NUMBER: DFN2DIP-PN4F0-120D110US950-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.57	12.41	12.53	13.38	14.63	7.54	8.38	8.49	9.34	10.60
	3H	13.25	14.00	14.22	14.98	16.26	8.73	9.48	9.69	10.45	11.73
	4H	13.86	14.57	14.84	15.55	16.84	9.18	9.89	10.16	10.87	12.15
	6H	14.29	14.94	15.28	15.93	17.23	9.50	10.15	10.49	11.14	12.44
	8H	14.42	15.04	15.41	16.04	17.34	9.59	10.21	10.59	11.21	12.51
	12H	14.48	15.07	15.48	16.06	17.39	9.64	10.23	10.64	11.22	12.54
4H	2H	11.59	12.30	12.58	13.28	14.57	8.14	8.85	9.12	9.82	11.11
	3H	13.43	14.02	14.42	15.02	16.32	9.49	10.08	10.48	11.08	12.39
	4H	14.12	14.66	15.12	15.66	16.98	10.04	10.58	11.04	11.58	12.90
	6H	14.64	15.10	15.65	16.13	17.45	10.46	10.92	11.47	11.94	13.27
	8H	14.82	15.25	15.83	16.26	17.60	10.59	11.02	11.60	12.04	13.37
	12H	14.91	15.30	15.94	16.33	17.68	10.65	11.04	11.68	12.07	13.42
8H	4H	14.09	14.52	15.10	15.54	16.87	10.32	10.75	11.33	11.77	13.11
	6H	14.66	15.02	15.70	16.07	17.41	10.84	11.20	11.88	12.25	13.59
	8H	14.88	15.19	15.92	16.24	17.59	11.03	11.35	12.08	12.39	13.74
	12H	15.02	15.29	16.07	16.33	17.73	11.15	11.43	12.20	12.47	13.86
12H	4H	14.04	14.43	15.07	15.46	16.81	10.32	10.71	11.36	11.75	13.09
	6H	14.63	14.95	15.68	15.99	17.35	10.89	11.20	11.94	12.25	13.60
	8H	14.86	15.13	15.91	16.17	17.57	11.10	11.38	12.15	12.42	13.81