

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925289

Luminaire Tested: DFN2DIP-PN4F0-120D120US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925289
REPORT IS A COMBINATION OF REPORTS P901289 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-120D120US950-FLLONL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22667.0 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 229.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925289

CATALOG NUMBER: DFN2DIP-PN4F0-120D120US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P925289

CATALOG NUMBER: DFN2DIP-PN4F0-120D120US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3252	3252	3252
5°	3257	3207	3228
10°	3230	3164	3185
15°	3183	3112	3118
20°	3119	3040	3048
25°	3055	2954	2968
30°	2975	2874	2866
35°	2899	2780	2758
40°	2806	2684	2655
45°	2713	2588	2550
50°	2611	2488	2428
55°	2504	2372	2316
60°	2384	2234	2188
65°	2253	2091	2037
70°	2085	1917	1874
75°	1853	1709	1725
80°	1574	1444	1438
85°	1139	985	963

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2713 cd/sqm

TEST NUMBER: P925289

CATALOG NUMBER: DFN2DIP-PN4F0-120D120US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	419.3	1.8
10°-20°	1179.6	5.2
20°-30°	1733.6	7.6
30°-40°	2013.5	8.9
40°-50°	2011.0	8.9
50°-60°	1753.5	7.7
60°-70°	1296.2	5.7
70°-80°	733.4	3.2
80°-90°	200.4	0.9
90°-100°	127.4	0.6
100°-110°	474.9	2.1
110°-120°	1259.5	5.6
120°-130°	2089.1	9.2
130°-140°	2219.1	9.8
140°-150°	2062.4	9.1
150°-160°	1658.1	7.3
160°-170°	1068.4	4.7
170°-180°	367.7	1.6
0°-30°	3332.5	14.7
0°-40°	5345.9	23.6
0°-60°	9110.4	40.2
0°-90°	11340.3	50.0
90°-120°	1861.9	8.2
90°-150°	8232.4	36.3
90°-180°	11327.0	50.0
0°-180°	22667.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4454	4454	4454	4454	4454	
5°	4454	4438	4390	4424	4416	423
15°	4240	4215	4159	4176	4155	1194
25°	3838	3804	3731	3739	3731	1766
35°	3311	3268	3200	3174	3152	2068
45°	2694	2664	2600	2553	2536	2079
55°	2039	2013	1962	1910	1889	1823
65°	1375	1349	1306	1268	1247	1360
75°	719	711	689	664	673	768
85°	175	171	167	154	150	196
90°	3	34	56	70	75	21
95°	182	89	109	123	120	215
105°	850	934	171	201	212	908
115°	1607	1655	1725	430	229	1582
125°	2273	2309	2362	2382	2390	2027
135°	2812	2857	2882	2910	2905	2173
145°	3263	3260	3307	3327	3313	2041
155°	3592	3567	3601	3618	3595	1655
165°	3785	3769	3777	3796	3777	1069
175°	3872	3852	3858	3878	3850	368
180°	3864	3864	3864	3864	3864	

TEST NUMBER: P925289

CATALOG NUMBER: DFN2DIP-PN4F0-120D120US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4454.5	4454.5	4454.5	4454.5	4454.5
2.5°	4480.4	4459.0	4411.8	4454.5	4446.3
5°	4454.5	4437.6	4390.4	4424.5	4416.3
7.5°	4424.5	4399.0	4351.8	4386.3	4377.7
10°	4377.7	4347.7	4296.3	4330.4	4317.7
12.5°	4313.1	4287.7	4236.3	4257.7	4249.0
15°	4240.4	4215.0	4159.1	4176.3	4155.0
17.5°	4150.5	4125.0	4069.1	4090.5	4069.1
20°	4051.8	4026.4	3966.4	3979.1	3962.3
22.5°	3953.7	3915.0	3859.1	3859.1	3850.5
25°	3837.8	3803.7	3731.0	3739.2	3731.0
27.5°	3709.2	3679.2	3623.8	3611.0	3589.7
30°	3581.0	3546.5	3482.4	3469.7	3452.4
32.5°	3443.7	3418.4	3349.7	3323.8	3306.6
35°	3311.0	3268.4	3199.7	3173.9	3152.5
37.5°	3161.1	3122.5	3053.8	3023.9	3002.5
40°	3007.1	2972.6	2903.9	2865.7	2848.5
42.5°	2857.1	2822.6	2754.4	2711.3	2685.8
45°	2694.4	2664.4	2599.8	2553.1	2535.8
47.5°	2535.8	2505.8	2437.2	2390.0	2364.5
50°	2368.6	2347.2	2287.2	2227.2	2205.8
52.5°	2205.8	2175.9	2120.5	2073.1	2043.2
55°	2039.1	2013.2	1961.8	1910.5	1889.1
57.5°	1871.8	1850.5	1794.6	1743.2	1726.0
60°	1704.6	1687.8	1627.8	1580.6	1567.8
62.5°	1542.0	1511.9	1469.3	1426.5	1409.2
65°	1375.2	1349.2	1306.5	1267.9	1246.6
67.5°	1203.9	1182.0	1143.8	1113.9	1096.6
70°	1045.2	1027.9	989.3	959.3	942.6
72.5°	882.5	865.3	843.9	814.0	801.2
75°	719.4	711.2	689.4	664.0	672.6
77.5°	573.9	556.7	548.1	535.3	522.6
80°	428.5	424.0	415.4	402.7	394.0
82.5°	291.3	291.3	287.2	270.0	270.0
85°	175.4	171.3	167.2	154.1	150.0
87.5°	77.3	68.6	60.0	47.2	42.7
90°	2.7	33.5	55.8	70.0	75.4
92.5°	70.0	58.8	67.1	72.7	75.4
95°	181.5	89.3	108.9	123.2	120.2
97.5°	327.0	98.0	142.4	151.0	153.7
100°	494.9	111.9	159.3	181.5	187.3
102.5°	679.2	673.9	164.9	195.6	204.2
105°	849.8	933.9	170.7	201.2	212.5
107.5°	1048.4	1118.1	176.3	206.8	218.1
110°	1238.6	1297.1	489.3	209.8	220.8

TEST NUMBER: P925289

CATALOG NUMBER: DFN2DIP-PN4F0-120D120US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1417.5	1467.6	1420.2	215.1	223.7
115°	1607.4	1654.9	1724.9	430.5	229.4
117.5°	1772.4	1828.2	1876.0	1475.9	743.6
120°	1957.0	1998.8	2049.3	2082.9	1705.4
122.5°	2113.4	2158.2	2214.3	2230.9	2233.9
125°	2272.7	2309.3	2362.4	2381.9	2390.2
127.5°	2418.1	2457.3	2499.5	2527.3	2530.0
130°	2555.2	2600.0	2630.6	2661.5	2658.8
132.5°	2695.0	2731.5	2762.0	2787.3	2784.6
135°	2812.5	2857.3	2882.2	2910.5	2904.8
137.5°	2935.4	2968.8	2997.1	3024.9	3016.6
140°	3055.6	3078.1	3108.6	3133.9	3120.0
142.5°	3156.4	3176.1	3212.2	3234.4	3220.5
145°	3262.7	3259.7	3307.1	3326.8	3312.8
147.5°	3354.6	3346.3	3393.9	3407.8	3396.8
150°	3444.2	3424.7	3469.5	3486.1	3472.2
152.5°	3519.6	3497.4	3539.2	3556.1	3536.6
155°	3592.3	3567.4	3601.0	3617.6	3595.3
157.5°	3651.1	3628.8	3654.1	3673.7	3651.1
160°	3701.5	3684.6	3701.5	3718.1	3698.6
162.5°	3746.1	3729.5	3743.4	3763.0	3737.8
165°	3785.2	3768.6	3776.9	3796.5	3776.9
167.5°	3816.1	3799.1	3807.8	3827.4	3802.2
170°	3841.3	3824.4	3830.0	3849.6	3824.4
172.5°	3857.9	3841.3	3847.0	3866.6	3841.3
175°	3871.8	3852.3	3857.9	3877.5	3849.6
177.5°	3877.5	3857.9	3860.9	3880.5	3855.3
180°	3863.6	3863.6	3863.6	3863.6	3863.6

TEST NUMBER: P925289

CATALOG NUMBER: DFN2DIP-PN4F0-120D120US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.38	12.24	12.34	13.21	14.48	10.94	11.80	11.90	12.77	14.04
	3H	13.04	13.81	14.01	14.80	16.09	12.56	13.33	13.53	14.31	15.60
	4H	13.63	14.36	14.61	15.35	16.65	13.14	13.88	14.13	14.86	16.16
	6H	14.03	14.71	15.03	15.70	17.01	13.54	14.22	14.53	15.21	16.52
	8H	14.14	14.78	15.14	15.79	17.10	13.65	14.29	14.65	15.30	16.61
	12H	14.19	14.80	15.19	15.80	17.14	13.69	14.30	14.69	15.30	16.64
4H	2H	11.84	12.57	12.83	13.56	14.86	11.49	12.22	12.48	13.21	14.51
	3H	13.71	14.32	14.71	15.33	16.65	13.31	13.92	14.30	14.93	16.25
	4H	14.43	14.98	15.43	15.99	17.33	14.01	14.57	15.01	15.57	16.91
	6H	14.94	15.42	15.96	16.46	17.79	14.52	15.00	15.54	16.03	17.37
	8H	15.10	15.54	16.11	16.57	17.92	14.67	15.12	15.68	16.14	17.49
	12H	15.17	15.58	16.21	16.61	17.97	14.73	15.14	15.77	16.17	17.53
8H	4H	14.62	15.07	15.64	16.10	17.45	14.25	14.70	15.27	15.72	17.08
	6H	15.26	15.63	16.30	16.69	18.04	14.88	15.25	15.92	16.32	17.67
	8H	15.48	15.81	16.53	16.86	18.23	15.10	15.42	16.15	16.47	17.84
	12H	15.61	15.90	16.67	16.95	18.36	15.21	15.50	16.27	16.55	17.96
12H	4H	14.61	15.01	15.65	16.05	17.41	14.25	14.65	15.28	15.69	17.05
	6H	15.29	15.62	16.34	16.67	18.03	14.92	15.25	15.97	16.30	17.67
	8H	15.53	15.82	16.59	16.87	18.28	15.16	15.45	16.21	16.49	17.90

END OF REPORT