

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903510

Luminaire Tested: DFN2DIP-SQ2F0-040D070US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903510
REPORT IS A COMBINATION OF REPORTS P899822 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-040D070US830-RLLFLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9043.7 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903510
CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US830-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P903510

CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36				36
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	31				31
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	31	26				26
3	79	70	63	58	71	64	58	53	52	48	44	41	38	36	31	29	27	23				23
4	73	62	55	49	65	57	50	45	46	42	38	37	33	31	27	25	24	20				20
5	67	56	48	42	60	51	44	39	42	37	33	33	29	27	25	23	21	17				17
6	61	50	42	37	55	46	39	34	37	32	29	30	26	24	23	20	18	15				15
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14				14
8	53	41	33	28	48	38	31	26	31	26	23	25	21	19	19	17	15	12				12
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	14	11				11
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	16	14	12	10				10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3426	3426	3426
5°	3426	3365	3389
10°	3386	3291	3274
15°	3334	3175	3099
20°	3266	3018	2886
25°	3197	2844	2680
30°	3106	2665	2422
35°	3016	2475	2194
40°	2925	2278	1935
45°	2819	2061	1699
50°	2710	1842	1469
55°	2595	1610	1249
60°	2461	1368	1024
65°	2308	1122	916
70°	2121	894	822
75°	1886	774	739
80°	1548	628	626
85°	1008	391	446

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2909 cd/sqm



TEST NUMBER: P903510

CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	1.6
10°-20°	400.9	4.4
20°-30°	562.8	6.2
30°-40°	613.5	6.8
40°-50°	563.9	6.2
50°-60°	442.9	4.9
60°-70°	288.3	3.2
70°-80°	148.4	1.6
80°-90°	43.8	0.5
90°-100°	129.1	1.4
100°-110°	410.3	4.5
110°-120°	702.1	7.8
120°-130°	923.3	10.2
130°-140°	1036.4	11.5
140°-150°	1016.3	11.2
150°-160°	852.6	9.4
160°-170°	565.4	6.3
170°-180°	197.6	2.2
0°-30°	1109.8	12.3
0°-40°	1723.3	19.1
0°-60°	2730.1	30.2
0°-90°	3210.5	35.5
90°-120°	1241.5	13.7
90°-150°	4217.6	46.6
90°-180°	5833.0	64.5
0°-180°	9043.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1558	1558	1558	1558	1558	
5°	1558	1551	1533	1546	1541	148
15°	1482	1466	1419	1392	1378	418
25°	1345	1300	1207	1149	1128	619
35°	1159	1087	963	874	843	726
45°	948	853	705	605	571	732
55°	721	611	458	374	347	644
65°	486	372	245	198	193	482
75°	259	161	113	103	102	274
85°	61	31	27	27	27	70
90°	2	23	62	58	60	9
95°	92	109	113	113	109	102
105°	379	384	388	391	391	400
115°	705	715	712	710	705	697
125°	1025	1040	1036	1030	1028	916
135°	1326	1345	1349	1347	1342	1025
145°	1609	1622	1632	1634	1627	1005
155°	1840	1845	1851	1860	1854	847
165°	2002	2000	2000	2012	2004	565
175°	2083	2078	2074	2087	2076	198
180°	2087	2087	2087	2087	2087	



TEST NUMBER: P903510

CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1558.2	1558.2	1558.2	1558.2	1558.2
2.5°	1565.3	1558.2	1542.7	1556.9	1554.0
5°	1558.2	1551.1	1532.8	1545.5	1541.3
7.5°	1545.5	1537.1	1517.4	1522.9	1515.9
10°	1528.6	1518.7	1490.5	1486.2	1477.9
12.5°	1507.5	1494.8	1456.6	1448.2	1432.7
15°	1482.1	1466.5	1418.6	1391.9	1377.8
17.5°	1452.5	1429.8	1370.6	1339.6	1317.0
20°	1418.6	1390.3	1319.8	1284.7	1253.6
22.5°	1382.0	1349.5	1267.6	1219.7	1198.7
25°	1345.3	1300.1	1207.0	1149.3	1128.0
27.5°	1301.7	1253.6	1150.7	1084.4	1051.9
30°	1255.1	1201.4	1088.5	1016.7	978.6
32.5°	1209.9	1145.0	1029.4	944.8	909.5
35°	1159.2	1087.2	963.2	874.3	843.2
37.5°	1109.8	1032.2	901.1	803.7	768.5
40°	1057.6	973.1	836.2	736.1	699.5
42.5°	1004.0	913.8	771.4	666.9	631.8
45°	947.6	853.1	705.1	604.9	571.1
47.5°	894.1	794.0	641.7	541.5	510.5
50°	834.8	734.7	579.6	482.2	452.7
52.5°	776.9	671.2	520.4	427.3	400.5
55°	720.6	610.6	458.3	373.7	346.9
57.5°	662.8	550.0	403.3	324.3	301.8
60°	603.5	490.7	345.4	273.6	251.1
62.5°	545.8	433.0	296.1	228.5	217.3
65°	486.5	372.2	245.3	197.5	193.1
67.5°	430.2	315.8	197.5	173.4	169.2
70°	370.9	260.9	163.5	149.5	143.7
72.5°	314.5	210.1	136.8	125.5	122.7
75°	259.4	160.7	112.8	102.9	101.6
77.5°	204.5	114.1	88.9	83.2	80.3
80°	153.6	81.8	67.6	62.1	62.1
82.5°	107.2	55.0	46.6	43.6	43.6
85°	60.6	31.0	26.8	26.8	26.8
87.5°	22.6	11.2	11.2	9.9	9.9
90°	1.9	22.6	61.6	57.9	59.8
92.5°	39.0	52.9	54.8	56.6	56.6
95°	91.8	109.4	112.6	112.6	109.4
97.5°	152.9	169.2	176.2	176.2	176.2
100°	223.3	237.8	242.8	242.8	240.9
102.5°	297.6	308.2	315.2	317.1	315.2
105°	378.7	383.7	387.5	390.7	390.7
107.5°	459.2	466.7	466.7	468.1	459.2
110°	537.2	547.3	547.3	547.3	542.2



TEST NUMBER: P903510

CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	621.5	632.3	630.4	625.3	621.5
115°	704.6	714.6	711.5	709.6	704.6
117.5°	786.9	800.8	792.0	786.9	781.9
120°	870.0	883.8	870.0	870.0	864.3
122.5°	945.5	963.1	954.3	949.2	945.5
125°	1024.7	1040.5	1035.5	1029.8	1027.9
127.5°	1102.1	1121.6	1114.7	1107.2	1102.1
130°	1174.5	1197.1	1194.0	1190.2	1183.3
132.5°	1255.7	1273.3	1274.5	1265.7	1260.7
135°	1325.5	1344.9	1348.8	1346.8	1341.8
137.5°	1403.4	1419.2	1422.3	1421.1	1413.5
140°	1472.1	1487.8	1496.6	1496.6	1489.7
142.5°	1542.5	1558.2	1563.2	1565.1	1558.2
145°	1609.2	1621.7	1631.8	1633.7	1626.8
147.5°	1669.0	1684.7	1692.2	1695.4	1688.5
150°	1730.6	1741.3	1748.2	1753.9	1748.2
152.5°	1785.3	1796.0	1804.8	1811.8	1804.8
155°	1840.0	1845.0	1850.8	1859.5	1853.9
157.5°	1887.3	1891.0	1894.1	1906.8	1897.9
160°	1929.4	1933.2	1935.0	1945.7	1938.1
162.5°	1968.4	1968.4	1970.3	1982.2	1973.4
165°	2001.7	1999.8	1999.8	2012.4	2003.6
167.5°	2031.9	2026.3	2026.3	2038.8	2030.0
170°	2054.6	2049.6	2047.7	2060.2	2049.6
172.5°	2070.3	2065.2	2063.3	2075.9	2065.2
175°	2082.8	2077.8	2074.1	2086.6	2075.9
177.5°	2089.8	2084.7	2080.9	2091.7	2080.9
180°	2086.6	2086.6	2086.6	2086.6	2086.6



TEST NUMBER: P903510
 CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.78	10.51	10.86	11.58	13.05	5.74	6.47	6.82	7.54	9.01
	3H	11.43	12.08	12.52	13.16	14.65	6.90	7.55	7.99	8.63	10.12
	4H	12.02	12.64	13.12	13.72	15.21	7.34	7.95	8.43	9.03	10.53
	6H	12.42	12.99	13.53	14.07	15.58	7.64	8.20	8.74	9.29	10.79
	8H	12.54	13.07	13.65	14.18	15.67	7.71	8.25	8.82	9.35	10.85
	12H	12.59	13.10	13.70	14.19	15.71	7.75	8.26	8.86	9.35	10.87
4H	2H	9.78	10.40	10.89	11.48	12.97	6.31	6.93	7.42	8.01	9.50
	3H	11.58	12.09	12.69	13.20	14.70	7.63	8.14	8.74	9.25	10.76
	4H	12.25	12.72	13.37	13.82	15.35	8.16	8.63	9.28	9.73	11.25
	6H	12.74	13.14	13.86	14.27	15.78	8.55	8.96	9.68	10.08	11.60
	8H	12.90	13.28	14.03	14.39	15.93	8.67	9.04	9.79	10.16	11.69
	12H	12.98	13.32	14.12	14.45	15.99	8.72	9.06	9.86	10.19	11.72
8H	4H	12.21	12.58	13.33	13.70	15.23	8.42	8.80	9.54	9.91	11.44
	6H	12.75	13.06	13.89	14.21	15.74	8.91	9.22	10.05	10.38	11.91
	8H	12.95	13.22	14.10	14.36	15.91	9.09	9.36	10.24	10.50	12.05
	12H	13.07	13.31	14.22	14.44	16.03	9.19	9.42	10.34	10.56	12.14
12H	4H	12.15	12.49	13.29	13.62	15.16	8.42	8.76	9.56	9.89	11.42
	6H	12.72	12.99	13.87	14.13	15.68	8.95	9.23	10.10	10.36	11.91
	8H	12.92	13.16	14.07	14.29	15.88	9.14	9.38	10.30	10.52	12.10