

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919624

Luminaire Tested: DFN2DIP-PN4F0-070D050US935-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P919624  
REPORT IS A COMBINATION OF REPORTS P899633 AND P896497  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-070D050US935-FLLFLL  
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9776.6 lumens  
Efficiency: N/A  
Efficacy: 93.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 104.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9789  
Total Harmonic Distortion (THDi): 0.074  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P919624  
CATALOG NUMBER: DFN2DIP-PN4F0-070D050US935-FLLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P919624

CATALOG NUMBER: DFN2DIP-PN4F0-070D050US935-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	61
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	56	56	56	51
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47	47	47	47	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	40	40	40	37
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35	35	35	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	30	30	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	34	30	33	30	27	27	27	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	24	24	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	21	21	21	19
9	52	39	32	27	48	37	30	25	33	27	23	30	25	21	26	22	19	19	19	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	17	17	17	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1712	1712	1712
5°	1715	1688	1700
10°	1701	1666	1677
15°	1676	1639	1641
20°	1642	1601	1605
25°	1608	1555	1563
30°	1566	1513	1509
35°	1526	1463	1452
40°	1477	1413	1398
45°	1428	1363	1342
50°	1375	1310	1278
55°	1318	1249	1219
60°	1255	1176	1152
65°	1186	1101	1072
70°	1098	1009	987
75°	976	900	908
80°	829	760	757
85°	600	519	507

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1428 cd/sqm



TEST NUMBER: P919624

CATALOG NUMBER: DFN2DIP-PN4F0-070D050US935-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	220.7	2.3
10°-20°	621.0	6.4
20°-30°	912.7	9.3
30°-40°	1060.0	10.8
40°-50°	1058.7	10.8
50°-60°	923.2	9.4
60°-70°	682.4	7.0
70°-80°	386.1	3.9
80°-90°	105.8	1.1
90°-100°	84.2	0.9
100°-110°	267.7	2.7
110°-120°	458.1	4.7
120°-130°	602.5	6.2
130°-140°	676.3	6.9
140°-150°	663.1	6.8
150°-160°	556.3	5.7
160°-170°	368.9	3.8
170°-180°	128.9	1.3
0°-30°	1754.4	17.9
0°-40°	2814.4	28.8
0°-60°	4796.3	49.1
0°-90°	5970.6	61.1
90°-120°	810.0	8.3
90°-150°	2751.9	28.1
90°-180°	3806.0	38.9
0°-180°	9776.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2345	2345	2345	2345	2345	
5°	2345	2336	2311	2329	2325	223
15°	2232	2219	2190	2199	2188	629
25°	2020	2002	1964	1969	1964	930
35°	1743	1721	1684	1671	1660	1089
45°	1418	1403	1369	1344	1335	1095
55°	1074	1060	1033	1006	994	960
65°	724	710	688	668	656	716
75°	379	374	363	350	354	404
85°	92	90	88	81	79	103
90°	1	15	40	38	39	9
95°	60	72	73	73	72	67
105°	247	250	253	255	255	261
115°	460	466	464	463	460	455
125°	669	679	676	672	671	598
135°	865	878	880	879	876	669
145°	1050	1058	1065	1066	1061	656
155°	1201	1204	1208	1213	1210	553
165°	1306	1305	1305	1313	1307	368
175°	1359	1356	1353	1362	1354	129
180°	1362	1362	1362	1362	1362	



TEST NUMBER: P919624

CATALOG NUMBER: DFN2DIP-PN4F0-070D050US935-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2345.1	2345.1	2345.1	2345.1	2345.1
2.5°	2358.8	2347.5	2322.6	2345.1	2340.8
5°	2345.1	2336.3	2311.4	2329.3	2325.0
7.5°	2329.3	2315.9	2291.0	2309.3	2304.7
10°	2304.7	2288.9	2261.8	2279.8	2273.1
12.5°	2270.7	2257.4	2230.3	2241.5	2237.0
15°	2232.5	2219.0	2189.6	2198.7	2187.5
17.5°	2185.0	2171.7	2142.2	2153.5	2142.2
20°	2133.1	2119.8	2088.2	2094.9	2086.0
22.5°	2081.5	2061.1	2031.7	2031.7	2027.1
25°	2020.5	2002.5	1964.3	1968.6	1964.3
27.5°	1952.7	1937.0	1907.8	1901.1	1889.8
30°	1885.3	1867.1	1833.4	1826.7	1817.6
32.5°	1813.0	1799.7	1763.5	1749.9	1740.8
35°	1743.2	1720.7	1684.5	1670.9	1659.7
37.5°	1664.2	1643.9	1607.7	1592.0	1580.7
40°	1583.1	1564.9	1528.8	1508.7	1499.6
42.5°	1504.2	1486.0	1450.1	1427.4	1413.9
45°	1418.5	1402.7	1368.7	1344.1	1335.0
47.5°	1335.0	1319.2	1283.1	1258.2	1244.8
50°	1247.0	1235.7	1204.1	1172.6	1161.3
52.5°	1161.3	1145.6	1116.4	1091.5	1075.6
55°	1073.5	1059.9	1032.9	1005.8	994.5
57.5°	985.5	974.2	944.8	917.7	908.7
60°	897.4	888.5	857.0	832.2	825.4
62.5°	811.7	796.0	773.5	751.0	741.9
65°	724.0	710.3	687.9	667.5	656.3
67.5°	633.8	622.3	602.2	586.4	577.3
70°	550.3	541.2	520.8	505.1	496.2
72.5°	464.6	455.6	444.3	428.5	421.8
75°	378.8	374.4	362.9	349.6	354.1
77.5°	302.2	293.1	288.5	281.8	275.2
80°	225.6	223.3	218.7	212.0	207.4
82.5°	153.3	153.3	151.2	142.2	142.2
85°	92.4	90.2	88.1	81.1	79.0
87.5°	40.6	36.2	31.6	24.9	22.5
90°	1.2	14.8	40.2	37.8	39.0
92.5°	25.5	34.4	35.7	36.9	36.9
95°	59.9	71.5	73.4	73.4	71.5
97.5°	99.7	110.4	114.9	114.9	114.9
100°	145.7	155.2	158.4	158.4	157.2
102.5°	194.2	201.1	205.6	206.9	205.6
105°	247.1	250.4	252.9	254.9	254.9
107.5°	299.6	304.5	304.5	305.4	299.6
110°	350.5	357.1	357.1	357.1	353.8



TEST NUMBER: P919624

CATALOG NUMBER: DFN2DIP-PN4F0-070D050US935-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	405.5	412.5	411.3	408.0	405.5
115°	459.7	466.3	464.3	463.0	459.7
117.5°	513.5	522.5	516.8	513.5	510.2
120°	567.7	576.7	567.7	567.7	564.0
122.5°	616.9	628.4	622.7	619.4	616.9
125°	668.7	678.9	675.6	671.9	670.7
127.5°	719.1	731.8	727.4	722.4	719.1
130°	766.4	781.1	779.0	776.6	772.1
132.5°	819.3	830.8	831.6	825.9	822.6
135°	864.9	877.5	880.0	878.8	875.5
137.5°	915.8	926.0	928.1	927.2	922.3
140°	960.4	970.8	976.5	976.5	972.0
142.5°	1006.4	1016.8	1020.0	1021.2	1016.8
145°	1050.0	1058.2	1064.7	1066.0	1061.4
147.5°	1089.0	1099.2	1104.1	1106.2	1101.6
150°	1129.2	1136.2	1140.6	1144.4	1140.6
152.5°	1164.9	1171.9	1177.6	1182.2	1177.6
155°	1200.6	1203.8	1207.5	1213.3	1209.6
157.5°	1231.4	1233.8	1235.9	1244.1	1238.4
160°	1258.9	1261.4	1262.6	1269.5	1264.6
162.5°	1284.4	1284.4	1285.6	1293.4	1287.6
165°	1306.1	1304.8	1304.8	1313.1	1307.3
167.5°	1325.8	1322.1	1322.1	1330.3	1324.6
170°	1340.6	1337.3	1336.1	1344.3	1337.3
172.5°	1350.8	1347.5	1346.3	1354.5	1347.5
175°	1359.1	1355.7	1353.3	1361.5	1354.5
177.5°	1363.6	1360.3	1357.8	1364.8	1357.8
180°	1361.5	1361.5	1361.5	1361.5	1361.5



TEST NUMBER: P919624  
 CATALOG NUMBER: DFN2DIP-PN4F0-070D050US935-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.11	11.08	10.96	11.96	13.06	9.67	10.64	10.52	11.52	12.62
	3H	11.78	12.65	12.65	13.54	14.67	11.30	12.17	12.16	13.05	14.18
	4H	12.37	13.20	13.26	14.09	15.23	11.89	12.71	12.77	13.60	14.74
	6H	12.78	13.54	13.68	14.44	15.60	12.29	13.05	13.19	13.95	15.10
	8H	12.89	13.61	13.80	14.53	15.69	12.40	13.12	13.30	14.04	15.19
	12H	12.94	13.63	13.85	14.55	15.72	12.44	13.13	13.35	14.05	15.22
4H	2H	10.58	11.41	11.47	12.30	13.44	10.23	11.06	11.12	11.95	13.09
	3H	12.46	13.15	13.36	14.07	15.23	12.06	12.75	12.96	13.67	14.83
	4H	13.18	13.81	14.10	14.73	15.91	12.77	13.39	13.68	14.31	15.49
	6H	13.71	14.25	14.63	15.19	16.38	13.28	13.82	14.21	14.77	15.95
	8H	13.86	14.37	14.79	15.31	16.50	13.43	13.94	14.36	14.88	16.07
	12H	13.94	14.40	14.89	15.35	16.56	13.50	13.96	14.45	14.91	16.12
8H	4H	13.39	13.89	14.32	14.83	16.03	13.02	13.52	13.95	14.46	15.66
	6H	14.03	14.45	14.98	15.43	16.62	13.65	14.07	14.61	15.05	16.25
	8H	14.25	14.62	15.22	15.59	16.81	13.87	14.24	14.83	15.21	16.42
	12H	14.39	14.72	15.36	15.68	16.94	13.99	14.32	14.96	15.28	16.54
12H	4H	13.38	13.84	14.33	14.79	15.99	13.02	13.47	13.97	14.43	15.63
	6H	14.06	14.43	15.02	15.40	16.61	13.69	14.07	14.66	15.04	16.25
	8H	14.31	14.64	15.28	15.60	16.86	13.94	14.26	14.90	15.23	16.49