

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919640

Luminaire Tested: DFN2DIP-PN4F0-070D090US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919640
REPORT IS A COMBINATION OF REPORTS P899705 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-070D090US935-FLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12824.5 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 133.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919640

CATALOG NUMBER: DFN2DIP-PN4F0-070D090US935-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P919640

CATALOG NUMBER: DFN2DIP-PN4F0-070D090US935-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47	47	47
1	97	93	89	85	89	85	82	79	71	69	67	59	57	55	47	46	45	39	39	39
2	88	81	75	70	81	75	69	65	63	59	55	51	49	46	41	39	38	33	33	33
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	37	34	32	28	28	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24	24	24
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24	21	21	21
6	62	50	42	36	57	47	39	34	39	34	30	33	29	25	27	24	21	18	18	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16	16	16
8	53	41	33	28	49	38	31	27	33	27	23	27	23	20	22	19	17	14	14	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13	13	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1712	1712	1712
5°	1715	1688	1700
10°	1701	1666	1677
15°	1676	1639	1641
20°	1642	1601	1605
25°	1608	1555	1563
30°	1566	1513	1509
35°	1526	1463	1452
40°	1477	1413	1398
45°	1428	1363	1342
50°	1375	1310	1278
55°	1318	1249	1219
60°	1255	1176	1152
65°	1186	1101	1072
70°	1098	1009	987
75°	976	900	908
80°	829	760	757
85°	600	519	507

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1919 cd/sqm

TEST NUMBER: P919640

CATALOG NUMBER: DFN2DIP-PN4F0-070D090US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.7	1.7
10°-20°	621.0	4.8
20°-30°	912.7	7.1
30°-40°	1060.0	8.3
40°-50°	1058.7	8.3
50°-60°	923.2	7.2
60°-70°	682.4	5.3
70°-80°	386.1	3.0
80°-90°	108.9	0.8
90°-100°	151.6	1.2
100°-110°	481.8	3.8
110°-120°	824.6	6.4
120°-130°	1084.4	8.5
130°-140°	1217.2	9.5
140°-150°	1193.6	9.3
150°-160°	1001.3	7.8
160°-170°	664.0	5.2
170°-180°	232.1	1.8
0°-30°	1754.4	13.7
0°-40°	2814.4	21.9
0°-60°	4796.3	37.4
0°-90°	5973.7	46.6
90°-120°	1458.0	11.4
90°-150°	4953.4	38.6
90°-180°	6851.0	53.4
0°-180°	12824.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2345	2345	2345	2345	2345	
5°	2345	2336	2311	2329	2325	223
15°	2232	2219	2190	2199	2188	629
25°	2020	2002	1964	1969	1964	930
35°	1743	1721	1684	1671	1660	1089
45°	1418	1403	1369	1344	1335	1095
55°	1074	1060	1033	1006	994	960
65°	724	710	688	668	656	716
75°	379	374	363	350	354	404
85°	92	90	88	81	79	103
90°	2	27	72	68	70	12
95°	108	128	132	132	128	120
105°	445	451	455	459	459	469
115°	828	839	836	833	828	818
125°	1204	1222	1216	1209	1207	1076
135°	1557	1580	1584	1582	1576	1203
145°	1890	1905	1916	1919	1911	1181
155°	2161	2167	2174	2184	2177	995
165°	2351	2349	2349	2364	2353	663
175°	2446	2440	2436	2451	2438	232
180°	2451	2451	2451	2451	2451	

TEST NUMBER: P919640

CATALOG NUMBER: DFN2DIP-PN4F0-070D090US935-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2345.1	2345.1	2345.1	2345.1	2345.1
2.5°	2358.8	2347.5	2322.6	2345.1	2340.8
5°	2345.1	2336.3	2311.4	2329.3	2325.0
7.5°	2329.3	2315.9	2291.0	2309.3	2304.7
10°	2304.7	2288.9	2261.8	2279.8	2273.1
12.5°	2270.7	2257.4	2230.3	2241.5	2237.0
15°	2232.5	2219.0	2189.6	2198.7	2187.5
17.5°	2185.0	2171.7	2142.2	2153.5	2142.2
20°	2133.1	2119.8	2088.2	2094.9	2086.0
22.5°	2081.5	2061.1	2031.7	2031.7	2027.1
25°	2020.5	2002.5	1964.3	1968.6	1964.3
27.5°	1952.7	1937.0	1907.8	1901.1	1889.8
30°	1885.3	1867.1	1833.4	1826.7	1817.6
32.5°	1813.0	1799.7	1763.5	1749.9	1740.8
35°	1743.2	1720.7	1684.5	1670.9	1659.7
37.5°	1664.2	1643.9	1607.7	1592.0	1580.7
40°	1583.1	1564.9	1528.8	1508.7	1499.6
42.5°	1504.2	1486.0	1450.1	1427.4	1413.9
45°	1418.5	1402.7	1368.7	1344.1	1335.0
47.5°	1335.0	1319.2	1283.1	1258.2	1244.8
50°	1247.0	1235.7	1204.1	1172.6	1161.3
52.5°	1161.3	1145.6	1116.4	1091.5	1075.6
55°	1073.5	1059.9	1032.9	1005.8	994.5
57.5°	985.5	974.2	944.8	917.7	908.7
60°	897.4	888.5	857.0	832.2	825.4
62.5°	811.7	796.0	773.5	751.0	741.9
65°	724.0	710.3	687.9	667.5	656.3
67.5°	633.8	622.3	602.2	586.4	577.3
70°	550.3	541.2	520.8	505.1	496.2
72.5°	464.6	455.6	444.3	428.5	421.8
75°	378.8	374.4	362.9	349.6	354.1
77.5°	302.2	293.1	288.5	281.8	275.2
80°	225.6	223.3	218.7	212.0	207.4
82.5°	153.3	153.3	151.2	142.2	142.2
85°	92.4	90.2	88.1	81.1	79.0
87.5°	40.6	36.2	31.6	24.9	22.5
90°	2.2	26.6	72.4	67.9	70.2
92.5°	45.8	62.1	64.3	66.5	66.5
95°	107.9	128.5	132.2	132.2	128.5
97.5°	179.5	198.7	206.9	206.9	206.9
100°	262.3	279.3	285.2	285.2	283.0
102.5°	349.5	362.0	370.1	372.4	370.1
105°	444.8	450.6	455.1	458.8	458.8
107.5°	539.3	548.2	548.2	549.7	539.3
110°	630.9	642.8	642.8	642.8	636.9

TEST NUMBER: P919640

CATALOG NUMBER: DFN2DIP-PN4F0-070D090US935-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	730.0	742.5	740.3	734.4	730.0
115°	827.5	839.3	835.6	833.4	827.5
117.5°	924.3	940.6	930.2	924.3	918.3
120°	1021.8	1038.0	1021.8	1021.8	1015.1
122.5°	1110.4	1131.2	1120.8	1114.9	1110.4
125°	1203.6	1222.0	1216.2	1209.4	1207.3
127.5°	1294.4	1317.3	1309.2	1300.4	1294.4
130°	1379.4	1406.0	1402.3	1397.8	1389.7
132.5°	1474.7	1495.4	1496.8	1486.5	1480.7
135°	1556.7	1579.6	1584.1	1581.8	1576.0
137.5°	1648.3	1666.8	1670.5	1669.0	1660.2
140°	1728.9	1747.3	1757.6	1757.6	1749.5
142.5°	1811.6	1830.1	1836.0	1838.2	1830.1
145°	1890.0	1904.7	1916.5	1918.7	1910.6
147.5°	1960.1	1978.6	1987.4	1991.1	1983.1
150°	2032.6	2045.1	2053.2	2059.9	2053.2
152.5°	2096.8	2109.4	2119.7	2127.9	2119.7
155°	2161.1	2167.0	2173.7	2184.0	2177.4
157.5°	2216.5	2220.9	2224.6	2239.4	2229.0
160°	2266.0	2270.5	2272.7	2285.2	2276.3
162.5°	2311.8	2311.8	2314.0	2328.1	2317.7
165°	2351.0	2348.7	2348.7	2363.5	2353.2
167.5°	2386.4	2379.8	2379.8	2394.5	2384.2
170°	2413.0	2407.1	2404.9	2419.7	2407.1
172.5°	2431.5	2425.6	2423.4	2438.2	2425.6
175°	2446.3	2440.3	2435.9	2450.7	2438.2
177.5°	2454.4	2448.5	2444.0	2456.6	2444.0
180°	2450.7	2450.7	2450.7	2450.7	2450.7

TEST NUMBER: P919640

CATALOG NUMBER: DFN2DIP-PN4F0-070D090US935-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.82	9.65	9.81	10.65	11.97	8.38	9.21	9.37	10.21	11.53
	3H	10.48	11.23	11.48	12.23	13.57	10.00	10.74	10.99	11.75	13.09
	4H	11.07	11.78	12.08	12.79	14.13	10.58	11.29	11.59	12.30	13.65
	6H	11.47	12.12	12.49	13.14	14.50	10.98	11.63	12.00	12.64	14.00
	8H	11.57	12.19	12.60	13.23	14.58	11.08	11.70	12.11	12.73	14.09
	12H	11.62	12.21	12.65	13.24	14.62	11.12	11.71	12.15	12.74	14.12
4H	2H	9.28	9.98	10.29	10.99	12.34	8.93	9.63	9.94	10.64	11.99
	3H	11.14	11.73	12.17	12.77	14.13	10.74	11.33	11.77	12.37	13.73
	4H	11.86	12.40	12.89	13.43	14.82	11.44	11.98	12.47	13.01	14.40
	6H	12.38	12.84	13.42	13.90	15.28	11.95	12.42	12.99	13.47	14.85
	8H	12.53	12.96	13.57	14.01	15.40	12.10	12.53	13.14	13.58	14.97
	12H	12.60	12.99	13.66	14.05	15.45	12.16	12.55	13.22	13.61	15.01
8H	4H	12.05	12.49	13.10	13.54	14.93	11.68	12.12	12.73	13.16	14.56
	6H	12.69	13.05	13.75	14.14	15.53	12.31	12.67	13.38	13.76	15.15
	8H	12.91	13.23	13.98	14.30	15.71	12.53	12.84	13.60	13.91	15.33
	12H	13.04	13.32	14.12	14.39	15.84	12.64	12.92	13.72	13.99	15.44
12H	4H	12.04	12.43	13.10	13.49	14.89	11.68	12.07	12.74	13.13	14.53
	6H	12.72	13.03	13.79	14.11	15.52	12.35	12.67	13.43	13.74	15.15
	8H	12.96	13.24	14.04	14.31	15.76	12.59	12.87	13.67	13.93	15.39